

Barcode Verifiers In-Line




V275 Print Quality Label Inspection

Standard Models

- ✓ 100% inspection of printed labels
- ✓ Barcode verification to ISO standards
- ✓ Verifies printed characters
- ✓ GS1 application identifier check
- ✓ Blemish inspection
- ✓ Matches human readable vs. barcode data
- ✓ Secure reporting layer

V275 Print Quality Inspection System



V275 Print Quality Label Inspection

Premium Models

- ✓ All features of Standard Models
- ✓ Additional Features:
 - “Backup & Overstrike”
 - “Peel & Present”




Premium Model additional features:

- ✓ “Backup & Overstrike” is the ability to print and immediately void out a section of the label, if the label fails verification. Making the failed label unusable
- ✓ “Peel & Present” is the ability to print and immediately “peel” the label backing off, exposing the adhesive for immediate application*

*Notes:

- Only one of the additional features can be active at a given time
- Peel & Present function requires the application to be confirmed, based on specific application details

Which verifier should I choose?



Click the picture to link to the individual product

V275
In-Line Verifier

[Web Page link](#)



V275-P46Z61030-CC

V275 In-Line Verifier and Print Quality Label Inspection

- Standard Model
- Print Quality Inspection Engine integrated into Printer
- 300dpi resolution Printer
- Print and Verify labels up to 4.1" Wide
- Print and Verify at 12" per Second
- Separate PC required for inspection software

- Part Number: V275-P46Z61030-CC

Click on pictures to link to datasheet

V275 In-Line Verifier

[Web Page link](#)



V275-P46Z61060-CC

V275 In-Line Verifier and Print Quality Label Inspection

- Standard Model
- Print Quality Inspection Engine integrated into Printer
- 600dpi resolution Printer
- Print and Verify labels up to 4.1" Wide
- Print and Verify at 6" per Second
- Separate PC required for inspection software

- Part Number: V275-P46Z61060-CC

Click on pictures to link to datasheet

V275 In-Line Verifier

[Web Page link](#)



V275-P86Z62030-CC

V275 In-Line Verifier and Print Quality Label Inspection

- Standard Model
- Print Quality Inspection Engine integrated into Printer
- 300dpi resolution printer
- Print and Verify labels up to 6.6" Wide
- Print and Verify at 8" per Second
- Separate PC required for inspection software

- Part Number: V275-P86Z62030-CC

Click on pictures to link to datasheet

V275
In-Line Verifier

[Web Page link](#)



V275-P46Z6103P-CC

V275 In-Line Verifier and Print Quality Label Inspection

- Premium Model with the option of :
 - ✓ Backup and Overstrike
 - ✓ Peel and Present
- Print Quality Inspection Engine integrated into Printer
- 300dpi resolution Printer
- Print and Verify labels up to 4.1” Wide
- Print and Verify at 12” per Second
- Separate PC required for inspection software
- Part Number: V275-P46Z6103P-CC

Click on pictures to link to datasheet

V275 In-Line Verifier

[Web Page link](#)



V275-P46Z6106P-CC

Click on pictures to link to datasheet

V275 In-Line Verifier and Print Quality Label Inspection

- Premium Model with the option of :
 - ✓ Backup and Overstrike
 - ✓ Peel and Present
- Print Quality Inspection Engine integrated into Printer
- 600dpi resolution Printer
- Print and Verify labels up to 4.1" Wide
- Print and Verify at 6" per Second
- Separate PC required for inspection software
- Part Number: V275-P46Z6106P-CC

V275 In-Line Verifier

[Web Page link](#)



V275-P86Z6203P-CC

Click on pictures to link to datasheet

V275 In-Line Verifier and Print Quality Label Inspection

- Premium Model with the option of :
 - ✓ Backup and Overstrike
 - ✓ Peel and Present
- Print Quality Inspection Engine integrated into Printer
- 300dpi resolution Printer
- Print and Verify labels up to 6.6" Wide
- Print and Verify at 8" per Second
- Separate PC required for inspection software
- Part Number: V275-P86Z6203P-CC

Omron In-line Verifiers

Your trusted partner in traceability