IO-Link Photoelectric Sensor

IO-Link Makes Sensor Level Information Visible and Solves the Three Major Issues at Manufacturing Sites! Standard Photoelectric Sensor.

CE

• Downtime can be reduced.

- Notifies you of faulty parts and changing conditions in the Sensor in real time.
- The frequency of sudden failure can be decreased.
- The incident light level monitor prevents false detection before it happens.
- The efficiency of changeover can be improved.
- The batch check for individual sensor IDs significantly decreases commissioning time.

IO-Link Model / Sensors [Refer to Dimensions on page 10.]

• Three types of sensing methods and three types of connection methods are available.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Red light Infrared light



Ordering Information

Model Sensing method Appearance **Connection method** Sensing distance **Baud rate** PNP E3Z-T81-IL2 2M Pre-wired (2 m) E3Z-T81-M1TJ-IL2 0.3M Pre-wired M12 connector COM2 Standard M8 connector E3Z-T86-IL2 Through-beam (Emitter + Receiver) <u>}</u>15 m 3 Pre-wired (2 m) E3Z-T81-IL3 2M Pre-wired M12 connector E3Z-T81-M1TJ-IL3 0.3M COM3 Standard M8 connector E3Z-T86-IL3 Pre-wired (2 m) E3Z-R81-IL2 2M Pre-wired M12 connector E3Z-R81-M1TJ-IL2 0.3M COM2 *2 Standard M8 connector E3Z-R86-IL2 Retro-reflective with 4 m (100 mm) MSR function Pre-wired (2 m) E3Z-R81-IL3 2M (When using E39-R1S) Pre-wired M12 connector E3Z-R81-M1TJ-IL3 0.3M COM3 Standard M8 connector E3Z-R86-IL3

Note: Please contact your OMRON sales representative regarding the IO-Link setup file (IODD file).

*1. The Reflector is sold separately. Select the Reflector model most suited to the application.

*2. The sensing distance specified is possible when the E39-R1S is used. Values in parentheses indicate the minimum required distance between the Sensor and Reflector. *3. Through-beam Sensors are sold in sets that include both the Emitter and Receiver.

E3Z-□-IL□

							Red light Infrared light
Sensing method Appearance		Connection method	Sensing distance		Baud rate	Model	
		Connection method				PNP	
		Pre-wired (2 m)					E3Z-D82-IL2 2M
Diffuse reflective	∑ +	Pre-wired M12 connector	1 m			COM2	E3Z-D82-M1TJ-IL2 0.3M
		Standard M8 connector		1			E3Z-D87-IL2
		Pre-wired (2 m)		_ 1 m			E3Z-D82-IL3 2M
		Pre-wired M12 connector				COM3	E3Z-D82-M1TJ-IL3 0.3M
		Standard M8 connector					E3Z-D87-IL3
Dilluse-lellective		Pre-wired (2 m)		im ow beam)			E3Z-L81-IL2 2M
		Pre-wired M12 connector				COM2	E3Z-L81-M1TJ-IL2 0.3M
		Standard M8 connector	90 mn				E3Z-L86-IL2
		Pre-wired (2 m)	(narro				E3Z-L81-IL3 2M
		Pre-wired M12 connector				COM3	E3Z-L81-M1TJ-IL3 0.3M
		Standard M8 connector	1				E3Z-L86-IL3

Note: Please contact your OMRON sales representative regarding the IO-Link setup file (IODD file).

Accessories (Sold Separately)

Slit (A Slit is not provided with Through-beam Sensors) Order a Slit separately if required.

Slit width	Sensing distance	Minimum detectable object	Model	Contents	
	E3Z-T	(Reference value)	Woder		
0.5-mm dia.	50 mm	0.2-mm dia.	E39-S65A		
1-mm dia.	200 mm	0.4-mm dia.	E39-S65B	_	
2-mm dia.	800 mm	0.7-mm dia.	E39-S65C	One set	
0.5 imes 10 mm	1 m	0.2-mm dia.	E39-S65D	Emitter and Receiver)	
$1 \times 10 \text{ mm}$	2.2 m	0.5-mm dia.	E39-S65E		
2 × 10 mm	5 m	0.8-mm dia.	E39-S65F		

Reflectors (Reflector required for Retroreflective Sensors) A Reflector is not provided with the Sensor. Be sure to order a Reflector separately.

	Sensing		Quantity		
Name	E3	Model		Remarks	
	Rated value	Reference value			
Reflector	3 m (100 mm)		E39-R1	1	
	4 m (100 mm)		E39-R1S	1	
		5 m (100 mm)	E39-R2	1	 Reflectors are not
		2.5 m (100 mm)	E39-R9	1 provided with	provided with
		3.5 m(100 mm)	E39-R10	1	Retro-reflective
Fog Preventive Coating		3 m (100 mm)	E39-R1K	1	• The MSR function of
Small Reflector		1.5 m (50 mm)	E39-R3	1	the E3Z-R is
		700 mm (150 mm)	E39-RS1	1	enabled.
Tape Reflector		1.1 m (150 mm)	E39-RS2	1	
		1.4 m (150 mm)	E39-RS3	1	

Note: 1. If you use the Reflector at any distance other than the rated distance, make sure that the stability indicator lights properly when you install the Sensor. 2. Refer to *Reflectors on E39-L/E39-S/E39-R* on your OMRON website for details.

* Values in parenthese indicate the minimum required distance between the Sensor and Reflector.

E3Z-D-ILD

Mounting Brackets A Mounting Bracket is not enclosed with the Sensor. Order a Mounting Bracket separately if required.							
Appearance	Model (material)	Quantity	Remarks	Appearance	Model (material)	Quantity	Remarks
	E39-L153 (SUS304) *1	1	Mauritian Developte		E39-L98 (SUS304) *2	1	Metal Protective Cover Bracket
As 5	E39-L104 (SUS304) *1	1	Mounting Brackets		E39-L150 (SUS304)	1	(Sensor adjuster)
	E39-L43 (SUS304) *2	1	Horizontal Mounting Brackets		E39-L151	1	Easily mounted to the aluminum frame rails of conveyors and easily adjusted.
	E39-L142 (SUS304) *2	1	Horizontal Protective Cover Bracket		(SUS304)		ment
	E39-L44 (SUS304)	1	Rear Mounting Bracket		E39-L144 (SUS304) *2	1	Compact Protective Cover Bracket (For E3Z only)

Note: 1. When using Through-beam models, order one bracket for the Receiver and one for the Emitter.

Refer to Mounting Brackets on E39-L/E39-S/E39-R on your OMRON website for details.
 *1. Cannot be used for Standard Connector models with mounting surface on the bottom. In that case, use Pre-wired Connector models.

*2. Cannot be used for Standard Connector models.

Sensor I/O Connectors

(Models for Connectors and Pre-wired Connectors: A Connector is not provided with the Sensor. Be sure to order a Connector separately.)

Size	Туре	Appearance		Cable length	Model
		Smartclick connector		2 m	XS5F-D421-D80-F
	Socket on one cable			5 m	XS5F-D421-G80-F
	end	Smartclick connector		2 m	XS5F-D422-D80-F
M12		L-shape 2 0		5 m	XS5F-D422-G80-F
		Smartclick connector		2 m	XS5W-D421-D81-F
	Socket and plug on cable ends *1	Straight *2	Here	5 m	XS5W-D421-G81-F
		Smartclick connector L-shape/L-shape *2 *3		2 m	XS5W-D422-D81-F
				5 m	XS5W-D422-G81-F
M8	Socket on one cable end	Straight *3	C Martin	2 m	XS3F-M421-402-A
				5 m	XS3F-M421-405-A
		L-shane *3 *4		2 m	XS3F-M422-402-A
				5 m	XS3F-M422-405-A
M8 socket/ M12 plug	Socket and plug on cable ends	M8-M12 (Smartclick) conversion cable *2		0.2 m	XS3W-M42C-4C2-A

Note: 1. When using Through-beam models, order one connector for the Receiver and one for the Emitter.
2. Refer to Sensor I/O Connectors/Sensor Controllers on your OMRON website for details.

*1. Straight type/L-shape type combinations are also available.
*2. The connectors will not rotate after they are connected.
*3. The cable is fixed at an angle of 180° from the sensor emitter/receiver surface.

E3Z-□-IL□

Ratings and Specifications

IO-Link Model

		Sensing method	Through-beam	Retro-reflective with MSR function	Diffuse-reflective	Narrow-beam Models			
		Pre-wired	E3Z-T81-IL	E3Z-R81-IL	E3Z-D82-IL	E3Z-L81-IL			
Model	PNP output	Pre-wired connector (M12)	E3Z-T81-M1TJ-IL	E3Z-R81-M1TJ-IL	E3Z-D82-M1TJ-IL	E3Z-L81-M1TJ-IL			
Item		Connector (M8)	E3Z-T86-IL	E3Z-R86-IL	E3Z-D87-IL	E3Z-L86-IL			
Sensing distance		15 m	4 m (100 mm) * (when using E39-R1S) 3 m (100 mm) * (when using E39-R1)	1 m (white paper: 300 × 300 mm)	90 + 30 mm (white paper: 100 × 100 mm)				
Spot dian	neter (re	ference value)		2 tr					
Standard	sensing	y object	Opaque: 12-mm dia. min.	Dpaque: 12-mm dia. min.					
Minimum	detecta	ble object		0.1 mm (copper wire)					
Differenti	al travel	example)			20% max. of setting distance	Refer to <i>Engineering</i> data on page 6			
Direction	al angle	- F - 7	Both emitter and receiver: 3 to 15°	2 to 10°	-				
Light sou	irce (wa	velength)	Infrared LED (870 nm)	Red LED (660 nm)	Infrared LED (860 nm)	Red LED (650 nm)			
Power su	pply vo	ltage	10 to 30 VDC (including 1	0% ripple (p-p))	, ,				
Current c	onsump	otion	50 mA max. (Emitter: 25 mA max., Receiver: 25 mA max.)	30 mA max.					
Control output			Load power supply voltage: 30 VDC max., Load current: 100 mA max. Residual voltage: Load current of less than 10 mA: 1 V max. Load current of 10 to 100 mA: 2 V max. PNP open collector output Light-ON/Dark-ON selectable						
Indicators	S		In the Standard I/O mode (SIO mode): Operation indicator (orange, lit) and stability indicator (green, lit) In the IO-Link Mode: Operation indicator (orange, lit) and communication indicator (green, blinking at 1 s interva						
Protection circuits			Reversed power supply polarity protection, out- put short-circuit protec- tion, and reversed output polarity protection	Reversed power supply polarity protection, out- put short-circuit protec- ion, and reversed output polarity protection, and mutual interference prevention polarity protection					
Response time			Operate or reset: 1 ms ma	ax.					
Sensitivity adjustment			Sensitivity adjuster / IO-Li	nk communications					
Ambient illumination (Receiver side)			Sunlight: 10,000 lx max.						
Ambient	tempera	ture range	Operating: -25 to 55°C (with no icing or condensation) Storage: -40 to 70°C (with no icing or condensation)						
Ambient	humidity	y range	Operating: 35% to 85%, 5	Storage: 35% to 95% (with	no condensation)				
Insulation	n resista	ince	20 MΩ min. at 500 VDC						
Dielectric	strengt	h	1,000 VAC, 50/60 Hz for 1 min						
Vibration	resistar	nce	Destruction: 10 to 55 Hz, 1.5 mm double amplitude for 2 hours each in X, Y, and Z directions						
Shock res	sistance) ••	Destruction: 500 m/s ² 3 times each in X, Y, and Z directions						
Connectie	on meth	od	Pre-wired cable (standard cable length 2 m), M12 pre-wired connector (standard cable length 0.3 m),						
Woight	Pre-wi	red cable (2 m)	Approx. 120 a	Approx, 65 a					
(packed	Pre-wire	ed connector (M12)	Approx. 60 g	Approx. 30 g					
state)	Conne	ctor (M8)	Approx. 30 g	Approx. 20 g					
	1	Case	Polybutylene terephthalat	e (PBT)					
Material		Display	Modified polyarylate						
		Lens	Modified polyarylate	Methacrylate resin (PMMA)	Modified polyarylate				
Main IO-Link functions		ctions	Operation mode switching between Light ON and Dark ON, setup of the instability detection level for light receiving and non-light receiving, timer function of the control output and timer time selecting, instability output (IO-Link mode) ON delay timer time selecting, setup of a teaching level and execution of teaching, setup of light receiving sensitivity level, monitor output, operating hours read-out, and initial reset						
		IO-Link specification	Ver 1.1						
Communio	cation	Baud rate	-IL3: COM3 (230.4 kbps),	-IL2: COM2 (38.4 kbps)					
specificati	ons	Data length	PD size: 2 bytes, OD size	: 1 byte (M-sequence type	: TYPE_2_2)				
		Minimum cycle time	-IL3 (COM3): 1 ms, -IL2 (COM2): 2.3 ms						
Accessor	ries		Instruction manual (Neither Reflectors nor Mounting Brackets are provided with any of the above models.)						

* Values in parentheses indicate the minimum required distance between the Sensor and Reflector.

Engineering Data (Reference Value)

Parallel Operating Range

Through-beam Models E3Z-T8 -IL



Through-beam Models E3Z-T8 -IL and Slit (A Slit is mounted to the Emitter and **Receiver.)** Distance Y (mm) 001 001 001 001

Distance

E39-S65F

X (m)

F

E39-S

E39-65C

50

-50

-100

-150

-200

-250





Operating Range

Diffuse-reflective Models E3Z-D8 -IL



Monitor Output vs. Sensing Distance Through-beam Models E3Z-T8 -IL



Narrow-beam Reflective Models E3Z-L8 -IL

E39-S65D

E39-S65E



Retro-reflective Models E3Z-R8 -IL and E39-R1 Reflector



40

20

0

Sensitivity adjuster: 1/3

0.2

0.4



Narrow-beam Reflective Models E3Z-L8



Sensing Object Size vs. Sensing Distance Diffuse-reflective Models E3Z-D8□-IL□

0.6 0.8

1.0

1.2

1.4 1.6

Distance (m)



Narrow-beam Reflective Models E3Z-L8



Spot Diameter vs. Sensing Distance Narrow-beam Reflective Models E3Z-L8□-IL□



Differential Travel vs. Sensing Distance Narrow-beam Reflective Models E3Z-L8□-IL□



I/O Circuit Diagrams



E3Z-🗆-IL

Plugs (Sensor I/O Connectors)

M8 connector



M12 connector



M8-M12 (Smartclick) conversion cable



Through-beam Models (Emitter)

Pin arrangement

Classifi- cation	Wire color	Connector pin No.	Application
DC	Brown	1	Power supply (+V)
	White	2	-
	Blue	3	Power supply (0 V)
	Black	4	Output C/Q

Note: Pins 2 is not used.

Through-beam Models (Receiver) Retro-reflective Models Diffuse-reflective Models Pin arrangement

Classifi- cation	Wire color	Connector pin No.	Application
DC	Brown	1	Power supply (+V)
	White	2	Output DO
	Blue	3	Power supply (0 V)
	Black	4	Output C/Q

Nomenclature

Through-beam Models E3Z-T8 -IL (Receiver)

Retro-reflective Models E3Z-R8□-IL□

Diffuse-reflective Models E3Z-D8-IL E3Z-L8-IL In the Standard I/O mode (SIO mode): Stability indicator (green) In the IO-Link mode: IO-Link communication indicator (green)

Operation selector



 Operation indicator (orange)
 Sensitivity adjuster



Safety Precautions

Be sure to read the precautions for all models in the website at: www.omron247.com. Warning Indications

	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

\bigcirc	General prohibition Indicates the instructions of unspecified prohibited action.
	Caution, explosion Indicates the possibility of explosion under specific conditions.
	Caution, fire Indicates the possibility of fires under specific conditions.

🕂 WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



The maximum power supply voltage is 30 VDC. Before turning the power ON, make sure that the power supply voltage does not exceed the maximum voltage.

Never use the product with an AC power supply. Otherwise, explosion may result.



Do not use the product with voltage in excess of the rated voltage. Excess voltage may result in malfunction or fire.

Do not use the product above rated load.



Precautions for Safe Use

- Be sure to follow the safety precautions below for added safety.
- Do not use the sensor under the environment with explosive or ignition gas.
- 2. Never disassemble, repair nor tamper with the product.

Precautions for Correct Use

- 1. Do not use the product under the following conditions.
 - In the place exposed to the direct sunlight.
 In the place where humidity is high and condensation may occur.
 - (3) In the place where vibration or shock is directly transmitted to the product.
- 2. Connection and Mounting
 - (1) If the sensor wiring is placed in the same conduits or ducts as high-voltage or high-power lines, inductive noise may cause malfunction or damage. Wire the cables separately or use a shielded cable.
 - (2) Use an extension cable less than 100 m long for Standard I/O mode and less than 20 m for IO-Link mode.
 - (3) Do not exceed the following force values applied to the cable. Tensile: 80 N max., torque: 0.1 Nm max., pressure: 20 N max., flexure: 3 kg max.

M8 metal connectors

(4) Fasten a fixed implement by hand. If you use pliers, it may cause malfunction or damage to it.

- 3. Cleaning
 - Do not use thinner, alcohol, or other organic solvents. Otherwise, the optical properties and degree of protection may be degraded.
- Power supply When using a commercially available switching regulator, be sure to ground the FG (Frame Ground) terminals.

5. Power supply reset time

The photoelectric switch will begin sensing no later than 100 ms after the power is turned on. If the load and the photoelectric switch is connected to different power supply, the photoelectric switch must be always turned on first.

- 6. Turning off the power supply When turning off the power, output pulse may be generated. We recommend turning off the power supply of the load or load line first.
- 7. Water resistance
- Though this is type IP67, do not use in the water, rain or outdoors.
- 8. Please process it as industrial waste.

E3Z-D-ILD

Dimensions

Sensors



* Models numbers for Through-beam Sensors (E3Z-T —) are for sets that include both the Emitter and Receiver. The model number of the Emitter is expressed by adding "-L" to the set model number (example: E3Z-T81-IL -L 2M), the model number of the Receiver, by adding "-D" (example: E3Z-T81-IL -D 2M.) Refer to *Ordering Information* to confirm model numbers for Emitter and Receivers.



Note: The lens for the E3Z-D 2/D 7 is black.

E3Z-🗆-IL



Reflectors

Refer to E39-R on your OMRON website for details.

Sensor I/O Connectors

Refer to XS3 or XS5 on your OMRON website for details.

Terms and Conditions of Sale

- 1. Offer; Acceptance. These terms and conditions (these "Terms") are deemed part of all quotes, agreements, purchase orders, acknowledgments, price lists, catalogs, manuals, brochures and other documents, whether electronic or in catalogs, manuals, brochures and other documents, whether electronic or in writing, relating to the sale of products or services (collectively, the "Products") by Omron Electronics LLC and its subsidiary companies ("Omron"). Omron objects to any terms or conditions proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these Terms. Prices: Payment Terms, All prices stated are current, subject to change without notice by Omron. Omron reserves the right to increase or decrease prices on any unshipped portions of outstanding orders. Payments for Products are due net 30 days unless otherwise stated in the invoice. Discounts, Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (i) the invoice is paid according to Omron's payment terms and (ii) Buyer has no past due amounts.
- 2
- 3.
- and (ii) Buyer has no past due amounts. Interest. Omron, at its option, may charge Buyer 1-1/2% interest per month or the maximum legal rate, whichever is less, on any balance not paid within the stated terms.
- Orders. Omron will accept no order less than \$200 net billing. Governmental Approvals. Buyer shall be responsible for, and shall bear all 6 costs involved in, obtaining any government approvals required for the impor-tation or sale of the Products.
- Taxes. All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Omron or required to be collected directly or 7. indirectly by Omron for the manufacture, production, sale, delivery, importa-tion, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Omron. <u>Financial.</u> If the financial position of Buyer at any time becomes unsatisfactory
- 8. <u>Einancial</u> If the financial position of Buyer at any time becomes unsatisfactory to Omron, Omron reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Omron may (without liabil-ity and in addition to other remedies) cancel any unshipped portion of Prod-ucts sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid accounts unpaid accounts.
- <u>Cancellation</u>, <u>Etc.</u> Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Omron against all related costs or expenses.
 <u>Force Majeure</u>. Omron shall not be liable for any delay or failure in delivery
- <u>Force mapping</u>. For any delay of lating in delivery resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.
 <u>Shipping</u>: Delivery. Unless otherwise expressly agreed in writing by Omron: a. Shipments shall be by a carrier selected by Omron; Omron will not drop ship expecting "break down" situations.
- except in "break down" situations. b. Such carrier shall act as the agent of Buyer and delivery to such carrier shall
 - constitute delivery to Buyer; c. All sales and shipments of Products shall be FOB shipping point (unless oth-
- c. All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Omron), at which point title and risk of loss shall pass from Omron to Buyer; provided that Omron shall retain a security interest in the Products until the full purchase price is paid;
 d. Delivery and shipping dates are estimates only; and
 e. Omron will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.
 12. Claims. Any claim by Buyer against Omron for shortage or damage to the Products occurring before delivery to the carrier must be presented in writing to Omron within 30 days of receipt of shipment and include the original transportation bill signed by the carrier received the Products
- portation bill signed by the carrier noting that the carrier received the Products from Omron in the condition claimed.
- <u>Warranties</u>. (a) <u>Exclusive Warranty</u>. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed 13 (b) <u>Limitations</u>. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABIL-

Certain Precautions on Specifications and Use

- Suitability of Use. Omron Companies shall not be responsible for conformity 1. with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request. Omron will provide application to use of the Froduct. At Buyer's application of use of the product applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Prod-uct in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. the particular Product with respect to Buyers application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given: (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document. (ii) Use in consumer products or any use in significant quantities. (iii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equip-ment and installicities construction of the construction of the construction.

inent, and installations subject to separate industry or government regulations. (iv) Systems, machines and equipment that could present a risk to life or prop erty. Please know and observe all prohibitions of use applicable to this Prod-

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO

ITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or oth-erwise of any intellectual property right. (c) <u>Buyer Remedy</u>. Omron's sole obli-gation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsi-ble for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were prop-erly handled, stored, installed and maintained and not subject to contamina-tion, abuse, misuse or inappropriate modification. Return of any Products by tion, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Compa-nies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty. See http://www.omron247.com or contact your Omron representative for published information.

- Iished information.
 Limitation on Liability: Etc. OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted. 14
- Indemnities. Buyer shall indemnify and hold harmless Omron Companies and their employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, inves-tigation, litigation or proceeding (whether or not Omron is a party) which arises 15 or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products. Without limiting the foregoing, Buyer (at its own expense) shall indemnify and hold harmless Omron and defend or set-tle any action brought against such Companies to the extent based on a claim that any Product made to Buyer specifications infringed intellectual property rights of another party.
- rights of another party. <u>Property: Confidentiality.</u> Any intellectual property in the Products is the exclu-sive property of Omron Companies and Buyer shall not attempt to duplicate it in any way without the written permission of Omron. Notwithstanding any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Omron. All information and materials supplied by Omron to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and strictly provent disclosure to any third party. 16
- prevent disclosure to any third party. <u>Export Controls.</u> Buyer shall comply with all applicable laws, regulations and licenses regarding (i) export of products or information; (iii) sale of products to "forbidden" or other proscribed persons; and (ii) disclosure to non-citizens of 17
- "forbidden" or other proscribed persons; and (ii) disclosure to non-citizens of regulated technology or information. <u>Miscellaneous</u>. (a) <u>Waiver</u>. No failure or delay by Omron in exercising any right and no course of dealing between Buyer and Omron shall operate as a waiver of rights by Omron. (b) <u>Assignment</u>. Buyer may not assign its rights hereunder without Omron's written consent. (c) <u>Law</u>. These Terms are governed by the law of the jurisdiction of the home office of the Omron company from which Buyer is purchasing the Products (without regard to conflict of law principles). (d) <u>Amendment</u>. These Terms constitute the entire agreement between Buyer and Omron relating to the Products, and no provision may be changed or waived unless in writing signed by the parties. (e) Severability. If any provi-18 or waived unless in writing signed by the parties. (e) <u>Severability</u>. If any provi-sion hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision. (f) Setoff, Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice. (g) <u>Definitions</u>. As used herein, "<u>including</u>" means "including without limitation"; and "<u>Omron Compa-</u> nies" (or similar words) mean Omron Corporation and any direct or indirect subsidiary or affiliate thereof.

ADDRESS THE RISKS, AND THAT THE OMRON'S PRODUCT IS PROP-ERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

- Programmable Products. Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof. <u>Performance Data</u>. Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitabil-ity and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application require-2 3 ments. Actual performance is subject to the Omron's Warranty and Limitations of Liability.
- Change in Specifications. Product specifications and accessories may be 4 Change in specifications. Product specifications and accessions may be changed at any time based on improvements and other reasons. It is our prac-tice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifica-tions of the Product may be changed without any notice. When in doubt, spe-cial part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual creating of purphased Product to confirm actual specifications of purchased Product. Errors and Omissions. Information presented by Omron Companies has been
- 5 checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.



OMRON AUTOMATION AMERICAS HEADQUARTERS • Chicago, IL USA • 847.843.7900 • 800.556.6766 • www.omron247.com

OMRON CANADA, INC. • HEAD OFFICE Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • www.omron247.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE México DF • 52.55.59.01.43.00 • 01-800-226-6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE Apodaca, N.L. • 52.81.11.56.99.20 • 01-800-226-6766 • mela@omron.com

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE São Paulo, SP, Brasil • 55.11.2101.6300 • www.omron.com.br OMRON ARGENTINA • SALES OFFICE Cono Sur • 54.11.4783.5300

OMRON CHILE • SALES OFFICE Santiago • 56.9.9917.3920

OTHER OMRON LATIN AMERICA SALES 54.11.4783.5300

OMRON EUROPE B.V. • Wegalaan 67-69, NL-2132 JD, Hoofddorp, The Netherlands. • +31 (0) 23 568 13 00 • www.industrial.omron.eu

Authorized Distributor:

Controllers & I/O

Machine Automation Controllers (MAC)
 Motion Controllers

Programmable Logic Controllers (PLC)
 Temperature Controllers
 Remote I/O

Robotics

Industrial Robots
 Mobile Robots

Operator Interfaces

• Human Machine Interface (HMI)

Motion & Drives

- Machine Automation Controllers (MAC)
 Motion Controllers
 Servo Systems
- Frequency Inverters

Vision, Measurement & Identification

Vision Sensors & Systems • Measurement Sensors • Auto Identification Systems

Sensing

- Photoelectric Sensors Fiber-Optic Sensors Proximity Sensors
- Rotary Encoders
 Ultrasonic Sensors

Safety

- Safety Light Curtains
 Safety Laser Scanners
 Programmable Safety Systems
- Safety Mats and Edges Safety Door Switches Emergency Stop Devices
- Safety Switches & Operator Controls Safety Monitoring/Force-guided Relays

Control Components

- Power Supplies
 Timers
 Counters
 Programmable Relays
- Digital Panel Meters
 Monitoring Products

Switches & Relays

Limit Switches • Pushbutton Switches • Electromechanical Relays
 Solid State Relays

Software

Programming & Configuration • Runtime