

## NC Integrated Controller

Machine Automation Controller NJ/NY Series



600 Z10.000  
601 X10.000 Y-5.000 Z0.000  
602 X15.000 Y-0.000 115.000 J-5.000  
601 X27.000 Y-0.000 Z0.000  
603 X30.000 Y3.000 127.000 J3.000  
601 X30.000 Y47.000 Z0.000  
603 X27.000 Y50.000 127.000 J47.000  
601 X3.000 Y50.000 Z0.000

603 X30.000 Y3.000  
601 X30.000 Y4.000  
603 X27.000 Y50.000  
601 X3.000 Y50.000  
601 X15.000 Y43.000  
603 X30.000 Y30.000

Integrated NC and PLC functionality  
for advanced processing machines

**sysmac**

# NC Integrated Controller brings further development of multi-purpose processing machines

Technological advancements and changes in consumer needs are making products more diverse and complex. Manufacturers are dealing with a greater variety of shapes and materials while also striving to achieve the high productivity rates necessary to stay in competitive.

To help manufacturers overcome today's challenges as well as those of the near future, Omron offers a solution that maximizes the throughput of multi-purpose machines designed to handle multiple processes.

Our NC Integrated Controller provides three key benefits:

NC and PLC functionality fully synchronized at high speed

Minimize machine cycle time

Versatile NC functions

Simplify complex profiling

One software for NC setting and PLC programming

Optimize engineering time

Experience new manufacturing with the NJ/NY NC Integrated Controller at the heart.



Sysmac Automation Platform  
NJ/NY Series NC Integrated Controller

ent



*SYSTMAC*



Minimize machine cycle time


# NC and PLC functionality fully synchronized at high speed

Efficient control of processing and other processes is crucial to performance and productivity of a multi-purpose machine which handles multiple processes. The NC Integrated Controller provides both NC and PLC functionality and synchronize all devices at high speed, significantly reducing the machine cycle time.

## Improved synchronization

### Conventional system PLC+NC


As CPU control cycles are not synchronized, communication jitter occurs



### NC Integrated Controller

NC functionality and PLC functionality are fully synchronized in the same task period

NJ/NY NC Integrated Controller




A  
Loader

## Control cycle as you designed

Programs for both PLC and NC are executed in the same task period, allowing both processes to be synchronized together within one cycle as you would expect from this unique controller.


### Conventional system


Two control cycles are inconsistent (Communications jitter must be taken into consideration)



### NC Integrated Controller

Two control cycles are fully synchronized





## High-speed synchronization reduces interlock time

Interlock time between NC (processing) and PLC (other processes) will be reduced to 1/4\* as compared to when separate controllers are used. Cycle time of a multi-purpose machine that generates many interlocks can be reduced. \*The NY Series is used under our measurement conditions.


**PATENT PENDING**

### Conventional system

Different controllers control different processes

### NC Integrated Controller

Integrated control



Simplify complex profiling

# Versatile NC functions

G-Code reduces time required to design and program complex profiling.

## Conventional controller

Processing programs are designed based on CAD data. Programming using PLC instructions and debugging are required for each figure.



CAD screen  
(example)

### Program design

- Exploding components into lines
- Types of lines: straight line, arc, free curve
- Target positions of lines
- Travel velocities
- Transition path between figures, etc.

## NC Integrated Controller

**CAD/CAM software makes design easy**



CAD/CAM

```
G00 Z10.000
G01 X10.000 Y-5.000 Z0.000
G02 X15.000 Y-0.000 I15.000 J-5.000
G01 X27.000 Y-0.000 Z0.000
G03 X30.000 Y3.000 I27.000 J3.000
G01 X30.000 Y47.000 Z0.000
G03 X27.000 Y50.000 I27.000 J47.000
G01 X3.000 Y50.000 Z0.000
.
.
.
G01 X15.000 Y43.000 Z0.000
G02 X20.000 Y38.000 I15.000 J38.000
G00 X20.000 Y38.000 Z10.000
M30
```

NC program in G-Code  
(example)



### Parameter setting

- 1 Parameters are set using CAD/CAM software

### Automatic generation

- 2 NC program in G-Code is generated

### Transferred

- 3 Program is transferred to NC integrated controller



## NC functions for complex profiling applications



### G-Code

G-Code NC programming language allows manual programming on operation software and use in combination with any CAD/CAM software.



### High-speed control

Logic sequence, motion control and NC functionality with the fastest cycle time of 500  $\mu$ s.



### Cutter compensation 2D

Tool diameter and shape compensation, matching the cutting point exactly as specified in G-Code.




### Lookahead

Future instructions are analyzed in advance, movements are blended and optimized in speed and acceleration for a better performance.




### Block Retrace

Path can be reverted in order to remove the tool from cutting area.



### Compensation

High-precision processing by compensating position of NC motors.



### 3D interpolation

Helical, spiral and conical interpolation for 3D profiling.



### Coordinate systems


Various profiling using machine coordinate system, workpiece coordinate system, and local coordinate system.




Milling



Grinding



Dispensing




Sewing



Optimize engineering time


# One software for NC setting and PLC programming

The Sysmac Studio provides a true Integrated Development Environment (IDE) for configuration, programming, monitoring, and 3D simulations. Programming based on IEC standard and PLCopen® Function Blocks (FBs) for motion control cuts programming time. FBs for NC control make program structure simple, even for synchronization between NC process and others.




Intuitive user interface reduces configuration time

Easy to find NC settings



Parameter setting by device



Description of parameters  
Description with graphics gives parameter details





# A choice of two controllers

## For specific purpose machines

A modular controller suitable for machines programmed for NC

- Combine with general-purpose HMI and your own PLC
- Traditional reliability and robustness
- Up to 16 synchronous axes, including NC processing and motion control



Machine Automation Controller  
NJ NC Integrated Controller

## For general purpose machines

A panel PC provides general-purpose HMI functionality that allows machine users to edit NC programs



Industrial Panel PC  
NY NC Integrated Controller

- Reliable and robust industrial panel PC
- Omron's unique CNC Operator for editing NC programs and performing functions
- Comes equipped with Windows OS, running Windows applications while performing motion control
- Up to 32 synchronous axes, including NC processing and motion control
- Intel® Core™ i7-4700EQ processor

### Graphic user interface for NC - CNC Operator




Operation software for PC to use NC functionality.  
Customizable software allows adding functionality by users  
(Requires Microsoft Visual Studio).

# Total solution to maximize machine throughput

## Integration and functionality

Sysmac is an integrated automation platform dedicated to providing complete control and management of your automation plant. At the core of this platform, the controller series offers synchronous control of all machine devices and advanced functionality. This multidisciplinary concept allows you to simplify solution architecture, reduce programming and optimize productivity.



### ✓ Integrated machine controller

Logic sequence, motion, safety, I/O, vision, and NC in one. One integrated controller offers speed, flexibility and scalability of software centric architecture without compromising on the traditional reliability and robustness that you have come to expect from Omron PLCs.

### ✓ Perfect match between fast machine control and plant data management.

Built-in ports: Machine control network EtherCAT® and factory automation network EtherNet/IP™. The two networks with one connection purpose is the perfect match between fast real-time machine control and plant data management.

### ✓ A wide range of products for complete production line

Our industry-leading lineup: Input (photoelectric/proximity/vision sensors, switches), Logic (PLCs, controllers), Output (servo systems, inverters, relays), and Safety.





# Product family

## MACHINE CONTROLLER






15.4' inch



12.1' inch












Product name		NJ/NY series NC Integrated Controller			
Model		NY532-5400-□			
Hardware		Industrial Panel PC			
Display		15.4' inch		12.1' inch	
Storage		128 GB SSD MLC	64 GB SSD SLC	128 GB SSD MLC	64 GB SSD SLC
Operating system		Windows Embedded Standard 7 – 64 bit			
Task		Multi-tasking program			
Control functionality		<ul style="list-style-type: none"> <li>Logic sequence</li> <li>Motion</li> <li>NC</li> </ul>			
Number of axes	Max. synchronous axis	32			
	Synchronous axes per channel	4			
	Number of channels	8			
Fastest cycle time		500 µs			
Software tool	Integrated Development Environment	Sysmac Studio: <ul style="list-style-type: none"> <li>Ladder, Structured Text, In-Line ST</li> <li>IEC61131-3</li> <li>PLCopen for Motion Control and Safety</li> <li>G/M Code</li> </ul>			
	Graphic user interface	CNC operator: <ul style="list-style-type: none"> <li>G/M Code</li> </ul>			
Interpolation functions	Compensation	Tool Radius/Length, Cross, LeadScrew			
	Interpolation	Linear, Circular, Helical, Conical, Spiral			
	Coordinate system	MCS, WCS, LCS, Mirror, Scaling, Rotation, Plane Selection...			
	Others	FeedRate Control, Accel/Decel Control, Lookahead, Machine Lock, Dry Run, Back Trace...			
Program capacity		40 MB			
NC program buffer		64 MB			
Memory card		SD and SDHC			
Built-in port		Ethernet, EtherNet/IP, EtherCAT, USB 3.0/2.0, DVI, RS-232C			
EtherCAT slaves		192			
Mounting		On panel			
Global standards		EU Directives, cULus, RCM and KC Registration			

SOFTWARE			
	Integrated Development Environment	Operation Software	
	 		
Product name	Sysmac Studio	CNC Operator License*	CNC Operator Software Development Kit
Model	SYSMAC-SE2□□□	SYSMAC-RTNC0001L	SYSMAC-RTNC0101D
Functions	<ul style="list-style-type: none"> <li>Sysmac Studio is the Integrated Development Environment to configure, program and maintain all Sysmac Controllers and devices.</li> <li>One single project file for the entire machine.</li> <li>Intuitive IDE for logic, motion, safety, robotics, drives, vision, HMI and networks NC.</li> <li>Reduce engineering and maintenance costs by using Omron libraries and IAGs. Develop your own libraries.</li> <li>IEC-61131-3 compliant.</li> <li>PLCopen FBs for motion and safety.</li> <li>G/M Code available</li> <li>Advanced functions for CAM editing, Drive tuning, 3D simulation, libraries and namespaces, vision algorithms, HMI design and complete machine maintenance.</li> <li>Full Digital Machine development environment including: EtherNet/IP, EtherCAT, IO-Link, SQL and FTP.</li> <li>Offline Simulation for logic, motion, robotics, safety and vision.</li> <li>Advanced security function with 32 digit security password.</li> </ul>	<ul style="list-style-type: none"> <li>G-Code File Editor</li> <li>Execution monitor Active G/M code display</li> <li>Command terminal</li> <li>Jogging, homing</li> </ul>	<ul style="list-style-type: none"> <li>The CNC Operator Software Development Kit provides a</li> <li>Environment for customization of CNC Operator.</li> </ul>

\*One CNC Operator License (SYSMAC-RTNC0001L) is bundled with a CPU Unit. Purchase additional licenses if required.

G-CODE			
Code	Function	Code	Function
G00	Rapid Positioning	G41	Tool Compensation, Left
G01	Linear Interpolation	G42	Tool Compensation, Right
G02	Circular Interpolation in CW direction	G43	Tool Offset, Positive
G03	Circular Interpolation in CCW direction	G44	Tool Offset, Negative
G04	Dwell	G49	Cancels Tool Offset
G09	Exact Stop	G50	Cancel Scaling
G17	X-Y Plane Selection	G51	Scaling
G18	Z-X Plane Selection	G50.1	Cancel Mirroring
G19	Y-Z Plane Selection	G51.1	Mirroring
G20	Inch Input	G52	Local Coordinate System Set
G21	Metric Input	G53	Dimension Shift Cancel
G28	Return to Reference Point	G54	1st work coordinate system
G30	Return to 2nd, 3rd or 4th Reference Point	G55	2nd work coordinate system
G31	Skip Function	G56	3rd work coordinate system
G40	Cancels Tool Compensation	G57	4th work coordinate system
		G58	5th work coordinate system
		G59	6th work coordinate system
		G61	Exact Stop Mode
		G64	Continuous-path Mode
		G68	Enables rotation
		G69	Disables rotation
		G74	Left-handed Tapping Cycle
		G80	Fixed Cycle Cancel
		G84	Tapping Cycle
		G90	Absolute command
		G91	Incremental command
		G98	Fixed Cycle Return to Initial Level
		G99	Fixed Cycle Return to R Point Level
		G500	Enables Multi-block Acceleration/Deceleration Rate
		G501	Disables Multi-block Acceleration/Deceleration Rate

## SERVOMOTORS/LINEAR MOTORS/DRIVES

				
<b>Product name</b>	<b>G5 Servo Drives</b>		<b>1S Servo Drives</b>	
<b>Type</b>	Built-in EtherCAT Communications		Built-in EtherCAT Communications	
<b>100 VAC Applicable motor capacity/force</b>	50 to 400 W		100 to 400W	
<b>200 VAC Applicable motor capacity/force</b>	50 W to 15 kW		100 to 3kW	
<b>400 VAC Applicable motor capacity/force</b>	400 W to 15 kW		600 to 3kW	
<b>Applicable servomotor</b>	G5 rotary servomotor, G5 linear motor		1S servomotor	
<b>Control mode</b>	Position, speed and torque control		Position, speed and torque control	
<b>Safety approvals</b>	<ul style="list-style-type: none"> <li>• ISO13849-1 (PL-c,d)</li> <li>• EN61508 (SIL2)</li> <li>• EN62061 (SIL2)</li> <li>• IEC61800-5-2 (STO)</li> </ul>		<ul style="list-style-type: none"> <li>• ISO13849-1 (PL-e/PL-d)</li> <li>• EN61508 (SIL3/SIL2)</li> <li>• EN62061 (SIL3/SIL2)</li> <li>• IEC61800-5-2 (STO)</li> </ul>	
<b>Full closed loop</b>	Built-in		No	
<b>Ordering information</b>	G5 Series Catalog (Cat. No.I815)		1S Series Catalog (Cat. No.I821)	
				
<b>Product name</b>	<b>G5 Servomotors</b>		<b>1S Servomotors</b>	
<b>Rated rotation speed</b>	3,000 r/min	2,000 r/min	3,000 r/min	2,000 r/min
<b>Momentary maximum rotation speed</b>	4,500 to 6,000 r/min	3,000 r/min	5000 to 6000 r/min	3000 r/min
<b>Rated torque</b>	0.16 to 15.9 Nm	1.91 to 23.9 Nm	0.318 to 9.55N-m	4.77 to 14.3 N-m
<b>Capacity</b>	50 W to 5 kW	400 W to 5 kW	100W to 3 kW	400W to 3kW
<b>Applicable servo drive</b>	G5 Servo Drive (for rotary servomotor)		1S Servo Drive	
<b>Encoder resolution</b>	20-bit incremental/ 17-bit absolute	20-bit incremental/ 17-bit absolute	23-bit absolute	23-bit absolute
<b>Protective structure</b>	IP67	IP67	IP67	IP67
<b>Ordering information</b>	G5 Series Catalog (Cat. No.I815)		1S Series Catalog (Cat. No.I821)	
				
<b>Product name</b>	<b>G5 Servomotors</b>		<b>1S Servomotors</b>	
<b>Rated rotation speed</b>	1,500 r/min	1,000 r/min	1,000 r/min	
<b>Momentary maximum rotation speed</b>	2,000 to 3,000 r/min	2,000 r/min	2000 r/min	
<b>Rated torque</b>	47.8 to 95.5 Nm	8.59 to 57.3 Nm	8.59 to 28.7 N-m	
<b>Capacity</b>	7.5 to 15 kW	900 W to 6 kW	900 W to 3kW	
<b>Applicable servo drive</b>	G5 Servo Drive (for rotary servomotor)		1S Servo Drive	
<b>Encoder resolution</b>	17-bit absolute	20-bit incremental/ 17-bit absolute	23-bit absolute	
<b>Protective structure</b>	IP67	IP67	IP67	
<b>Ordering information</b>	G5 Series Catalog (Cat. No.I815)		1S Series Catalog (Cat. No.I821)	



## I/O



Series	NX	GX
Type	Modular I/O	Block I/O
Communications interface	EtherCAT	EtherCAT
Number of connectable units	<ul style="list-style-type: none"> <li>63 units max.</li> <li>Input: 1,024 bytes max., output: 1,024 bytes max.</li> </ul>	One expansion unit can be connected with one digital I/O terminal (16 inputs + 16 outputs)
I/O types	<ul style="list-style-type: none"> <li>Digital I/O</li> <li>Pulse output</li> <li>Analog I/O</li> <li>Temperature input</li> <li>Encoder input</li> <li>Safety</li> </ul>	<ul style="list-style-type: none"> <li>Digital I/O</li> <li>Encoder input</li> <li>Analog I/O</li> <li>Expansion unit</li> </ul>
Features	<ul style="list-style-type: none"> <li>Over 100 models of I/O units including position interface, temperature inputs and integrated safety</li> <li>High-speed I/O units synchronized with the EtherCAT cycle</li> <li>NsynX technology provides deterministic I/O response with nanosecond resolution</li> <li>Detachable front connector with push-in type screw-less terminals in all NX I/O units</li> <li>Up to 32 digital inputs or outputs</li> </ul>	<ul style="list-style-type: none"> <li>Wide variety of lineup: digital I/O, analog I/O, and encoder input units</li> <li>Easy maintenance: removable I/O terminal</li> <li>Easy set-up: automatic and manual address setting</li> </ul>
Mounting	DIN track	DIN track
Ordering information	NX-series I/O System Catalog (Cat. No.R183)	GX Series Data Sheet

## SAFETY



Product name	NX Safety CPU Unit	NX Safety Input Unit	NX Safety Output Unit
Network	FSoE – Safety over EtherCAT	FSoE – Safety over EtherCAT	FSoE – Safety over EtherCAT
Applicable Standards	EN ISO 13849-1, 2 (PLe/Safety Category 4), IEC 61508 (SIL3), EN 62061 (SIL CL3), EN 61131-2	EN ISO 13849-1, 2 (PLe/Safety Category 4), IEC 61508 (SIL3), EN 62061 (SIL CL3), EN 61131-2	EN ISO 13849-1, 2 (PLe/Safety Category 4), IEC 61508 (SIL3), EN 62061 (SIL CL3), EN 61131-2
Programming	<ul style="list-style-type: none"> <li>IEC 61131-3 standard</li> <li>PLCopen Function Blocks for Safety</li> </ul>	---	---
Number of safety master connections	32/128	---	---
Number of safety input/output points	---	<ul style="list-style-type: none"> <li>4 points</li> <li>8 points</li> </ul>	<ul style="list-style-type: none"> <li>2 points</li> <li>4 points</li> </ul>
Number of test output points	---	2 points	---
Terminal block	---	Screwless clamping terminal block	Screwless clamping terminal block
Features	<ul style="list-style-type: none"> <li>Freely mixing with standard NX I/O</li> <li>Reusable certified programs</li> <li>NX variables sharing in the NJ controller project</li> </ul>	<ul style="list-style-type: none"> <li>Freely mixing with standard NX I/O</li> <li>The 4-point unit can be directly connected with OMRON non-contact switches and singlebeam sensors</li> <li>I/O data monitoring in the NJ controller project</li> </ul>	<ul style="list-style-type: none"> <li>Freely mixing with standard NX I/O</li> <li>The 2-point unit is characterized by large output breaking current of 2.0 A</li> <li>I/O data monitoring in the NJ controller project</li> </ul>
Mounting	DIN track	DIN track	DIN track
Ordering information	NX-SL/SI/SO Data Sheet		

**OMRON AUTOMATION AMERICAS HEADQUARTERS** • Chicago, IL USA • 847.843.7900 • 800.556.6766 • [www.omron247.com](http://www.omron247.com)

**OMRON CANADA, INC. • HEAD OFFICE**

Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • [www.omron247.com](http://www.omron247.com)

**OMRON ELECTRONICS DE MEXICO • HEAD OFFICE**

México DF • 52.55.59.01.43.00 • 01-800-226-6766 • [mela@omron.com](mailto:mela@omron.com)

**OMRON ELECTRONICS DE MEXICO • SALES OFFICE**

Apodaca, N.L. • 52.81.11.56.99.20 • 01-800-226-6766 • [mela@omron.com](mailto:mela@omron.com)

**OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE**

São Paulo, SP, Brasil • 55.11.2101.6300 • [www.omron.com.br](http://www.omron.com.br)

**OMRON ARGENTINA • SALES OFFICE**

Cono Sur • 54.11.4783.5300

**OTHER OMRON LATIN AMERICA SALES**

54.11.4783.5300

*Authorized Distributor:*

**Controllers & I/O**

- Machine Automation Controllers (MAC) • Motion Controllers
- Programmable Logic Controllers (PLC) • Temperature Controllers • Remote I/O

**Robotics**

- Industrial Robots • Mobile Robots

**Operator Interfaces**

- Human Machine Interface (HMI)

**Motion & Drives**

- Machine Automation Controllers (MAC) • Motion Controllers • Servo Systems
- Frequency Inverters

**Vision, Measurement & Identification**

- Vision Sensors & Systems • Measurement Sensors • Auto Identification Systems

**Sensing**

- Photoelectric Sensors • Fiber-Optic Sensors • Proximity Sensors
- Rotary Encoders • Ultrasonic Sensors

**Safety**

- Safety Light Curtains • Safety Laser Scanners • Programmable Safety Systems
- Safety Mats and Edges • Safety Door Switches • Emergency Stop Devices
- Safety Switches & Operator Controls • Safety Monitoring/Force-guided Relays

**Control Components**

- Power Supplies • Timers • Counters • Programmable Relays
- Digital Panel Meters • Monitoring Products

**Switches & Relays**

- Limit Switches • Pushbutton Switches • Electromechanical Relays
- Solid State Relays

**Software**

- Programming & Configuration • Runtime