OMRON

Solid-state Timer H3Y Series

Miniature Timer Compatible with the MY Relay

- The Push-In Plus Terminal Block Socket-compatible H3Y--B/H3YN--B Timers in a black design join the Single-mode H3Y and Multi-mode H3YN.
- The H3Y-----B and H3YN-----B are UL listed when they are used together with Push-In Plus Terminal Block Sockets.
- Large transparent time setting knob facilitates time setting.

A flat-blade and Phillips screwdriver can also be used for time setting.

- Conforms to EMC standards.
- Conforms to EN 61812-1 and approved by UL and CSA.

Model Number Structure



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



H3Y Series Model Number Structure

H3Y- [(1	$\frac{1}{1}$ - $\frac{1}{(2)}$ - $\frac{1}{(3)}$				
(1) Outpu	ıt	(2) Termi	nal Type	(3) Body	Color and Terminal Arrangement
Symbol	Meaning	Symbol	Meaning	Symbol	Meaning
2	DPDT	None	Plug-in terminals	None	Beige with output terminals on top and power supply terminals on bottom
4	4PDT	0	PCB terminals	В	Black with power supply terminals on top and output terminals on bottom
	(2 100 to 120)/AC 0 50		<u>.</u>		

Ex) H3Y-2 100 to 120VAC 0.5S

Rated time
Bupply Voltage

Note: Specify both the model number, supply voltage, and rated time when ordering.

H3YN - \square \square \square \square \square - \square (4)

(1) Output		(2) Time	(2) Time Range		(3) Contact Type	
Symbol	Meaning	Symbol	Meaning	Symbol	Meaning	
2	DPDT	None	Short-time range	None	Single contact	
4	4PDT	0	Long-time range	Z	Twin contacts	

(4) Body Color and Terminal Arrangement

Symbol	Meaning
None	Beige with output terminals on top and power supply terminals on bottom
В	Black with power supply terminals on top and output terminals on bottom

Note: Specify both the model number and the supply voltage when ordering.

Ex) H3YN-2 100 to 120VAC

Supply Voltage

Solid-state Timer

Miniature Timer Compatible with the MY Relay

• Multiple supply voltage options.

• Large transparent time setting knob facilitates time setting.

A flat-blade and Phillips screwdriver can also be used for time setting.

- Pin configuration compatible with MY Power Relay.
- LED indication for power and output statuses.
- Conforms to EMC standards.
- Conforms to EN 61812-1 and approved by UL and CSA.

Refer to Safety Precautions on page 36.

Ordering Information



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

	Time-limit contact	Time ranges		Mounting	
Operation/ resetting system			Supply voltage	Surface/DIN-track mounting (with socket)	Surface mounting (with PCB terminals)
Time-limit operation/	DPDT (for power switching)	0.04 s to 3 h	24, 100 to 120, 200 to 230, 240 VAC (50/60 Hz);	H3Y-2	H3Y-2-0
self-resetting	4PDT		12, 24, 48, 125, 100 to 110 VDC	H3Y-4 *	H3Y-4-0 *

Note: Sockets and Hold-down Clips are not included with the H3Y. They must be ordered separately. * Use the H3Y-4 or H3Y-4-0 Series when switching micro loads.

Accessories (Order Separately) Adapter, Mounting Plate, Clip

Name/specific	ation	Model
Flush mountin	ng adapter	Y92F-78
Mounting	For 1 Socket	PYP-1
Plate for Socket	For 18 Sockets	РҮР-18
	For PYF A	Y92H-3
Clip	For PY and PYF M	Y92H-4

Note: For details, refer to *Precautions for H3Y-series Timers* on page 31.

Socket

Timer		Square Sockets				
Contact	Model	Pin	Connection	Terminal	Model	
		8-pin	Front Connecting	DIN track mounting	PYF08A	
DPDT	НЗҮ-2			DIN track mounting (Finger-safe type)	PYF08A-E	
				Screw mounting	PYF08F	
			Back Connecting	Solder terminal	PY08	
	H3Y-4 14-pin			DIN track mounting	PYF14A	
4PDT		14-pin	Front Connecting	DIN track mounting (Finger-safe type)	PYF14A-E	
			Back Connecting	Solder terminal	PY14	

Note: 1. Cannot be used with the H3Y-□-0 (PCB terminals).
2. The PYF□□A-E has a finger-protection structure. Round crimp

terminals cannot be used. Use forked crimp terminals. **3.** For details, refer to *Precautions for H3Y-series Timers* on page 31.

(E 91) () LR ((())

H3Y

Specifications

Time Ranges

Rated time	Time setting range	Rated time	Time setting range
0.5 s	0.04 to 0.5 s	3 min	0.1 to 3 min
1 s	0.1 to 1 s	5 min	0.2 to 5 min
5 s	0.2 to 5 s	10 min	0.5 to 10 min
10 s	0.5 to 10 s	30 min	1 to 30 min
30 s	1.0 to 30 s	60 min	2 to 60 min
60 s	2.0 to 60 s	3 h	0.1 to 3 h
120 s	5.0 to 120 s		

Ratings

Item	H3Y-2(-0)/H3Y-4(-0)				
Rated supply voltage *6, *7	100 to 120 (50/60 Hz), 200 to 230 VAC (50/60 Hz), 24 VAC (50/60 Hz) * 1 12, 24, 48, 125, 100 to 110 VDC * 2, * 3				
Operating voltage range	All rated voltages except 12 VDC: 85% to 110% of rated supply voltage 12 VDC: 90% to 110% of rated supply voltage * 4				
Reset voltage	10% min. of rated supply voltage *5				
Power consumption	100 to 120 VAC: 1.5 VA (at 120 VAC) 200 to 230 VAC: 1.8 VA (at 230 VAC) 24 VAC: 1.5 VA (at 24 VAC) 12 VDC: 0.9 W (at 12 VDC) 24 VDC: 0.9 W (at 24 VDC) 48 VDC: 1.0 W (at 48 VDC) 100 to 110 VDC: 1.3 W (at 110 VDC) 125 VDC: 1.3 W (at 125 VDC)				
Control outpute	H3Y-2(-0): 5 A at 250 VAC, resistive load ($cos\phi = 1$) The minimum applicable load is 1 mA at 5 VDC (P reference value). Contact materials: Ag				
Control outputs	H3Y-4(-0): 3 A at 250 VAC, resistive load ($cos\phi = 1$) The minimum applicable load is 1 mA at 1 VDC (P reference value). Contact materials: Au-clad + Ag-alloy				
Ambient operating temperature	-10°C to 50°C (with no icing)				
Storage temperature	-25°C to 65°C				
Ambient operating humidity	35% to 85%				

*1. Do not use the output from an inverter as the power supply. Refer to Safety Precautions for All Timers for details on your OMRON website.

*2. With DC ratings, single-phase full-wave rectified power sources may be used.

***3.** Only the H3Y-2 and H3Y-2-0 Series include 2-VDC models.

*4. Use the Timer within 90% to 110% of the rated supply voltage (95% to 110% for 12 VDC) when using it continuously under an ambient operating temperature of 50°C.

*5. Set the reset voltage as follows to ensure proper resetting.

100 to 120 VAC: 10 VAC max. 200 to 230 VAC: 20 VAC max.

100 to 110 VDC: 10 VDC max.

*6. Refer to Safety Precautions for All Timers on your OMRON website when combining the Timer with an AC 2-wire proximity sensor.

*7. A diode to prevent reverse voltages is provided only on models with a DC power supply.

4

Characteristics

Accuracy of operating time	±1% FS max. (0.5 s range: ±1%±10 ms max.) * 1
Setting error	±10%±50 ms FS max.
Reset time	Min. power-opening time: 0.1 s max. (including halfway reset)
Influence of voltage	±2% FS max. * 1
Influence of temperature	±2% FS max. * 1
Insulation resistance	100 MΩ min. (at 500 VDC)
Dielectric strength	 2,000 VAC, 50/60 Hz for 1 min (between current-carrying terminals and exposed non-current-carrying metal parts) \$2 2,000 VAC, 50/60 Hz for 1 min (between operating power circuit and control output) \$2 2,000 VAC, 50/60 Hz for 1 min (between different pole contacts; 2-pole model) \$2 1,500 VAC, 50/60 Hz for 1 min (between different pole contacts; 4-pole model) 1,000 VAC, 50/60 Hz for 1 min (between non-continuous contacts)
Impulse withstand voltage	Between power terminals: 3 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1 kV for 12 VDC, 24 VDC, 48 VDC Between exposed non-current-carrying metal parts: 4.5 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1.5 kV for 12 VDC, 24 VDC, 48 VDC
Noise immunity	±1.5 kV, square-wave noise by noise simulator (pulse width: 100 ns/1 μs, 1-ns rise)
Static immunity	Destruction: 8 kV Malfunction: 4 kV
Vibration resistance	Destruction:10 to 55 Hz, 0.75-mm single amplitudeMalfunction:10 to 55 Hz, 0.5-mm single amplitude
Shock resistance	Destruction: 1,000 m/s ² (approx. 100G) * 3 Malfunction: 100 m/s ² (approx. 10G)
Life expectancy	Mechanical:10,000,000 operations min. (under no load at 1,800 operations/h) Electrical: H3Y-2: 500,000 operations min. (5 A at 250 VAC, resistive load at 1800 operations/h) H3Y-4: 200,000 operations min. (3 A at 250 VAC, resistive load at 1800 operations/h) * 4
Enclosure rating	IP40
Weight	Approx. 50 g
EMC	(EMI) EN 61812-1 Emission Enclosure: EN 55011 Group 1 class A Emission AC Mains: EN 55011 Group 1 class A (EMS) EN 61812-1 Immunity ESD: IEC 61000-4-2 Immunity Burst: IEC 61000-4-3 Immunity Surge: IEC 61000-4-5 Immunity Conducted Disturbance: IEC 61000-4-6 Immunity Voltage Dip/Interruption: IEC 61000-4-11
Approved standards	UL 508, CSA C22.2 No. 14, Lloyds, CCC Conforms to EN 61812-1 and IEC 60664-1. (2.5 kV/2 for H3Y-2/-2-0, 2.5 kV/1 for H3Y-4/-4-0) * 5

***1.** Add ±10 mS to the above value for the 0.5-S range model. ***2.** Terminal screw sections are excluded.

*3. The destructive shock resistance test was performed on the Timer.
*4. Check the electrical life curve.
*5. Overvoltage category II.

H3Y Engineering Data

H3Y-2, H3Y-2-0 H3Y-2, H3Y-2-0 250 VAC, $\cos\phi = 1$ 24 VDC, $\cos\phi = 1$ 250 VAC, $\cos\phi = 0.4$ 24 VDC, L/R = 7 ms Switching operations (×10⁴) Switching operations (×10⁴) 500 500 100 100 50 50 20 20 0 0 3 6 Load current (A) Load current (A)

Reference: A maximum current of 0.6 A can be switched at 125 VDC ($\cos\phi = 1$). Maximum current of 0.2 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected.The minimum applicable load is 1 mA at 5 VDC (P reference value).



Reference: A maximum current of 0.5 A can be switched at 125 VDC ($\cos\phi = 1$). Maximum current of 0.2 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected.The minimum applicable load is 1 mA at 1 VDC (P reference value).

Connect the DC power supply to

terminals 13 and 14 according

to the polarity marks.

Connections

Connections

H3Y-2, H3Y-2-0





(DIN notation)

H3Y-4, H3Y-4-0

14

ç

13



(DIN notation)

5

6, 9

Connect the DC power supply to terminals 13 and 14 according to the polarity marks.



Operation

Timing Chart



Nomenclature

Output Indicator (Orange) (Lit: Output ON)

Main Dial

Set the desired time according to time range selectable by DIP switch.



Run/Power Indicator (Green) (Lit: Power ON)

H3Y

Dimensions

Timers

H3Y-2



=1 4= =5 8= =9 12=

21.5⁻ max.

4 1

28 max.

6.3



P.A.A \otimes 6.4 4

52.6

(60.7)



H3Y-4

H3Y-2-0











Solid-state Timer

Miniature Timer with Multiple Time Ranges and Multiple Operating Modes

- Minimizes stock.
- Pin configuration compatible with MY Power Relay.
- User selectable operating modes include ON-delay, Interval, Flicker ON-start and Flicker OFF-start.
- Multiple time ranges between 0.1 s to 10 min and 0.1 min to 10 h depending on model
- Conforms to EN 61812-1 and IEC 60664-1 for Low Voltage, and EMC Directives.





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Refer to Safety Precautions on page 36.

Ordering Information

List of Models

Supply voltage	Time-limit contact	Short-time range model (0.1 s to 10 min)	Long-time range model (0.1 min to 10 h)
24, 100 to 120, 200 to 230 VAC;	DPDT	H3YN-2	H3YN-21
12, 24, 48, 100 to 110, 125 VDC	4PDT	H3YN-4 *1	H3YN-41 *1
24 VDC	4PDT (Twin contacts)	H3YN-4-Z * 1, * 2	H3YN-41-Z * 1, * 2

Note: Sockets and Hold-down Clips are not included with the H3YN. They must be ordered separately.

*1. Use the H3YN-4 or H3YN-41 Series when switching micro loads, and use the H3YN-4-Z or H3YN-41-Z Series when switching even smaller loads.

***2.** Only models with 24-VDC power supply are available.

Accessories (Order Separately)

Adapter, Mounting Plate, Clip

Name/specification	Model	
Flush mounting adapter	Y92F-78	
Mounting Dista for Costat	For 1 Socket	PYP-1
Mounting Plate for Socket	For 18 Sockets	PYP-18
Clip	For PYF A	Y92H-3
Cilp	For PY and PYF M	Y92H-4

Note: For details, refer to *Precautions for H3Y-series Timers* on page 31.

Socket

Timer			Square Sockets			
Contact Model		Pin	Connection	Terminal	Model	
DPDT		8-pin	Front Connecting	DIN track mounting	PYF08A	
	H3YN-2□			DIN track mounting (Finger-safe type)	PYF08A-E	
				Screw mounting	PYF08F	
			Back Connecting	Solder terminal	PY08	
	H3YN-4	H3YN-4 14-pin		DIN track mounting	PYF14A	
4PDT			Front Connecting	DIN track mounting (Finger-safe type)	PYF14A-E	
			Back Connecting	Solder terminal	PY14	

2. The PYFDA-E has a finger-protection structure. Round crimp terminals cannot be used. Use forked crimp terminals.

3. For details, refer to Precautions for H3Y-series Timers on page 31.

H₃YN

Specifications

Ratings

Item	H	3YN-2/-4/-4-Z		H3YN-21/-41/-41-Z			
Time ranges	0.1 s to 10 min (1 s, 10 s, 1 min, or 10 min max. selectable)		0.1 min to 10 h (1 min, 10 min, 1 h, or 10 h m selectable)				
Rated supply voltage * 5, *6	24, 100 to 120, 200 to 230 VAC (50/60 Hz) * 1 12, 24, 48, 100 to 110, 125 VDC * 2						
Pin type	Plug-in						
Operating mode	ON-delay, interval,	ON-delay, interval, flicker OFF start, or flicker ON start (selectable with DIP switch)					
Operating voltage range	85% to 110% of ra	ted supply volta	age (12 VDC: 90	0% to 110% of rated supply voltage) * 3			
Reset voltage	10% min. of rated s	supply voltage	* 4				
	100 to 120 VAC: 200 to 230 VAC: 24 VAC: 12 VDC:	Relay ON: Relay OFF: Relay ON: Relay OFF: Relay ON:	Approx. 1 VA Approx. 2.2 V Approx. 1.5 V Approx. 1.8 V Approx. 0.3 V Approx. 1.1 W				
Power consumption	24 VDC: 48 VDC: 100 to 110 VDC: 125 VDC:	Relay ON: Relay OFF: Relay ON: Relay OFF: Relay ON: Relay OFF: Relay ON:	Approx. 0.1 W Approx. 1.2 W Approx. 0.3 W	4 at 24 VDC 4 at 24 VDC 4 at 48 VDC 4 at 48 VDC 4 at 48 VDC 4 at 110 VDC 4 at 110 VDC 4 at 125 VDC			
Control outputs		icable load is 1 Ag sistive load (co : The minimum eries: The minin	$\dot{m}A \text{ at } 5 \text{ VDC (I}$ $s\phi = 1)$ applicable load num applicable	^D reference value). is 1 mA at 1 VDC (P reference value). load is 1 mA at 1 VDC (P reference value).			
Ambient operating temperature	-10°C to 50°C (with	n no icing)					
Storage temperature	-25°C to 65°C						
Ambient operating humidity	35% to 85%						

*1. Do not use the output from an inverter as the power supply. Refer to Safety Precautions for All Timers for details on your OMRON website.
*2. Single-phase, full-wave-rectified power supplies can be used.
*3. When using the H3YN continuously in any place where the ambient temperature is in a range of 45°C to 50°C, supply 90% to 110% of the provide the provided and rated supply voltages (supply 95% to 110% with 12 VDC type).

*4. Set the reset voltage as follows to ensure proper resetting. 100 to 120 VAC: 10 VAC max. 200 to 230 VAC: 20 VAC max.

100 to 110 VDC: 10 VDC max.

*5. Refer to Safety Precautions for All Timers on your OMRON website when combining the Timer with an AC 2-wire proximity sensor. *6. A diode to prevent reverse voltages is provided only on models with a DC power supply.

Characteristics

Item	H3YN-2/-21/-4/-41				
Accuracy of operating time	±1% FS max. (1 s range: ±1%±10 ms max.)				
Setting error	±10%±50 ms FS max.				
Reset time	Min. power-opening time: 0.1 s max. (including halfway reset)				
Influence of voltage	±2% FS max.				
Influence of temperature	±2% FS max.				
Insulation resistance	100 MΩ min. (at 500 VDC)				
Dielectric strength	 2,000 VAC, 50/60 Hz for 1 min (between current-carrying terminals and exposed non-current-carrying metal parts) * 2,000 VAC, 50/60 Hz for 1 min (between operating power circuit and control output) 2,000 VAC, 50/60 Hz for 1 min (between different pole contacts; 2-pole model) 1,500 VAC, 50/60 Hz for 1 min (between different pole contacts; 4-pole model) 1,000 VAC, 50/60 Hz for 1 min (between non-continuous contacts) 				
Vibration resistance	Destruction:10 to 55 Hz, 0.75-mm single amplitude for 1 h each in 3 directionsMalfunction:10 to 55 Hz, 0.5-mm single amplitude for 10 min each in 3 directions				
Shock resistance	Destruction: 1,000 m/s ² * 2 Malfunction: 100 m/s ²				
Life expectancy	Mechanical: 10,000,000 operations min. (under no load at 1,800 operations/h) Electrical: DPDT: 500,000 operations min. (5 A at 250 VAC, resistive load at 1,800 operations/h) 4PDT: 200,000 operations min. (H3YN-4-Z/-41-Z: 100,000 operations min.) (3 A at 250 VAC, resistive load at 1,800 operations/h) * 3				
Impulse withstand voltage	Between power terminals: 3 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1 kV for 12 VDC, 24 VDC, 48 VDC, 24 VAC Between exposed non-current-carrying metal parts: 4.5 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1.5 kV for 12 VDC, 24 VDC, 48 VDC, 24 VAC				
Noise immunity	\pm 1.5 kV, square-wave noise by noise simulator (pulse width: 100 ns/1 us, 1-ns rise)				
Static immunity	Destruction: 8 kV Malfunction: 4 kV				
Degree of protection	IP40				
Weight	Approx. 50 g				
EMC	(EMI)EN 61812-1Emission Enclosure:EN 55011 Group 1 class AEmission AC Mains:EN 55011 Group 1 class A(EMS)EN 61812-1Immunity ESD:IEC 61000-4-2Immunity RF-interference:IEC 61000-4-3Immunity Burst:IEC 61000-4-4Immunity Surge:IEC 61000-4-5Immunity Conducted Disturbance:IEC 61000-4-6Immunity Voltage Dip/Interruption:IEC 61000-4-11				
Approved standards	UL 508, CSA C22.2 No. 14, Lloyds, CCC Conforms to EN 61812-1 and IEC 60664-1. (2.5 kV/2 for H3YN-2/-21, 2.5 kV/1 for H3YN-4/-41, H3YN-4-Z/-41-Z) * 4				

*1. Terminal screw sections are excluded.
*2. The destructive shock resistance test was performed on the Timer.
*3. Refer to the *Life-test Curve.**4. Overvoltage category II.

Life-test Curve (Reference Value)

H3YN-2/-21





The minimum applicable load is 1 mA at 5 VDC (P reference value)













Load current (A)

 $\begin{array}{rl} \mbox{Reference:} & A \mbox{maximum current of } 0.5 \mbox{ A can be switched at } 125 \mbox{VDC } (\cos \phi = 1). \\ \mbox{Maximum current of } 0.2 \mbox{ A can be switched if } L/R \mbox{ is } 7 \mbox{ ms. In both cases, a } \\ \mbox{life of } 100,000 \mbox{ operations can be expected.} \\ \mbox{The minimum applicable load is } 0.1 \mbox{ mA at } 1 \mbox{ VDC } (P \mbox{ reference value}) \end{array}$

DIN Notation

Ľ

9 2

14 ~ 9

13~

Ŷ

8

12

14

(+) (\sim)

Connections

Connection

H3YN-2/-21



(Bottom View)

Pulse Operation

A pulse output for a certain period can be obtained with a random external input signal. Use the H3YN in interval mode as shown in the following timing charts.

H3YN-2/-21



Time limit contact NO (12-8) Time limit contact NC (12-4) Run/Power indicator (PW) Output indicator (UP)

Power (9-14)

External short circuit (5-13) External input (9-13)

-	-t	Rt	-	- t•	Rt	-	- t	-
<u> </u>		T	1		T			<u> </u>
	+50 ms min.							
	ta a faadaa a							
					8			

Note: t: Set time Rt: Reset time

H3YN-4/-41 H3YN-4-Z/-41-Z

> Timer circuit

₩₩

VP PW

(Bottom View)

5

13

(~)

H3YN-4/-41 H3YN-4-Z/-41-Z



Power (9-14)
External short circuit (5-13)
External input (9-13)
Time limit contact NO (10-6, 11-7, 12-8)
Time limit contact NC (10-2, 11-3, 12-4)
Run/Power indicator (PW) Output indicator (UP)

 Rt	-t-Rt	t
 	<u> </u>	<u></u>
 n.		

Note: t: Set time Rt: Reset time

Caution Be careful when connecting wires.

Mode	Terminals
Pulse operation	Power supply between 9 and 14 Short-circuit between 5 and 13 Input signal between 9 and 13
Operating mode; interval and all other modes	Power supply between 13 and 14

H₃YN Nomenclature

Output Indicator (Orange) (Lit: Output ON)

Set the desired time according

Main Dial



Run/Power Indicator (Green) (Lit: Power ON)

to time range selectable by DIP switch.

Dimensions

(Unit: mm)

4.1

1

Timers

H3YN-2/-21 Front Mounting





H3YN-4/-41 Front Mounting H3YN-4-Z/-41-Z





Operation

DIP Switch Settings

The 1-s range and ON-delay mode for H3YN-2/-4/-4-Z, the 1-min range and ON-delay mode for H3YN-21/-41/-41-Z are factory-set before shipping.

Time Ranges

Model	Time range	Time setting range	Setting	Factory-set
	1 s	0.1 to 1 s		Yes
H3YN-2,	10 s	1 to 10 s		No
H3YN-4 H3YN-4-Z	1 min	0.1 to 1 min		No
	10 min	1 to 10 min		No
	1 min	0.1 to 1 min		Yes
H3YN-21,	10 min	1 to 10 min		No
H3YN-41 H3YN-41-Z	1 h	0.1 to 1 h		No
	10 h	1 to 10 h		No

Note: The top two DIP switch pins are used to select the time ranges.

Operating Modes

Operating mode	Setting	Factory-set
ON-delay		Yes
Interval		No
Flicker OFF-start		No
Flicker ON-start		No



Note: The bottom two DIP switch pins are used to select the operating mode.

H3YN

Operating made	Timing chart					
Operating mode	H3YN-2/-21	H3YN-4/-41				
ON-delay Power	Power (13-14) Time limit contact NC (9-1, 12-4) Time limit contact NO (9-5, 12-8) Run/Power indicator (PW) Output indicator	Power (13-14) Time limit contact NC (9-1, 10-2, 11-3, 12-4) Time limit contact NO (9-5, 10-6, 11-7, 12-8) Run/Power indicator (PW) Output indicator (UP)				
Interval Power Output	Power (13-14) Time limit contact NC (9-1, 12-4) Time limit contact NO (9-5, 12-8) Run/Power indicator (PW) Output indicator (UP)	Power (13-14) Time limit contact NC (9-1, 10-2, 11-3, 12-4) Time limit contact NO (9-5, 10-6, 11-7, 12-8) Run/Power indicator (PW) Output indicator (UP)				
Flicker OFF-start	Power (13-14) Time limit contact NC (9-1, 12-4) Time limit contact NO (9-5, 12-8) Run/Power indicator (PW) Output indicator (UP)	Power (13-14) Time limit contact NC (9-1, 10-2, 11-3, 12-4) Time limit contact NO (9-5, 10-6, 11-7, 12-8) Run/Power indicator (PW) Output indicator (UP)				
Flicker ON-start	Power (13-14) Time limit contact NC (9-1, 12-4) Time limit contact NO (9-5, 12-8) Run/Power indicator (PW) Output indicator	Power (13-14) Time limit contact NC (9-1, 10-2, 11-3, 12-4) Time limit contact NO (9-5, 10-6, 11-7, 12-8) Run/Power indicator (PW) Output indicator (UP)				

Note: t: Set time Rt: Reset time

Solid-state Timer

Miniature ON-Delay Timer with Fixed Time Range Fits the MY Relay Footprint

- UL listed when used with a Push-In Plus Terminal Block Socket. * Conforms to CSA, CE Marking, CCC and LR.
- Black design with power supply terminals on top and contact output terminals on bottom.
- Timers plug into P2RF-PU Sockets with Push-In Plus Terminals reducing wiring time by 60 percent
- Large transparent time setting knob facilitates time setting.
- A flat-blade and Phillips screwdriver can also be used for time setting.
- Multiple supply voltage options.

*When used in combination with a Push-In Plus Terminal Block Socket (PYF--PU-L).

Refer to Safety Precautions on page 36.

Ordering Information

Operation/resetting system	Time-limit contact	Time ranges	Supply voltage	Mounting Surface/DIN-track mounting (with socket)
Time-limit operation/ self-resetting	DPDT (for power switching)	0.04 s to 3 h	100 to 120, 200 to 230 VAC (50/60 Hz); 12, 24, 48, 100 to 110 VDC	H3Y-2-B
sen-resetting	4PDT		12, 24, 48, 100 to 110 VDC	H3Y-4-B *

Note: Sockets and Hold-down Clips are not included with the H3Y-B. They must be ordered separately. * Use the H3Y-4-B Series when switching micro loads.

Accessories (Order Separately)

Clip

Name/specification		Model		
Clip	For PYFPU-L	Y92H-3		

Note: For details, refer to Precautions for H3Y-series Timers on page 31.

Socket

Timer		Square Sockets				
Contact	Model	Pin	Connection	Terminal	Model	Terminal Type
DPDT	H3Y-2-B	8-pin	Front Connecting	DIN track mounting	PYF-08-PU-L	Push-In Plus Terminal Block
4PDT	H3Y-4-B	14-pin	Front Connecting	DIN track mounting	PYF-14-PU-L	Push-In Plus Terminal Block

Note: 1. Cannot be used with the H3Y---0 (PCB terminals).

2. For details, refer to Precautions for H3Y-series Timers on page 31.





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

H3Y-□-B

Specifications

Time Ranges

Rated time	Time setting range	Rated time	Time setting range
0.5 s	0.04 to 0.5 s	3 min	0.1 to 3 min
1 s	0.1 to 1 s	5 min	0.2 to 5 min
5 s	0.2 to 5 s	10 min	0.5 to 10 min
10 s	0.5 to 10 s	30 min	1 to 30 min
30 s	1.0 to 30 s	60 min	2 to 60 min
60 s	2.0 to 60 s	3 h	0.1 to 3 h
120 s	5.0 to 120 s		

Ratings

Item	H3Y-2-B/H3Y-4-B		
Rated supply voltage *6, *7	100 to 120 (50/60 Hz), 200 to 230 VAC (50/60 Hz), 24 VAC (50/60 Hz) * 1 12, 24, 48, 125, 100 to 110 VDC * 2, * 3		
Operating voltage range	All rated voltages except 12 VDC: 85% to 110% of rated supply voltage 12 VDC: 90% to 110% of rated supply voltage * 4		
Reset voltage	10% min. of rated supply voltage *5		
Power consumption	100 to 120 VAC: 1.5 VA (at 120 VAC) 200 to 230 VAC: 1.8 VA (at 230 VAC) 24 VAC: 1.5 VA (at 24 VAC) 12 VDC: 0.9 W (at 12 VDC) 24 VAC: 1.0 W (at 24 VDC) 48 VDC: 1.0 W (at 48 VDC) 100 to 110 VDC: 1.3 W (at 110 VDC) 125 VDC: 1.3 W (at 125 VDC)		
Oceated autouts	H3Y-2-B: 5 A at 250 VAC, resistive load ($\cos\phi = 1$) The minimum applicable load is 1 mA at 5 VDC (P reference value). Contact materials: Ag		
Control outputs	H3Y-4-B: 3 A at 250 VAC, resistive load ($\cos\phi = 1$) The minimum applicable load is 1 mA at 1 VDC (P reference value). Contact materials: Au-clad + Ag-alloy		
Ambient operating temperature	-10°C to 55°C (with no icing)		
Storage temperature	-25°C to 65°C		
Ambient operating humidity	35% to 85%		

*1. Do not use the output from an inverter as the power supply. Refer to Safety Precautions for All Timers for details on your OMRON website.

*2. With DC ratings, single-phase full-wave rectified power sources may be used.

***3.** Only the H3Y-2-B Series include 2-VDC models.

*4. Use the Timer within 90% to 110% of the rated supply voltage (95% to 110% for 12 VDC) when using it continuously under an ambient operating temperature of 50°C.

*5. Set the reset voltage as follows to ensure proper resetting.

100 to 120 VAC: 10 VAC max. 200 to 230 VAC: 20 VAC max.

100 to 110 VDC: 10 VDC max.

*6. Refer to Safety Precautions for All Timers on your OMRON website when combining the Timer with an AC 2-wire proximity sensor. *7. A diode to prevent reverse voltages is provided only on models with a DC power supply.

Characteristics

Accuracy of operating time	±1% FS max. (0.5 s range: ±1%±10 ms max.) * 1		
Setting error	±10%±50 ms FS max.		
Reset time	Min. power-opening time: 0.1 s max. (including halfway reset)		
Influence of voltage	±2% FS max. * 1		
Influence of temperature	±2% FS max. * 1		
Insulation resistance	100 MΩ min. (at 500 VDC)		
Dielectric strength	 2,000 VAC, 50/60 Hz for 1 min (between current-carrying terminals and exposed non-current-carrying metal parts) \$2 2,000 VAC, 50/60 Hz for 1 min (between operating power circuit and control output) \$2 2,000 VAC, 50/60 Hz for 1 min (between different pole contacts; 2-pole model) \$2 1,500 VAC, 50/60 Hz for 1 min (between different pole contacts; 4-pole model) 1,000 VAC, 50/60 Hz for 1 min (between non-continuous contacts) 		
Impulse withstand voltage	 Between power terminals: 3 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1 kV for 12 VDC, 24 VDC, 48 VDC Between exposed non-current-carrying metal parts: 4.5 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1.5 kV for 12 VDC, 24 VDC, 48 VDC 		
Noise immunity	±1.5 kV, square-wave noise by noise simulator (pulse width: 100 ns/1 μs, 1-ns rise)		
Static immunity	Destruction: 8 kV Malfunction: 4 kV		
Vibration resistance	Destruction:10 to 55 Hz, 0.75-mm single amplitudeMalfunction:10 to 55 Hz, 0.5-mm single amplitude		
Shock resistance	Destruction: 1,000 m/s ² (approx. 100G) *3 Malfunction: 100 m/s ² (approx. 10G)		
Life expectancy	Mechanical:10,000,000 operations min. (under no load at 1,800 operations/h) Electrical: H3Y-2-B: 500,000 operations min. (5 A at 250 VAC, resistive load at 1800 operations/h) H3Y-4-B: 200,000 operations min. (3 A at 250 VAC, resistive load at 1800 operations/h) * 4		
Enclosure rating	IP40		
Weight	Approx. 50 g		
EMC	(EMI) EN 61812-1 Emission Enclosure: EN 55011 Group 1 class A Emission AC Mains: EN 55011 Group 1 class A (EMS) EN 61812-1 Immunity ESD: IEC 61000-4-2 Immunity RF-interference: IEC 61000-4-3 Immunity Surge: IEC 61000-4-5 Immunity Conducted Disturbance: IEC 61000-4-6 Immunity Voltage Dip/Interruption: IEC 61000-4-11		
Approved standards	UL 508/CSA C22.2 No.14 * 5, CSA C22.2 No.14, Lloyds, CCC Conforms to EN 61812-1 and IEC 60664-1. (2.5 kV/2 for H3Y-2-B * 6, 2.5 kV/1 for H3Y-4-B * 6)		

***1.** Add ±10 mS to the above value for the 0.5-S range model. ***2.** Terminal screw sections are excluded.

***3.** The destructive shock resistance test was performed on the Timer. ***4.** Check the electrical life curve.

Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the electrical life curve.
 Source the e

H3Y-□-B

Engineering Data



Reference: A maximum current of 0.6 A can be switched at 125 VDC ($\cos\phi = 1$). Maximum current of 0.2 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected.The minimum applicable load is 1 mA at 5 VDC (P reference value).



Reference: A maximum current of 0.5 A can be switched at 125 VDC ($\cos\phi = 1$). Maximum current of 0.2 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected.The minimum applicable load is 1 mA at 1 VDC (P reference value).

Connections

Connections

H3Y-2-B



(Bottom View)



H3Y-4-B

Connect the DC power supply to terminals A1(13) and A2(14) according to the polarity marks.



Connect the DC power supply to terminals A1(13) and A2(14) according to the polarity marks.

20

Operation

Timing Chart



Nomenclature

Main Dial

Set the desired time according to time range selectable by DIP switch.

Run/Power Indicator (Green) (Lit: Power ON)



Output Indicator (Orange) (Lit: Output ON)

Н3Ү-□-В

Dimensions

Timers



Solid-state Timer

Miniature Timer with Multiple Time Ranges and Multiple Operating Modes

- UL listed when used with a Push-In Plus Terminal Block Socket. * Conforms to CSA, CE Marking, LR, and CCC.
- Black design with power supply terminals on top and contact output terminals on bottom.
- Standard multiple operating modes and multiple time ranges.
- Pin configuration compatible with MY Power Relay.
- Minimizes stock.
- *When used in combination with a Push-In Plus Terminal Block Socket (PYF---PU-L).

Refer to Safety Precautions on page 36.

Ordering Information

List of Models

Supply voltage	Time-limit contact	Short-time range model (0.1 s to 10 min)	Long-time range model (0.1 min to 10 h)
24, 100 to 120, 200 to 230 VAC;	DPDT	H3YN-2-B	H3YN-21-B
12, 24, 48, 100 to 110, 125 VDC	4PDT	H3YN-4-B * 1	H3YN-41-B * 1
24 VDC	4PDT (Twin contacts)	H3YN-4-Z-B * 1, * 2	H3YN-41-Z-B * 1, * 2

Note: 1. Sockets and Hold-down Clips are not included with the H3YN-B. They must be ordered separately.

*1. Use the H3YN-4-B or H3YN-41-B Series when switching micro loads, and use the H3YN-4-Z-B or H3YN-41-Z-B Series when switching even smaller loads.

***2.** Only models with 24-VDC power supply are available.

Accessories (Order Separately)

Clip

Name/specification		Model
Clip	For PYFPU-L	Y92H-3

Note: For details, refer to Precautions for H3Y-series Timers on page 31.

Socket

Timer		Square Sockets				
Contact	Model	Pin	Connection	Terminal	Model	Terminal Type
DPDT	H3YN-2□-B	8-pin	Front Connecting	DIN track mounting	PYF-08-PU-L	Push-In Plus Terminal Block
4PDT	H3YN-4□-B	14-pin	Front Connecting	DIN track mounting	PYF-14-PU-L	Push-In Plus Terminal Block

2. For details, refer to Precautions for H3Y-series Timers on page 31.





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

H3YN-D-B

Specifications

Ratings

Item	H3YN	I-2-B/-4-B/-4-Z-	·B	H3YN-21-B/-41-B/-41-Z-B
Time ranges	0.1 s to 10 min (1 s selectable)	s, 10 s, 1 min, o	r 10 min max.	0.1 min to 10 h (1 min, 10 min, 1 h, or 10 h max selectable)
Rated supply voltage * 5, * 6		24, 100 to 120, 200 to 230 VAC (50/60 Hz) * 1 12, 24, 48, 100 to 110, 125 VDC * 2		
Pin type	Plug-in			
Operating mode	ON-delay, interval,	flicker OFF sta	rt, or flicker ON	start (selectable with DIP switch)
Operating voltage range	85% to 110% of rat	ted supply volta	ge (12 VDC: 90)% to 110% of rated supply voltage) * 3
Reset voltage	10% min. of rated s	supply voltage	* 4	
Power consumption	100 to 120 VAC: 200 to 230 VAC: 24 VAC: 12 VDC: 24 VDC: 48 VDC: 100 to 110 VDC: 125 VDC:	Relay ON: Relay OFF: Relay ON:	Approx. 1 VA Approx. 2.2 V/ Approx. 1.5 V/ Approx. 0.3 V/ Approx. 0.1 W Approx. 0.1 W Approx. 0.1 W Approx. 0.1 W Approx. 0.2 W Approx. 0.3 W	at 12 VDC at 24 VDC at 24 VDC at 24 VDC at 48 VDC at 48 VDC at 110 VDC at 110 VDC at 125 VDC
Control outputs	 DPDT: 5 A at 250 VAC, resistive load (cos\u03c6 = 1) The minimum applicable load is 1 mA at 5 VDC (P reference value). Contact materials: Ag 4PDT: 3 A at 250 VAC, resistive load (cos\u03c6 = 1) H3YN-4-B/-41-B series: The minimum applicable load is 1 mA at 1 VDC (P reference value). H3YN-4-Z-B/-41-Z-B series: The minimum applicable load is 1 mA at 1 VDC (P reference value). Contact materials: Au-clad + Ag-alloy 			
Ambient operating temperature	-10°C to 55°C (with	n no icing)		
Storage temperature	-25°C to 65°C			
Ambient operating humidity	35% to 85%			

*1. Do not use the output from an inverter as the power supply. Refer to Safety Precautions for All Timers for details on your OMRON website.
*2. Single-phase, full-wave-rectified power supplies can be used.
*3. When using the H3YN-B continuously in any place where the ambient temperature is in a range of 45°C to 50°C, supply 90% to 110% of the

rated supply voltages (supply 95% to 110% with 12 VDC type).

*4. Set the reset voltage as follows to ensure proper resetting. 100 to 120 VAC: 10 VAC max. 200 to 230 VAC: 20 VAC max.

100 to 110 VDC: 10 VDC max.

*5. Refer to Safety Precautions for All Timers on your OMRON website when combining the Timer with an AC 2-wire proximity sensor. *6. A diode to prevent reverse voltages is provided only on models with a DC power supply.

Characteristics

Item	H3YN-2-B/-21-B/-4-B/-41-B		
Accuracy of operating time	±1% FS max. (1 s range: ±1%±10 ms max.)		
Setting error	±10%±50 ms FS max.		
Reset time	Min. power-opening time: 0.1 s max. (including halfway reset)		
Influence of voltage	±2% FS max.		
Influence of temperature	±2% FS max.		
Insulation resistance	100 MΩ min. (at 500 VDC)		
Dielectric strength	 2,000 VAC, 50/60 Hz for 1 min (between current-carrying terminals and exposed non-current-carrying metal parts) *1 2,000 VAC, 50/60 Hz for 1 min (between operating power circuit and control output) 2,000 VAC, 50/60 Hz for 1 min (between different pole contacts; 2-pole model) 1,500 VAC, 50/60 Hz for 1 min (between different pole contacts; 4-pole model) 1,000 VAC, 50/60 Hz for 1 min (between non-continuous contacts) 		
Vibration resistance	Destruction:10 to 55 Hz, 0.75-mm single amplitude for 1 h each in 3 directionsMalfunction:10 to 55 Hz, 0.5-mm single amplitude for 10 min each in 3 directions		
Shock resistance	Destruction: 1,000 m/s ² Malfunction: 100 m/s ²		
Life expectancy	Mechanical: 10,000,000 operations min. (under no load at 1,800 operations/h) Electrical: DPDT: 500,000 operations min. (5 A at 250 VAC, resistive load at 1,800 operations/h) 4PDT: 200,000 operations min. (H3YN-4-Z/-41-Z: 100,000 operations min.) (3 A at 250 VAC, resistive load at 1,800 operations/h) * 2		
Impulse withstand voltage	Between power terminals: 3 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1 kV for 12 VDC, 24 VDC, 48 VDC, 24 VAC Between exposed non-current-carrying metal parts: 4.5 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1.5 kV for 12 VDC, 24 VDC, 48 VDC, 24 VAC		
Noise immunity	\pm 1.5 kV, square-wave noise by noise simulator (pulse width: 100 ns/1 μ s, 1-ns rise)		
Static immunity	Destruction: 8 kV Malfunction: 4 kV		
Degree of protection	IP40		
Weight	Approx. 50 g		
EMC	(EMI)EN 61812-1Emission Enclosure:EN 55011 Group 1 class AEmission AC Mains:EN 55011 Group 1 class A(EMS)EN 61812-1Immunity ESD:IEC 61000-4-2Immunity RF-interference:IEC 61000-4-3Immunity Surge:IEC 61000-4-4Immunity Surge:IEC 61000-4-5Immunity Voltage Dip/Interruption:IEC 61000-4-11		
Approved standards	cULus (or cURus): UL 508/CSA C22.2 No.14 * 3, CSA C22.2 No.14, Lloyds, CCC Conforms to EN 61812-1 and IEC 60664-1. (2.5 kV/2 for H3YN-2-B/-21-B * 4, 2.5 kV/1 for H3YN-4-B/-41-B, H3YN-4-Z-B/-41-Z-B * 4)		

*1. Terminal screw sections are excluded.
*2. Refer to the *Life-test Curve*.
*3. cULus listing applies when the OMRON PYF-□-PU-L is used. cURus recognition applies when any other socket is used.
*4. Overvoltage category II

Life-test Curve (Reference Value)

H3YN-2-B/-21-B





The minimum applicable load is 1 mA at 5 VDC (P reference value)









H3YN-4-Z-B/-41-Z-B



Load current (A)

Reference: A maximum current of 0.5 A can be switched at 125 VDC ($\cos \phi = 1$). Maximum current of 0.2 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected. The minimum applicable load is 0.1 mA at 1 VDC (P reference value)

26

Connections

Connection

H3YN-2-B/-21-B



Pulse Operation

A pulse output for a certain period can be obtained with a random external input signal. Use the H3YN-B in interval mode as shown in the following timing charts.

(12)

6 44

6 42 (4)

6 12 (1) (5)

H3YN-2-B/-21-B



Caution

Be careful when connecting wires.

Mode	Terminals
Pulse operation	Power supply between 11(9) and A2(14) Short-circuit between 14(5) and A1(13) Input signal between 11(9) and A1(13)
Operating mode; interval and all other modes	Power supply between A1(13) and A2(14)

H3YN-4-B/-41-B H3YN-4-Z-B/-41-Z-B

A2 (14)

44 (8) 42 (4)

(12)

PW ∕ U⊦ ſĦ

Time

24 (6) 14 (5)

22 (2)

(Bottom View)

(11)

34 (7)

32 (3)

A1 (13 circuit

12

(1)

21

(10) (9) (9)



(DIN Notation)

H3YN-□-B Nomenclature



Dimensions

Timers

H3YN-2-B/-21-B Front Mounting





H3YN-4-B/-41-B Front Mounting H3YN-4-Z-B/-41-Z-B





(Unit: mm)

Operation

DIP Switch Settings

The 1-s range and ON-delay mode for H3YN-2-B/-4-B/-4-Z-B, the 1-min range and ON-delay mode for H3YN-21-B/-41-B/-41-Z-B are factory-set before shipping.

Time Ranges

Model	Time range	Time setting range	Setting	Factory-set
H3YN-2-B,	1 s	0.1 to 1 s		Yes
	10 s	1 to 10 s		No
H3YN-4-B H3YN-4-Z-B	1 min	0.1 to 1 min		No
	10 min	1 to 10 min		No
	1 min	0.1 to 1 min		Yes
H3YN-21-B, H3YN-41-B H3YN-41-Z-B	10 min	1 to 10 min		No
	1 h	0.1 to 1 h		No
	10 h	1 to 10 h		No

 PW
 PV

 H-T-+T-+T-+
 H-T-+T-+

 TIME
 I

 TIME
 I

 TIME
 I

 TIME
 I

 I - 1
 ZZZ

 I - 1
 ZZZ

Note: The top two DIP switch pins are used to select the time ranges.

Operating Modes

Operating mode	Setting	Factory-set
ON-delay		Yes
Interval		No
Flicker OFF-start		No
Flicker ON-start		No

Note: The bottom two DIP switch pins are used to select the operating mode.

H3YN-□-B

Operating mode		g chart
opo	H3YN-2-B/-21-B	H3YN-4-B/-41-B
ON-delay	Power (A1(13)-A2(14)) Rt I Time limit contact NC (11(9)-12(1), 41(12)-42(4)) I I Time limit contact NO (11(9)-14(5), 41(12)-44(8)) I I Run/Power indicator (PW) I I I Output indicator (UP) I I I I	Power Rt t (A1(13)-A2(14))
Interval Power	Power Rt (A1(13)-A2(14))	Power (A1(13)-A2(14)) Rt Time limit contact NC (11(9)-12(1), 21(10)-22(2), 31(11)-32(3), 41(12)-42(4)) Image: Contact NO (11(9)-14(5), 21(10)-24(6), 31(11)-34(7), 41(12)-44(8)) Run/Power indicator (PW) Image: Contact NO Output indicator (UP) Image: Contact NO (UP)
Flicker OFF-start	Power (A1(13)-A2(14)) Time limit contact NC (11(9)-12(1), 41(12)-42(4)) Time limit contact NO (11(9)-14(5), 41(12)-44(8)) Run/Power indicator (PW) Output indicator (UP)	Power (A1(13)-A2(14)) t <tht< th=""> t t <tht>t</tht></tht<>
Flicker ON-start	Power (A1(13)-A2(14)) Time limit contact NC (11(9)-12(1), 41(12)-42(4)) Time limit contact NO (11(9)-14(5), 41(12)-44(8)) Run/Power indicator (PW) Output indicator (UP)	Power (A1(13)-A2(14)) Image: Ima

Note: t: Set time Rt: Reset time

Mounting H3Y Series Timers

Flush Mounting Adapter

Y92F-78

(Excluding the H3Y----B and H3YN-----B)



Note: 1. Push the H3Y in until the Adaptor (Y92F-78) hooks engage with its rear panel.
2. Do not round the corners of the cutout on the rear panel surface, otherwise the Adaptor (Y92F-78) tabs may not engage properly.

Mounting Height

PYF08A/PYF08A-N/PYF08A-E (PYF14A/PYF14A-N/PYF14A-E *1)



PY08 (PY14 *1)



PY08QN (PY14QN *1)



PYF08A (PYF14A)

PYF-08-PU-L (PYF-14-PU-L *2)



PYF-08-PU-L (PYF-14-PU-L)

Note: 1. There are no restrictions to the mounting direction.

Always use the PYF- \Box -PU-L with the H $\breve{3}$ Y- \Box -B or H $\breve{3}$ YN- \Box -B.

***1.** Models in parentheses are Connecting Sockets to the H3Y-4, H3YN-4/-41, or H3YN-4-Z/-41-Z.

*2. Models in parentheses are Connecting Sockets to the H3Y-4-B, H3YN-4-B/-41-B, or H3YN-4-Z-B/-41-Z-B.

Connecting Sockets (Sold Separately)

H3Y/H3YN Series

Use one of the following Connecting Sockets: PYF_A, PYF_M, PY_, PY_-02, or PY_QN(2)(-Y3). (:: 08 or 14)

H3Y-D-B/H3YN-D-B Series

Use one of the following Connecting Sockets: PYF-□-PU-L. (□: 08 or 14)

Accessories (Order Separately)

Use the PYF_A, PY_, PY_-02, or PY_QN(2) to mount the H3Y/H3YN. Use the PYF--PU-L to mount the H3Y--B/H3YN--B. When ordering any one of these sockets, replace "
"with "08" or "14."

Socket Mounting Plates (t = 1.6)

(Excluding the H3Y-□-B and H3YN-□-B)

Use a Socket Mounting Plate to mount multiple Connecting Sockets in a row.

Applicable socket	For mounting 1 socket	For mounting 18 sockets
PY08, PY14, PY08QN(2), PY14QN(2)	PYP-1	PYP-18

Note: PYP-18 may be cut to any desired length.

PYP-1



Relay Hold-down Clips

The Hold-down Clip makes it possible to mount the H3Y securely and prevent the H3Y from falling out due to vibration or shock.

Note: When you attach the Hold-down Clip to or remove it from the Socket, take sufficient precautions to not injury your fingers, such as wearing gloves.

Y92H-3

Y92H-4 H3Y/H3YN Series for PYF A Socket Y92H-3 (Set of Two Clips)



Y92H-4 for PY Socket (Excluding the H3Y-D-B and H3YN-D-B)

OMRON



H3Y-D-B/H3YN-D-B Series for PYF-D-PU-L Socket Y92H-3 (Set of Two Clips)





H3Y/H3YN Series Track Mounting/Front Connecting Sockets

PYF08A



H3Y Series



H3Y/H3YN Series **Back Connecting Sockets**

PY08, PY14



PY08QN, PY14QN PY08QN(2), PY14QN(2)



Note: With PY QN(2), dimension * should read 20 max. and dimension ** 36.5 max.

PY08-02, PY14-02



Terminal Arrangement (Bottom View)

0	4	00	84
6	8	66	08
9	Ð	90	00
13	0	ß	12
P۱	PY08		′14

Terminal Arrangement (Bottom View)

0	4	00	80
6	8	66	08
9	Ð	90	00
ß	12	₿	14
PY08QN PY08QN(2)		PY140 PY140	

0	4	00	84
6	8	60	08
0	Ð	90	00
ß	1	ß	14

Panel Cutout





PY□, PY□-02, PY□QN(2)





Mounting Track PFP-100N/PFP-50N (see note 1)



Note: 1. Meets DIN EN50022 2. This dimension applies to PFP-50N.

Spacer PFP-S



End Plate PFP-M

24 27±0.15

35±0.3



Safety Precautions

Be sure to read precautions for all models in the website at the following URL: http://www.ia.omron.com/.

Warning Indications

	Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

0	Used for general mandatory action precautions for which there is no specified symbol.	
	Use to indicate prohibitions when there is a risk of minor injury from electrical shock or other source if the product is disassembled.	
\bigcirc	Used for general prohibitions for which there is no specific symbol.	

Risk of fire and explosion due to arcing and relay heat generation that accompanies switching. Do not use in an environment where flammable or explosive gas is present.



The service life of the output relay varies widely depending on switching capacity and switching conditions. Use only within the rated load and electrical life count, based on actual conditions of use. Risk of contact sticking and burning if used past the service

life. Always use a load current that does not exceed the rating, and if a heater is used, use a thermal switch in the load circuit.

Do not remove the outer casing.



In rare circumstances there is a risk of slight electrical shock, fire, or device damage. Do not disassemble, modify, repair, or otherwise touch the inside.



Tighten the screws for the lead wires to the Socket to the following torque.

PYF Socket: 0.78 to 1.18 N·m

OMRON

This is the recommended range when crimp terminals are used.

If the screws are not tightened sufficiently on Front-connecting Sockets, the lead wires may come off, connection failure may cause abnormal heating, or fires may occur.

If they are tightened excessively, the screw threads may be damaged.

Precautions for Safe Use

Confirm that the setting dial, indicators and plastic parts are operating normally. Depending on the operating environment, the setting dial, indicators and plastic parts may deteriorate faster than expected, causing the indicators to fail. Periodically perform inspections and replacements.

We recommend that you use a surge absorber if surge voltages may occur. When you dispose of the Timer, do so according to all local ordinances for processing industrial waste.

Precautions for Correct Use

- When selecting a control output, use the H3Y-2/H3YN-2/H3Y-2-B/ H3YN-2-B for switching ON and OFF the power and the H3Y-4/ H3YN-4/H3Y-4-B/H3YN-4-B for switching ON and OFF the minute load. Gold-plated relays are used in the H3Y-4, H3YN-4, H3Y-4-B, H3YN-4-B, H3YN-4-Z, H3YN-41-Z, H3YN-4-Z-B, and H3YN-41-Z-B Series.
- Connect the power supply between terminals A1 (13) and A2 (14). For a DC power supply, connect the negative side to A1 (13) and the positive side to A2 (14).
- The operating voltage will increase when using the H3Y/H3YN/ H3Y-B/H3YN-B in any place where the ambient temperature is more than 50°C. Supply 90% to 110% of the rated voltages (at 12 VDC: 95% to 110%) when operating at 45°C or higher.
- Do not leave the H3Y/H3YN/H3Y-B/H3YN-B in time-up condition for a long period of time (for example, more than one month in any place where the ambient temperature is high), otherwise the internal parts (aluminum electrolytic capacitor) may become damaged. Therefore, the use of the H3Y/H3YN/H3Y-B/H3YN-B with a relay as shown in the following circuit diagram is recommended to extend the service life of the H3Y/H3YN/H3Y-B/ H3YN-B.



 $\otimes\colon \operatorname{Auxiliary}$ relay such as MY Relay

- The H3YN/H3YN-B must be disconnected from the Socket when setting the DIP switch, otherwise the user may touch a terminal imposed with a high voltage and get an electric shock.
- Do not connect the H3Y/H3YN/H3Y-B/H3YN-B as shown in the following circuit diagram on the right hand side, otherwise the H3Y's/H3YN's/H3Y-B's/H3YN-B's internal contacts different from each other in polarity may become short-circuited.



 Use the following safety circuit when building a self-holding or selfresetting circuit with the H3Y/H3YN/H3Y-B/H3YN-B and an auxiliary relay, such as an MY Relay, in combination.



- In the case of the above circuit, the H3YN will be in pulse operation. Therefore, if the circuit shown on page 13 is used, no auxiliary relay will be required.
- Do not set to the minimum setting in the flicker modes, otherwise the contact may become damaged.
- Be careful not to apply any voltage to the terminal screws on the back of the Timer. Mount the product so that the screws will not come in contact with the panel or metal parts.
- Do not use the H3Y/H3YN/H3Y-B/H3YN-B in places where there is excessive dust, corrosive gas, or direct sunlight.
- Do not mount more than one H3Y/H3YN/H3Y-B/H3YN-B closely together, otherwise the internal parts may become damaged. Make sure that there is a space of 5 mm or more between any H3Y/ H3YN/H3Y-B/H3YN-B Models next to each other to allow heat radiation.
- The internal parts may become damaged if a supply voltage other than the rated ones is imposed on the H3Y/H3YN/H3Y-B/H3YN-B. When more than 100 V is applied to 12- or 24-VDC models, the internal element (varistor) may break.

Precautions for EN 61812-1 Conformance

The H3Y/H3YN/H3Y-B/H3YN-B as a built-in timer conforms to EN 61812-1 provided that the following conditions are satisfied.

Handling

- Do not touch the DIP switch while power is supplied to the H3YN/ H3YN-B.
- Before dismounting the H3YN/H3YN-B from the Socket, make sure that no voltage is imposed on any terminal of the H3YN/ H3YN-B.
- The applicable Socket is the PYF A (H3Y/H3YN) or PYF-D-PU-L (H3Y-B/H3YN-B).
- Only basic insulation is ensured between the Y92H-3 Hold-down Clips and H3Y/H3YN/H3Y-B/H3YN-B internal circuits.
- Do not allow the Y92H-3 Hold-down Clips to contact other parts.
- The insulation test voltage between different pole contacts for the 4-pole model is the impulse voltage of 2.95 kV.

Wiring

- The power supply for the H3Y/H3YN/H3Y-B/H3YN-B must be protected with equipment such as a breaker approved by VDE.
- Basic insulation is ensured between the H3Y's/H3YN's/H3Y-B's/
- H3YN-B's operating circuit and control output. • Insulation requirement:
 - Overvoltage category II,

pollution degree 1 (H3Y-4/-4-0/-4-B, H3YN-4/41/-4-B/-41-B, H3YN-4-Z/-41-Z/-4-Z-B/-41-Z-B),

- pollution degree 2 (H3Y-2/-2-0/-2-B, H3YN-2/21/-2-B/-21-B) (with a clearance of 1.5 mm and a creepage distance of 2.5 mm at 240 VAC)
- Output terminals next to each other on the H3Y-4 or H3Y-4-0 must have the same polarity.

- In order to conform to UL and CSA requirements when using the H3Y-4/-4-0/-4-B, H3YN-4/-41/-4-B/-41-B, or H3YN-4-Z/-41-Z/ -4-Z-B/-41-ZB, connect the Unit so that output contacts (contacts of different poles) have the same electric potential.
- In cases such as PLC input where the load is extremely small for the control output of a timer containing a power relay (using other than gold-plated contacts), reliability can be increased by using contacts of the same poles (e.g., the H3Y-2) in parallel.
- Always use the same type of wire.
- Installation
 - There are no restrictions on the installation orientation. Install the Timer securely.

Recommended Replacement Periods and Periodic Replacement as Preventive Maintenance

The recommended replacement period for preventive maintenance is greatly influenced by the application environment of the product. As a guideline for models that do not have a Maintenance Forecast Monitor, the recommended replacement period is 7 to 10 years.* To prevent failures that can be caused by using a product beyond its service live, we recommend that you replace the product as early as possible within the recommended replacement period. However, realize that the recommended replacement period is for reference only and does not guarantee the life of the product.

Many electronic components are used in the product and the product depends on the correct operation of these components to achieve product functions and performance. However, the influence of the ambient temperature on aluminum electrolytic capacitors is large, and the service life is reduced by half for each 10°C rise in temperature (Arrhenius law). When the capacity reduction life of the electrolytic capacitor is reached, the product may fail. We therefore recommend that you replace the product periodically to minimize product failures in advance.

* The following conditions apply: rated input voltage, load rate of 50% max., ambient temperature of 35°C max., and the standalone mounting method.

This product model is designed with a service life of 10 years minimum under the above conditions.

МЕМО

Terms and Conditions of Sale

- 1. Offer; Acceptance. These terms and conditions (these "Terms") are deemed part of all quotes, agreements, purchase orders, acknowledgments, price lists, catalogs, manuals, brochures and other documents, whether electronic or in catalogs, manuals, brochures and other documents, whether electronic or in writing, relating to the sale of products or services (collectively, the "Products") by Omron Electronics LLC and its subsidiary companies ("Omron"). Omron objects to any terms or conditions proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these Terms. Prices: Payment Terms, All prices stated are current, subject to change without notice by Omron. Omron reserves the right to increase or decrease prices on any unshipped portions of outstanding orders. Payments for Products are due net 30 days unless otherwise stated in the invoice. Discounts, Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (i) the invoice is paid according to Omron's payment terms and (ii) Buyer has no past due amounts.
- 2
- 3.
- and (ii) Buyer has no past due amounts. Interest. Omron, at its option, may charge Buyer 1-1/2% interest per month or the maximum legal rate, whichever is less, on any balance not paid within the stated terms.
- Orders. Omron will accept no order less than \$200 net billing. Governmental Approvals. Buyer shall be responsible for, and shall bear all 6 costs involved in, obtaining any government approvals required for the impor-tation or sale of the Products.
- Taxes. All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Omron or required to be collected directly or 7. indirectly by Omron for the manufacture, production, sale, delivery, importa-tion, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Omron. <u>Financial.</u> If the financial position of Buyer at any time becomes unsatisfactory
- 8. <u>Einancial</u> If the financial position of Buyer at any time becomes unsatisfactory to Omron, Omron reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Omron may (without liabil-ity and in addition to other remedies) cancel any unshipped portion of Prod-ucts sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid accounts unpaid accounts.
- <u>Cancellation</u>, <u>Etc.</u> Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Omron against all related costs or expenses.
 <u>Force Majeure</u>. Omron shall not be liable for any delay or failure in delivery
- Force majeure. Other shall not be liable for any delay or lating in delivery resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.
 Shipping: Delivery. Unless otherwise expressly agreed in writing by Omron: a. Shipments shall be by a carrier selected by Omron; Omron will not drop ship expert in "break down" situations.
- except in "break down" situations. b. Such carrier shall act as the agent of Buyer and delivery to such carrier shall
 - constitute delivery to Buyer; c. All sales and shipments of Products shall be FOB shipping point (unless oth-
- c. All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Omron), at which point title and risk of loss shall pass from Omron to Buyer; provided that Omron shall retain a security interest in the Products until the full purchase price is paid;
 d. Delivery and shipping dates are estimates only; and
 e. Omron will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.
 12. Claims. Any claim by Buyer against Omron for shortage or damage to the Products occurring before delivery to the carrier must be presented in writing to Omron within 30 days of receipt of shipment and include the original transportation bill signed by the carrier received the Products
- portation bill signed by the carrier noting that the carrier received the Products from Omron in the condition claimed.
- <u>Warranties</u>. (a) <u>Exclusive Warranty</u>. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed 13 (b) <u>Limitations</u>. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABIL-

Certain Precautions on Specifications and Use

- Suitability of Use. Omron Companies shall not be responsible for conformity 1. with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request. Omron will provide application to use of the Froduct. At Buyer's application of use of the product applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Prod-uct in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. the particular Product with respect to Buyers application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given: (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document. (ii) Use in consumer products or any use in significant quantities. (iii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equip-ment and installicitors cubications of the consumer to construct the construction.

inent, and installations subject to separate industry or government regulations. (iv) Systems, machines and equipment that could present a risk to life or prop erty. Please know and observe all prohibitions of use applicable to this Prod-

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO

ITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or oth-erwise of any intellectual property right. (c) <u>Buyer Remedy</u>. Omron's sole obli-gation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsi-ble for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were prop-erly handled, stored, installed and maintained and not subject to contamina-tion, abuse, misuse or inappropriate modification. Return of any Products by tion, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Compa-nies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty. See http://www.omron247.com or contact your Omron representative for published information.

- Iished information.
 Limitation on Liability: Etc. OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted. 14
- Indemnities. Buyer shall indemnify and hold harmless Omron Companies and their employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, inves-tigation, litigation or proceeding (whether or not Omron is a party) which arises 15 or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products. Without limiting the foregoing, Buyer (at its own expense) shall indemnify and hold harmless Omron and defend or set-tle any action brought against such Companies to the extent based on a claim that any Product made to Buyer specifications infringed intellectual property rights of another party.
- rights of another party. <u>Property: Confidentiality.</u> Any intellectual property in the Products is the exclu-sive property of Omron Companies and Buyer shall not attempt to duplicate it in any way without the written permission of Omron. Notwithstanding any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Omron. All information and materials supplied by Omron to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and strictly provent disclosure to any third party. 16
- 17
- "forbidden" or other proscribed persons; and (ii) disclosure to non-citizens of regulated technology or information. <u>Miscellaneous</u>. (a) <u>Waiver</u>. No failure or delay by Omron in exercising any right and no course of dealing between Buyer and Omron shall operate as a waiver of rights by Omron. (b) <u>Assignment</u>. Buyer may not assign its rights hereunder without Omron's written consent. (c) <u>Law</u>. These Terms are governed by the law of the jurisdiction of the home office of the Omron company from which Buyer is purchasing the Products (without regard to conflict of law principles). (d) <u>Amendment</u>. These Terms constitute the entire agreement between Buyer and Omron relating to the Products, and no provision may be changed or waived unless in writing signed by the parties. (e) Severability. If any provi-18 or waived unless in writing signed by the parties. (e) <u>Severability</u>. If any provision hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision. (f) Setoff, Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice. (g) <u>Definitions</u>. As used herein, "<u>including</u>" means "including without limitation"; and "<u>Omron Compa-</u> nies" (or similar words) mean Omron Corporation and any direct or indirect subsidiary or affiliate thereof.

ADDRESS THE RISKS, AND THAT THE OMRON'S PRODUCT IS PROP-ERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

- Programmable Products. Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof. <u>Performance Data</u>. Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitabil-ity and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application require-2 3 ments. Actual performance is subject to the Omron's Warranty and Limitations of Liability.
- Change in Specifications. Product specifications and accessories may be 4 Change in specifications. Product specifications and accessions may be changed at any time based on improvements and other reasons. It is our prac-tice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifica-tions of the Product may be changed without any notice. When in doubt, spe-cial part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual creating of purphased Product to confirm actual specifications of purchased Product. Errors and Omissions. Information presented by Omron Companies has been
- 5 checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.



OMRON AUTOMATION AND SAFETY • THE AMERICAS HEADQUARTERS • Chicago, IL USA • 847.843.7900 • 800.556.6766 • www.omron247.com

OMRON CANADA, INC. • HEAD OFFICE Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • www.omron247.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE México DF • 52.55.59.01.43.00 • 01-800-226-6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE Apodaca, N.L. • 52.81.11.56.99.20 • 01-800-226-6766 • mela@omron.com

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE São Paulo, SP, Brasil • 55.11.2101.6300 • www.omron.com.br OMRON ARGENTINA • SALES OFFICE Cono Sur • 54.11.4783.5300

OMRON CHILE • SALES OFFICE Santiago • 56.9.9917.3920

OTHER OMRON LATIN AMERICA SALES 54.11.4783.5300

OMRON EUROPE B.V. • Wegalaan 67-69, NL-2132 JD, Hoofddorp, The Netherlands. • +31 (0) 23 568 13 00 • www.industrial.omron.eu

Authorized Distributor:

Automation Control Systems

- Machine Automation Controllers (MAC)
 Programmable Controllers (PLC)
- Operator interfaces (HMI)
 Distributed I/O
 Software

Drives & Motion Controls

- Servo & AC Drives
 Motion Controllers & Encoders
- **Temperature & Process Controllers**
- Single and Multi-loop Controllers

Sensors & Vision

- Proximity Sensors
 Photoelectric Sensors
 Fiber-Optic Sensors
- Amplified Photomicrosensors
 Measurement Sensors
- Ultrasonic Sensors
 Vision Sensors

Industrial Components

- RFID/Code Readers
 Relays
 Pushbuttons
 Indicators
- Limit and Basic Switches
 Timers
 Counters
 Metering Devices
- Power Supplies

Safety

• Laser Scanners • Safety Mats • Edges and Bumpers • Programmable Safety Controllers • Light Curtains • Safety Relays • Safety Interlock Switches

© 2016 Omron Electronics LLC