

UMAC

For more than 20 years, the Universal Motion and Automation Controller (UMAC) series has provided a reliable platform for countless innovative applications across both the Turbo PMAC and Power PMAC product families.

As the platform has matured, the cost of sustaining legacy technology has continued to increase due to component obsolescence, supply chain challenges, and evolving regulatory requirements, including compliance with the EU Cyber Resilience Act (CRA). To better serve our customers and focus our engineering resources on future innovation, we have made the strategic decision to concentrate ongoing development on the CK series of PMAC controllers.

Accordingly, we regret to announce that the UMAC series will be discontinued.

We remain committed to supporting our customers throughout this transition and will provide migration guidance and recommended replacement solutions to help ensure a smooth path forward.

Product Discontinuation		Recommended Replacements	
UMAC Series		CK Series	
			

IMPORTANT NOTE: Any other UMAC-related part number, whether included in this document or not, that is currently in a Last Time Buy (LTB) period will be aligned with the terms and timelines specified in this announcement.

			Product Discontinuation		Recommended Replacements
	Type	Name	UMAC Series		CK Series
	CPU 2x Core	1020	3-4112AEU-***-***** 9-4112AEU-200-B02517		CK3M-CPU□□□□
	CPU 4x Core	1040	3-4114BEU-***-***** 9-4241BEU-2J0-B000EK		CK5M-CPU□□□□
	Axis Card	ACC-24E3	3-4002A-*****		CK3W-AX□□□□□□
	Mezzanine	ACC-24E3	3-400*A-*****		N/A
	Axis Card	ACC-24E2	3-3397A-00-****-**** 9-3397A-00-****-****		CK3W-AX□3□3□
		ACC-24E2A	3-3398A-00-1***-**** 9-3398A-00-1***-****		CK3W-AX□5□5□
		ACC-24E2S	3-3441A-00-0000-**** 9-3441A-00-0000-****		N/A
		ACC-24E2X	3-3398A-00-1***-**** 9-3397A-00-1***-****		CK3W-AX□□□□□□
		ACC-51E	3-3438A-00-****-****		CK3W-AX2□2□□
		ACC-84E	3-3927A-00-00**-****		CK3W-ECS300, CK3W-GC□□□00
	Analog I/O	ACC-28E	3-3404A-00-****-**** 3VR-603404-10X 3VR1-603404-10X		CK3W-AD□□100
		ACC-59E3	3-3959A-00-****-****		CK3W-AD□□100
	Digital I/O	ACC-11E	3-3377A-00-****-****		CK3W-MD71□□0
		ACC-14E	3-3380A-00-****-****		N/A
		ACC-65E	3-3575A-00-****-****		CK3W-MD71□□0
		ACC-66E	3-3576A-00-****-**** 9-3576A-00-1000-****		CK3W-MD71□□0
		ACC-67E	3-3577A-00-****-****		CK3W-MD71□□0
		ACC-68E	3-3578A-00-****-****		CK3W-MD71□□0
	CPU	MACRO8	3-3719C0-0A02-B00000		N/A
		MACRO16	3-3719C0-0A03-*00000		N/A
	Fieldbus	ACC-72EX	3-3958A-00-****-****		N/A
	MACRO	ACC-5E3	3-4017A-00-****-****		N/A
	Power Supply	ACC-E1	3-3269A-00-C000-*000		N/A
		ACC-F1	3-3909A-00-000*-*000		CK3W-PD048
	Backplane	ACC-Ux	300-6034**-10X		N/A
	Chassis	ACC-Px	3-2932A-00-****-B000 9-2932A-00-****-****		N/A
	Rack	ACC-Rx	5-4269-00-****-***** 9-4269-00-****-*****		N/A
		ACC-RFx	5-4269-24-****-***** 9-4269-00-****-*****		N/A
		Custom	9-UMAC-***** 9-4269-G2-****-*****		

[Final order entry date]

March 31, 2027

[Date of The Last Shipping]

August 31, 2027

[Scheduled date of maintenance close]

August 31, 2030 (subject to part availability)

[Difference from discontinued product]

Recommended replacement	Body Color	Dimensions	Wire Connection	Mounting Dimensions	Form Factor	Operation Ratings	Operation Methods
CK Series	-	--	--	--	--	-	*

** : Compatible

* : Minor change/Almost compatible

-- : Not compatible

- : No corresponding specification

UMAC Function		CK Compatibility
CPU	Performance	Compatible (same)
Motion	Programming/Firmware	Compatible (same)
Digital I/Os	Standard sourcing/sinking 24V ACC-11E, ACC-65E, ACC-67E, ACC-68E	Compatible
	Parallel ACC-14E	Not compatible (on roadmap for CK)
Axis Cards Feedback	Quadrature Sine/Cosine Serial (ASIC)/Gate3 defaults	Compatible
	ACI Sine/Cosine	Not compatible (on roadmap for CK)
	ACC-84 Serial	Compatible
Axis Cards Output	16-bit DAC	
	18-bit DAC	Not compatible (on roadmap for CK)
	Direct PWM	Compatible
	Step & Direction (ACC-24E2S)	Not compatible, but possible
	Galvo	Compatible
Analog I/Os	ACC-28E	Compatible
	ACC-59E3	Not compatible (on roadmap for CK)
MACRO	ACC-5E3	Not compatible (on roadmap for CK)
Fieldbus	ACC-72EX	Not compatible

[Product Discontinuation and Recommended Replacement]

PART NUMBER	ODT PRODUCT	REPLACEMENT
3-3307A-00-0000-B100	ACC-11E	CK3W-MD71□0
3-3307A-00-0000-B200	ACC-11E	CK3W-MD71□0
3-3307A-00-0000-F100	ACC-11E	CK3W-MD71□0
3-3307A-00-0000-F200	ACC-11E	CK3W-MD71□0
3-3307A-00-0100-B200	ACC-11E	CK3W-MD71□0
3-3307A-00-0100-F200	ACC-11E	CK3W-MD71□0
3-3474A-00-0000-B300	ACC-14E	N/A
3-3474A-00-0000-F300	ACC-14E	N/A
3-3397A-00-0000-B100	ACC-24E2	CK3W-AX□3□3□
3-3397A-00-0000-B200	ACC-24E2	CK3W-AX□3□3□
3-3397A-00-0000-F100	ACC-24E2	CK3W-AX□3□3□
3-3397A-00-0000-F200	ACC-24E2	CK3W-AX□3□3□
3-3397A-00-0007-B100	ACC-24E2	CK3W-AX□3□3□
3-3397A-00-0007-B200	ACC-24E2	CK3W-AX□3□3□
3-3397A-00-0007-F100	ACC-24E2	CK3W-AX□3□3□
3-3397A-00-0007-F200	ACC-24E2	CK3W-AX□3□3□
9-3397A-00-0000-F200	ACC-24E2	CK3W-AX□3□3□
9-3397A-00-0007-F200	ACC-24E2	CK3W-AX□3□3□
3-3398A-00-1000-F100	ACC-24E2A	CK3W-AX□5□5□
3-3398A-00-1000-FU00	ACC-24E2A	CK3W-AX□5□5□
3-3398A-00-1008-FU00	ACC-24E2A	CK3W-AX□5□5□
9-3398A-00-1000-F200	ACC-24E2A	CK3W-AX□5□5□
9-3398A-00-1008-B200	ACC-24E2A	CK3W-AX□5□5□
9-3398A-00-1008-F100	ACC-24E2A	CK3W-AX□5□5□
9-3398A-00-1008-F200	ACC-24E2A	CK3W-AX□5□5□
3-3441A-00-0000-B200	ACC-24E2S	N/A

3-3441A-00-0000-F100	ACC-24E2S	N/A
3-3441A-00-0000-F200	ACC-24E2S	N/A
9-3441A-00-0000-B200	ACC-24E2S	N/A
9-3441A-00-0000-F200	ACC-24E2S	N/A
3-3398A-00-1007-B200	ACC-24E2X	CK3W-AX□5□5□
9-3397A-00-1008-F200	ACC-24E2X	CK3W-AX□5□5□
3-4002A0010-0000-B00	ACC-24E3	N/A
3-4002A1000-0000-B00	ACC-24E3	N/A
3-4002A5000-3100-B00	ACC-24E3	CK3W-AX□3□3□
3-4002A5000-4200-B00	ACC-24E3	N/A
3-4002A5000-4500-B00	ACC-24E3	CK3W-AX2323□
3-4002A5000-4600-B00	ACC-24E3	N/A
3-4002A5000-4600-F00	ACC-24E3	N/A
3-4002A5050-3131-B00	ACC-24E3	CK3W-AX□3□3□
3-4002A5050-4242-B00	ACC-24E3	N/A
3-4002A5050-4545-B00	ACC-24E3	CK3W-AX2323□
3-4002A5062-3232-B00	ACC-24E3	N/A
3-4002A5062-4141-B00	ACC-24E3	CK3W-AX2323□
3-4002A5062-4646-B00	ACC-24E3	N/A
3-4002A5066-4141-B00	ACC-24E3	CK3W-AX2323□
3-4002A5067-3232-B00	ACC-24E3	N/A
3-4002A5067-3232-F00	ACC-24E3	N/A
3-4002A5067-4132-F00	ACC-24E3	N/A
3-4002A6100-3100-B00	ACC-24E3	CK3W-AX□5□5□
3-4002A6100-3100-F00	ACC-24E3	CK3W-AX□5□5□
3-4002A6100-3200-B00	ACC-24E3	CK3W-AX□5□5□
3-4002A6100-3200-F00	ACC-24E3	CK3W-AX□5□5□
3-4002A6150-3131-B00	ACC-24E3	CK3W-AX□5□5□

3-4002A6161-3131-F00	ACC-24E3	CK3W-AX□5□5□
3-4002A6161-3232-B00	ACC-24E3	CK3W-AX□5□5□
3-4002A6161-3232-F00	ACC-24E3	CK3W-AX□5□5□
3-4002A6161-4231-B00	ACC-24E3	N/A
3-4002A6200-4100-B00	ACC-24E3	N/A
3-4002A6200-4100-F00	ACC-24E3	N/A
3-4002A6200-4200-B00	ACC-24E3	N/A
3-4002A6200-4500-B00	ACC-24E3	N/A
3-4002A6250-3232-B00	ACC-24E3	N/A
3-4002A6262-4132-B00	ACC-24E3	N/A
3-4002A6262-4242-B00	ACC-24E3	N/A
3-4002A6262-4242-F00	ACC-24E3	N/A
3-4002A6262-4545-B00	ACC-24E3	N/A
3-4002A6600-4100-B00	ACC-24E3	N/A
3-4002A6600-4100-F00	ACC-24E3	N/A
3-4002A6600-4500-B00	ACC-24E3	N/A
3-4002A6650-3232-B00	ACC-24E3	N/A
3-4002A6650-3241-B00	ACC-24E3	N/A
3-4002A6650-4141-B00	ACC-24E3	N/A
3-4002A6666-4141-B00	ACC-24E3	N/A
3-4002A6666-4141-F00	ACC-24E3	N/A
3-4002A6666-4545-B00	ACC-24E3	N/A
3-4002A6666-4646-B00	ACC-24E3	N/A
3-4002A6666-4646-F00	ACC-24E3	N/A
3-4002A6700-4100-B00	ACC-24E3	N/A
3-4002A6700-4100-F00	ACC-24E3	N/A
3-4002A6700-4200-B00	ACC-24E3	N/A
3-4002A6700-4500-B00	ACC-24E3	N/A

3-4002A6700-4600-B00	ACC-24E3	N/A
3-4002A6750-3232-B00	ACC-24E3	CK3W-AX□5□5□
3-4002A6767-3232-B00	ACC-24E3	CK3W-AX□5□5□
3-4002A6767-4141-B00	ACC-24E3	N/A
3-4002A6767-4141-F00	ACC-24E3	N/A
3-4002A6767-4242-B00	ACC-24E3	N/A
3-4002A6767-4545-B00	ACC-24E3	N/A
3-4002A6767-4646-B00	ACC-24E3	N/A
3-4003A0000-0031-B00	ACC-24E3	N/A
3-4003A0000-0032-B00	ACC-24E3	N/A
3-4003A0000-3100-B00	ACC-24E3	N/A
3-4003A0000-3200-B00	ACC-24E3	N/A
3-4004A0000-0041-B00	ACC-24E3	N/A
3-4004A0000-0042-B00	ACC-24E3	N/A
3-4004A0000-0045-B00	ACC-24E3	N/A
3-4004A0000-4100-B00	ACC-24E3	N/A
3-4004A0000-4200-B00	ACC-24E3	N/A
3-4004A0000-4500-B00	ACC-24E3	N/A
3-4005A0050-0000-B00	ACC-24E3	N/A
3-4005A5000-0000-B00	ACC-24E3	N/A
3-4006A0061-0000-B00	ACC-24E3	N/A
3-4006A0062-0000-B00	ACC-24E3	N/A
3-4006A0066-0000-B00	ACC-24E3	N/A
3-4006A0067-0000-B00	ACC-24E3	N/A
3-4006A6100-0000-B00	ACC-24E3	N/A
3-4006A6200-0000-B00	ACC-24E3	N/A
3-4006A6600-0000-B00	ACC-24E3	N/A
3-4006A6700-0000-B00	ACC-24E3	N/A

3-4024A0000-0046-B00	ACC-24E3	N/A
3-4024A0000-4600-B00	ACC-24E3	N/A
3-3483A-00-0000-B100	ACC-36E	CK3W-AD□100
3-3483A-00-0000-B200	ACC-36E	CK3W-AD□100
3-3438A-00-0000-B100	ACC-51E	CK3W-AX2□2□□
3-3438A-00-0001-B100	ACC-51E	CK3W-AX2□2□□
3-3438A-00-0001-B200	ACC-51E	CK3W-AX2□2□□
3-3438A-00-0001-F200	ACC-51E	CK3W-AX2□2□□
3-4027A-00-0222-B200	ACC-59E3	CK3W-AD□100
3-4027A-00-0222-F200	ACC-59E3	CK3W-AD□100
9-3576A-00-1000-B100	ACC-66E	CK3W-MD71□0
9-3576A-00-1000-B200	ACC-66E	CK3W-MD71□0
3-3577A-00-0000-B100	ACC-67E	CK3W-MD71□0
3-3577A-00-0000-B200	ACC-67E	CK3W-MD71□0
3-3577A-00-0000-F100	ACC-67E	CK3W-MD71□0
3-3595A-00-0000-B100	ACC-68E	CK3W-MD71□0
3-3595A-00-0000-B200	ACC-68E	CK3W-MD71□0
3-3595A-00-0000-F100	ACC-68E	CK3W-MD71□0
3-3595A-00-0000-F200	ACC-68E	CK3W-MD71□0
3-3958A-00-0000-B000	ACC-72EX	N/A
3-3958A-00-0000-F000	ACC-72EX	N/A
3-3958A-00-110M-B000	ACC-72EX	N/A
3-3958A-00-110M-F000	ACC-72EX	N/A
3-3958A-00-121M-B000	ACC-72EX	N/A
3-3958A-00-121M-F000	ACC-72EX	N/A
3-3958A-00-210M-B000	ACC-72EX	N/A
3-3958A-00-210M-F000	ACC-72EX	N/A
3-3958A-00-221M-B000	ACC-72EX	N/A

3-3958A-00-221M-F000	ACC-72EX	N/A
3-3958A-00-3100-B000	ACC-72EX	N/A
3-3958A-00-310M-B000	ACC-72EX	N/A
3-3958A-00-310M-F000	ACC-72EX	N/A
3-3958A-00-610M-B000	ACC-72EX	N/A
3-3958A-00-610M-F000	ACC-72EX	N/A
3-3958A-00-7100-B000	ACC-72EX	N/A
3-3958A-00-710M-B000	ACC-72EX	N/A
3-3958A-00-710M-F000	ACC-72EX	N/A
3-3958A-00-7110-B000	ACC-72EX	N/A
3-3958A-00-711M-B000	ACC-72EX	N/A
3-3958A-00-711M-F000	ACC-72EX	N/A
3-3958A-00-8100-B000	ACC-72EX	N/A
3-3958A-00-810M-B000	ACC-72EX	N/A
3-3958A-00-810M-F000	ACC-72EX	N/A
3-3958A-00-910M-B000	ACC-72EX	N/A
3-3958A-00-910M-F000	ACC-72EX	N/A
3-3958A-00-911M-B000	ACC-72EX	N/A
3-3958A-00-911M-F000	ACC-72EX	N/A
3-3927A-00-0002-0200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0002-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0002-F200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0003-0200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0006-0200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0006-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0006-F200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0007-0200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0007-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00

3-3927A-00-0007-F200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0008-0200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0008-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0009-0200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0009-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0009-F200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-000B-0200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-000B-F200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-000D-0200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-000D-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-000D-F200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-000E-0200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-000E-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-000E-F200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0TBC-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0TBC-F200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0XY2-0200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0XY2-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0XY2-F200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3909A-00-0000-B000	ACC-F1	N/A
3-3909A-00-0000-F000	ACC-F1	N/A
3-3909A-00-0001-B000	ACC-F1 22A	N/A
3-3909A-00-0001-F000	ACC-F1 22A	N/A
3-2932A-00-1050-B000	ACC-P1	N/A
9-2932A-00-1050-B001	ACC-P1	N/A
3-2932A-00-1575-B000	ACC-P2	N/A
9-2932A-00-1575-B001	ACC-P2	N/A
3-2932A-00-2100-B000	ACC-P3	N/A

9-2932A-00-2100-B001	ACC-P3	N/A
9-4269-00-0610-B0101	ACC-R1	N/A
9-4269-00-1821-B0101	ACC-R3	N/A
5-4269-24-0610-B0000	ACC-RF1	N/A
5-4269-24-1215-B0000	ACC-RF2	N/A
9-4269-00-1215-B0101	ACC-RF2	N/A
5-4269-24-1821-B0000	ACC-RF3	N/A
300-603464-10X	ACC-U10	N/A
300-603491-10X	ACC-U18	N/A
300-603403-10X	ACC-U6	N/A
9-UMAC-A0000017	Custom	N/A
9-UMAC-00000020	Custom	N/A
9-UMAC-00000022	Custom	N/A
9-4269-G2-0000-00002	Custom	N/A
9-4269-G2-0000-000E0	Custom	N/A
3-4112ACU-220-B00000	Power 1020	CK3M-CPU1□1
3-4112ACU-220-F00000	Power 1020	CK3M-CPU1□1
3-4112ACU-230-B00000	Power 1020	CK3M-CPU1□1
3-4112ACU-230-F00000	Power 1020	CK3M-CPU1□1
3-4112ACU-250-B00000	Power 1020	CK3M-CPU1□1
3-4112ACU-250-F00000	Power 1020	CK3M-CPU1□1
3-4112ACU-290-B00000	Power 1020	CK3M-CPU1□1
3-4112ACU-290-F00000	Power 1020	CK3M-CPU1□1
3-4112ACU-400-B00000	Power 1020	CK3M-CPU1□1
3-4112ACU-400-F00000	Power 1020	CK3M-CPU1□1
3-4112ACU-410-B00000	Power 1020	CK3M-CPU1□1
3-4112ACU-410-F00000	Power 1020	CK3M-CPU1□1
3-4112ACU-420-B00000	Power 1020	CK3M-CPU1□1
3-4112ACU-420-F00000	Power 1020	CK3M-CPU1□1
3-4112ACU-430-B00000	Power 1020	CK3M-CPU1□1

3-4112ACU-430-F00000	Power 1020	CK3M-CPU1□1
3-4112ACU-450-B00000	Power 1020	CK3M-CPU1□1
3-4112ACU-450-F00000	Power 1020	CK3M-CPU1□1
3-4112ACU-490-B00000	Power 1020	CK3M-CPU1□1
3-4112ACU-490-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-200-B000T1	Power 1020	CK3M-CPU1□1
3-4112AEU-200-B000T2	Power 1020	CK3M-CPU1□1
3-4112AEU-200-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-210-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-210-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-220-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-220-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-250-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-250-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-400-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-400-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-410-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-410-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-420-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-420-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-430-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-430-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-450-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-450-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-490-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-490-F00000	Power 1020	CK3M-CPU1□1
9-4112AEU-200-B02517	Power 1020	CK3M-CPU1□1
3-4241BEU-200-F00000	Power 1040	CK5M-CPU1□1

3-4241BEU-201-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-201-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-211-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-211-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-251-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-251-B000E1	Power 1040	CK5M-CPU1□1
3-4241BEU-251-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-291-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-291-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-2J1-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-2J1-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-400-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-400-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-401-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-401-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-410-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-410-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-411-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-411-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-450-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-450-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-451-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-451-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-490-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-490-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-491-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-491-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-4J0-B00000	Power 1040	CK5M-CPU1□1

3-4241BEU-4J0-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-4J1-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-4J1-F00000	Power 1040	CK5M-CPU1□1
9-4241BEU-2J0-B000EK	Power 1040	CK5M-CPU1□1
3-3307A-00-0100-B100	ACC-11E	CK3W-MD71□0
3-3307A-00-0100-F100	ACC-11E	CK3W-MD71□0
3-3474A-00-0000-B400	ACC-14E	N/A
3-3474A-00-0000-F400	ACC-14E	N/A
3-3398A-00-1000-B100	ACC-24E2A	CK3W-AX□5□5□
3-3398A-00-1000-B200	ACC-24E2A	CK3W-AX□5□5□
3-3398A-00-1000-F200	ACC-24E2A	CK3W-AX□5□5□
3-3398A-00-1008-B100	ACC-24E2A	CK3W-AX□5□5□
3-3398A-00-1008-B200	ACC-24E2A	CK3W-AX□5□5□
3-3398A-00-1008-F100	ACC-24E2A	CK3W-AX□5□5□
3-3398A-00-1008-F200	ACC-24E2A	CK3W-AX□5□5□
3-3441A-00-0000-B100	ACC-24E2S	N/A
3-4002A5000-3200-B00	ACC-24E3	CK3W-AX□3□3□
3-4002A5000-3200-F00	ACC-24E3	CK3W-AX□3□3□
3-4002A5000-4100-B00	ACC-24E3	CK3W-AX2323□
3-4002A5000-4100-F00	ACC-24E3	CK3W-AX2323□
3-4002A5050-3232-B00	ACC-24E3	CK3W-AX□3□3□
3-4002A5050-3232-F00	ACC-24E3	CK3W-AX□3□3□
3-4002A5050-4141-B00	ACC-24E3	CK3W-AX2323□
3-4002A5050-4141-F00	ACC-24E3	CK3W-AX2323□
3-4002A5050-4646-B00	ACC-24E3	N/A
3-4002A5050-4646-F00	ACC-24E3	N/A
3-4002A6161-3131-B00	ACC-24E3	CK3W-AX□5□5□
3-4002A6200-3200-B00	ACC-24E3	CK3W-AX□5□5□

3-4002A6200-3200-F00	ACC-24E3	CK3W-AX□5□5□
3-4002A6200-4600-B00	ACC-24E3	N/A
3-4002A6200-4600-F00	ACC-24E3	N/A
3-4002A6262-3232-B00	ACC-24E3	CK3W-AX□5□5□
3-4002A6262-3232-F00	ACC-24E3	CK3W-AX□5□5□
3-4002A6262-4141-B00	ACC-24E3	N/A
3-4002A6262-4141-F00	ACC-24E3	N/A
3-4002A6262-4646-B00	ACC-24E3	N/A
3-4002A6262-4646-F00	ACC-24E3	N/A
3-4002A6600-3200-B00	ACC-24E3	N/A
3-4002A6600-3200-F00	ACC-24E3	N/A
3-4002A6600-4600-B00	ACC-24E3	N/A
3-4002A6600-4600-F00	ACC-24E3	N/A
3-4002A6666-3232-B00	ACC-24E3	N/A
3-4002A6666-3232-F00	ACC-24E3	N/A
3-4002A6700-3200-B00	ACC-24E3	CK3W-AX□5□5□
3-4002A6700-3200-F00	ACC-24E3	CK3W-AX□5□5□
3-4002A6767-3232-F00	ACC-24E3	CK3W-AX□5□5□
3-4002A6767-3241-B00	ACC-24E3	N/A
9-4002A6767-3232-F00	ACC-24E3	CK3W-AX□5□5□
3-3404A-00-0000-B100	ACC-28E	CK3W-AD□100
3-3404A-00-0000-B200	ACC-28E	CK3W-AD□100
3-3404A-00-0000-F100	ACC-28E	CK3W-AD□100
3-3404A-00-0000-F200	ACC-28E	CK3W-AD□100
3-3404A-00-0001-B100	ACC-28E	CK3W-AD□100
3-3404A-00-0001-B200	ACC-28E	CK3W-AD□100
3-3404A-00-0001-F100	ACC-28E	CK3W-AD□100
3-3404A-00-0001-F200	ACC-28E	CK3W-AD□100
3VR1-603404-10X	ACC-28E	CK3W-AD□100

3VR-603404-10X	ACC-28E	CK3W-AD□100
3-3438A-00-0000-B200	ACC-51E	CK3W-AX2□2□□
3-3438A-00-0000-F200	ACC-51E	CK3W-AX2□2□□
3-4027A-00-0200-B200	ACC-59E3	CK3W-AD□100
3-4027A-00-0200-F200	ACC-59E3	CK3W-AD□100
3-4027A-00-0211-B200	ACC-59E3	CK3W-AD□100
3-4027A-00-0211-F200	ACC-59E3	CK3W-AD□100
3-4017A-00-A001-B100	ACC-5E3	N/A
3-4017A-00-A001-F100	ACC-5E3	N/A
3-4017A-00-A002-B100	ACC-5E3	N/A
3-4017A-00-A002-F100	ACC-5E3	N/A
3-3575A-00-0000-B100	ACC-65E	CK3W-MD71□0
3-3575A-00-0000-B200	ACC-65E	CK3W-MD71□0
3-3575A-00-0000-F100	ACC-65E	CK3W-MD71□0
3-3575A-00-0000-F200	ACC-65E	CK3W-MD71□0
3-3958A-00-611M-B000	ACC-72EX	N/A
3-3958A-00-611M-F000	ACC-72EX	N/A
3-3927A-00-0003-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-0003-F200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3927A-00-000B-B200	ACC-84E	CK3W-ECS300, CK3W-GC□□00
3-3269A-00-C000-B000	ACC-E1	N/A
3-3269A-00-C000-F000	ACC-E1	N/A
5-4269-00-0610-B0100	ACC-R1	N/A
5-4269-00-1215-B0100	ACC-R2	N/A
5-4269-00-1821-B0100	ACC-R3	N/A
300-603465-10X	ACC-U12	N/A
300-603463-10X	ACC-U8	N/A
9-UMAC-00000021	Custom	N/A
3-4112ACU-200-B00000	Power 1020	CK3M-CPU1□1

3-4112ACU-200-F00000	Power 1020	CK3M-CPU1□1
3-4112ACU-210-B00000	Power 1020	CK3M-CPU1□1
3-4112ACU-210-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-200-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-230-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-230-F00000	Power 1020	CK3M-CPU1□1
3-4112AEU-290-B00000	Power 1020	CK3M-CPU1□1
3-4112AEU-290-F00000	Power 1020	CK3M-CPU1□1
3-4241BEU-200-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-210-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-210-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-250-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-250-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-290-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-290-F00000	Power 1040	CK5M-CPU1□1
3-4241BEU-2J0-B00000	Power 1040	CK5M-CPU1□1
3-4241BEU-2J0-F00000	Power 1040	CK5M-CPU1□1

Specifications and prices in this product news are as of the issue date and are subject to change without notice.
Only main changes in specifications are described in this document. Please be sure to read the relevant catalogs, datasheets, product specifications, instructions, and manuals for precautions and necessary information when using products.

Rev	Description	Date	Prepared By	Approved By
A	Released	09/01/2026	RN	HR