


# OMRON

## solution GUIDE

### Cleanroom Equipment Protection

Non-contact safety barriers, high sensitivity, fast response times, easy integration, and compliance with safety standards to prevent contamination risks



### Key Features

- Area Beam Indicators (ABI) - Tri-color indicators for easy & instant status
- Back-up & restore settings with Intelligent Tap – can reduce maintenance setup time by 90%
- Perfect fit – Protective heights in 40 mm increments
- IO-Link – Easy remote monitoring of process & service data
- Bluetooth connection option for configuration and monitoring

### Challenges:

- False Triggers / Nuisance trips
- Alignment and Installation
- Maintenance and Calibration

### Why F3SG-SR light curtains for Cleanrooms?

- Advanced technology that minimizes false triggers and ensures reliable detection of hazards
- Comprehensive support and guidance for the proper alignment and installation
- Designed for easy maintenance and calibration

Scan or  
Click Me



Part Number	Description
<a href="#">F3SG-4SRA0400-14</a>	Finger safe light curtain, 400mm height, Advanced Model
<a href="#">F3SG-4SRA1200-25</a>	Finger safe light curtain, 1200mm height, Advanced Model
<a href="#">F3SG-4SRB0400-14</a>	Finger safe light curtain, 400mm height, Basic Model
<a href="#">F3SG-4SRB1040-25</a>	Finger safe light curtain, 1200mm height, Basic Model
<a href="#">F39-LSGA</a>	Adjustable Side Mount Bracket, +/- 15 degrees
<a href="#">F39-SGIT-IL3</a>	Intelligent Tap Module for Advanced Configuration