$(48 \times 96 \text{ mm/}96 \times 96 \text{ mm})$

Programmable Controllers Join the E5□**C Series!**

Program up to 256 segments can handle a wide variety of applications.

- Set up to 8 Programs (Patterns) with 32 Segments (Steps) Each
- A white LCD PV display with a height of approx. 18 mm for the E5EC-T and 25 mm for the E5AC-T improves visibility.
- Tool ports are provided both on the top panel and the front panel. Set up the Controller without wiring the power supply by connecting to the computer with a Communications Conversion Cable (sold separately). Setup is easy with the CX-Thermo (sold separately).
- High-speed sampling at 50 ms.
- Models are available with up to 4 auxiliary outputs, up to 6 event inputs, and a transfer output to cover a wide range of applications.
- Short body with depth of only 60 mm.
- Easy connections to a PLC with programless communications. Use component communications to link Temperature Controllers to each other.
- The new position-proportional control models allow you to control valves as well. (The position-proportional control models are scheduled to be released in May, 2014.)




Refer to your OMRON website for the most recent information on applicable safety standards.



Refer to Safety Precautions on page 104.

Main I/O Functions



This datasheet is provided as a guideline for selecting products.

Be sure to refer to the following manuals for application precautions and other information required for operation before attempting to use the product.

E5□C-T Digital Temperature Controllers Programmable Type User's Manual (Cat. No. H185)

E5 C-T Digital Temperature Controllers Programmable Type Communications Manual (Cat. No. H186)

Model Number Legend and Standard Models

Model Number Legend

Models with Screw Terminals

E5EC-T 4 5 M - (Example: E5EC-TRX4A5M-000)

1 2 3 4 5 6

E5AC-T 4 5 M - (**Example: E5AC-TRX4A5M-000**)

1 2 3 4 5 6

	(-	1)	2	3	4	(5)	6							
Model	Control	outputs nd 2	No. of auxiliary outputs	Power supply voltage	Terminal type		Options	Meaning						
E5EC-T								48	× 96 mm Progra	• •				
E5AC-T								96	× 96 mm Progra	mmable	Туре			
								Control	output 1	Control output 2				
	RX							-	output		None			
	QX								e output ing SSR)		None			
*2	CX							Linear cur	rent output		None			
	QQ								e output ing SSR)	Vo (for	oltage output driving SSR)			
	QR								e output ing SSR)	Relay output				
	RR							Relay	output	R	elay output			
*2	CC							Linear cur	rent output	Linear current output				
*2	CQ							Linear cur	rent output	Voltage output (for driving SSR)				
	PR								rtional relay out- ut	Position-proportional re- lay output				
			4	4 (auxiliary outputs 1 and 2 with s auxiliary outputs 3 and 4 with s										
				Α					100 to 240					
				D					24 VAC/					
					5				Screw terminals	(with cover)				
	Contr	ol outputs 1	and 2			М			Universal	input				
	For RX, QX, QQ, QR, RR, or CQ	QX, QQ, QR, RR, or CC F						HB alarm and HS alarm	Communications	Event inputs	Transfer output			
01	Selectable	Selectable	Selectable				000							
Option selection		Selectable	Selectable				004		RS-485	2				
conditions		Selectable					005			4				
*1	Selectable	Selectable					800	1 RS-485		2				
	Selectable						010	1		4				
	Selectable						019	1		6	Provided.			
		Selectable					021			6	Provided.			
		Selectable	Selectable				022		RS-485	4	Provided.			

^{*1.} The options that can be selected depend on the type of control output.

Heating and Cooling Control

Using Heating and Cooling Control

① Control Output Assignment

If there is no control output 2, an auxiliary output is used as the cooling control output.

If there is a control output 2, the two control outputs are used for heating and cooling.

(It does not matter which output is used for heating and which output is used for cooling.)

(2) Contro

If PID control is used, you can set PID control separately for heating and cooling.

This allows you to handle control systems with different heating and cooling response characteristics.

^{*2.} The linear current output cannot be used as a transfer output.

Optional Products (Order Separately)

USB-Serial Conversion Cable

Model	
E58-CIFQ2	

Communications Conversion Cable

Model	
E58-CIFQ2-E	

Note: Always use this product together with the E58-CIFQ2.

This Cable is used to connect to the front-panel Setup Tool port.

Terminal Covers

Model	
E53-COV24 (3pcs)	

Note: The Terminal Covers E53-COV24 are provided with the Digital Temperature Controller.

Waterproof Packing

Applicable Controller	Model
E5EC-T	Y92S-P9
E5AC-T	Y92S-P10

Note: This Waterproof Packing is provided with the Digital Temperature Controller.

Waterproof Cover

Applicable Controller	Model
E5EC-T	Y92A-49N
E5AC-T	Y92A-96N

Front Port Cover

Model
Y92S-P7

Note: This Front Port Cover is provided with the Digital Temperature Controller.

Mounting Adapter

•	-	
	Model	
YS	2F-51 (2pcs)	

Note: This Mounting Adapter is provided with the Digital Temperature Controller.

Current Transformers (CTs)

Hole diameter	Model
5.8 mm	E54-CT1
12.0 mm	E54-CT3

CX-Thermo Support Software

• •
Model
EST2-2C-MV4

Note: CX-Thermo version 4.61 or higher is required for the E5EC-T/ E5AC-T.

For the system requirements for the CX-Thermo, refer to information on the EST2-2C-MV4 on the OMRON website (www.ia.omron.com).

Specifications

Ratings

natings			-							
Power supply voltage			A in model number: 100 to 240 VAC, 50/60 Hz D in model number: 24 VAC, 50/60 Hz; 24 VDC							
Operating vo	oltage range		85% to 110% of rated supply voltage							
Power consu	umntion	E5EC-T	8.7 VA max. at 100 to 240 VAC, and 5.5 VA max. at 24 VAC or 3.2 W max. at 24 VDC							
rower const	umption	E5AC-T	9.0 VA max. at 100 to 240 VAC, and 5.6 VA max. at 24 VAC or 3.4 W max. at 24 VDC							
Sensor inpu	ıt		Temperature input Thermocouple: K, J, T, E, L, U, N, R, S, B, W, or PL II Platinum resistance thermometer: Pt100 or JPt100 Infrared temperature sensor (ES1B): 10 to 70°C, 60 to 120°C, 115 to 165°C, or 140 to 260°C Analog input Current input: 4 to 20 mA or 0 to 20 mA Voltage input: 1 to 5 V, 0 to 5 V, or 0 to 10 V							
Input impedance			Current input: 150 Ω max., Voltage input: 1 M Ω min. (Use a 1:1 connection when connecting the ES2-HB/THB.)							
Control meti	hod		2-PID control (with auto-tuning) or ON/OFF control							
0	Relay output		SPST-NO, 250 VAC, 5 A (resistive load), electrical life: 100,000 operations, minimum applicable load: 5 V, 10 mA (reference value)							
Control output	Voltage output (for driving SSR)	Output voltage: 12 VDC ±20% (PNP), max. load current: 40 mA, with short-circuit protection circuit (The maximum load current is 21 mA for models with two control outputs.)							
	Linear current	output	4 to 20 mA DC/0 to 20 mA DC, load: 500 Ω max., resolution: approx. 10,000							
Auxiliary	Number of outp	outs	4							
output	Output specific	ations	SPST-NO. relay outputs, 250 VAC, Models with 4 outputs: 2 A (resistive load), Electrical life: 100,000 operations, Minimum applicable load: 10 mA at 5 V (reference value)							
Number of inputs			2, 4 or 6 (depends on model)							
Event input	External contact input specifications		Contact input: ON: 1 k Ω max., OFF: 100 k Ω min.							
			Non-contact input: ON: Residual voltage: 1.5 V max., OFF: Leakage current: 0.1 mA max.							
	specifications		Current flow: Approx. 7 mA per contact							
	Number of outp	outs	1 (only on models with a transfer output)							
Transfer output	Output specific	ations	Current output: 4 to 20 mA DC, Load: 500 Ω max., Resolution: Approx. 10,000 Linear voltage output: 1 to 5 VDC, load: 1 k Ω min., Resolution: Approx. 10,000							
Potentiomet	er input		100 Ω to 10 k Ω							
Setting meth	nod		Digital setting using front panel keys							
Indication method			11-segment digital display and individual indicators Character height: E5EC-T: PV: 18.0 mm, SV: 11.0 mm, MV: 7.8 mm							
Bank switch	ing		None							
Other functions			Manual output, heating/cooling control, loop burnout alarm, other alarm functions, heater burnout (HB) alarm (including SSR failure (HS) alarm), 40% AT, 100% AT, MV limiter, input digital filter, robust tuning, PV input shift, protection functions, extraction of square root, MV change rate limit, logic operations, temperature status display, moving average of input value, and display brightness setting							
Ambient ope	Ambient operating temperature		−10 to 55°C (with no condensation or icing), For 3-year warranty: −10 to 50°C with standard mounting (with no condensation or icing)							
Ambient operating humidity			25% to 85%							
Storage tem	perature		-25 to 65°C (with no condensation or icing)							
Altitude			2,000 m max.							
Recommend	ded fuse		T2A, 250 VAC, time-lag, low-breaking capacity							
Installation environment			Installation Category II, Pollution Degree 2 (IEC 61010-1 compliant)							

Input Ranges

●Thermocouple/Platinum Resistance Thermometer (Universal inputs)

Sen: typ		e		Thermocouple												Infrared temperature sensor										
Sensor specifica- tion			Pt100		JPt	100	I	к	,	J	•	Г	E	L	ı	U	N	R	S	В	w	PLII	10 to 70°C	60 to 120°C	115 to 165°C	140 to 260°C
	2300																				2300					
	1800																			1800						
	1700																	1700	1700							
	1600																	_								
	1500																				-					
ည	1400						1300										1300					1300				-
e G	1300						1300										1300					1500				
ä	1200						+																			
9	1100																									
Temperature range (°C)	1000	850							850					850												
<u>a</u>	900																									
훁	800																									
亘	700 600												600													
_	500		500.0		500.0			500.0																		
	400									400.0	400	400.0			400	400.0										
	300	_																								260
	200	_																						120	165	
	100	_		100.0		100.0	4																90			
	0														H					100						
	-100			0.0		0.0	+	-20.0	-100	-20.0				-100			-	0	0		0	0	0	0	0	0
	-200	-200	-199.9		199.9		-200	-20.0	-100	-20.0	-200	-199.9	-200	-100	-200	-199.9	-200									-
Set v	alue	0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24

Shaded settings are the default settings.

The applicable standards for the input types are as follows:

K, J, T, E, N, R, S, B: JIS C 1602-1995, IEC 60584-1

L: Fe-CuNi, DIN 43710-1985

U: Cu-CuNi, DIN 43710-1985

W: W5Re/W26Re, ASTM E988-1990

JPt100: JIS C 1604-1989, JIS C 1606-1989

Pt100: JIS C 1604-1997, IEC 60751

PL II: According to Platinel II electromotive force charts from BASF (previously Engelhard)

Analog input

Input type	Current		Voltage		
Input specification	4 to 20 mA 0 to 20 mA		1 to 5 V	0 to 5 V	0 to 10 V
Setting range	Usable in the following ranges by scaling: -1999 to 9999, -199.9 to 999.9, -19.99 to 99.99 or -1.999 to 9.999				
Set value	25	26	27	28	29

Alarm Types


Each alarm can be independently set to one of the following 17 alarm types. The default is 2: Upper limit. (see note.)

Auxiliary outputs are allocated for alarms. ON delays and OFF delays (0 to 999 s) can also be specified.


Note: In the default settings for models with HB or HS alarms, alarm 1 is set to a heater alarm (HA) and the Alarm Type 1 parameter is not displayed. To use alarm 1, set the output assignment to alarm 1.

Set		Alarm outpu	ut operation		
value	when alarm value X When alarm value X When alarm is positive is negative		When alarm value X is negative	Description of function	
0	Alarm function OFF	Outpu	t OFF	No alarm	
1	Upper- and lower-limit *1	ON L H PV	*2	Set the upward deviation in the set point for the alarm upper limit (H) and the lower deviation in the set point for the alarm lower limit (L). The alarm is ON when the PV is outside this deviation range.	
2 (default)	Upper-limit	ON OFF SP PV	ON X PV	Set the upward deviation in the set point by setting the alarm value (X). The alarm is ON when the PV is higher than the SP by the deviation or more.	
3	Lower-limit	ON X PV	ON X PV	Set the downward deviation in the set point by setting the alarm value (X). The alarm is ON when the PV is lower than the SP by the deviation or more.	
4	Upper- and lower-limit range *1	ON OFF SP PV	*3	Set the upward deviation in the set point for the alarm upper limit (H) and the lower deviation in the set point for the alarm lower limit (L). The alarm is ON when the PV is inside this deviation range.	
5	Upper- and lower-limit with standby sequence *1	ON L H PV	*4	A standby sequence is added to the upper- and lower-limit alarm (1). *6	
6	Upper-limit with standby sequence	ON OFF SP PV	ON X P	A standby sequence is added to the upper-limit alarm (2). *6	
7	Lower-limit with standby sequence	ON X PV	ON X PV	A standby sequence is added to the lower-limit alarm (3). *6	
8	Absolute-value upper-limit	ON OFF 0	ON OFF O PV	The alarm will turn ON if the process value is larger than the alarm value (X) regardless of the set point.	
9	Absolute-value lower-limit	ON OFF O PV	ON OFF PV	The alarm will turn ON if the process value is smaller than the alarm value (X) regardless of the set point.	
10	Absolute-value upper-limit with standby sequence	ON OFF 0 PV	ON ←X→ PV	A standby sequence is added to the absolute-value upper-limit alarm (8). *6	
11	Absolute-value lower-limit with standby sequence	ON →X→ PV	ON OFF PV	A standby sequence is added to the absolute-value lower-limit alarm (9). *6	
12	LBA (alarm 1 type only)	-		*7	
13	PV change rate alarm	-	-	*8	
14	SP absolute-value upper-limit alarm	ON OFF 0 SP	ON OFF SP	This alarm type turns ON the alarm when the set point (SP) is higher than the alarm value (X).	
15	SP absolute-value lower-limit alarm	ON →X→ OFF 0 SP	ON OFF SP	This alarm type turns ON the alarm when the set point (SP) is lower than the alarm value (X).	
	MV absolute-value upper-limit alarm *9	Standard Control	Standard Control		
40		ON OFF 0 MV	ON OFF 0 MV	This alarm type turns ON the alarm when the manipulated	
16		Heating/Cooling Control (Heating MV)	Heating/Cooling Control (Heating MV)	variable (MV) is higher than the alarm value (X).	
		ON OFF MV	Always ON		
		Standard Control	Standard Control		
	MV absolute-value lower-limit alarm *9	ON OFF 0 MV	ON OFF		
17		Heating/Cooling Control (Cooling MV)	Heating/Cooling Control (Cooling MV)	This alarm type turns ON the alarm when the manipulated variable (MV) is lower than the alarm value (X).	
		ON OFF 0	Always ON		

- *1 With set values 1, 4 and 5, the upper and lower limit values can be set independently for each alarm type, and are expressed as "L" and "H."
- *2 Set value: 1, Upper- and lower-limit alarm



*3 Set value: 4, Upper- and lower-limit range



- *4 Set value: 5, Upper- and lower-limit with standby sequence For Upper- and Lower-Limit Alarm Described Above *2
 - Case 1 and 2
 <u>Always OFF</u> when the upper-limit and lower-limit hysteresis overlaps.
 Case 3: <u>Always OFF</u>
- *5. Set value: 5, Upper- and lower-limit with standby sequence Always OFF when the upper-limit and lower-limit hysteresis overlaps.
- *6 Refer to the E5©C-T Digital Temperature Controllers Programmable Type User's Manual (Cat. No. H185) for information on the operation of the standby sequence
- standby sequence.

 *7 Refer to the E5□C-T Digital Temperature Controllers Programmable Type User's Manual (Cat. No. H185) for information on the loop burnout alarm (LBA). This setting cannot be used with a position-proportional model.

 *8 Refer to the E5□C-T Digital Temperature Controllers Programmable Type
- '8 Refer to the E5\(\subseteq\text{C-T Digital Temperature Controllers Programmable Type User's Manual (Cat. No. H185) for information on the PV change rate alarm.
- *9 When heating/cooling control is performed, the MV absolute upper limit alarm functions only for the heating operation and the MV absolute lower limit alarm functions only for the cooling operation.

Characteristics

	1131163					
Indication accuracy (at the ambient temperature of 23°C)		ture of	Thermocouple: $(\pm 0.3\%$ of indication value or $\pm 1^{\circ}$ C, whichever is greater) ± 1 digit max. *1 Platinum resistance thermometer: $(\pm 0.2\%$ of indication value or $\pm 0.8^{\circ}$ C, whichever is greater) ± 1 digit max. Analog input: $\pm 0.2\%$ FS ± 1 digit max. CT input: $\pm 5\%$ FS ± 1 digit max. Potentiometer input: $\pm 5\%$ FS ± 1 digit max.			
Transfer output accuracy			±0.3% FS max.			
Influence of	temperature	Thermocouple input (R, S, B, W, PL II): (±1% of indication value or ±10°C, whichever is greater) ±1 di max.				
Influence of voltage *2			Other thermocouple input: $(\pm 1\% \text{ of indication value or } \pm 4^{\circ}\text{C}$, whichever is greater) ± 1 digit max. *3 Platinum resistance thermometer: $(\pm 1\% \text{ of indication value or } \pm 2^{\circ}\text{C}$, whichever is greater) ± 1 digit max. Analog input: $\pm 1\% \text{FS} \pm 1$ digit max. CT input: $\pm 5\% \text{ FS} \pm 1$ digit max.			
Input sampli	ng period		50ms			
Hysteresis			Temperature input: 0.1 to 999.9°C or °F (in units of 0.1°C or°F) Analog input: 0.01% to 99.99% FS (in units of 0.01% FS)			
Proportional	band (P)		Temperature input: 0.1 to 999.9°C or °F (in units of 0.1°C or °F) Analog input: 0.1 to 999.9% FS (in units of 0.1% FS)			
Integral time			Standard, heating/cooling, or Position-proportional (Close): 0 to 9999 s (in units of 1 s), 0.0 to 999.9 s (in units of 0.1 s) Position-proportional (Floating): 1 to 9999 s (in units of 1 s), 0.1 to 999.9 s (in units of 0.1 s)*4			
Derivative tir	ne (D)		0 to 9999 s (in units of 1 s), 0.0 to 999.9 s (in units of 0.1 s) *4			
Proportional			Temperature input: 0.1 to 999.9°C or °F (in units of 0.1°C or °F) Analog input: 0.1 to 999.9% FS (in units of 0.1% FS)			
Integral time		-	0 to 9999 s (in units of 1 s), 0.0 to 999.9 s (in units of 0.1 s) *4			
Derivative tir	• • •	ooling	0 to 9999 s (in units of 1 s), 0.0 to 999.9 s (in units of 0.1 s) *4			
Control perio			0.1, 0.2, 0.5, 1 to 99 s (in units of 1 s)			
Manual reset			0.0 to 100.0% (in units of 0.1%)			
Alarm setting			-1999 to 9999 (decimal point position depends on input type)			
Influence of signal source resistance		ce resis-	Thermocouple: 0.1° C/ Ω max. (100 Ω max.) Platinum resistance thermometer: 0.1° C/ Ω max. (10 Ω max.)			
Insulation resistance			20 M Ω min. (at 500 VDC)			
Dielectric str	ength		3,000 VAC, 50/60 Hz for 1 min between terminals of different charge			
Vibration	Malfunction	n	10 to 55 Hz, 20 m/s ² for 10 min each in X, Y, and Z directions			
VIDIU.	Resistance		10 to 55 Hz, 20 m/s² for 2 hrs each in X, Y, and Z directions			
Shock	Malfunction		100 m/s², 3 times each in X, Y, and Z directions			
0.1.00.1.	Resistance		300 m/s², 3 times each in X, Y, and Z directions			
Weight		E5EC-T	Controller: Approx. 210 g, Adapter: Approx. 4 g × 2			
		E5AC-T	Controller: Approx. 250 g, Adapter: Approx. 4 g × 2			
Degree of pro			Front panel: IP66, Rear case: IP20, Terminals: IP00			
Memory prot	ection		Non-volatile memory (number of writes: 1,000,000 times)			
Setup Tool			CX-Thermo version 4.61 or higher			
Setup Tool port			E5EC-T/E5AC-T top panel: An E58-CIFQ2 USB-Serial Conversion Cable is used to connect to a USB port on the computer.*5 E5EC-T/E5AC-T front panel: An E58-CIFQ2 USB-Serial Conversion Cable and E58-CIFQ2-E Conversion Cable are used together to connect to a USB port on the computer.*5			
Standards Approved standards Conformed standards			UL 61010-1, Korean Radio Waves Act (Act 10564) EN 61010-1 (IEC 61010-1): Pollution Degree 2, overvoltage category II			
	Comonie	Stanuarus	EMI EN61326			
EMC			Radiated Interference Electromagnetic Field Strength: EN 55011 Group 1, class A Noise Terminal Voltage: EN 55011 Group 1, class A EMS: EN 61326 ESD Immunity: EN 61000-4-2 Electromagnetic Field Immunity: EN 61000-4-3 Burst Noise Immunity: EN 61000-4-4 Conducted Disturbance Immunity: EN 61000-4-6 Surge Immunity: EN 61000-4-5			
			Voltage Dip/Interrupting Immunity: EN 61000-4-11			

The indication accuracy of K thermocouples in the -200 to 1300°C range, T and N thermocouples at a temperature of -100°C max., and U and L thermocouples at any temperatures is ±2°C ±1 digit max. The indication accuracy of the B thermocouple at a temperature of 400°C max. is not specified. The indication accuracy of B thermocouples at a temperature of 200°C max. is ±3°C ±1 digit max. The indication accuracy of W thermocouples is (±0.3% of PV or ±3°C, whichever is greater) ±1 digit max. The indication accuracy of PL II thermocouples is (±0.3% of PV or ±2°C, whichever is greater) ±1 digit max. Ambient temperature: -10°C to 23°C to 55°C, Voltage range: -15% to 10% of rated voltage K thermocouple at -100°C max.: ±10°C max.

The unit is determined by the setting of the Integral/Derivative Time Unit parameter.

External communications (RS-485) and USB-serial conversion cable communications can be used at the same time.

Program Control			
Number of programs (patterns)		8	
Number of segments (steps)		32	
C		Time setting (Segment set with set point and time.)	
Segment setting method		Slope setting (Segment set with segment type, set point, slope, and time.)	
Commont times		0 h 0 min to 99 h 59 min	
Segment times		0 min 0 s to 99 min 59 s	
Alarm setting		Set separately for each program.	
Reset operation		Select either stopping control or fixed SP operation.	
Startup operation		Select continuing, resetting, manual operation, or run mode.	
PID sets	Number of sets	8	
PID sets	Setting method	Set separately for each program (automatic PID group selection also supported)	
Alarm SP function		Select from ramp SP and target SP.	
Drogram status control	Segment operation	Advance, segment jump, hold, and wait	
Program status control	Program operation	Program repetitions and program links	
Wait operation	Wait method	Waiting at segment ends	
wait operation	Wait width setting	Same wait width setting for all programs	
	Number of outputs	2	
Time signals	Number of ON/OFF Operations	1 each per output	
	Setting method	Set separately for each program.	
Program status output		Program end output (pulse width can be set), run output, stage output	
	PV start	Select from segment 1 set point, slope-priority PV start	
Program startup operation	Standby	0 h 0 min to 99 h 59 min	
Standby		0 day 0 h to 99 day 23h	
Operation end operation	•	Select from resetting, continuing control at final set point, and fixed SP control.	
Program SP shift		Same program SP shift for all programs	

USB-Serial Conversion Cable

Applicable OS	Windows XP/Vista/7/8	
Applicable software	CX-Thermo version 4.61 or higher	
Applicable models	E5□C-T Series, E5□C Series, and E5CB Series	
USB interface standard	Conforms to USB Specification 2.0.	
DTE speed	38400 bps	
Connector specifications	Computer: USB (type A plug) Digital Temperature Controller: Special serial connector	
Power supply	Bus power (Supplied from USB host controller.)*	
Power supply voltage	5 VDC	
Current consumption	450 mA max.	
Output voltage	4.7±0.2 VDC (Supplied from USB-Serial Conversion Cable to the Digital Temperature Controller.)	
Output current	250 mA max. (Supplied from USB-Serial Conversion Cable to the Digital Temperature Controller.)	
Ambient operating temperature	0 to 55°C (with no condensation or icing)	
Ambient operating humidity	10% to 80%	
Storage temperature	-20 to 60°C (with no condensation or icing)	
Storage humidity	10% to 80%	
Altitude	2,000 m max.	
Weight	Approx. 120 g	

Windows is a registered trademark of Microsoft Corporation in the United States and or other countries.

* Use a high-power port for the USB port.

Note: A driver must be installed on the computer. Refer to the Instruction Manual included with the Cable for the installation procedure.

Communications Specifications

Transmission line connection method	RS-485: Multidrop	
Communications	RS-485 (two-wire, half duplex)	
Synchronization method	Start-stop synchronization	
Protocol	CompoWay/F, or Modbus	
Baud rate*	9600, 19200, 38400, or 57600 bps	
Transmission code	ASCII	
Data bit length*	7 or 8 bits	
Stop bit length*	1 or 2 bits	
Error detection	Vertical parity (none, even, odd) Block check character (BCC) with CompoWay/F or CRC-16 Modbus	
Flow control	None	
Interface	RS-485	
Retry function	None	
Communications buffer	217 bytes	
Communications response wait time	0 to 99 ms Default: 20 ms	

The baud rate, data bit length, stop bit length, and vertical parity can be individually set using the Communications Setting Level.

Communications Functions

Programless communications ⁻¹	You can use the memory in the PLC to read and write E5□C-T parameters, start and reset operation, etc. The E5□C-T automatically performs communications with PLCs. No communications programming is required. Number of connected Digital Temperature Controllers: 32 max. Applicable PLCs OMRON PLCs CS Series, CJ Series, or CP Series Mitsubishi Electric PLCs MELSEC Q Series, L Series

Component Communications	When Digital Temperature Controllers are connected, set points and RUN/STOP commands can be sent from the Digital Temperature Controller that is set as the master to the Digital Temperature Controllers that are set as slaves. Slope and offsets can be set for the set point. Number of connected Digital Temperature Controllers: 32 max. (including master)	
Copying ^{*1}	When Digital Temperature Controllers are connected, the parameters can be copied from the Digital Temperature Controller that is set as the master to the Digital Temperature Controllers that are set as slaves.	

MELSEC is a registered trademark of Mitsubishi Electric Corporation.

Current Transformer (Order Separately) Ratings


Dielectric strength	1,000 VAC for 1 min	
Vibration resistance	50 Hz, 98 m/s ²	
Weight	E54-CT1: Approx. 11.5 g, E54-CT3: Approx. 50 g	
Accessories (E54-CT3 only)	Armatures (2) Plugs (2)	

Heater Burnout Alarms and SSR Failure Alarms

CT input (for heater current detection)	Models with detection for single-phase heaters: One input	
Maximum heater current	50 A AC	
Input current indication accuracy	±5% FS ±1 digit max.	
Heater burnout alarm setting range *1	0.1 to 49.9 A (in units of 0.1 A) Minimum detection ON time: 100 ms *3	
SSR failure alarm setting range *2	0.1 to 49.9 A (in units of 0.1 A) Minimum detection OFF time: 100 ms *4	


- *1 For heater burnout alarms, the heater current will be measured when the control output is ON, and the output will turn ON if the heater current is lower than the set value (i.e., heater burnout detection current value).
- *2 For SSR failure alarms, the heater current will be measured when the control output is OFF, and the output will turn ON if the heater current is higher than the set value (i.e., SSR failure detection current value).
- The value is 30 ms for a control period of 0.1 s or 0.2 s. The value is 35 ms for a control period of 0.1 s or 0.2 s.

Electrical Life Expectancy Curve for Relays (Reference Values)



^{*1} Both the programless communications and the component communications support the copying.


External Connections




- Note: 1. The application of the terminals depends on the model.
 - 2. Do not wire the terminals that are shown with a gray background.
 - 3. When complying with EMC standards, the cable that connects the sensor must be 30 m or less. If the cable length exceeds 30 m, compliance with EMC standards will not be possible.
 - 4. Connect M3 crimped terminals.

Isolation/Insulation Block Diagrams


Models with 4 Auxiliary Outputs



Nomenclature



E5AC-T




Dimensions (Unit: mm)

Controllers

E5EC-T






0

The Setup Tool ports are on the front and top of the Digital Temperature Controller. It is used to connect the Temperature Controller to the computer to use the Setup Tool. The E58-CIFQ2 USB-Serial Conversion Cable is required to make the connection. Refer to the instructions that are provided with the USB-Serial Conversion Cable for the connection procedure.


Note: Do not leave the USB-Serial Conversion Cable connected when you use the Temperature Controller.






- Recommended panel thickness is 1 to 8 mm.
- Group mounting is not possible in the vertical direction. (Maintain the specified mounting space between Controllers.)
- To mount the Controller so that it is waterproof, insert the waterproof packing onto the Controller.
- When two or more Controllers are mounted, make sure that the surrounding temperature does not exceed the allowable operating temperature specified in the specifications.

Selections for Control Outputs 1 and 2: QQ, QR, RR, CC, PR, or CQ If you also specify 019, 021, 022 for the option selection and use group mounting, the ambient temperature must be 45°C or less. If the ambient temperature is 55°C, maintain the following mounting spaces between Controllers.




E5AC-T



The Setup Tool ports are on the front and top of the Digital Temperature Controller. It is used to connect the Temperature Controller to the computer to use the Setup Tool. The E58-CIFQ2 USB-Serial Conversion Cable is required to make the connection. Refer to the instructions that are provided with the USB-Serial Conversion Cable for the connection procedure.

Note: Do not leave the USB-Serial Conversion Cable connected when you use the Temperature Controller.




- Recommended panel thickness is 1 to 8 mm.
- Group mounting is not possible in the vertical direction. (Maintain the specified mounting space between Controllers.)
- To mount the Controller so that it is waterproof, insert the waterproof packing onto the Controller.
- · When two or more Controllers are mounted, make sure that the surrounding temperature does not exceed the allowable operating temperature specified in the specifications.

Accessories (Order Separately)

USB-Serial Conversion Cable E58-CIFQ2







Conversion Cable E58-CIFQ2-E

Conversion Cable

Connecting to the E58-CIFQ2 USB-Serial Conversion Cable







Note: Always use this product together with the E58-CIFQ2.

Terminal Covers

E53-COV24 (Three Covers provided.)



● Waterproof Packing Y92S-P9 (for DIN 48 × 96)



The Waterproof Packing is provided with the Temperature Controller.

Order the Waterproof Packing separately if it becomes lost or damaged.

The degree of protection when the Waterproof Packing is used is IP66.


Also, keep the Port Cover on the front-panel Setup Tool port of the E5EC-T/E5AC-T securely closed.

To maintain an IP66 degree of protection, the Waterproof Packing and the Port Cover for the front-panel Setup Tool port must be periodically replaced because they may deteriorate, shrink, or harden depending on the operating environment. The replacement period will vary with the operating environment.


Check the required period in the actual application. Use 3 years or sooner as a guideline.

If a waterproof structure is not required, then the Waterproof Packing does not need to be installed.






Setup Tool Port Cover for top panel Y92S-P7



Order this Port Cover separately if the Port Cover on the front-panel Setup Tool port is lost or damaged. The Waterproof Packing must be periodically replaced because it may deteriorate, shrink, or harden depending on the operating environment.


Mounting AdapterY92F-51 (Two Adapters provided.)




One pair is provided with the Controller.


Order this Adapter separately if it becomes lost or damaged.


● Watertight Cover Y92A-49N (48 × 96)





● Watertight Cover Y92A-96N (96 × 96)






Current Transformers


E54-CT1






E54-CT3






E54-CT3 Accessories


• Armature



• Plug



Connection Example




Thru-current (lo) vs. Output Voltage (Eo) (Reference Values) E54-CT1

L34-C11

Maximum continuous heater current: 50 A (50/60 Hz) Number of windings: 400±2

Number of windings: 400 \pm 2 Winding resistance: 18 \pm 2 Ω




Thru-current (Io) A (r.m.s.)

Thru-current (Io) vs. Output Voltage (Eo) (Reference Values) E54-CT3

Maximum continuous heater current: 120 A (50/60 Hz) (Maximum continuous heater current for an OMRON Digital Temperature Controller is 50 A.)


Number of windings: 400 ± 2 Winding resistance: $8\pm0.8~\Omega$



Thru-current (Io) A (r.m.s.)


E5□C-T


This diagram shows all of the setting levels. To move to the advanced function setting level and calibration level, you must enter passwords. Some parameters are not displayed depending on the protect level setting and the conditions of use.




- *1 Set the PF Setting parameter to #-M (Auto/Manual).
- *2 The No. 1 display will flash when the keys are pressed for 1 s or longer.
- *3 Set the PF Setting parameter to PF dP (monitor/setting items).

E5□**C-T**Some parameters may not be displayed depending on the model and other settings.







Error Displays (Troubleshooting)


When an error occurs, the No. 1 display or No. 2 display shows the error code. Take necessary measure according to the error code, referring the following table.

Display	Name		Meaning	Action	Operation
S.ERR	Input error	range.* The input type is not set correctly. The sensor is disconnected or short- circuited. The sensor is not wired correctly. The sensor is not wired. * Control Range Temperature resistance thermometer or thermocouple input: SP Lower Limit - 20°C to SP Upper Limit + 20°C (SP Lower Limit - 40°F to SP Upper Limit + 40°F)		Check the wiring for input to be sure it is wired correctly, not broken, and not shorted. Also check the input type. If there are no problems in the wiring or input type settings, cycle the power supply. If the display remains the same, replace the Digital Temperature Controller. If the display is restored to normal, then the probable cause is external noise affecting the control system. Check for external noise. Note: For a temperature resistance thermometer, the input is considered disconnected if the A, B, or B' line is broken.	After the error occurs and it is displayed, the alarm output will operate as if the upper limit was exceeded. It will also operate as if transfer output exceeded the upper limit. If an input error is assigned to a control output or auxiliary output, the output will turn ON when the input error occurs. The error message will appear in the display for the PV. Note: 1. The heating and cooling control outputs will turn OFF. 2. When the manual MV, MV at stop, MV at reset, or MV at error is set, the control output is determined by the set value.
CCCC	Display - range exceeded	Below -1,999	This is not an error. It is displayed when the control range is wider than the display range and the PV exceeds the display range. The PV is	-	Control continues and operation is normal. The value will appear in the display for the PV. Refer to the E5□C Digital Temperature Controllers User's Manual (Cat. No. H174) or the
ככככ	CXCCCCCC	Above 9,999	displayed for the range that is given on the left (the number without the decimal point).		E5 C-T Digital Temperature Controllers Programmable Type User's Manual (Cat. No. H185) for information on the controllable range.
E333	A/D converter error	There is an error in the internal circuits.		After checking the input error, turn the power OFF then back ON again. If the display remains the same, the controller must be repaired. If the display is restored to normal, then a probable cause can be external noise affecting the control system. Check for external noise.	The control outputs, auxiliary outputs, and transfer outputs turn OFF. (A current output will be approx. 0 mA and a linear voltage output will be approx. 0V.)
EIII	Memory error	There is an error in the internal memory operation.		First, cycle the power supply. If the display remains the same, the controller must be repaired. If the display is restored to normal, then a probable cause can be external noise affecting the control system. Check for external noise.	The control outputs, auxiliary outputs, and transfer outputs turn OFF. (A current output will be approx. 0 mA and a linear voltage output will be approx. 0V.)
FFFF	Overcurrent	This error is displayed when the peak current exceeds 55.0 A.		-	Control continues and operation is normal. The error message will appear for the following displays. Heater Current Value 1 Monitor Heater Current Value 2 Monitor Leakage Current Value 1 Monitor Leakage Current Value 2 Monitor
[HB or HS alarm	If there is a HB or HS alarm, the No. 1 display will flash in the relevant setting level.		-	The No. 1 display for the following parameter flashes in Operation Level or Adjustment Level. Heater Current Value 1 Monitor Heater Current Value 2 Monitor Leakage Current Value 1 Monitor Leakage Current Value 2 Monitor However, control continues and operation is normal.
	Potentiometer Input Error (Position- proportional Models Only)	"" will be displayed for the Valve Opening Monitor parameter if any of the following error occurs. • Motor calibration has not been performed. • The wiring of the potentiometer is incorrect or broken. • The potentiometer input value is incorrect (e.g., the input is out of range or the potentiometer has failed).		Check for the above errors.	Close control: The control output is OFF or the value that is set for the MV at PV Error parameter is output. Floating control: Operation will be normal.


Safety Precautions

■ Be sure to read the precautions for all E5□C/E5□C-T models in the website at: http://www.ia.omron.com/.

Warning Indications



Meaning of Product Safety Symbols






Used for general CAUTION, WARNING, or DANGER precautions for which there is no specified symbol. (This symbol is also used as the alerting symbol, but shall not be used in this meaning on the product.)



Used for general mandatory action precautions for which there is no specified symbol.

CAUTION

Do not touch the terminals while power is being





Electric shock may occur. Do not touch any cables or connectors with wet hands.



Electric shock, fire, or malfunction may occasionally occur. Do not allow metal objects, conductors, cuttings from installation work, or moisture to enter the Digital Temperature Controller or the Setup Tool port or ports. Attach the cover to the front-panel Setup Tool port whenever you are not using it to prevent foreign objects from entering the port.

Do not use the Digital Temperature Controller where subject to flammable or explosive gas. Otherwise, minor injury from explosion may occasionally occur.



Not doing so may occasionally result in fire. Do not allow dirt or other foreign objects to enter the Setup Tool port or ports, or between the pins on the connectors on the Setup Tool cable.



Minor electric shock or fire may occasionally occur. Do not use any cables that are damaged.



Never disassemble, modify, or repair the product or touch any of the internal parts. Minor electric shock, fire, or malfunction may occasionally occur.



CAUTION - Risk of Fire and Electric Shock


a. This product is UL listed*1 as Open Type Process Control Equipment. It must be mounted in an enclosure that does not allow fire to escape externally.



- b. More than one disconnect switch may be required to deenergize the equipment before servicing the product.
- c. Signal inputs are SELV, limited energy. *2
- d. Caution: To reduce the risk of fire or electric shock, do not interconnect the outputs of different Class 2 circuits. *3


If the output relays are used past their life expectancy, contact fusing or burning may occasionally occur. Always consider the application conditions and use the output relays within their rated load and electrical life expectancy. The life expectancy of output relays varies considerably with the output load and switching conditions.

Even if you replace only the Main Unit of the E5DC, check the condition of the Terminal Unit.



If the terminals are corroded, replace the Terminal Unit as well.

Tighten the terminal screws to the rated torque of between 0.43 and 0.58 Nem. *4





Set the parameters of the product so that they are suitable for the system being controlled. If they are not suitable, unexpected operation may occasionally result in property damage or accidents.



A malfunction in the product may occasionally make control operations impossible or prevent alarm outputs, resulting in property damage. To maintain safety in the event of malfunction of the product, take appropriate safety measures, such as installing a monitoring device on a separate line.

- *1. E5CC, E5EC, E5AC, and E5DC Digital Temperature Controllers that were shipped through November 2013 are UL recognized
- *2. An SELV (separated extra-low voltage) system is one with a power supply that has double or reinforced insulation between the primary and the secondary circuits and has an output voltage of 30 V r.m.s. max. and 42.4 V peak max. or 60 VDC max.
- *3. A class 2 circuit is one tested and certified by UL as having the current and voltage of the secondary output restricted to specific levels.
- *4. The specified torque is 0.5 N·m for the E5CC-U.

Precautions for Safe Use

Be sure to observe the following precautions to prevent malfunction or adverse affects on the performance or functionality of the product. Not doing so may occasionally result in faulty operation. Do not handle the Digital Temperature Controller in ways that exceed the ratings.

- 1. This product is specifically designed for indoor use only. Do not use this product in the following places:
 - · Places directly subject to heat radiated from heating equipment.
 - · Places subject to splashing liquid or oil atmosphere.
 - · Places subject to direct sunlight.
 - Places subject to dust or corrosive gas (in particular, sulfide gas and ammonia gas).
 - Places subject to intense temperature change.
 - · Places subject to icing and condensation.
 - · Places subject to vibration and large shocks.
- Use and store the product within the rated ambient temperature and humidity.

Gang-mounting two or more Digital Temperature Controllers, or mounting Digital Temperature Controllers above each other may cause heat to build up inside the Digital Temperature Controllers, which will shorten their service life. In such a case, use forced cooling by fans or other means of air ventilation to cool down the Digital Temperature Controllers.

- To allow heat to escape, do not block the area around the Digital Temperature Controller.
 - Do not block the ventilation holes on the Digital Temperature Controller.
- Be sure to wire properly with correct signal name and polarity of terminals.
- 5. Use the specified size of crimped terminals (M3, width of 5.8 mm or less) to wire the E5CC, E5EC, E5AC, E5DC, or E5□C-T. To connect bare wires to the terminal block of the E5CC, E5EC, E5AC, E5DC, or E5□C-T, use copper braided or solid wires with a gage of AWG24 to AWG18 (equal to a cross-sectional area of 0.205 to 0.823 mm²). (The stripping length is 6 to 8 mm.) Up to two wires of the same size and type, or two crimped terminals can be inserted into a single terminal.

Use the specified size of crimped terminals (M3.5, width of 7.2 mm or less) to wire the E5CC-U. To connect bare wires to the terminal block of the E5CC-U, use copper braided or solid wires with a gage of AWG24 to AWG14 (equal to a cross-sectional area of 0.205 to 2.081 mm²). (The stripping length is 5 to 6 mm.) Up to two wires of the same size and type, or two crimped terminals can be inserted into a single terminal.

Use the specified size of crimped terminals (M3, width of 5.8 mm or less) to wire the E5GC.*

To connect bare wires to the terminal block of the E5GC, use copper braided or solid wires with a gauge of AWG24 to AWG18 (equal to a cross-sectional area of 0.205 to 0.823 mm2). (The stripping length for Digital Temperature Controllers with screw terminal blocks is 6 to 8 mm. The stripping length for Digital Temperature Controllers with screwless clamp terminal blocks is 8 to 12 mm.)

Up to two wires of the same size and type, or two crimped terminals can be inserted into a single terminal. When connecting two wires into one terminal of a Digital Temperature Controller with a screwless clamp terminal block, use ferrules with a diameter of 0.8 to 1.4 mm and an exposed conductor length of 8 to 12 mm that two wires are crimped for a ferrule.*

- * The Digital Temperature Controller with screwless clamp terminals underwent UL testing with one braided wire connected.
- 6. Do not wire the terminals that are not used.
- 7. Use a commercial power supply for the power supply voltage input to a Digital Temperature Controller with AC input specifications. Do not use the output from an inverter as the power supply. Depending on the output characteristics of the inverter, temperature increases in the Digital Temperature Controller may cause smoke or fire damage even if the inverter has a specified output frequency of 50/60 Hz.
- 8. To avoid inductive noise, keep the wiring for the product's terminal block away from power cables carry high voltages or large currents. Also, do not wire power lines together with or parallel to product wiring. Using shielded cables and using separate conduits or ducts is recommended.
 - Attach a surge suppressor or noise filter to peripheral devices that

generate noise (in particular, motors, transformers, solenoids, magnetic coils, or other equipment that have an inductance component).

When a noise filter is used at the power supply, first check the voltage or current, and attach the noise filter as close as possible to the product.

- Allow as much space as possible between the product and devices that generate powerful high frequencies (high-frequency welders, high-frequency sewing machines, etc.) or surge.
- 9. Use this product within the rated load and power supply.
- 10.Make sure that the rated voltage is attained within two seconds of turning ON the power using a switch or relay contact. If the voltage is applied gradually, the power may not be reset or output malfunctions may occur.
- 11.Make sure that the Digital Temperature Controller has 30 minutes or more to warm up after turning ON the power before starting actual control operations to ensure the correct temperature display.
- 12. When executing self-tuning with E5□C, turn ON power to the load (e.g., heater) at the same time as or before supplying power to the product. If power is turned ON to the product before turning ON power to the load, self-tuning will not be performed properly and optimum control will not be achieved.
- 13.A switch or circuit breaker must be provided close to the product. The switch or circuit breaker must be within easy reach of the operator, and must be marked as a disconnecting means for this unit.
- 14.Use a soft and dry cloth to clean the product carefully. Do not use organic solvent, such as paint thinner, benzine or alcohol to clean the product.
- 15.Design the system (e.g., control panel) considering the 2 seconds of delay that the product's output to be set after power ON.
- 16. The output may turn OFF when you move to the initial setting level. Take this into consideration when performing control operations.
- 17. The number of non-volatile memory write operations is limited. Therefore, use RAM write mode when frequently overwriting data during communications or other operations.
- 18.Always touch a grounded piece of metal before touching the Digital Temperature Controller to discharge static electricity from your body.
- 19. Use suitable tools when taking the Digital Temperature Controller apart for disposal. Sharp parts inside the Digital Temperature Controller may cause injury.
- **20.**For compliance with Lloyd's standards, the E5CC, E5CC-U, E5EC, and E5AC must be installed under the conditions that are specified in *Shipping Standards*.
- 21. For the Digital Temperature Controller with two Setup Tool ports (E5EC/E5AC/E5DC/E5GC), do not connect cables to both ports at the same time. The Digital Temperature Controller may be damaged or may malfunction.
- **22.**Do not place heavy object on the Conversion Cable, bend the cable past its natural bending radius, or pull on the cable with undue force.
- 23.Do not disconnect the Communications Conversion Cable or the USB-Serial Conversion Cable while communications are in progress. Damage or malfunction may occur.
- 24. Do not touch the external power supply terminals or other metal parts on the Digital Temperature Controller.
- **25.**Refer to the E5 □C Digital Temperature Controllers User's Manual (Cat. No. H174) for information on the communications distances and cables for the E5 □C.
 - For details on the E5□C-T, refer to the *E5□C-T Digital*Temperature Controllers Programmable Type User's Manual (Cat. No. H185).
- **26.** Do not bend the communications cables past their natural bending radius. Do not pull on the communications cables.
- 27.Do not turn the power supply to the Digital Temperature Controller ON or OFF while the USB-Serial Conversion Cable is connected. The Digital Temperature Controller may malfunction.
- 28.Make sure that the indicators on the USB-Serial Conversion Cable are operating properly. Depending on the application conditions, deterioration in the connectors and cable may be accelerated, and normal communications may become impossible. Perform periodic inspection and replacement.
- 29. Connectors may be damaged if they are inserted with excessive force. When connecting a connector, always make sure that it is oriented correctly. Do not force the connector if it does not connect smoothly.

- 30. Noise may enter on the USB-Serial Conversion Cable, possibly causing equipment malfunctions. Do not leave the USB-Serial Conversion Cable connected constantly to the equipment.
- 31. For the E5DC, when you attach the Main Unit to the Terminal Unit, make sure that the hooks on the Main Unit are securely inserted into the Terminal Unit.
- 32. For the E5CC-U, when you attach the Main Unit to the socket, make sure that the hooks on the socket are securely inserted into the Main Unit.
- 33. Install the DIN Track vertically to the ground.
- 34. For the E5DC, always turn OFF the power supply before connecting the Main Unit to or disconnecting the Main Unit from the Terminal Unit, and never touch nor apply shock to the terminals or electronic components. When connecting or disconnecting the Main Unit, do not allow the electronic components to touch the case.
- **35.**Observe the following precautions when you remove the terminal block or pulling out the interior of the product of the E5GC.
 - Always follow the instructions provided in the E5□C Digital Temperature Controllers User's Manual (Cat. No. H174).
 - Turn OFF the power supply before you start and never touch nor apply shock to the terminals or electric components.
 When you insert the interior body of the Digital Temperature Controller, do not allow the electronic components to touch the case.
 - · Check for any corrosion on the terminals.
 - When you insert the interior body into the rear case, confirm that the hooks on the top and bottom are securely engaged with the case.

Shipping Standards

The E5CC, E5CC-U, E5EC, and E5AC comply with Lloyd's standards. When applying the standards, the following installation requirements must be met in the application.

Application Conditions

Installation Location

The E5CC, E5CC-U, E5EC, and E5AC comply with installation category ENV1 and ENV2 of Lloyd's standards. Therefore, they must be installed in a location equipped with air conditioning. They cannot be used on the bridge or decks, or in a location subject to strong vibration.

Precautions for Correct Use

Service Life

- Use the product within the following temperature and humidity ranges:
 Temperature: -10 to 55°C (with no icing or condensation)
 Humidity: 25% to 85%
 - If the product is installed inside a control board, the ambient temperature must be kept to under 55°C, including the temperature around the product.
- 2. The service life of electronic devices like Digital Temperature Controllers is determined not only by the number of times the relay is switched but also by the service life of internal electronic components. Component service life is affected by the ambient temperature: the higher the temperature, the shorter the service life and, the lower the temperature, the longer the service life. Therefore, the service life can be extended by lowering the temperature of the Digital Temperature Controller.
- 3. When two or more Digital Temperature Controllers are mounted horizontally close to each other or vertically next to one another, the internal temperature will increase due to heat radiated by the Digital Temperature Controllers and the service life will decrease. In such a case, use forced cooling by fans or other means of air ventilation to cool down the Digital Temperature Controllers. When providing forced cooling, however, be careful not to cool down the terminals sections alone to avoid measurement errors.

Measurement Accuracy

- 1. When extending or connecting the thermocouple lead wire, be sure to use compensating wires that match the thermocouple types.
- When extending or connecting the lead wire of the platinum resistance thermometer, be sure to use wires that have low resistance and keep

- the resistance of the three lead wires the same.

 Mount the product so that it is horizontally level.
- If the measurement accuracy is low, check to see if input shift has been set correctly.

Waterproofing (Not applicable to the E5CC-U/ E5DC.)

The degree of protection is as shown below. Sections without any specification on their degree of protection or those with $IP \square 0$ are not waterproof.

Front panel: IP66, Rear case: IP20, Terminal section: IP00 When waterproofing is required, insert the Waterproof Packing on the backside of the front panel. Keep the Port Cover on the front-panel Setup Tool port of the E5EC/E5AC/E5EC-T/E5AC-T securely closed. The degree of protection when the Waterproof Packing is used is IP66. To maintain an IP66 degree of protection, the Waterproof Packing and the Port Cover for the front-panel Setup Tool port must be periodically replaced because they may deteriorate, shrink, or harden depending on the operating environment. The replacement period will vary with the operating environment. Check the required period in the actual application. Use 3 years or sooner as a guideline. If the Waterproof Packing and Port Cover are not periodically replaced, waterproof performance may not be maintained. If a waterproof structure is not required, then the Waterproof Packing does not need to be installed.

Operating Precautions


- When using self-tuning, turn ON power for the load (e.g., heater) at the same time as or before supplying power to the Digital Temperature Controller. If power is turned ON for the Digital Temperature Controller before turning ON power for the load, self-tuning will not be performed properly and optimum control will not be achieved.
 - When starting operation after the Digital Temperature Controller has warmed up, turn OFF the power and then turn it ON again at the same time as turning ON power for the load. (Instead of turning the Digital Temperature Controller OFF and ON again, switching from STOP mode to RUN mode can also be used.)
- Avoid using the Digital Temperature Controller in places near a radio, television set, or wireless installing. These devices can cause radio disturbances which adversely affect the performance of the Controller.

Others

- Do not Connect or disconnect the Conversion Cable connector repeatedly over a short period of time.
 The computer may malfunction.
- After connecting the Conversion Cable to the computer, check the COM port number before starting communications. The computer requires time to recognize the cable connection. This delay does not indicate failure.
- Do not connect the Conversion Cable through a USB hub. Doing so may damage the Conversion Cable.
- Do not use an extension cable to extend the Conversion Cable length when connecting to the computer. Doing so may damage the Conversion Cable.

MountingMounting to a Panel

E5EC-T/E5AC-T




- For waterproof mounting, waterproof packing must be installed on the Digital Temperature Controller. Waterproofing is not possible when group mounting several Digital Temperature Controllers. Waterproof packing is not necessary when there is no need for the waterproofing function.
- 2. Insert the E5EC/E5AC/E5EC-T/E5AC-T into the mounting hole in the panel.
- 3. Push the adapter from the terminals up to the panel, and temporarily fasten the E5EC/E5AC/E5EC-T/E5AC-T.
- 4. Tighten the two fastening screws on the adapter. Alternately tighten the two screws little by little to maintain a balance. Tighten the screws to a torque of 0.29 to 0.39 N·m.

Mounting the Terminal Cover

E5EC-T/E5AC-T

Slightly bend the E53-COV24 Terminal Cover to attach it to the terminal block as shown in the following diagram. The Terminal Cover cannot be attached in the opposite direction.




Precautions when Wiring


- Separate input leads and power lines in order to prevent external noise
- Use a shielded, AWG24 to AWG18 (cross-sectional area of 0.205 to 0.8231 mm²) twisted-pair cable. Use a shielded, AWG24 to AWG14 (cross-sectional area of 0.205 to 2.081 mm²) twisted-pair cable for the E5CC-U. The stripping length is 6 to 8 mm for the E5CC, E5EC, E5AC, E5DC, or E5CC-T and 5 to 6 mm for the E5CC-U.

The E5GC stripping length is 6 to 8 mm for models with screw terminal blocks and 8 to 12 mm for models with screwless clamp terminal blocks

- Use crimp terminals when wiring the terminals.
- Use the suitable wiring material and crimp tools for crimp terminals.
- Tighten the terminal screws to a torque of 0.43 to 0.58 N⋅m.
 The specified torque is 0.5 N⋅m for the E5CC-U.
- For the E5GC, E5CC, E5EC, E5AC, E5DC, or E5□C-T, use the following types of crimp terminals for M3 screws.




 For the E5CC-U, use the following types of crimp terminals for M3.5 screws.



 For E5GC Controllers with screwless clamp terminal blocks, use braided or solid wires with a gauge of AWG24 to AWG18 (equal to a cross-sectional area of 0.205 to 0.823 mm²).

The length of the conductive portion inserted into the terminal must be 8 to 12 mm. Ferrules must be 0.8 to 1.4 mm in diameter..



• Recommended Ferrules for E5GC Screwless Clamp Terminals

Manuf	acturer	Model number	
Altech Corp.		2623.0	
Daido Solderless	Terminal Mfg. Co.	AVA-0.5	
J.S.T. Mfg. Co.		TUB-0.5	
Nichifu Co.	Single (1 wire)	TGNTC-1.25-9T TGVTC-1.25-11T TGNTC-1.25-11T TC0.3-9.5 TC1.25-11S-ST TC1.25-11S TC2-11S	
	Double (2 wires)	TGWVTC-1.25-9T TGWVTC-1.25-11T	

Three-year Guarantee

Period of Guarantee


The guarantee period of the Unit is three years starting from the date the Unit is shipped from the factory.

Scope of Guarantee

The Unit is guaranteed under the following operating conditions.

- 1. Average Operating Temperature (see note): -10°C to 50°C
- 2. Mounting Method: Standard mounting

Note: Average Operating Temperature
Refer to the process temperature
of the Unit mounted to a control
panel and connected to peripheral
devices on condition that the Unit
is in stable operation, sensor input
type K is selected for the Unit, the



positive and negative thermocouple input terminals of the Unit are short-circuited, and the ambient temperature is stable.

Should the Unit malfunction during the guarantee period, OMRON shall repair the Unit or replace any parts of the Unit at the expense of OMRON.

Terms and Conditions of Sale

- Offer; Acceptance. These terms and conditions (these "Terms") are deemed part of all quotes, agreements, purchase orders, acknowledgments, price lists, catalogs, manuals, brochures and other documents, whether electronic or in catalogs, manuals, brochures and other documents, whether electronic or in writing, relating to the sale of products or services (collectively, the "Products") by Omron Electronics LLC and its subsidiary companies ("Omron"). Omron objects to any terms or conditions proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these Terms. Prices: Payment Terms. All prices stated are current, subject to change without notice by Omron. Omron reserves the right to increase or decrease prices on any unshipped portions of outstanding orders. Payments for Products are due net 30 days unless otherwise stated in the invoice. Discounts. Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (i) the invoice is paid according to Omron's payment terms and (ii) Buyer has no past due amounts.

- and (ii) Buyer has no past due amounts.

 Interest. Omron, at its option, may charge Buyer 1-1/2% interest per month or the maximum legal rate, whichever is less, on any balance not paid within the
- Orders. Omron will accept no order less than \$200 net billing.

 Governmental Approvals. Buyer shall be responsible for, and shall bear all costs involved in, obtaining any government approvals required for the importation or sale of the Products.
- Taxes. All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Omron or required to be collected directly or indirectly by Omron for the manufacture, production, sale, delivery, importation, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Omron.

 Financial. If the financial position of Buyer at any time becomes unsatisfactory
- <u>Financial</u>. If the financial position of Buyer at any time becomes unsatisfactory to Omron, Omron reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Omron may (without liability and in addition to other remedies) cancel any unshipped portion of Products sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid accounts. unpaid accounts
- Cancellation: Etc. Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Omron against all related costs or expenses.

 10. Force Majeure. Omron shall not be liable for any delay or failure in delivery
- resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.

 11. Shipping: Delivery. Unless otherwise expressly agreed in writing by Omron:
 a. Shipments shall be by a carrier selected by Omron; Omron will not drop ship
- - except in "break down" situations.
 b. Such carrier shall act as the agent of Buyer and delivery to such carrier shall
 - constitute delivery to Buyer; c. All sales and shipments of Products shall be FOB shipping point (unless oth-
- c. All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Omron), at which point title and risk of loss shall pass from Omron to Buyer; provided that Omron shall retain a security interest in the Products until the full purchase price is paid;
 d. Delivery and shipping dates are estimates only; and
 e. Omron will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.

 12. Claims. Any claim by Buyer against Omron for shortage or damage to the Products occurring before delivery to the carrier must be presented in writing to Omron within 30 days of receipt of shipment and include the original transportation bill signed by the carrier noting that the carrier received the Products. portation bill signed by the carrier noting that the carrier received the Products from Omron in the condition claimed.
- Warranties. (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

 (b) <u>Limitations</u>. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABIL-

- ITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by tion, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty. See http://www.omron247.com or contact your Omron representative for published information.
- lished information.

 Limitation on Liability: Etc. OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.
- Indemnities. Buyer shall indemnify and hold harmless Omron Companies and their employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, investigation, litigation or proceeding (whether or not Omron is a party) which arises or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products. Without limiting the foregoing, Buyer (at its own expense) shall indemnify and hold harmless Omron and defend or settle any action brought against such Companies to the extent based on a claim that any Product made to Buyer specifications infringed intellectual property rights of another party.
- rights of another party.

 <u>Property: Confidentiality.</u> Any intellectual property in the Products is the exclusive property of Omron Companies and Buyer shall not attempt to duplicate it in any way without the written permission of Omron. Notwithstanding any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Omron. All information and materials supplied by Omron to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and strictly prevent disclosure to any third party.
- prevent disclosure to any third party.

 <u>Export Controls.</u> Buyer shall comply with all applicable laws, regulations and licenses regarding (i) export of products or information; (iii) sale of products to "forbidden" or other proscribed persons; and (ii) disclosure to non-citizens of
- "forbidden" or other proscribed persons; and (ii) disclosure to non-citizens of regulated technology or information.

 Miscellaneous. (a) Waiver. No failure or delay by Omron in exercising any right and no course of dealing between Buyer and Omron shall operate as a waiver of rights by Omron. (b) Assignment. Buyer may not assign its rights hereunder without Omron's written consent. (c) Law. These Terms are governed by the law of the jurisdiction of the home office of the Omron company from which Buyer is purchasing the Products (without regard to conflict of law principles). (d) Amendment. These Terms constitute the entire agreement between Buyer and Omron relating to the Products, and no provision may be changed or waived unless in writing signed by the parties. (e) Severability If any provior waived unless in writing signed by the parties. (e) <u>Severability</u> If any provision hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision. (f) Setoff. Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice. (g) <u>Definitions</u>. As used herein, "<u>including</u>" means "including without limitation"; and "<u>Omron Companies</u>" (or similar words) mean Omron Corporation and any direct or indirect subsidiary or affiliate thereof.

Certain Precautions on Specifications and Use

- Suitability of Use. Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request. Omron will provide application of use of the Product. At Buyer's lequest, omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given:

 (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document.

 (ii) Use in consumer products or any use in significant quantities.

 (iii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject and industrial consumers and consumers are severed to expect and consumers.
 - ment, and installations subject to separate industry or government regulations. (iv) Systems, machines and equipment that could present a risk to life or prop erty. Please know and observe all prohibitions of use applicable to this Prod-
 - NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO

- ADDRESS THE RISKS, AND THAT THE OMRON'S PRODUCT IS PROP-ERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.
- Programmable Products. Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof. Performance Data. Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requires ments. Actual performance is subject to the Omron's Warranty and Limitations
- Change in Specifications. Product specifications and accessories may be change in specifications. Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time
- to confirm actual specifications of purchased Product.

 <u>Errors and Omissions.</u> Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.



OMRON AUTOMATION AND SAFETY • THE AMERICAS HEADQUARTERS • Chicago, IL USA • 847.843.7900 • 800.556.6766 • www.omron247.com

OMRON CANADA, INC. • HEAD OFFICE

Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • www.omron247.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE

México DF • 52.55.59.01.43.00 • 01-800-226-6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE

Apodaca, N.L. • 52.81.11.56.99.20 • 01-800-226-6766 • mela@omron.com

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE

São Paulo, SP, Brasil • 55.11.2101.6300 • www.omron.com.br

OMRON ARGENTINA • SALES OFFICE

Cono Sur • 54.11.4783.5300

OMRON CHILE • SALES OFFICE

Santiago • 56.9.9917.3920

OTHER OMRON LATIN AMERICA SALES

54.11.4783.5300

OMRON EUROPE B.V. • Wegalaan 67-69, NL-2132 JD, Hoofddorp, The Netherlands. • +31 (0) 23 568 13 00 • www.industrial.omron.eu

Authorized Distributor:

Automation Control Systems

- Machine Automation Controllers (MAC) Programmable Controllers (PLC)
- Operator interfaces (HMI) Distributed I/O Software

Drives & Motion Controls

• Servo & AC Drives • Motion Controllers & Encoders

Temperature & Process Controllers

• Single and Multi-loop Controllers

Sensors & Vision

- Proximity Sensors Photoelectric Sensors Fiber-Optic Sensors
- Amplified Photomicrosensors Measurement Sensors
- Ultrasonic Sensors Vision Sensors

Industrial Components

- RFID/Code Readers Relays Pushbuttons & Indicators
- $\bullet \ Limit \ and \ Basic \ Switches \ \bullet \ Timers \ \bullet \ Counters \ \bullet \ Metering \ Devices$
- Power Supplies

Safety

• Laser Scanners • Safety Mats • Edges and Bumpers • Programmable Safety Controllers • Light Curtains • Safety Relays • Safety Interlock Switches

: ");Ž7Ž'\$ 0'/14

Note: Specifications are subject to change.

© 2014 Omron Electronics LLC

Printed in U.S.A.