

Pioneering innovation

Your trusted partner in technology solutions

Omron has been a global leader in industrial automation for over 70 years and is a leading industrial automation supplier to some of the largest and most widely known global manufacturing companies.

Omron has earned a reputation for providing high-quality, industry-leading solutions that benefit society by helping customers ensure quality products in automotive, food, beverage,

pharmaceutical, packaging, semiconductor and electronics, oil and gas, and many more industries.

Elements of Omron's earned reputation are the quality, support and longevity of its products. Omron will continue to support and repair its products as long as possible. The global manufacturing companies who count on Omron rely on the stability of their manufacturing systems and the long-term functionality of individual components.

Innovation track record for over 83 years



1933

Kazuma Tateishi establishes Omron in Osaka, Japan



1969

The world's first ATM, dubbed the "Money Machine"



1973

Omron expands into North America



2011

Sysmac machine controller is integrated to enable next-generation machine automation



2014

Strategic acquisitions of Delta Tau, Adept and Microscan

36,000

Employees worldwide

300

Sales offices worldwide
in 80 countries

8.5

Billion USD annual sales

4.3

Billion USD annual
Industrial Automation sales

11,000

Issued and pending patents

Technology you can trust


Your trusted partner for long-term technical support

Many Omron Programmable Logic Controller (PLC) and Human Machine Interface (HMI) products are in production for over 20 years. Once the end of manufacture is announced for these PLCs, customers have at least a year to make final purchases, and migration tools are provided. Technical support and repair services are also available for seven more years, and later support will be on a contingent basis. If resources are


available, Omron will continue to support and repair its products as long as possible. This philosophy applies to Omron's full line of automation solutions. When considering an industrial automation supplier for the long term, make sure Omron Industrial Automation is on your short list. Visit our website to view our products and find an Omron distribution partner.

► www.automation.omron.com

Omron PLC life cycle



Omron HMI life cycle



OMRON AUTOMATION AMERICAS HEADQUARTERS • Chicago, IL USA • 847.843.7900 • 800.556.6766 • automation.omron.com

OMRON CANADA, INC. • HEAD OFFICE

Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • automation.omron.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE

Ciudad de México • 52.55.5901.4300 • 01.800.386.6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE

San Pedro Garza García, N.L. • 81.12.53.7392 • 01.800.386.6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE

Eugenio Garza Sada, León, Gto • 01.800.386.6766 • mela@omron.com

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE

São Paulo, SP, Brasil • 55.11.2101.6300 • www.omron.com.br

OMRON ARGENTINA • SALES OFFICE

Buenos Aires, Argentina • +54.11.4521.8630 • +54.11.4523.8483
mela@omron.com

OTHER OMRON LATIN AMERICA SALES

+54.11.4521.8630 • +54.11.4523.8483 • mela@omron.com

Authorized Distributor:

Controllers & I/O

- Machine Automation Controllers (MAC) • Motion Controllers
- Programmable Logic Controllers (PLC) • Temperature Controllers • Remote I/O

Robotics

- Industrial Robots • Mobile Robots

Operator Interfaces

- Human Machine Interface (HMI)

Motion & Drives

- Machine Automation Controllers (MAC) • Motion Controllers • Servo Systems
- Frequency Inverters

Vision, Measurement & Identification

- Vision Sensors & Systems • Measurement Sensors • Auto Identification Systems

Sensing

- Photoelectric Sensors • Fiber-Optic Sensors • Proximity Sensors
- Rotary Encoders • Ultrasonic Sensors

Safety

- Safety Light Curtains • Safety Laser Scanners • Programmable Safety Systems
- Safety Mats and Edges • Safety Door Switches • Emergency Stop Devices
- Safety Switches & Operator Controls • Safety Monitoring/Force-guided Relays

Control Components

- Power Supplies • Timers • Counters • Programmable Relays
- Digital Panel Meters • Monitoring Products

Switches & Relays

- Limit Switches • Pushbutton Switches • Electromechanical Relays
- Solid State Relays

Software

- Programming & Configuration • Runtime