
# Large Rectangular-bodied Indicators

- Excellent illumination with even surface brightness.
- Three-color models (green, orange, red; chameleon lighting) included in lineup.



۵	Refer to Safety Precautions for All Pushbutton Switches/
<u> </u>	Refer to Safety Precautions for All Pushbutton Switches/ Indicators and Safety Precautions of A3P.


# List of Models



Panel cutout dimensions: Refer to page 12.

- Dimensions: Refer to page 11.
- Accessories, replacements, and tools: Refer to the A3P. Specifications: Refer to the A3P.

### **Model Number Structure**




\*2. These split screen models are available only as individual Units.

They cannot be ordered as sets.

the Display, Lamp, and Socket.

#### M2PJ (Rectangular) Single Screen Models





Case color Lighting method		Black	Light gray	Display color symbol
	5 VDC	M2PJ-90A11-05E(1)	M2PJ-90A12-05E(1)	R
LED	12 VAC/VDC	M2PJ-90A11-12E(1)	M2PJ-90A12-12E(1)	G
	24 VAC/VDC	M2PJ-90A11-24E(1)	M2PJ-90A12-24E(1)	Ŵ
Chameleon	12 VDC	M2PJ-90AG1-12EK	M2PJ-90AG2-12EK	*1
Chameleon	24 VDC	M2PJ-90AG1-24EK	M2PJ-90AG2-24EK	
	6 VAC/VDC	M2PJ-90A11-06	M2PJ-90A12-06	
Incandescent lamp	14 VAC/VDC	M2PJ-90A11-14	M2PJ-90A12-14	*2
·····Þ	28 VAC/VDC	M2PJ-90A11-28	M2PJ-90A12-28	

Note: Enter the desired color symbol for the Display in (1). (R) = Red, (O) = Orange, (G) = Green, (W) = White.

Example: Red MPJ-90A11-24E R


\*1. You can change the screen colors of chameleon models between red, green, and orange by changing the terminal wiring. Refer to page 14 for details. \*2. Incandescent lamps are supplied with colored plates (white, red, green, blue, and orange) and legend plates (milk-white and transparent). Use the appropriate

combination.

Rectangular	Chilles 8		
(Single Screen)		2-split	(1)
		screen	(2)

Case color Lighting method		color	Black	Light gray	Display color symbol
LED	24 VDC		M2PJ-90A21-24E(1)(2)	M2PJ-90A22-24E(1)(2)	ROGW
	6 VAC/\	DC	M2PJ-90A21-06		
Incand cent la	14 VAC:	VDC	M2PJ-90A21-14	M2PJ-90A22-14	*
	28 VAC	VDC	M2PJ-90A21-28	M2PJ-90A22-28	

Note: Enter the desired color symbols for the Display in (1) and (2). (R) = Red, (O) = Orange, (G) = Green, (W) = White.



\* Incandescent lamps are supplied with colored plates (white, red, green, blue, and orange) and legend plates (milk-white and transparent). Use the appropriate combination.

Individual models: Refer to pages 6 to 8. (The Display, Lamp, and Socket can be ordered separately.) ■ Specifications: Refer to the A3P.

Dimensions: Refer to page 11. Accessories: Refer to the A3P.

the Display, Lamp, and Socket.

### M2PA (Square) Single Screen Models

Square (Single Screen)		Single screen (1)			
Lighting method	Case color	В	lack	Light gray	Display color symbol
	5 VDC	M2PA-90	A11-05E(1)	M2PA-90A12-05E(1)	
LED	12 VAC/VDC	M2PA-90	A11-12E(1)	M2PA-90A12-12E(1)	ROGW
	24 VAC/VDC	M2PA-90	A11-24E(1)	M2PA-90A12-24E(1)	
Chameleon	12 VDC	M2PA-90	AG1-12EK		*1
Chameleon	24 VDC	M2PA-90	AG1-24EK	M2PA-90AG2-24EK	
	6 VAC/VDC	M2PA-90	A11-06	M2PA-90A12-06	
Incandescent lamp	14 VAC/VDC	M2PA-90	A11-14	M2PA-90A12-14	*2
ion ip	28 VAC/VDC	M2PA-90	A11-28	M2PA-90A12-28	

Note: Enter the desired color symbol for the Display in (1). (R) = Red, (O) = Orange, (G) = Green, (W) = White.


Example: Red M2PA-90A11-24E R

\*1. You can change the screen colors of chameleon models between red, green, and orange, by changing the terminal wiring. Refer to page 14 for details. \*2. Incandescent lamps are supplied with colored plates (white, red, green, blue, and orange) and legend plates (milk-white and transparent). Use the appropriate combination.

Square		<u>ER</u>	2-split	(1)
(Horizontal 2-split	screen)	2.1	screen	(2)

	Case color	Black	Light gray	Display color symbol
Lighting method			5 5 7	
LED	24 VDC	M2PA-90A21-24E(1)(2)	M2PA-90A22-24E(1)(2)	ROGW
	6 VAC/VDC	M2PA-90A21-06	M2PA-90A22-06	
Incandescent lamp	14 VAC/VDC	M2PA-90A21-14	M2PA-90A22-14	*
lamp	28 VAC/VDC	M2PA-90A21-28	M2PA-90A22-28	

Note: Enter the desired color symbols for the Display in (1) and (2). (R) = Red, (O) = Orange, (G) = Green, (W) = White.



\* Incandescent lamps are supplied with colored plates (white, red, green, blue, and orange) and legend plates (milk-white and transparent). Use the appropriate combination.

#### M2PT (Round) Single Screen Models

1	Round	
	(Single Scre	en)



Lighting method	Case color	Light gray	Display color symbol
	5 VDC	M2PT-90A12-05C(1)	
LED lamp	12 VDC	M2PT-90A12-12C(1)	ROGW
	24 VDC	M2PT-90A12-24C(1)	-
Incandescent lamp	28 VAC/VDC	M2PT-90A12-28	*

(1)

Note: Enter the desired color symbol for the Display in (1). (R) = Red, (O) = Orange, (G) = Green, (W) = White.

Example: Red M2PT-90A12-24C R

\* Incandescent lamps are supplied with a colored plates (white, red, green, blue, and orange). Use the appropriate combination. Models A3PT and M2PT (round models), however, are not supplied with legend plates.

Individual models: Refer to pages 6 to 8.

(The Display, Lamp, and Socket can be ordered separately.)


■ Specifications: Refer to the A3P.

Dimensions: Refer to page 11. Accessories: Refer to the A3P.

#### Illumination-only and Colored-illumination LED Models


"Illumination only" describes LED models for which the screen color is the same whether the LED is lit or not. The screen simply becomes brighter when the LED lights.

#### Example: Red LED



"Colored illumination" describes LED models for which the screen color is white when the LED is not lit and changes to the color of the LED lamp when the LED is lit.

#### **Example: Red LED**



Ordering: For a colored-illumination Indicator, order the Display, Lamp, and Socket as shown in the following table.

Display	Lamp	Socket
• Select the LED lamp-lighted model required from the selection on page 7. Each assembly includes the number of white colored plates required to enable colored illumination for the corresponding screen-split configuration. For example, 4-split screen models includes 4 white colored plates.	<ul> <li>Select the LED lamps to suit your desired coloration from the selection on page 8.</li> <li>Number of necessary LED lamps (standard): M2PJ (rectangular): 4 M2PA (square): 2 M2PT (round): 2</li> </ul>	Select from the Sockets on page 8.

**Ordering Information** Ordering Individually ...... Displays, Lamps, and Sockets can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and repairs. LED-lighted/Chameleon Models **LED Lamp-lighted Models** Incandescent Lamp-lighted Models (LED is built into the Display.) (LED lamp and Display are separate.) (Incandescent lamp and Display are separate.) Display Display Display Round (M2PT) models not available. • M2P -5 ----E • M2P -502 • M2P -501 (for Indicator) (for Indicator) (for Indicator) Lamp (LED Lamp) \*1 Lamp (Incandescent Lamp) \*2 • Standard lamp: SLL-SLL-DDED • Low-power lamp: SLL-Socket \* Socket Socket • M2P -7 -0 • M2P -7 -0 -0 (for Indicator) (for Indicator) (for Indicator) The Socket is compatible with LED-lighted, LED lamp-lighted, and incandescent lamp-lighted models. \*1. Number of necessary LED lamps. \*2. Number of necessary incandescent lamps.

Screen pattern	M2PJ	M2PA	M2PT		
Single screen		2	2		
Horizontal 2-split screen		2			
Vertical 2-split screen	4				
Vertical 3-split screen Horizontal 3-split screen					
4-split screen					

Screen pattern	M2PJ	M2PA	M2PT
Single screen	2	1	2
Horizontal 2-split screen	4	2	
Vertical 2-split screen	(low- power in- candes-		
Vertical 3-split screen Horizontal 3-split screen	cent lamp)		
4-split screen	·		

Ordering set combinations: Refer to pages 3 to 4.

- Specifications: Refer to the A3P.
- Dimensions: Refer to page 11. Accessories: Refer to the A3P.

Ordering Individually ...... Displays, Lamps, and Sockets can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and repairs.

### Display LED-lighted Models (LED is built-in.)

Appearance	Split-scree (color sy		White (W)	Red (R)	Green (G)	Orange (O)	Selection precautions
Rectangular models	Single screen		M2PJ-5701-□□E	M2PJ-5702-□□E	M2PJ-5703-□□E	M2PJ-5706-□□E	<ul> <li>Enter the voltage to be used in the</li></ul>
~		White	M2PJ-5711-□□E	M2PJ-5712-□□E	M2PJ-5713-□□E	M2PJ-5716-□□E	end of the model number.
	Horizontal 2- 2 split	Red	M2PJ-5721-□□E	M2PJ-5722-□□E	M2PJ-5723-□□E	M2PJ-5726-□□E	Examples of voltage
	screen	Green	M2PJ-5731-□□E	M2PJ-5732-□□E	M2PJ-5733-□□E	M2PJ-5736-□□E	used: 5 V=05E
		Orange	M2PJ-5741-□□E	M2PJ-5742-□□E	M2PJ-5743-□□E	M2PJ-5746-□□E	12 V=12E 24 V=24E
Square models	Single screen		M2PA-5701-□□E	M2PA-5702-□□E	M2PA-5703-□□E	M2PA-5706-□□E	Horizontal 2-split
models		White	M2PA-5711-□□E	M2PA-5712-□□E	M2PA-5713-□□E	M2PA-5716-□□E	support only 24V.
	Horizontal 2-split	Red	M2PA-5721-□□E	M2PA-5722-□□E	M2PA-5723-□□E	M2PA-5726-□□E	<ul> <li>For the color of the shaded part, select the</li> </ul>
	screen	Green	M2PA-5731-□E M2PA-5732-□E M2PA-5733-□	M2PA-5733-□□E	M2PA-5736-□□E	model according to the	
		Orange	M2PA-5741-□□E	M2PA-5742-□□E	M2PA-5743-□□E	M2PA-5746-□□E	colors given at the top of the table.

Note: 1. A cap, legend plate (transparent), colored plate, white plunger case, and LED (with a current-limiting resistor) are built into the standard lighting unit. 2. Split-screen coloring configurations are given with the "OMRON" mark on the Sockets facing down.

#### LED Lamp-lighted Models (LED is not built-in.)

Model	Rectan- gular models		Square models		Round models		Selection precautions				
Screen pattern	Screen	Model	Screen	Model	Screen	Model					
Single screen		M2PJ-5021		M2PA-5021	$\bigcirc$	M2PT-5021	<ul> <li>Colored plates (white, red, green, and orange), a legend plate (transparent), and a light baffle (split-screen models only) are included. Use the appropriate combination for the LED coloring required.</li> <li>The number of white colored plates required to enable colored illumination for the corresponding screen-split</li> </ul>				
Horizontal 2-split screen		M2PJ-5022		M2PA-5022							
Vertical 2-split screen		M2PJ-5023					<ul> <li>configuration is included. (For example, 4-split screen models include 4 white colored plates).</li> <li>The number of colored plates included for each model ar shown in the following table.</li> </ul>				
Horizontal 3-split screen		M2PJ-5024					Screen pattern	White	Red	Green	Orange
							Single screen	1	1	1	1
Vertical 3-split screen		M2PJ-5025					Horizontal 2-split screen Vertical 2-split screen	2	1	1	1
4-split screen		M2PJ-5026					Horizontal 3-split screen Vertical 3-split screen *	3	2	2	2
		W2F 0-5020					4-split screen	4	1	1	1

\* The following types of colored plates are included with Horizontal and Vertical 3-splitScreen Switches.

White: One colored plate for a 2-split screen and two colored plates for a 4-split screen.

Red, green, or orange: One colored plate for a 2-split screen and one colored plates for a 4-split screen.

Ordering set combinations: Refer to pages 3 to 4.

- Specifications: Refer to the A3P.
- Dimensions: Refer to page 11. Accessories: Refer to the A3P.

# Ordering Individually..........Displays, Lamps, and Sockets can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and repairs.

Display

#### Incandescent Lamp-lighted Models (Incandescent lamp is not built-in.)

Model	Rectan- gular models		Square models		Round models		Selection precautions					
Screen pattern	Screen	Model	Model	Model	Model	Model						
Single screen		M2PJ-5011		M2PA-5011	$\bigcirc$	M2PT-5011 * • Colored plates (white, red, green, orange, and blue), a legend plate (transparent), and a light baffle (split-screen models only)						
Horizontal 2- split screen		M2PJ-5012		M2PA-5012	are supplied. * M2PT (round) models do not contain a legend plate. • The number of colored plates supplied is shown in the following				ollowina			
Vertical 2-split screen		M2PJ-5013					table.					
Horizontal 3-		M2PJ-5014					Screen pattern	White	Red	Green	Orange	Blue
split screen		M2PJ-5014					Single screen	1	1	1	1	1
Vertical 3-split screen		M2PJ-5015					Horizontal 2-split screen Vertical 2-split screen	1	1	1	1	1
						Horizontal 3-split screen Vertical 3-split screen *	2	2	2	2	2	
4-split screen		M2PJ-5016					4-split screen	2	2	2	2	2

\* The following types of colored plates are included with Horizontal and Vertical 3-splitScreen Switches.

All colors: One colored plate for a 2-split screen and one colored plate for a 4-split screen.

#### Chameleon Models (with Built-in LED)

	Shape	Rated voltage	Chameleon indicator
Rectangular		12 VDC	M2PJ-5800-12E
		24 VDC	M2PJ-5800-24E
Squara		12 VDC	M2PA-5800-12E
Square		24 VDC	M2PA-5800-24E

Note: 1. With the chameleon models, the whole screen lights red, green, or orange (i.e., red and green simultaneously).

 A cap, legend plate (transparent), white colored plate, and LED (with a current-limiting resistor) are built into the Display.

Lamp (For mounting, refer to the A3P.)

#### **LED Lamp**

Voltage	5 VDC	12 VDC	24 VDC	Applicable cap (color)	Selection precautions		
Color	Model (DC only)	Model (DC only)	Model (DC only)	(colored plate)	Selection precautions		
Red	SLL-05ER	SLL-12ER	SLL-24ER	Red			
Yellow	SLL-05EY	SLL-12EY	SLL-24EY	Orange	In the standard setup, 4 LED lamps are used with M2PJ models and 2 LED lamps		
Green	SLL-05EG	SLL-12EG	SLL-24EG	Green	are used with M2PA and M2PT models.		
White	SLL-05EW	SLL-12EW	SLL-24EW	White			

#### Incandescent Lamp

Voltage Lamp type	Standard lamp	Low-voltage lamp	Selection precautions			
5 VAC/VDC SLL-06		SLL-06H	<ul> <li>In the standard setup for M2PJ models, 2 lamps are used with single screen models, and 4 lamps are used with split-screen models. If 3 or 4 lamps are lit continuously, use low-</li> </ul>			
12 VAC/VDC	SLL-14	SLL-14H	<ul> <li>power lamps.</li> <li>In the standard setup for M2PA models, 1 lamp is used with single screen models, and 2</li> </ul>			
24 VAC/VDC SLL-28		SLL-28H	lamps are used with split-screen models. • In the standard setup for M2PT models, 2 lamps are used.			

Socket (common to both incandescent lamp-lighted and LED-lighted models)

Rectangular	Square	Round	Selection precautions
Model	Model	Model	
M2PJ-7010-1 M2PA-7010-1 M2PT-701		M2PT-7010-2	• The end digit denotes the color of the flange: -1 denotes a black flange, and -2 denotes a light gray flange. Round switches are available only in light gray, and not in black.

Ordering set combinations: Refer to pages 3 to 4.

■ Specifications: Refer to the A3P.

Dimensions: Refer to page 11. Accessories: Refer to the A3P.

Accessories are the same as those for the A3P Lighted Pushbutton Switches. Refer to the A3P.

# LED and Incandescent Lamp Ratings and Characteristics

Ratings and characteristics the same as those for the A3P Lighted Pushbutton Switches. Refer to the A3P.

# Nomenclature

### Construction


# Approved Standard Ratings

UL (File No. E41515), CSA (File No. LR45258)

LED: 24 VDC max.

Incandescent lamp: 28 VAC/VDC,1.2 W max.


Note: Certification has been obtained for the Indicator. For detailed information on individual products that have received certification, consult your supplier.



Note: The above diagram for LED lamp-lighted and incandescent lamp-lighted models shows the M2PJ model.

## Nomenclature


#### M2P Lighting Method Diagram




# M2P

## Dimensions

#### M2PJ (Rectangular) Models



### M2PT (Round) Models




Note: Use a panel thickness of 0.5 mm for tab terminals #110 and solder terminals.

#### **Accessory Mounting Dimensions**

Dimensions for mounting accessories are the same as those for the A3P Lighted Pushbutton Switches. Refer to the A3P.

#### M2PA (Square) Models



(Unit: mm)

## **Dimensions**

### **Panel Cutout** M2PJ (Rectangular) Models

Classification		Mounting de	esign	Panel cutout	Remarks
Flange mount models	Individual mount- ing (Horizontal)	25±0.1		30.5±0.3 23.5±0.3	
	Multiple mount- ing (Horizontal)	25±0.1 1 2 n		32n-1.5±0.3 23.5±0.3	Panel cutout spacing between rows of Units:
	Individual mount- ing (Vertical)	32±0.1	Mount to long mount- ing plate (A3PJ- 3002) before use.	23.5±0.3 30.5±0.3 j.3	6 min.
	Multiple mount- ing (Vertical)	32±0.1 1 2 n	Mount to long mount- ing plate (A3PJ- 3002) before use.	25n-1.5±0.3 30.5±0.3	
	Individual mount- ing (Horizontal)	27		36.4±0.3 23.5±10.3	For barrier mount models, refer to Ac-
Barrier mount models	Multiple mount- ing (Horizontal)	27 1 2 33n+6±1	n	23.5±0.3 23.5±0.3	Panel cutout spacing between rows of Units: Dotted line indicates the position of each mounting barrier.
	Individual mount- ing (Vertical)	34	Mount to long mount- ing plate (A3PJ- 3002) before use.	30.5±0.3 t	
	Multiple mount- ing (Vertical)	34 1 2 n 26n+6±1	Mount to long mount- ing plate (A3PJ- 3002) before use.	25.9n+3.5±0.3 30.5±0.3	

Note: 1. n: Number of Units

Recommended panel thickness: 1 to 5 mm
 Mount the panel before mounting the Switch Guard.
 If the panel is to be finished (e.g., coated), make sure that the panel meets the specified dimensions after the coating.


#### M2PA (Square) Models

Cla	ssification	Mounting design	Panel cutout	Remarks
Flange mount models	Individual mount- ing	25:0.1	23.5±0.3	Panel cutout spacing between rows of Units:
	Multiple mount- ing	25±0.1 1 2 n - 25∩±0.1	23.5±03 25n-2.5±0.3	6 min.
Barrier mount models	Individual mount- ing	27	23.5±d3 27.8±0.3	Panel cutout spacing between rows of Units: Dotted line indicates the position of each mounting barrier.
	Multiple mount- ing	27 1 2 n 26n+6.5±1	23.5±0 <u>1</u> - 26n+2.5±0.3 -	1.3 6 min. 6 min.

Note: 1. n: Number of Units

Recommended panel thickness: 1 to 5 mm
 If the panel is to be finished (e.g., coated), make sure that the panel meets the specified dimensions after the coating.

#### M2PT (Round) Models



Note: 1. Recommended panel thickness: 1 to 5 mm

If the panel is to be finished (e.g., coated), make sure that the panel meets the specified dimensions after the coating

(Unit: mm)

# Dimensions

# Terminal connections

LED-lighted Mo	odels
----------------	-------


Ra Model	ted voltage Screen pattern	5 VDC	12 VAC/VDC	24 VAC/VDC
M2PJ	Single screen	BOTTOM VIEW TOP VIEW L4-L2-L1-L3-LC2+L1-L3-LC2+L1-L3-LC2+L1-L3-LC2+L1-L2-L2-L2-L2-L2-L2-L2-L2-L2-L2-L2-L2-L2-	BOTTOM VIEW TOP VIEW L4-UL2-UL-UL2-UL2-UL2-UL2-UL2-UL2-UL2-UL2-	BOTTOM VIEW TOP VIEW
M2PA	Single screen	arrangement BOTTOM VIEW TOP VIEW LC <sup>+</sup> L1-IL2-IL2-IL2-IL2-IL2-IL2-IL2-IL2-IL2-IL2	arrangement BOTTOM VIEW	TOP VIEW Lighting block
		Terminal Lighting block	Terminal Lig arrangement	hting block

#### Incandescent Lamp-lighted/LED Lamp-lighted Models

(All are shown with the OMRON logo facing down. The terminal arrangements are the same as for the LED-lighted models.)

Model Type	Rectangular M2PJ models	Square M2PA models	Round M2PT models
Indicator	BOTTOM VIEW TOP VIEW TOP VIEW Torminal arrangement	BOTTOM VIEW TOP VIEW	BOTTOM VIEW TOP VIEW

#### **LED Chameleon Models**



#### Terminal Arrangement and Coloring Chameleon Models

Wiring	LC+	LC+	LC+
	L1-	L2-	L1- and L2- shorted
Coloring	Green	Red	Orange

# **Safety Precautions**

Refer to Safety Precautions for All Pushbutton Switches/Indicators and Safety Precautions for the A3P.

#### Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warrantv.

See http://www.omron.com/global/ or contact your Omron representative for published information.

#### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

#### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

#### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

#### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

#### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2019.11

In the interest of product improvement, specifications are subject to change without notice.

**OMRON** Corporation Industrial Automation Company

http://www.ia.omron.com/