

Emergency stop pushbutton switches

A22E/A22NE-P/A22NE-PD Series





Standard Screw Terminal Block Types A22E Series



Mid-grade Vibration Resistant A22NE-P Series



Premium

Lock detection & Vibration Resistant

A22NE-PD Series

Creating a safer work environment

A variety of functions for enhanced safety and reliability

Providing additional peace of mind that your machine will stop when you need it to.

An emergency stop pushbutton switch is crucial to the safety of workers. Improper installation of the switch or malfunctioning of the switch can lead to a major accident or damage to the machine equipment. Omron focused on improving the level of reliability and safety of our A22 emergency stop design.





Three available features to enhance reliability

Minimizes Emergency Stop malfunctions



Lock Detection

- Detects improper installations and damage to the lock lever.
- Disconnects switch contacts when lock lever in unlocked or damaged.

Refer to page 4 for details.



Reduces loose and detached wiring



- Terminal Block
- Provides greater vibration resistance and secured wiring.
- Reduces work for wiring and maintenance.

Refer to page 5 for details.




Protected in the harshest environments



IP69K

- Usable up to 80°C and pressures of 80 to 100 BAR.
- Ideal for frequent wash-down applications.

Refer to page 5 for details.



A Lineup That Allows You to Choose According to Your Needs

Max Safety and Protection

A22NE-PD Series









Vibration Resistant in harsh conditions

A22NE-P Series







Standard E-stop for everyday use

A22E Series



Accident prevention & reliable operation

Reduce emergency stop malfunctions with the A22NE-PD's Lock Detection Feature




Lock Detection

A22NE-PD Series

Detects improper installations and damage to the lock lever



If the operator unit is not locked in properly to the switch, the emergency stop contacts may not function properly in an event of an emergency. With the Lock Detection feature, the switch detects improper installation and minimizes E-stop failures.



For machine equipment that requires additional safety measures

Ensures the machine equipment has proper emergency shut downs







Push-In Plus Terminal Block

A22NE-PD/A22NE-P Series


Less wiring time required and greater vibration resistance

Push-in Plus terminals are maintenance-free connections and greatly reduce wiring time compared to the standard screw terminals.

Less wiring work

Just insert wires like you would into an earphone jack. No tools are required.





* Information for Push-In Plus Terminal Blocks and screw terminal blocks is based on OMRON's actual measurement value data for the XW2R.



Optional IP69K

A22NE-PD/A22NE-P Series

High level of protection for harsh environments

The IP69K rated emergency stop buttons provides a peace of mind when being used in high wash-down applications. The unique rubber designed cover resists high-temperature and high pressure sprays from any direction.



Ordering information

art number structure				A22NE- 1 2 -PD 3 -4 -5		
	No.	Туре	Code	Meaning		
		30 mm dia.	S	Operator head size		
	1	40 mm dia.	М	Operator head size		
		60 mm dia.	L	Operator head size		
	_	Turn-reset	None	Reset function type		
	2	Pull-reset	Р	Reset function type		
		1NC	01	Contact block type		
		2NC	02	Contact block type		
		1NO/1NC	11	Contact block type		
		3NC	03	Contact block type		
_	3	2NO/1NC	21	Contact block type		
A22NE-PD		1NO/2NC	12	Contact block type		
Lock Detection		2NO/2NC	22	Contact block type		
& Push-in Plus Terminals (Non-removable		1NO/3NC	13	Contact block type		
		4NC	04	Contact block type		
contact blocks)		Non-lighted	N	Lighting type		
	4	24 VAC/VDC LED	С	Lighting type (only available with 40mm operator head)		
		IP65	None	IP Rating		
	5	IP69K	IP69K	IP Rating		
rt number structure		A22NE- 1 2 -P 3 -4 -5				
	No.	Туре	Code	Meaning		
		30 mm dia.	S	Operator head size		
	1	40 mm dia.	М	Operator head size		
		60 mm dia.	L	Operator head size		
		Turn-reset	None	Reset function type		
	2	Pull-reset	Р	Reset function type		
100		1NC	002	Contact block type		
		1NO/1NC	102	Contact block type		
	3	2NC	202	Contact block type		
		1NO/2NC	212	Contact block type		
		3NC	222	Contact block type		
		Non-lighted	N	Lighting type		
			٨	Lighting type		
A22NE-P		6 VAC/DC LED	А	(only available with 002,102,202 contact block & 40mm operator hea		
AZZINE-P lush-in Plus Terminals movable contact blocks)		12 VAC/DC LED	В	Lighting type (only available with 002,102,202 contact block & 40mm operator hea		
	4	24 VAC/DC LED	C	Lighting type		
		100/110/120		(only available with 002,102,202 contact block & 40mm operator hea Lighting type		
		VAC LED	D	(only available with 002,102,202 contact block & 40mm operator hea		
		200/220/230/240 VAC LED) E	Lighting type		
				(only available with 002,102,202 contact block & 40mm operator hea		
		IP65	None	IP Rating		
	5	IP69K	IP69K	IP Rating		
	1	Control box	В	Switch with integrated control box		

(only available with 40mm operator head)

Part Number Structure	A22E 11-[2]-[3]-[4]-[5]-[6							
	No.	Type	Code	Meaning				
	1	Non-lighted	None	Lighting type				
		Lighted	L	Lighting type (only available with 40 mm operator head)				
	2	30 mm dia./Turn-reset	S	Operator head size/Reset function				
		40 mm dia./Turn-reset	М	Operator head size/Reset function				
		40 mm dia./Pull-reset	MP	Operator head size/Reset function				
		60 mm dia./Turn-reset	L	Operator head size/Reset function				
	3	Non-lighted	None	Lighting type				
***		6 VAC/DC LED	6A	Lighting type (only available with 01,11,02 contact block)				
A22E		12 VAC/DC LED	12A	Lighting type (only available with 01,11,02 contact block)				
		24 VAC/DC LED	24A	Lighting type (only available with 01,11,02 contact block)				
		100 VAC LED	T1	Lighting type (voltage-reduction lighting unit and only available with 01,11,02 contact block)				
		200 VAC LED	T2	Lighting type (voltage-reduction lighting unit and only available with 01,11,02 contact block)				
	4	1NC	01	Contact block type				
		1NO/1NC	11	Contact block type				
Screw terminals		2NC	02	Contact block type				
(Removable contact blocks)		1NO/2NC	12	Contact block type				
		3NC	03	Contact block type				
	5	Switch assembly	None	Configuration				
		Switch with integrated control box	В	Configuration (only available with 40 mm operator head)				
	6	Plain operator head	None	Labels on operator head				
		EMO + arrows printed in white	EMO	Labels on operator head				
		EMO printed in white + red arrows	EMO-RD	Labels on operator head				
		EMS + arrows printed in white	EMS	Labels on operator head				
		EMS printed in white + red arrows	EMS-RD	Labels on operator head				



Recommended part numbers

Series	Operator unit size	Lighting	Contact	Reset method	Туре	Part number
A22NE-PD Lock Detection & Push-in Plus Terminals	40 mm	None	1NC	Turn-reset	Switch assembly	A22NE-M-PD01-N
		None	2NC	Turn-reset	Switch assembly	A22NE-M-PD02-N
		None	1NO/1NC	Turn-reset	Switch assembly	A22NE-M-PD11-N
		None	1NC	Pull-reset	Switch assembly	A22NE-MP-PD01-N
		None	1NO/1NC	Pull-reset	IP69K Switch assembly	A22NE-MP-PD11-N-69K
A22NE-P Push-in Plus Terminals	40 mm	None	1NC	Turn-reset	Switch assembly	A22NE-M-P002-N
		None	2NC	Turn-reset	Switch assembly	A22NE-M-P202-N
		None	2NC	Turn-reset	Switch with integrated control box	A22NE-M-P202-N-B
A22E Screw Terminals	40 mm	None	1NC	Turn-reset	Switch assembly	A22E-M-01
		None	1NC	Pull-reset	Switch assembly	A22E-MP-01
		24 VAC/DC LED	1NC	Turn-reset	Switch assembly	A22EL-M-24A-01
		24 VAC/DC LED	2NC	Turn-reset	Switch assembly	A22EL-M-24A-02
		24 VAC/DC LED	1NO/1NC	Turn-reset	Switch assembly	A22EL-M-24A-11

 $\textbf{OMRON AUTOMATION AMERICAS HEADQUARTERS} \bullet Chicago, IL USA \bullet 847.843.7900 \bullet 800.556.6766 \bullet automation.omron.com$

OMRON CANADA, INC. • HEAD OFFICE

Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • automation.omron.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE

Ciudad de México • 52.55.5901.4300 • 01.800.386.6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE

San Pedro Garza García, N.L. • 81.12.53.7392 • 01.800.386.6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE

Eugenio Garza Sada, León, Gto • 01.800.386.6766 • mela@omron.com

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE

São Paulo, SP, Brasil • 55.11.2101.6300 • www.omron.com.br

OMRON ARGENTINA • SALES OFFICE

Buenos Aires, Argentina • +54.11.4521.8630 • +54.11.4523.8483 mela@omron.com

OTHER OMRON LATIN AMERICA SALES

+54.11.4521.8630 • +54.11.4523.8483 • mela@omron.com

Note: Specifications are subject to change.