

Industrial Handheld DPM Reader  
V460-H

**OMRON**

# An Intelligent Barcode Reader for Direct Part Marks and Labels






**An intuitive out-of-box reading experience, as well as seamless PLC connectivity. Its durable and long-lasting body ensures reliable performance in industrial environments.**

- All in one rugged industrial handheld barcode reader
- Reliably reads while automatically adjusting for barcodes of different sizes, types, surfaces or distances
- Simple PLC connection and integration with pre-built function blocks
- Hands Free Intelligent Presentation Mode




## Performance

A barcode reader that adjusts for variations in barcode size, type and distance .....	P. 4
“Auto-Everything”: Just click and read .....	P. 5
Reliable reading of direct part marks — every time .....	P. 6
Experience the advanced rugged design for uninterrupted performance .....	P. 7



## Plug & Play

The game-changing technologies behind the V460’s “Auto-everything” .....	P.8
Quick integration and easy PLC setup with built-in Ethernet & fieldbus communications .....	P.9
Easy Setup and no software to install with Weblink HH, Web browser based setup .....	P.10



## Applications

Automotive	
Aerospace	
Life Science	
Logistics .....	P.11



## Handheld Barcode Reader Lineup

Full line of Handheld barcode readers to complete your traceability solution .....	P.12
--	------

# A barcode reader that automatically adjusts for variations in size, type, and distance

In industry, having a mixture of both low-contrast Direct Part Marks and high-contrast printed barcodes is common. With the V460, there's no need to purchase multiple units for different size barcodes, surfaces or types, as the reader automatically adjusts to decode the direct part mark or label presented. It's never been easier to improve your traceability solution.



## Predictive Autofocus & Intelligent Lighting for Labels

Example 1



Automatically adjusts focus for labels at different distances.

Example 2



Automatic lighting adjustment to properly capture barcode Labels.

## Intelligent Lighting for Difficult Direct Part Marks

Example 1



Intelligent Lighting adjusts automatically for direct part marks on cylindrical or curved surfaces.

Example 2



Intelligent lighting corrects for Low contrast direct part marks on metallic surfaces.

# “Auto-Everything”: Just click and read

This intelligent handheld allows reading of a very broad range of challenging DPM codes and labels with variable code densities, sizes, part geometries, surface conditions and working distances without any user intervention or adjustment. A superior out-of-box reading experience in a wide variety of traceability applications.



## Intelligent Presentation Mode - Hands Free Operation

**Intelligent Presentation Mode** allows direct part marks and barcodes to be presented to the reader and it will automatically begin reading while adjusting for optimal settings without any user intervention.



# Reliable reading of direct part marks – every time

While Traceability requires 100% reading of every part marked, variations in barcode size, surface texture, and reflectivity can make reading direct part marks a significant challenge. The V460's game-changing technology, allows the handheld to tackle even the most difficult-to-read Direct Part Marks with ease!



## V460H Can read even the most challenging part marks



Iron gear, with  
base processing  
Cell size: 0.127mm



Aluminum hairline  
processing,  
unclear, no  
base processing  
Cell size: 0.127mm




Aluminum buffing  
(mirror surface),  
with groundwork  
Cell size: 0.127mm



Aluminum casting,  
no base treatment  
Cell size: 0.127mm



Iron gear, with  
base processing  
Cell size: 0.127mm



Substrate, no  
base treatment  
with many high  
contrast pattern  
Cell size: 0.127mm

# Experience the advanced rugged design for uninterrupted performance

The V460 is a ruggedized handheld designed for long life in industrial situations. The barcode reader is built to withstand the harsh treatment of the manufacturing environment. Thanks to the V460's longevity, you can dramatically reduce the cost of repairing or replacing your barcode readers.

## Rugged design at a glance



### Extreme Durability



- **50 drops**  
to concrete from 6.6 feet/2 meters
- **3,000 tumbles**  
from a height of 3.3 feet/1 meter
- **Exceeds IEC 60068-2-31**



### Ingress Protection



- Protection against dust and water ingress
- **IP65-rated**



### Oil & Chemical Resistance



- Motor/engine oil, automatic transmission fluid (ATF), continuously variable transmission fluid (CVT), industrial degreaser (Engine Brite Heavy Duty), brake fluid (DOT4) per ISO 16750-5
- **ISO 16750-5 Compliant**

# The game-changing technologies behind the V460's "Auto-everything"

## Intelligent Lighting


PATENT PENDING



Dome High-intensity Torch Low-Angle


Our intelligent lighting ensures that all Direct Part Marks can be read.

## Predictive Autofocus



Predictive autofocus automatically adjust for the distance the barcode reader is from the surface and makes reading various sizes of codes, simple.


The V460's incredible ability to automatically read a broad range of challenging direct part marks and printed labels without adjustment, is built upon three key technologies: predictive autofocus, X-Mode decoding algorithms, and intelligent lighting.



## X-Mode Algorithms


### Example 1

Dot Peen on Curved Surface



### Example 2

Laser Etch



X-Mode algorithms ensures that all Direct "Part Marks can be read as easily as a printed label.




# Quick Connection and easy PLC setup

Save time and integration cost with V460's pre-built function blocks for the Ethernet & Fieldbus communications, eliminating the need for time consuming PLC communication setup and testing.

## Designed with PLC connection in mind

The V460 offers a built-in Power over Ethernet (PoE) port with fieldbus connectivity. A single Ethernet cable connection for power and communications, eliminating the cost and complexity of additional modules, while fieldbus connectivity simplifies the communication to the PLC.



### Ethernet & Fieldbus connectivity:

- EtherNet/IP™
- PROFINET
- TCP/IP
- FTP

## Time and cost savings with pre-built function blocks<sup>1</sup>

With pre-built Function Blocks Installed



Without pre-built Function Blocks Installed



1. Contact to your sales representatives to get the function blocks and manual

# OMRON Weblink



## Plug and Play

The V460 is entirely plug-and-play. Simply plug in the reader to view images and explore setting options in real time with live, high resolution images using a standard web browser.




## WebLink HH Features:

- Web Browser Based Setup
- Supports standard browsers: Google Chrome®, Microsoft Edge®, Firefox®, Safari® etc.
- No Software to install or maintain
- Easy and intuitive setup
- Live image viewing
- Optional custom programming code creation



Try scanning this programming code and the V460 will be able to read the barcode on the front cover picture. See User Manual to check other programming codes.



# Applications

## Automotive



The V460 will automatically adjust for the varying contrasts of different surfaces for both 1D or 2D direct part marks and labels.

## Aerospace



Small direct part marks on turbine blades or other components are no problem for the V460's "Auto-everything" technology.

## Life Science



Direct Part Marks on highly reflective surfaces may be a challenge for some, but the V460's Intelligent Lighting and X-Mode algorithms make this as easy as point & click.

## Logistics



Different size barcodes at different distances are a snap with the V460's Predictive Autofocus, that's ready when you are.

# Handheld Barcode Reader Lineup

OMRON has a full lineup of handheld barcode readers as part of your ideal traceability solution.

						
	V410-SR	V410-HC	V410-XD	V450-H	V450-H	V460-H
Communication	RS-232 / USB	RS-232 / USB	RS-232 / USB	RS-232 / USB	Bluetooth Wireless, Cradle: RS-232 / USB	<ul style="list-style-type: none"> <li>• Ethernet (POE)</li> <li>• EtherNet/IP™</li> <li>• PROFINET</li> <li>• TCP/IP</li> <li>• FTP</li> </ul>
Application	Light Industrial for Labels	Health Care Model, for Labels (Disinfectant Resistant)	Light industrial for direct part marks and labels	Rugged industrial for direct part marks and labels	Rugged industrial for direct part marks and labels	Rugged Industrial for the most challenging direct part marks and labels
Model	V410- HDS4608HC	V410- HDS4608SR	V410- HDS4608XD	V450- HDS3608-0001	V450- HDS3678-0001	V460-H0PX







**OMRON AUTOMATION AMERICAS HEADQUARTERS** • Chicago, IL USA • 847.843.7900 • 800.556.6766 • [automation.omron.com](http://automation.omron.com)

**OMRON CANADA, INC. • HEAD OFFICE**

Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • [automation.omron.com](http://automation.omron.com)

**OMRON ELECTRONICS DE MEXICO • HEAD OFFICE**

Ciudad de México • 52.55.5901.4300 • 01.800.386.6766 • [mela@omron.com](mailto:mela@omron.com)

**OMRON ELECTRONICS DE MEXICO • SALES OFFICE**

San Pedro Garza García, N.L. • 81.12.53.7392 • 01.800.386.6766 • [mela@omron.com](mailto:mela@omron.com)

**OMRON ELECTRONICS DE MEXICO • SALES OFFICE**

Eugenio Garza Sada, León, Gto • 01.800.386.6766 • [mela@omron.com](mailto:mela@omron.com)

**OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE**

São Paulo, SP, Brasil • 55 11 5171-8920 • [automation.omron.com](http://automation.omron.com)

**OMRON ARGENTINA • SALES OFFICE**

Buenos Aires, Argentina • +54.11.4521.8630 • +54.11.4523.8483  
[mela@omron.com](mailto:mela@omron.com)

**OTHER OMRON LATIN AMERICA SALES**

+54.11.4521.8630 • +54.11.4523.8483 • [mela@omron.com](mailto:mela@omron.com)