

# OMRON

## G6D-F4PU Terminal Relay

### Product Guide





### Overview

For panel builders, OEMS and customers seeking to reduce their panel size or implement on-line I/O panels, G6D-F4PU and G3DZ-F4PU provide an effective and scalable solution. Mechanical and solid-state relay options are available and allow the purchase of one part with four relays for PLC I/O control.

With a product depth of 35mm, G6D-F4PU and G3DZ-F4PU are ideal for very small machine panels or I/O panels on a production line. The separate mechanical relay contacts are rated up to 5A.

#### **Applications**

- Linking Box (or relay box) on conveyors
- On Machine Operating Panel
- Inside of small machines
- PLCs with I/O cards for 500mA (can switch up to 5A).

#### **Primary Benefits**

- More I/O interposing options depending on the number of I/O points
- Smaller volume required for 4-relay package
- Less infrastructure change when upgrading controller with AC outputs

### **Key features**

- 5A rating for the mechanical relay contact
- Mechanical and power MOS FET relay models are available
- Push-In plus terminals help reduce wiring work and the need for re-tightening screws
- Each relay has independent input and contacts for PLC output compatibility
- LED operation indicator, diode for coil surge absorbing and tools for easy removal
- UL and CSA cer tification for standard models



### **G6D-F4PU Product Selection**

| Mounting Relay<br>Type | Contact<br>Form       | Part Number       | Operation Coil<br>Rating | Contact Rating                   |
|------------------------|-----------------------|-------------------|--------------------------|----------------------------------|
| Mechanical Relay       | SPST X 4<br>(1NO X 4) | G6D-F4PU<br>DC12  | 12 VDC                   | 5A @ 250VAC/30VDC                |
|                        |                       | G6D-F4PU<br>DC24  | 24 VDC                   | 5A @ 250VAC/30VDC                |
| Power MOS FET<br>Relay |                       | G3DZ-F4PU<br>DC12 | 12 VDC                   | 100μA - 0.3A (3-264VAC/3-125VDC) |
|                        |                       | G3DZ-F4PU<br>DC24 | 24 VDC                   | 100μA - 0.3A (3-264VAC/3-125VDC) |

## Related I/O Products

| Product Name | G2RV-SR        | G6D-F4PU                  | G2RV-SR                   | G70V                           |
|--------------|----------------|---------------------------|---------------------------|--------------------------------|
| Type         | 1 point        | 4 point                   | 8 point                   | 16 point                       |
| Description  | Slim I/O Relay | Terminal Relay<br>4-point | 8 point<br>Slim I/O Relay | I/O relay terminal<br>16 point |