

Empowering people through automation

core product CATALOG

OMRON

Industrial Automation

Spring, 2024
automation.omron.com



Omron Automation is an industrial automation partner that creates, sells, and services complete automation solutions that include sensing, control, safety, vision, motion, robotics and more.

Established in 1933, Omron's 30,000 employees help businesses solve problems with creativity in more than 110 countries. Our flexible, customizable solutions successfully tackle challenges across industries, whether these be a need for high-performance machines in food and beverage packaging or plant-wide traceability in automotive manufacturing.

As a total solutions provider, we carry a rich and diverse portfolio of automation technologies and services. From sensors, barcode readers, and control panel components to vision systems, collaborative and mobile robots, and programmable logic controllers, our offering can be used to solve nearly any application in any industry. We also offer related product services such as training and maintenance support for Omron technologies as well as professional services for when you need industry expertise.

To help you navigate our wide-ranging portfolio and home in on the specific products needed for your application, we have developed this core product guide that presents our most popular technologies and services in a clear and concise format.

[Learn more >](#)





OMRON

Our Mission: To improve lives and contribute to a better society

90+ ↑

Years automation experience

350

Offices in 117 countries

5.9 ↑

Billion USD annual sales



Contents

06 Sensors and Components

- 6 Sensors
- 19 Power Supplies
- 22 Timers and Counters
- 24 Mechanical & Solid State Relays
- 26 Temperature Controllers
- 26 Limit Switches /Basic Switches
- 27 Monitoring Products
- 30 Pushbuttons & Indicators

32 Automation Products

- 32 Programmable Logic Controllers
- 37 Machine Automation Controllers
- 46 Human Machine Interfaces
- 48 Industrial PC
- 50 Supervisory Control and Data Acquisition (SCADA)

51 Barcode, RFID and Verification

- 51 Barcode Readers
- 55 RFID
- 57 Verification & Print Quality Inspection

59 Vision Systems

- 59 Machine Vision
- 62 Machine Vision Cameras



70 Machine Safety Technology

- 70 Safety Controllers
- 73 Safety Sensing
- 79 Safety Relays
- 82 Safety Door Switches

88 Motion and Drives

- 88 Advanced Motion Controller
- 92 Servos

94 Robotics

- 94 Mobile Robots
- 96 Collaborative Robots
- 99 Fixed Robots
- 105 Fixed Robot Software
- 106 Fixed Robot Controllers

108 Services

- 108 Robotics Services
- 109 Safety Services

E2E Next - Long Range DC 3 Wire Inductive Sensors

- Industry leading sensing distances with up to 4x the sensing range of standard models
- IO-Link is standard with DC 3-wire PNP models Multiple connection Types
- Multiple connection Types (including M8 QD, M12 QD, M12 Pig-tail QD, PVC cable and PVC Robot Cable)
- Harsh condition robustness with IP67, IP69K, and IP67G


 Product Page

 Product Video

Barrel Size	Sensing Distance	Shielded /Unshielded	Connection Method	PNP Model	NPN Model	
M8	1.5 mm	Shielded	M8 Connector (3 pins)	E2E-X1R5B1D8-M5	E2E-X1R5C18-M5	
	2mm			E2E-X2B1D8-M5	E2E-X2C18-M5	
	4mm			E2E-X4B1D8-M5	E2E-X4C18-M5	
	1.5 mm		M12 Pigtail*	E2E-X1R5B1D8-M1TJ 0.3M	E2E-X1R5C18-M1TJ 0.3M	
	2mm			E2E-X2B1D8-M1TJ 0.3M	E2E-X2C18-M1TJ 0.3M	
	4mm			E2E-X4B1D8-M1TJ 0.3M	E2E-X4C18-M1TJ 0.3M	
	M12	2 mm	Unshielded	M8 Connector (3 pins)	E2E-X2MB1D8-M5	E2E-X2MC18-M5
		4mm			E2E-X4MB1D8-M5	E2E-X4MC18-M5
		8mm			E2E-X8MB1D8-M5	E2E-X8MC18-M5
		2 mm		M12 Pigtail*	E2E-X2MB1D8-M1TJ 0.3M	E2E-X2MC18-M1TJ 0.3M
		4mm			E2E-X4MB1D8-M1TJ 0.3M	E2E-X4MC18-M1TJ 0.3M
		8mm			E2E-X8MB1D8-M1TJ 0.3M	E2E-X8MC18-M1TJ 0.3M
M18	2 mm	Shielded	M12 Connector (4 pins)	E2E-X2B1D12-M1	E2E-X2C112-M1	
	4mm			E2E-X4B1D12-M1	E2E-X4C112-M1	
	9mm			E2E-X9B1D12-M1	E2E-X9C112-M1	
	5 mm	Unshielded		E2E-X5MB1D12-M1	E2E-X5MC112-M1	
	8mm			E2E-X8MB1D12-M1	E2E-X8MC112-M1	
	16mm			E2E-X16MB1D12-M1	E2E-X16MC112-M1	
M30	5 mm	Shielded	M12 Connector (4 pins)	E2E-X5B1D18-M1	E2E-X5C118-M1	
	8mm			E2E-X8B1D18-M1	E2E-X8C118-M1	
	14mm			E2E-X14B1D18-M1	E2E-X14C118-M1	
	10 mm	Unshielded		E2E-X10MB1D18-M1	E2E-X10MC118-M1	
	16mm			E2E-X16MB1D18-M1	E2E-X16MC118-M1	
	30mm			E2E-X30MB1DL18-M1	E2E-X30MC118-M1	
M30	10 mm	Shielded	M12 Connector (4 pins)	E2E-X10B1D30-M1	E2E-X10C130-M1	
	15mm			E2E-X15B1D30-M1	E2E-X15C130-M1	
	23mm			E2E-X23B1D30-M1	E2E-X23C130-M1	
	18 mm	Unshielded		E2E-X18MB1D30-M1	E2E-X18MC130-M1	
	30mm			E2E-X30MB1DL30-M1	E2E-X30MC1L30-M1	
	50mm			E2E-X50MB1DL30-M1	E2E-X50MC1L30-M1	

Note: Models shown are normally open, normally closed options are available.

* 0.3M pre-wired with 4 pin M12 connector on the end.

Tables include representative part numbers. Please consult the product page for more details.

E2EW - Metal Face Proximity Sensors

- Extended sensing range, models from 1x to 4x standard sensing range
- Factor 1 sensing of ferrous and non-ferrous metals
- Weld field immunity
- IP67 rating for environmental robustness
- Proprietary slag resistance coating
- IO-link configurability and output monitoring



Product Page



Product Video

DC 3-Wire Standard Metal Body					
Connection	Sensing Range	Size	Sensing Distance	PNP	NPN
M12 pigtail*	4X	M12	7 mm	E2EW-X7B1T12-M1TJ 0.3M	E2EW-X7C112-M1TJ 0.3M
		M18	12 mm	E2EW-X12B1T18-M1TJ 0.3M	E2EW-X12C118-M1TJ 0.3M
		M30	22 mm	E2EW-X22B1T30-M1TJ 0.3M	E2EW-X22C130-M1TJ 0.3M
2m Cable		M12	7 mm	E2EW-X7B1T12 2M	E2EW-X7C112 2M
		M18	12 mm	E2EW-X12B1T18 2M	E2EW-X12C118 2M
		M30	22 mm	E2EW-X22B1T30 2M	E2EW-X22C130 2M
DC 3-Wire Metal Body with Spatter Resistant Coating					
Connection	Sensing Range	Size	Sensing Distance	PNP	NPN
M12 pigtail*	4X	M12	7 mm	E2EW-QX7B1T12-M1TJ 0.3M	E2EW-QX7C112-M1TJ 0.3M
		M18	12 mm	E2EW-QX12B1T18-M1TJ 0.3M	E2EW-QX12C118-M1TJ 0.3M
		M30	22 mm	E2EW-QX22B1T30-M1TJ 0.3M	E2EW-QX22C130-M1TJ 0.3M
M12 4pin		M12	7 mm	E2EW-QX7B1T12-M1	E2EW-QX7C112-M1
		M18	12 mm	E2EW-QX12B1T18-M1	E2EW-QX12C118-M1
		M30	22 mm	E2EW-QX22B1T30-M1	E2EW-QX22C130-M1
M12 Pigtail	2x	M12	3 mm	E2EW-QX3D112-M1TGJ 0.3M	—
M12 Pigtail		M18	7 mm	E2EW-QX7D118-M1TGJ 0.3M	—
M12 Pigtail		M30	12 mm	E2EW-QX12D130-M1TGJ 0.3M	—
2m Cable		M12	3 mm	E2EW-QX3D112 2M	E2EW-QX3D212 2M
2m Cable		M18	7 mm	E2EW-QX7D118 2M	E2EW-QX7D218 2M
2m Cable		M30	12 mm	E2EW-QX12D130 2M	E2EW-QX12D230 2M
DC 2-Wire Standard Metal Body					
Connection	Sensing Range	Size	Sensing Distance	PNP	NPN
M12 Pigtail	2x	M12	3 mm	E2EW-X3D112-M1TGJ 0.3M	—
M12 Pigtail		M18	7 mm	E2EW-X7D118-M1TGJ 0.3M	—
M12 Pigtail		M30	12 mm	E2EW-X12D130-M1TGJ 0.3M	—
2m Cable		M12	3 mm	E2EW-X3D112 2M	E2EW-X3D212 2M
2m Cable		M18	7 mm	E2EW-X7D118 2M	E2EW-X7D218 2M
2m Cable		M30	12 mm	E2EW-X12D130 2M	E2EW-X12D230 2M

E3Z - Compact Photoelectric Sensor

- General purpose photoelectric family with all common sensing modes at long range
- Minimal optical axis deviation for easy alignment
- IP67 for water resistance
- Intensive shielding for highest noise immunity (EMC)
- Multiple molding housing for high mechanical resistance


 Product Page

Sensor Type	Sensor Distance	Connection	PNP Model	NPN Model
Through-beam (emitter+receiver)	10m (Red LED)	2m Cable	E3Z-T81A	E3Z-T61A
		M8 Connector (4 pins)	E3Z-T86A	E3Z-T66A
	15m (Infrared LED)	2m Cable	E3Z-T81	E3Z-T61
		M8 Connector (4 pins)	E3Z-T86	E3Z-T66
	30m (Infrared LED)	2m Cable	E3Z-T82 2M	E3Z-T62 2M
		M8 Connector (4 pins)	E3Z-T87	E3Z-T67
Retro-reflective with MSR function	0.1 to 4m (Red LED)	2m Cable	E3Z-R81	E3Z-R61
		M8 Connector (4 pins)	E3Z-R86	E3Z-R66
Diffuse-reflective	1m (Infrared LED)	2m Cable	E3Z-D82	E3Z-D62
		M8 Connector (4 pins)	E3Z-D87	E3Z-D67
Background suppression	20 to 200mm (Red LED)	2m Cable	E3Z-LS81	E3Z-LS61
		M8 Connector (4 pins)	E3Z-LS86	E3Z-LS66

Note:

For sensors with IO-Link, refer to the catalog on the website automation.omron.com

Note: Tables include representative part numbers. Please consult the product page for more details.

E3FA - M18 Barrel Photoelectric Sensor

- Simplicity in selection and installation
- Compact size with flush mounting option
- IP67, IP69K for wash down resistance
- Straight or right angle (E3RA) models in cylindrical M18 plastic housing
- Background suppression, Limited Distance and Transparent detection models available



 [Product Page](#)

Sensor Type	Sensor Distance	Connection	PNP Model	NPN Model
Through-beam (emitter + receiver)*	20m (Red LED)	2m Cable	E3FA-TP11 2M	E3FA-TN11 2M
		M12 Connector (4 pins)	E3FA-TP21	E3FA-TN21
Retro-reflective with MSR function	0.1 to 4m (Red LED)	2m Cable	E3FA-RP11 2M	E3FA-RN11 2M
		M12 Connector (4 pins)	E3FA-RP21	E3FA-RN21
Diffuse-reflective*	100mm (Red LED)	2m Cable	E3FA-DP11 2M	E3FA-DN11 2M
		M12 Connector (4 pins)	E3FA-DP21	E3FA-DN21
	300mm (Red LED)	2m Cable	E3FA-DP12 2M	E3FA-DN12 2M
		M12 Connector (4 pins)	E3FA-DP22	E3FA-DN22
	1m (Red LED)	2m Cable	E3FA-DP13 2M	E3FA-DN13 2M
		M12 Connector (4 pins)	E3FA-DP23	E3FA-DN23
Background suppression	100mm (Red LED)	2m Cable	E3FA-LP11 2M	E3FA-LN11 2M
		M12 Connector (4 pins)	E3FA-LP21	E3FA-LN21
	200mm (Red LED)	2m Cable	E3FA-LP12 2M	E3FA-LN12 2M
		M12 Connector (4 pins)	E3FA-LP22	E3FA-LN22

*Note for these sensing modes Infrared LED models are available.

Note: Tables include representative part numbers. Please consult the product page for more details.

E3Z-F - M18 Barrel Mount Photoelectric Sensor

- Visible alignment spot simplifies set-up
- Popular M18 nose mounting
- Models with infrared LEDs available
- Offers various types of sensing distances


 Product Page

Sensor Type	Sensor Distance	Connection	PNP Model	NPN Model
Through-beam (emitter+receiver)*	20 m	2m Cable	E3Z-FTP11 2M	E3Z-FTN11 2M
		M12 Connector (4 pins)	E3Z-FTP21	E3Z-FTN21
Retro-reflective with MSR Function	0.1 to 4m	2m Cable	E3Z-FRP11 2M	E3Z-FRN11 2M
		M12 Connector (4 pins)	E3Z-FRP21	E3Z-FRN21
Diffuse-reflective*	100 mm	2m Cable	E3Z-FDP11 2M	E3Z-FDN11 2M
		M12 Connector (4 pins)	E3Z-FDP21	E3Z-FDN21
	300 mm	2m Cable	E3Z-FDP12 2M	E3Z-FDN12 2M
		M12 Connector (4 pins)	E3Z-FDP22	E3Z-FDN22
	500 mm	2m Cable	E3Z-FDP13 2M	E3Z-FDN13 2M
		M12 Connector (4 pins)	E3Z-FDP23	E3Z-FDN23
	1 m	2m Cable	E3Z-FDP14 2M	E3Z-FDN14 2M
		M12 Connector (4 pins)	E3Z-FDP24	E3Z-FDN24

Note:

Reflectors for retroreflective models are sold separately under code E39-R1S

*Note for these sensing modes Infrared LED models are available

Note: Tables include representative part numbers. Please consult the product page for more details.

E3AS-HL - Photoelectric Sensor

- Limited effect of color or reflectivity
- Small and complex object detection
- Line and spot beam for 150mm and 500mm sensing distances
- IP69K and IP67G
- Ecolab tested and certified detergent resistance
- Advanced ease-of-use, single teach button, OLED screen
- IO-Link distance output monitoring and configuration



 [Product Page](#)

 [Product Video](#)

Sensor Type	Sensor Distance	Beam Type	Connection	PNP Model (I/O Link)	NPN Model
CMOS laser	500 mm	Spot	Pre-wire M12 Connector	E3AS-HL500MT-M1TJ 0.3M	E3AS-HL500MN-M1TJ 0.3M
		Line		E3AS-HL500LMT-M1TJ 0.3M	E3AS-HL500LMN-M1TJ 0.3M
	150 mm	Spot		E3AS-HL150MT-M1TJ 0.3M	E3AS-HL150MN-M1TJ 0.3M
		Line		E3AS-HL150LMT-M1TJ 0.3M	E3AS-HL150LMN-M1TJ 0.3M
	500 mm	Spot	M8 4pin	E3AS-HL500MT M3	E3AS-HL500MN M3
		Line		E3AS-HL500LMT M3	E3AS-HL500LMN M3
	150 mm	Spot		E3AS-HL150MT M3	E3AS-HL150MN M3
		Line		E3AS-HL150LMT M3	E3AS-HL150LMN M3

E3AS-F - Photoelectric Sensor

- Minimal color influence on sensing distance
- 50mm to 1500mm sensing range
- IP69K and IP67G
- Ecolab tested and certified detergent resistance
- Single teach button
- IO-Link distance output monitoring and configuration



 [Product Page](#)

Sensor Type	Sensor Distance	Material	Connection	PNP Model (I/O Link)	NPN Model
Time of Flight with Background Suppression	50 - 1500 mm	Stainless Steel	Pre-wired M12 Connector	E3AS-F1500IMT-M1TJ 0.3M	E3AS-F1500IMN-M1TJ 0.3M
			M8 4pin Connector	E3AS-F1500IMT M3	E3AS-F1500IMN M3
		Plastic	Pre-wired M12 Connector	E3AS-F1500IPT- M1TJ 0.3M	E3AS-F1500IPN-M1TJ 0.3M
			M8 4pin Connector	E3AS-F1500IPT M3	E3AS-F1500IPN M3
	50 - 1000 mm	Stainless Steel	Pre-wired M12 Connector	E3AS-F1000IMT-M1TJ 0.3M	E3AS-F1000IMN-M1TJ 0.3M
			M8 4pin Connector	E3AS-F1000IMT M3	E3AS-F1000IMN M3
		Plastic	Pre-wired M12 Connector	E3AS-F1000IPT-M1TJ 0.3M	E3AS-F1000IPN-M1TJ 0.3M
			M8 4pin Connector	E3AS-F1000IPT M3	E3AS-F1000IPN M3

Note: Tables include representative part numbers. Please consult the product page for more details.

E3AS-L - Photoelectric Sensor

- Enhanced background suppression-Reduced black/white error and differential travel
- 200mm or 80mm sensing range
- IP69K and IP67G
- Ecolab tested and certified detergent resistance
- Single teach button
- IO-Link configurability


[Product Page](#)

Sensor Type	Sensor Distance	Material	Connection	PNP Model (I/O Link)	NPN Model
Diffuse with Background Suppression	10 - 200 mm	Stainless Steel	Pre-wired M12 Connector	E3AS-L200MT-M1TJ 0.3M	E3AS-L200MN-M1TJ 0.3M
	10 - 80 mm			E3AS-L80MT-M1TJ 0.3M	E3AS-L80MN-M1TJ 0.3M
	10 - 200 mm		M8 4pin Connector	E3AS-L200MT M3	E3AS-L200MN M3
	10 - 80 mm			E3AS-L80MT M3	E3AS-L80MN M3

E3S-DC - Color Mark Detection Sensor

- High signal to noise ratio detects subtle color differences.
- High luminance, three-element (RGB) LED light source for greater light intensity.
- Highly efficient optics technology provides high power and enables stable detection even of subtle color differences.


[Product Page](#)

Type	Sensor Distance	Connection	Output	Baud Rate (IO-Link)	Model
Diffuse - reflective (mark detection)	10 ± 3mm	M12 Connector	PNP	COM 3 (230, 4 kbps)	E3S-DCP21-IL3
			NPN	---	E3S-DCN21

Note: Tables include representative part numbers. Please consult the product page for more details.

E3NX-FA - High Speed Digital Fiber Amplifier

- Easy teaching by Smart tuning within a few seconds
- New N-Smart technology provides significant improvement for sensing distance, minimum object detection and speed
- Easy and transparent information about sensor status by Solution Viewer and Change Finder function
- EtherCAT Communication unit for high-speed field bus connectivity



[Product Page](#)

Setting/Function	Sensor Distance	Inputs/Outputs	Connection	PNP Model	NPN Model
Standard Models	Sensing distance up to 4m depending on fiber used	1 output	2 m	E3NX-FA41 2M	E3NX-FA11 2M
Advanced Models		2 outputs + 1 input	2 m	E3NX-FA51 2M	E3NX-FA21 2M
Analog Output Models		2 outputs	2 m	E3NX-FA41AN 2M	E3NX-FA11AN 2M

Note: Infrared standard models are available as well as connector options for standard, advanced, and infrared models.

E3X-ZV/MZV - Advanced Fiber Amplifier

- Simple one-button smart tuning for sensor threshold and light intensity
- Confirm settings and status easily with dual digital display
- Automatic compensation for large objects and low reflectance dark targets



[Product Page](#)

Product Category	Part Number	Description
Sensing	E3X-ZV41 2M	Standard, 2 m Cable, PNP
	E3X-ZV11 2M	Standard, 2 m Cable, NPN
	E3X-MZV11 2M	2-Channel, 2 m cable, NPN
	E3X-MZV41 2M	2-Channel, 2 m cable, PNP

Note: Tables include representative part numbers. Please consult the product page for more details.

E3X-NA / SD - Fiber Optic Amplifiers

- Easy adjustment with potentiometer
- Mutual interference prevention
- Enhanced water resistance types



[Product Page](#)

Setting / Function	Distance	Connection	PNP Model	NPN Model
Potentiometer and Bargraph	Depending on the fiber optic model	2m Cable	E3X-NA41	E3X-NA11
Teach Button and digital display			E3X-SD51	E3X-SD21

E3NX-CA - Colormark Fiber Amplifier

- High signal to noise ratio makes subtle color difference detection easy
- Able to handle glossy materials
- Stable even when lots change



[Product Page](#)

Model	Sensor Distance	Connection	Inputs / Outputs	PNP Model	NPN Model
Standard Model	Sensor distance depends on selected fiber model	2m Cable	1 output	E3NX-CA41 2M	E3NX-CA11 2M
Advanced Model			2 outputs / 1 input	E3NX-CA51 2M	E3NX-CA21 2M

*For fiber options, or models for special applications, refer to the E32 fibers catalog on the Omron website.

Note: Tables include representative part numbers. Please consult the product page for more details.

E3ZM-V - Colormark Detection Sensor

- Compact SUS 316L colormark photoelectric sensor
- Ideal for high contrast colormark detection in a small package
- IP69K and IP67 rated for environmental robustness
- 50 us response time
- Single teach button



[Product Page](#)

Type	Sensor Distance	Connection	PNP	NPN
Diffuse - reflective (color mark detection)	12 ± 2mm	Pre-wired	E3ZM-V81 2M	E3ZM-V61 2M
		M8 Connector	E3ZM-V86	E3ZM-V66

Notes: Additional model numbers with different cable lengths, connections and options are available. Tables include representative part numbers. Please consult the product page for more details.

ZW Confocal Displacement - Measurement Sensors

- Static Resolution of 0.25 μm
- EtherCAT, EtherNet/IP, EtherNet TCP/UDP, and Serial RS-232C Network communications included
- Analog and Discrete I/O for measurement and functions
- Stable measurements for any material including glass and mirror-like surfaces
- Simple programming with Sysmac Studio software
- Compact sensor heads with no electronic parts - electrical noise immune and does not generate heat


 Product Page

Measuring Range	Spot Diameter	Cable Length	Controller	Sensor Head
10 \pm 0.5 mm	4 μm	2 m	ZW-8000T	ZW-S8010 2M
20 \pm 1 mm	7 μm	2 m		ZW-S8020 2M
30 \pm 2 mm	10 μm	2 m		ZW-S8030 2M
10 \pm 0.5 mm	50 μm	2 m	ZW-7000T	ZW-S7010 2M
20 \pm 1 mm	70 μm	2 m		ZW-S7020 2M
30 \pm 2 mm	100 μm	2 m		ZW-S7030 2M
40 \pm 3 mm	120 μm	2 m		ZW-S7040 2M
10 \pm 0.5 mm	9 μm	2 m	ZW-5000T	ZW-S5010 2M
20 \pm 1 mm	13 μm	2 m		ZW-S5020 2M
30 \pm 2 mm	18 μm	2 m		ZW-S5030 2M
Accessories				
Type	Cable Length		Sensor Head	
Serial RS-232C Cable for personal computer	2m		ZW-XRS2	

Notes: Pen-shaped straight and right-angle sensor heads are also available. Shorter 0.3 meter sensor cables are available along with Extension Fiber Cables (2, 5, 10, 20, and 30 meters long).

Note: Tables include representative part numbers. Please consult the product page for more details.

ZX1 and ZX2 CMOS Laser Measurement Sensors

- Down to 1.5um resolution
- Best in class performance for accuracy and speed
- Increased measurement range
- Stable measurement for objects with any surface
- Simple configuration by one-button, Smart Tuning
- Compact size for quick mounting



 [Product Page](#)

ZX1 Sensor Heads with built-in Amplifier				
Range	Resolution	Connection	PNP Model	NPN Model
50 ± 10 mm	2um	2 m Cable	ZX1-LD50A81 2M	ZX1-LD50A61 2M
100 ± 35 mm	7um		ZX1-LD100A81 2M	ZX1-LD100A61 2M
300 ± 150 mm	30um		ZX1-LD300A81 2M	ZX1-LD300A61 2M
600 ± 400 mm	80um		ZX1-LD600A81 2M	ZX1-LD600A61 2M
ZX2 Sensor Heads				
Range	Resolution	Connection	Line-Beam Model	Spot-Beam Model
50 ± 10 mm	1.5um	Amplifier Unit	ZX2-LD50L	ZX2-LD50
100 ± 35 mm	5um	Amplifier Unit	ZX2-LD100L	ZX2-LD100
ZX2 Amplifier Units				
Range	Resolution	Connection	PNP Model	NPN Model
N/A	N/A	2 m Cable	ZX2-LDA41 2M	ZX2-LDA11 2M

Note: Tables include representative part numbers. Please consult the product page for more details.

Sensor Cordsets

- Standard PVC or PUR cordsets for a wide variety of applications
- M8 and M12 connector sizes with 3 and 4 pin configurations
- Straight, right angle, and double ended variations available
- 2m, 5m, and 10m cordset lengths are available. Alternative lengths are also available


 Product Page

Material	Connector Size	No. of Pins	Length	Straight Connector	Right Angle Connector
PUR	M8	3 Pins	2 m	XS3F-M8PUR3S2M	XS3F-M8PUR3A2M
			5 m	XS3F-M8PUR3S5M	XS3F-M8PUR3A5M
			10 m	XS3F-M8PUR3S10M	XS3F-M8PUR3A10M
		4 Pins	2 m	XS3F-M8PUR4S2M	XS3F-M8PUR4A2M
			5 m	XS3F-M8PUR4S5M	XS3F-M8PUR4A5M
			10 m	XS3F-M8PUR4S10M	XS3F-M8PUR4A10M
	M12	3 Pins	2 m	XS2F-M12PUR4S2M	XS2F-M12PUR4A2M
			5 m	XS2F-M12PUR4S5M	XS2F-M12PUR4A5M
			10 m	XS2F-M12PUR4S10M	XS2F-M12PUR4A10M
		4 Pins	2 m	XS2F-M12PUR4S2M	XS2F-M12PUR4A2M
			5 m	XS2F-M12PUR4S5M	XS2F-M12PUR4A5M
			10 m	XS2F-M12PUR4S10M	XS2F-M12PUR4A10M
PVC	M8	3 Pins	2 m	XS3F-M8PVC3S2M	XS3F-M8PVC3A2M
			5 m	XS3F-M8PVC3S5M	XS3F-M8PVC3A5M
			10 m	XS3F-M8PVC3S10M	XS3F-M8PVC3A10M
		4 Pins	2 m	XS3F-M8PVC4S2M	XS3F-M8PVC4A2M
			5 m	XS3F-M8PVC4S5M	XS3F-M8PVC4A5M
			10 m	XS3F-M8PVC4S10M	XS3F-M8PVC4A10M
	M12	3 Pins	2 m	XS2F-M12PVC3S2M	XS2F-M12PVC3A2M
			5 m	XS2F-M12PVC3S5M	XS2F-M12PVC3A5M
			10 m	XS2F-M12PVC3S10M	XS2F-M12PVC3A10M
		4 Pins	2 m	XS2F-M12PVC4S2M	XS2F-M12PVC4A2M
			5 m	XS2F-M12PVC4S5M	XS2F-M12PVC4A5M
			10 m	XS2F-M12PVC4S10M	XS2F-M12PVC4A10M

Double-ended cordsets

Material	Connector Size	No. of Pins	Length	Straight Connector	Right Angle (Socket)/Straight (Plug)
PVC	M12	4	2 m	XS2W-D421-D81-F	XS2W-D424-D81-F
			5 m	XS2W-D421-G81-F	XS2W-D424-G81-F
			10 m	XS2W-D421-J81-F	XS2W-D424-J81-F

Note: Tables include representative part numbers. Please consult the product page for more details.

S8VK - Complete Line Of Power Supplies

- Compact single-phase and three-phase power supplies
- Operating Temperature: -40°C to 70°C (S8VK-G and S8VK-T) and -25°C to 60°C (S8VK-C)
- 5 year warranty
- Power Boost Function: 120% for 10s (S8VK-G/T)



 Product Page

Line	Power	Output Voltage	Output Current	Capacity	Model
Economy Single-Phase		24V	2.5 A	60 W	S8VK-C06024
			5 A	120 W	S8VK-C12024
			10 A	240 W	S8VK-C24024
			20 A	480 W	S8VK-C48024
General Purpose Single-phase	100 to 240 VAC	5V	3 A	15 W	S8VK-G01505
		12V	2.5 A	30 W	S8VK-G03012
	90 to 350 VDC	24V	1.3 A	30 W	S8VK-G03024
			2.5 A	60 W	S8VK-G06024
			5 A	120 W	S8VK-G12024
			10 A	240 W	S8VK-G24024
			20 A	480 W	S8VK-G48024
		48V	10 A	480 W	S8VK-G48048
Three-phase	380 to 480 VAC	24V	5 A	120 W	S8VK-T12024
	450 to 600 VDC		10 A	240 W	S8VK-T24024
			20 A	480 W	S8VK-T48024
			40 A	960 W	S8VK-T96024
Environmentally Resistant 3-Phase Power Supply with Reduced Footprint and Predictive Maintenance Features	380V to 480 VAC	24VDC	10A	240W	S8VK-WB24024
		48VDC	5A		S8VK-WB24048
	450 to 600 VDC"	24VDC	20A	480W	S8VK-WB48024
		48VDC	10A		S8VK-WB48048
		24VDC	60A	960W	S8VK-WB96024
		48VDC	30A		S8VK-WB96048

Note: Tables include representative part numbers.


Please refer to the [Component selection guide](#) for more details.

S8VK-X - Power Supply With EtherNet / IP

- Product replacement time, output voltage, output current, and more can be monitored remotely on the Ethernet/IP network
- Product status can be checked on-site using the indication monitor
- Remote monitoring with included software tool



 [Product Page](#)

 [Product Video](#)

Line	Power	Output Voltage	Output Current	Capacity	Model
EtherNet/IP Communication With Display	100 to 240 VAC 90 to 350 VDC	24V	3.75 A	90 W	S8VK-X09024A-EIP
			5 A	120 W	S8VK-X12024A-EIP
			10 A	240 W	S8VK-X24024A-EIP
EtherNet/IP Communication Without Display			2.5 A	60 W	S8VK-X06024-EIP
			3.75 A	90 W	S8VK-X09024-EIP
			5 A	120 W	S8VK-X12024-EIP
			10 A	240 W	S8VK-X24024-EIP
			20 A	480 W	S8VK-X48024-EIP

Note: Tables include representative part numbers.
Please refer to the [Component selection guide](#) for more details.

S8V-CP - Electronic Circuit Protector

- Compact design saves panel space compared to standard circuit breakers
- 3-step LED indicators for easy identification of channel status
- 4 and 8 channel models available with individual output current adjustments for various loads
- Available UL Class-2 output model



[Product Page](#)

Power	Output Voltage	Number of Outputs	Maximum Input Current	Adjustment Output Current	Model
24 VDC	24 VDC	4	40A	2 A up to 10 A	S8V-CP0424
		8	70A	2 A up to 10 A	S8V-CP0824

Note: Tables include representative part numbers.
Please refer to the [Component selection guide](#) for more details.

H5CC - Digital Timer

- The H5CC is the improved version of our digital timer with added visual clarity
- 15 different timing modes
- Replacement time notification function alert the user of potential maintenance needs.
- User-friendly interface in a white LCD screen
- Status indicators integrated into front buttons.



[Product Page](#)

Power Supply	Terminal Type	Outputs	Model
100-240 VAC	Screw Terminal	Contact Output (time-limit SPDT)	H5CC-A
		Contact Output (SPDT) + Transistor Output (SPST)	H5CC-AU
	11-pin Socket		H5CC-A11
12-48 VDC / 24 VAC	Screw Terminal	Contact Output (time-limit SPDT)	H5CC-AD
		Contact Output (SPDT) + Transistor Output (SPST)	H5CC-AUD
24-240 VDC / VAC	11-pin Socket	Contact Output (time-limit SPDT)	H5CC-A11F

Note: Tables include representative part numbers. Please consult the product page for more details.

H7CC - Digital Counter & Tachometer

- The H7CC is a new and improved version of our digital counter with an available tachometer function
- Improved LED Display makes the screen easier to read
- LED indicators built into the push buttons for visual feedback
- Preventative maintenance features alert you when the product is nearing the end of its life
- Simple and easy to use programming interface saves time



[Product Page](#)

Type	Classification	External Connections	Outputs	Power Supply Voltage	Model
H7CC-A	Preset Counter	11 Pin	Contact output (SPDT)	100 to 240 VAC	H7CC-A11
		Screw Terminals	Contact output (SPDT)	100 to 240 VAC	H7CC-A
			Contact output (SPDT)	24 VAC / 12 to 48 VDC	H7CC-AD
	Preset Counter / Tachometer	Contact output (SPST+SPDT)	100 to 240 VAC	H7CC-AW	
		Contact output (SPST+SPDT)	24 VAC / 12 to 48 VDC	H7CC-AWD	
H7CC-R	Tachometer	11 Pin	Contact output (SPDT)	100 to 240 VAC	H7CC-R11

Note: Tables include representative part numbers.
 Please refer to the [Component selection guide](#) for more details.

Note: Tables include representative part numbers. Please consult the product page for more details.

G2RV-ST - Slim I/O Relay

- Push-in plus Technology for easy wiring
- Lockable test switch models available for circuit troubleshooting
- LED/mechanical flag available for checking operation
- Slim 6mm width – space saving
- Gold plate contact models available for micro loads


 Product Page

Coil Voltage	Contact Rating	Contact Form	Screw Terminal Model	Push-in Terminal Model	Individual Relay for Replacement
24 VDC	6 A	SPDT	G2RV-ST700 DC24	G2RV-ST500 DC24	G2RV-1-S-G DC21
110 VAC			G2RV-ST700 AC110	G2RV-ST500 AC110	G2RV-1-S-G DC48
230VAC			G2RV-ST700 AC230	G2RV-ST500 AC230	

Accessories

Description	Number of Poles	Red	Blue	Yellow
Jumper bar	20	PYDN-6.2T-200R	PYDN-6.2T-200S	PYDN-6.2T-200Y

Note: Tables include representative part numbers.

Please refer to the [Component selection guide](#) for more details.

G2R-S - Slim Mechanical Relay

- Lockable test switch models available for circuit troubleshooting
- LED/mechanical flag available for checking operation
- Available DIN-rail mount relay sockets
- Slim 16mm design with socket



[Product Page](#)

Coil Voltage	Contact Rating	Contact Form	Relay Socket Model	Relay Model
12 VDC	10 A	SPDT	P2RFZ-05E/P2RF-05-PU	G2R-1-S DC12(S)
24 VDC				G2R-1-S DC24(S)
120 VAC				G2R-1-SN AC120(S)
240 VAC				G2R-1-SN AC240(S)
12 VDC	5 A	DPDT	P2RFZ-08E/P2RF-08-PU	G2R-2-S DC12(S)
24 VDC				G2R-2-S DC24(S)
120 VAC				G2R-2-S AC120(S)
240 VAC				G2R-2-S AC240(S)

MY-GS-R - General Purpose Ice Cube Relay

- DPDT type 10 A / 4PDT type 5 A
- Vibration resistance and reduced wiring time with push in plus technology
- Mechanical operation indicator
- Industry standard global certifications UL, CSA, IEC (VDE certification), and CQC
- Lockable test switch models available for circuit troubleshooting
- Low power switching (1 mA at 5 VDC) / Bifurcated 4PDT (0.1 mA at 1 VDC)



[Product Page](#)

Coil Voltage	Contact Rating	Contact Form	Relay Socket Model	Relay Model
24VDC	10A	DPDT	PYFZ-08-E/PYF-08-PU	MY2N-GS-R DC24
120VAC				MY2N-GS-R AC110/120
220VAC				MY2N-GS-R AC220/240
24VDC	6A	4PDT	PYFZ-14-E/PYF-14-PU	MY4N-GS-R DC24
120VAC				MY4N-GS-R AC110/120
220VAC				MY4N-GS-R AC220/240

Note: Tables include representative part numbers.

Please refer to the [Component selection guide](#) for more details.

E5CC/E5DC - General-Purpose Temperature Controllers

- High contrast white PV display
- High-speed sampling at 50ms
- Available auxiliary outputs, event inputs, a transfer output, and a remote SP input
- Short body with a depth of 60mm
- Available IP66 rating with optional waterproof cover
- Additional DIN sizes available 1/4, 1/8, 1/16, 1/32



[Product Page](#)

Dimensions	Type of Input	Power	Type of Output	Auxiliary Output	Standard Model
48 x 48 x 60 mm	Thermocouple, PT100, Analogical	100 -240 VAC	Relay	SPST-NO contacts (Relay Output)	E5CC-RX3A5M-000
			Voltage		E5CC-QX3A5M-000
Current			E5CC-CX3A5M-000		
24 VAC / VDC		Relay	E5CC-RX3D5M-000		
		Voltage	E5CC-QX3D5M-000		
		Current	E5CC-CX3D5M-000		
22.5mm For DIN rail mount	100-240 VAC	Relay	E5DC-RX2ASM-000		
		Current	E5DC-CX2ASM-000		
24VAC / VDC		Relay	E5DC-RX2DSM-000		
		Voltage	E5DC-QX2DSM-002		

Limit & Basic Switches

- Limit switches and basic switches are electromechanical switches used to detect and limit motion within industrial environments
- Available in a wide variety of actuator arms, lever arms and plungers
- Multiple switch designs for use in a variety of applications and environments
- Additional limit and basic switch configurations available on Omron website



[Product Page](#)

Type	Series	Features	Applications	Models
General Limit Switches	D4A	Wide temperature range from -40°C to +100°C (standard type) for use in heavy duty applications	Machine tool, material handling, palletizer, injection molding, packaging equipment, automotive hoist/lift machinery	D4A-1101-N
	WL-N	Two-circuit switch for reliable switching		D4A-2918-N
	D4C	Slim body and designed for easy side-by-side mounting (Plunger type: 6 switches maximum)	Machine tool, material handling, palletizer, packaging equipment, mobile lift equipment, robotics	WLG2-LD
	ZE	Long service life and high breaking capacity	Conveyor controls, packaging equipment, material handling, printing machinery, waste & recycling compacting machinery	WLG2-LD-M1J
Basic Switches	Z	A large switching capacity of 15A and high repeat accuracy	Elevators, mobile lift equipment, forklift, injection molding, utility switchgear, controls for doors/gates/valves, foot switches	D4C-1602
	X	Direct current switch that incorporates a permanent magnet in the contact mechanism to deflect arcs and increases switch life	Mobile lift equipment, forklift, injection molding, utility switchgear, controls for doors/gates/valves, foot switches	D4C-1601
	DZ	Double pole double throw basic switch for two independent circuit control. Ideal for switching the circuits operating on two different voltages, and controlling two circuits.		ZE-NJ-2S
	TZ	High temperature switch that maintains stable operation at an ambient temperature of 400°C	Industrial boilers, power plant, incinerators, industrial heaters	ZE-N-2S
				Z-15GQ-B
				Z-15GD-B
				X-10GW22-B
				X-10GW-B
				DZ-10GW22-1B
				DZ-10GW-1B
				TZ-1GV
				TZ-1GV22

Note: Tables include representative part numbers.
Please refer to the [Component selection guide](#) for more details.

K6CM - Motor Condition Monitor

- 24/7 remote monitoring of critical 3-phase induction motors
- Can monitor motor vibration, temperature, current, and insulation resistance depending on model
- EtherNet/IP and Modbus TCP communication
- Included monitoring software tool can monitor up to 10 motors at one time



 [Product Page](#)

Motor failure mode	Description	Power	Controller model	Sensor Model
Bearing Wear	Monitors motor vibration/temperature with sensor	24 VAC/DC	K6CM-VBMD-EIP	K6CM-VBS1
Overload Condition	Monitors motor current and degradation level using a CT sensor	24 VAC/DC	K6CM-CI2MD-EIP	K6CM-CICB025 K6CM-CICB100 K6CM-CICB200 K6CM-CICB400
Insulation breakdown	Monitors motor insulation and current leakage with sensor	24 VAC/DC	K6CM-ISMD-EIP	K6CM-ISZBI52

K7DD - Adv. AC Motor Condition Monitor

- Comprehensive AC Motor Condition analysis with programable alerts
- Reduce or eliminate unplanned downtime through failure prediction
- Automates the measurement and condition analysis of AC motors with status indicators
- Transistor Alarm Outputs, RS-485 communication
- Especially useful for AC motors that change speed or direction often



 [Product Page](#)

Unit	Supply Voltage	Model
Controller Unit	100-240 VAC	K7DD-PQMA
	24 VDC	K7DD-PQMD

Rated Primary-Side Current	Model	UL Compliant Models
5 A	K6CM-CICB005	K6CM-CICB005-C
25 A	K6CM-CICB025	K6CM-CICB025-C
100 A	K6CM-CICB100	K6CM-CICB100-C
200 A	K6CM-CICB200	K6CM-CICB200-C
400 A	K6CM-CICB400	K6CM-CICB400-C

Note: Tables include representative part numbers.

Please refer to the [Component selection guide](#) for more details.

K6PM - Thermal Condition Monitor

- 24/7 remote thermal monitoring of equipment using infrared thermal image sensors
- Thermal Imaging Sensor that detects temperatures 32-392°F (0-200°C)
- EtherNet/IP and Modbus TCP communication
- Included monitoring software tool can monitor up to 155 sensors at one time




[Product Page](#)

Power	Controller	Thermal image Sensor
24 VAC/DC	K6PM-THMD-EIP	K6PM-THS3232

K7TM – Heater Condition Monitor

- Three-phase and single-phase relays for voltage and current monitoring
- Complete line for monitoring sequence and phase drop, asymmetry, under or over control
- Supply voltages: 24 VAC/DC, 100 to 240 VAC, 380-480 VAC
- Special models for monitoring temperature and liquid level



[Product Page](#)

Unit	Supply Voltage	Model
Controller Unit	100-240 VAC	K7TM-A2MA
	24 VAC/VDC	K7TM-A2MD
CT Clamp		
Rated Primary Side Current	Model	UL Compliant Models
5 A	K6CM-CICB005	K6CM-CICB005-C
25 A	K6CM-CICB025	K6CM-CICB025-C
100 A	K6CM-CICB100	K6CM-CICB100-C
200 A	K6CM-CICB200	K6CM-CICB200-C
400 A	K6CM-CICB400	K6CM-CICB400-C
600 A	K6CM-CICB600	-

Note: Tables include representative part numbers.

Please refer to the [Component selection guide](#) for more details.

K8AK / K8DS – Monitoring Relays

- Three-phase and single-phase relays for voltage and current monitoring
- Complete line for monitoring sequence and phase drop, asymmetry, under or over control
- Supply voltages: 24 VAC/DC, 100 to 240 VAC, 380-480 VAC
- Special models for monitoring temperature and liquid level



 [Product Page](#)

Phase	Dimensions	Monitoring Type	Input	Output Contact Form	Model
Single-Phase	K8AK - 22.5 x 90 x 100 [mm] K8DS: 17.5 x 80 x 69 [mm]	Over Current	24 VAC/DC or 100 to 240 VAC	SPDT	K8AK-AS2 24VAC/DC
		Overvoltage and Undervoltage	24 VAC/DC or 100 to 240 VAC	SPDT	K8AK-VW2 24VAC/DC
Three-Phase		Phase Drop and Phase Sequence	200-480 VAC	DPDT SPDT	K8AK-PH1 200/500VAC K8DS-PH1 200/480VAC
		Phase Drop, Phase Sequence, Overvoltage and Undervoltage	200-240 VAC	(2) SPDT	K8AK-PM1 200/240VAC
380-480 VAC	K8AK-PM2 380/480VAC				

K7GE – Insulation Resistance Monitoring

- Reliable, Safe and Accurate Automatic Insulation Resistance Measurements
- Modular Product units for multiple motor insulation resistance monitoring
- 50 VDC measurement voltage
- Monitor up to 8 motors with additional probes
- Transistor Alarm Outputs, RS-485 communication
- Especially useful for servo/motors operating in harsh environments



 [Product Page](#)

Unit	Supply Voltage	Model
Controller Unit	100-240 VAC	K7GE-MGMA
	24 VAC/VDC	K7GE-MGMD
Probe Unit	—	K7GE-MG1

A2W - Wireless Pushbutton

- 8 pushbuttons can be assigned to one receiver unit
- Each receiver has 8 transistor outputs (one-shot operation)
- LED signal strength indicator on each button
- Battery-less pushbutton (uses self-generating power)



[Product Page](#)

Type	Button type	Frequency (MHz)	Area	Button color	Flange color	Model
Pushbutton	Mushroom	922.5	United States or Canada	Green	Black	A2W-TC-WC1 US1GB
	Full guard			Red	Black	A2W-TC-WC1 US2RB
				Green	Black	A2W-TC-WC1 US2GB
				Yellow	Black	A2W-TC-WC1 US2YB
				Blue	Black	A2W-TC-WC1 US2AB
				Black	Black	A2W-TC-WC1 US2BB

Type	Frequency (MHz)	Area	Output configuration	Model
Receiver	922.5	United States or Canada	PNP	A2W-RCP-WC1 US

Note: This product is a wireless device that conforms to the radio regulations of United States or Canada. It cannot be used outside of United States or Canada.

Accessories (sold separately)	Model	Remarks
High-sensitivity magnetic-base antenna	A2W-AT2.5-WC1	Frequencies: all frequencies supported, cable length 2.5 m Degree of protection: IP65

Note: Tables include representative part numbers.

Please refer to the [Component selection guide](#) for more details.


Note: Tables include representative part numbers.

Please refer to the [Component selection guide](#) for more details.

A22N / M22N - Push Buttons And Indicators

- Complete line with Ø 22mm assemblies
- Various colors and models with plastic or metallic bezels
- Color coded contact blocks to prevent assembly errors
- Easy installation and IP66 degree of protection



 [Product Page](#)

Type	Bezel material	Color	Contact	LED Voltage	Model	
A22NN - Push Button	(1) Bezel Material B – Plastic R – Metallic	(2) Color B – Red G – Green Y – Yellow W – White A – Blue B – Black	1 NO	(3) LED Voltage N – No lighting A – 6 VAC/VDC B – 12 VAC/VDC C – 24VAC/VDC D – 100/120 VAC/VDC E – 200/240 VAC/VDC	A22NN-RNM-NGA-G100-NN	
			1 NO		A22NN-RNM-NBA-G100-NN	
A22NL - Lighted Push Button			1 NO		A22NL-BGM-TGA-G100-GC	
			1 NO		A22NL-RPM-TRA-G100-RC	
M22N - Indicators			---		M22N-BC-TYA-YC	
			---		M22N-BN-TGA-GC	
A22NS - Selector			2 positions - 1NO		A22NS-2RM-NBA-G100-NN	
			3 positions - 2NO		A22NS-3RM-NBA-G101-NN	
A22NK - Selector with Key			---		2 positions - 1NO	A22NK-2RM-01AA-G100
			---		2 positions - 1NO	A22NK-2RL-01BA-G100

Item	Model
Contact block 1NO	A22NZ-S-G1A
Contact block 1NC	A22NZ-S-G1B

Note: Tables include representative part numbers. Please consult the product page for more details.

CP1H – MicroPLC for 4 Axis Position Control and High Speed Control

- High-speed counters with differential phases and pulse outputs for 4 axes control. Easily handles multi-axis control with a single unit.
- Up to two Ethernet ports and two serial ports when selecting the appropriate optional communications boards
- Up to 40 Built in I/O points with Analog I/O built in on XA CPU units
- Over 30 different expansion units for I/O, temperature sensing and communications



[Product Page](#)

[Training Services](#)

Type	Input Points	Output Points	Expandable up to*	Program Capacity	Data Memory Capacity	Power Supply	Output Method	Built-In Functions			Model
								E	I/C	P	
CP1H-X with pulse outputs for 4 axes	24	16	320 points	20K steps	32K words	85 to 264 VAC	Relay output	4	8	--	CP1H-X40DR-A
						20.4 to 26.4 VDC	Transistor output (sink type)	4	8	4	CP1H-X40DT-D
CP1H-XA with built-in analog I/O (4 analog inputs/2 analog outputs; 1/12,000 resolution)	24	16	320 points	20K steps	32K words		85 to 264 VAC	Relay output	4	8	--
						20.4 to 26.4 VDC	Transistor output (sink type)	4	8	4	CP1H-XA40DT-D
CP1H-Y with 1-MHz pulse I/O	12	8	300 points	20K steps	32K words		20.4 to 26.4 VDC	Transistor output (source type)	4	8	4
						Transistor output (sink type)		4**	6	4**	CP1H-Y20DT-D

Note: Built-in functions: E = Encoder inputs; I/C = Interrupts/counters; P = Pulse outputs

*CP1H CPU series can be expanded with CP-series Expansion Units and CJ1 Special I/O Units.

** Encoder inputs: 2x 1 MHz + 2x 100 kHz; Pulse outputs: 2x 1 MHz + 2x 100 kHz.

Note: Tables include representative part numbers. Please consult the product page for more details.

CP2E - Micro PLC for Data Collection and Machine-To-Machine Communication

- Up to five communications channels: dual Ethernet and up to three serial ports for data collection, machine-to-machine or IIoT
- Built-in I/O of either 14, 20, 30, 40 or 60 points with up to 180 I/O points when using expansion modules
- Up to four axes of motion control for precise machine movement



[Product Page](#)

[Training Services](#)

CP2E-N/Network Models

I/O points	Specifications								
	Power Supply	Inputs	Outputs	Output Type	Communications	Axis	Option Boards	Expansion Units	Model
14	100 to 240 VAC	8	6	Relay	1 Ethernet port Up to 2 serial ports	2	1		CP2E-N14DR-A
				Transistor (sinking)					CP2E-N14DT-A
	24 VDC			Relay					CP2E-N14DR-D
				Transistor (sinking)					CP2E-N14DT-D
				Transistor (sourcing)					CP2E-N14DT1-D
20	100 to 240 VAC	12	8	Relay	1 Ethernet port Up to 2 serial ports	2	1		CP2E-N20DR-A
				Transistor (sinking)					CP2E-N20DT-A
	24 VDC			Relay					CP2E-N20DR-D
				Transistor (sinking)					CP2E-N20DT-D
				Transistor (sourcing)					CP2E-N20DT1-D
30	100 to 240 VAC	18	12	Relay	2 Ethernet ports Up to 3 serial ports	4	2	3	CP2E-N30DR-A
				Transistor (sinking)					CP2E-N30DT-A
	24 VDC			Relay					CP2E-N30DR-D
				Transistor (sinking)					CP2E-N30DT-D
				Transistor (sourcing)					CP2E-N30DT1-D
40	100 to 240 VAC	24	16	Relay	2 Ethernet ports Up to 3 serial ports	4	2	3	CP2E-N40DR-A
				Transistor (sinking)					CP2E-N40DT-A
	24 VDC			Relay					CP2E-N40DR-D
				Transistor (sinking)					CP2E-N40DT-D
				Transistor (sourcing)					CP2E-N40DT1-D
60	100 to 240 VAC	36	24	Relay	2 Ethernet ports Up to 3 serial ports	4	2	3	CP2E-N60DR-A
				Transistor (sinking)					CP2E-N60DT-A
	24 VDC			Relay					CP2E-N60DR-D
				Transistor (sinking)					CP2E-N60DT-D
				Transistor (sourcing)					CP2E-N60DT1-D

Note: Tables include representative part numbers. Please consult the product page for more details.

CP2E - Micro PLC (continued)

- Function block library for expedited program development
- Analog, high speed counters, pulse outputs, linear interpolation and PWM output facilitates a wide range of applications



[Product Page](#)

[Training Services](#)

CP2E-S/Standard Models

I/O points	Specifications								
	Power Supply	Inputs	Outputs	Output Type	Communications	Axis	Option Boards	Expansion Units	Model
30	100 to 240 VAC	18	12	Relay	1 x RS-232C port 1 x RS-485 port	2	----	3	CP2E-S30DR-A
	24 VDC			Transistor (sinking)					CP2E-S30DT-D
				Transistor (sourcing)					CP2E-S30DT1-D
40	100 to 240 VAC	24	16	Relay	1 x RS-232C port 1 x RS-485 port	2	----	3	CP2E-S40DR-A
	24 VDC			Transistor (sinking)					CP2E-S40DT-D
				Transistor (sourcing)					CP2E-S40DT1-D
60	100 to 240 VAC	36	24	Relay	1 x RS-232C port 1 x RS-485 port	2	----	3	CP2E-S60DR-A
	24 VDC			Transistor (sinking)					CP2E-S60DT-D
				Transistor (sourcing)					CP2E-S60DT1-D

CP2E-E/Essential Models

I/O points	Specifications								
	Power Supply	Inputs	Outputs	Output Type	Communications	Axis	Option Boards	Expansion Units	Model
14	100 to 240 VAC	8	6	Relay	1 x RS-232C port	----	----	3	CP2E-E14DR-A
20		12	8	Relay	1 x RS-232C port	----	----	3	CP2E-E20DR-A
30		18	12	Relay	1 x RS-232C port	----	----	3	CP2E-E30DR-A
40		24	16	Relay	1 x RS-232C port	----	----	3	CP2E-E40DR-A
60		36	24	Relay	1 x RS-232C port	----	----	3	CP2E-E60DR-A


Note: Tables include representative part numbers. Please consult the product page for more details.

CP1L - Micro PLC

- Compact PLC for up to 180 I/O points
- Programming via USB port or Ethernet port based on model
- Optional boards for Analog, Serial and Ethernet communication on select models
- Supports up to 4 encoders and 2 pulse train outputs (transistor models only)



 [Product Page](#)

 [Training Services](#)

Family	Power Supply	Amount of I/Os in the CPU			Expansion Units	Communication Ports	Option Boards	Output Type	Model
		Digital		Analog					
		Inputs	Outputs	Inputs					
CP1L-EM	24 VDC	24	16	2 (0-10V)	3	Ethernet FINS	2	Transistor (sourcing)	CP1L-EM40DT1-D
	24 VDC	24	16	2 (0-10V)	3	Ethernet FINS	2	Relay	CP1L-EM40DR-D
	24 VDC	18	12	2 (0-10V)	3	Ethernet FINS	2	Transistor (sourcing)	CP1L-EM30DT1-D
	24 VDC	18	12	2 (0-10V)	3	Ethernet FINS	2	Relay	CP1L-EM30DR-D
CP1L-EL	24 VDC	12	8	2 (0-10V)	1	Ethernet FINS	1	Transistor (sourcing)	CP1L-EL20DT1-D
	24 VDC	12	8	2 (0-10V)	1	Ethernet FINS	1	Relay	CP1L-EL20DR-D
CP1L-M	100 to 240 VAC	24	16	No	3	USB	2	Relay	CP1L-M40DR-A
	24 VDC	24	16	No	3	USB	2	Relay	CP1L-M40DR-D
	24 VDC	24	16	No	3	USB	2	Transistor (sourcing)	CP1L-M40DT1-D
	100 to 240 VAC	18	12	No	3	USB	2	Relay	CP1L-M30DR-A
	24 VDC	18	12	No	3	USB	2	Relay	CP1L-M30DR-D
	24 VDC	18	12	No	3	USB	2	Transistor (sourcing)	CP1L-M30DT1-D
CP1L-L	24 VDC	12	8	No	1	USB	1	Transistor (sourcing)	CP1L-L20DT1-D
	24 VDC	12	8	No	1	USB	1	Transistor (sinking)	CP1L-L20DT-D
	100 to 240 VAC	12	8	No	1	USB	1	Relay	CP1L-L20DR-A
	24 VDC	12	8	No	1	USB	1	Relay	CP1L-L20DR-D
	24 VDC	8	6	No	1	USB	1	Transistor (sinking)	CP1L-L14DT-D
	100 to 240 VAC	8	6	No	1	USB	1	Relay	CP1L-L14DR-A

Expansion Modules and Accessories

Family	Communication Ports	Model
Digital Expansions	8 Inputs	CP1W-8ED
	8 Relay Outputs	CP1W-8ER
	16 Relay Outputs	CP1W-16ER
	12 Inputs and 8 PNP Transistor Outputs	CP1W-20EDT1
	24 Inputs and 16 Relay Outputs	CP1W-40EDR
Analog Expansions Resolution of 12000 points	4 Inputs (0 to 5V, 1 to 5V, 0 to 10V, -10 to + 10V, 0 to 20mA and 4 to 20mA)	CP1W-AD042
	4 Outputs (1 to 5V, 0 to 10V, -10 to + 10V, 0 to 20mA and 4 to 20mA)	CP1W-DA042
	2 Inputs (0 to 5V, 1 to 5V, 0 to 10V, -10 to + 10V, 0 to 20mA and 4 to 20mA)	CP1W-MAD42
	1 Output (1 to 5V, 0 to 10V, -10 to + 10V, 0 to 20mA and 4 to 20mA)	CP1W-MAD42
Optional Communication Adapters	RS-232C Serial Port (15m Distance)	CP1W-CIF01
	RS-422A/485 Serial Port (50m Distance)	CP1W-CIF11
	RS-422A/485 Serial Port (500m Distance)	CP1W-CIF12
Software	Programming Software with 1 license	CXONE-AL01D-V4

Note: Tables include representative part numbers. Please consult the product page for more details.

NX1P - Machine Automation Controllers

- Compact entry model with integrated motion and machine control. Connectivity to safety and vision systems
- Up to 4 axes of coordinated motion control plus 4 axes point to point control
- Expandable I/O using up to 8 NX series I/O cards on local bus
- Built in EtherCAT and EtherNet/IP ports
- Connect up to 16 EtherCAT Slaves
- Sysmac Studio IDE for flexible, scalable programming



[Product Page](#)

[Training Services](#)

[Fieldbus Communication Configuration](#)

Built-In Digital I/O		Specifications	Number of Coordinated axes*	Number of point-to-point axes**	Total Axes	Option Boards	Model	
Digital								
Inputs	Outputs							
14	10	1.5MB of programming memory, min cycle time up to 2ms	0	4	4	1 Slot	NX1P2-9024-DT1	
24	16		2		6		2 Slots	NX1P2-1040-DT1
24	16		4		8			NX1P2-1140-DT1

* Coordinated Axes Include:

- Point to Point Positioning
- Synchronized Motion (Gearing/Camming)
- Multi-Axes Coordinated Motion (Circular/Linear Interpolation)
- Axes grouping

**Point to Point axes Include:

- Only Point to Point Positioning
- No Synchronized Motion
- No Multi-Axes Coordinated Motion
- No Axes Grouping

Note: PNP transistor Output options shown. For NPN options, go to automation.omron.com

Option Boards

Type	Description	Communication Protocol	Model
Serial Communication	1 x RS-232C port Transmission Distance: 15 m Connector type: Spring terminal (9 terminals)	Host link, Modbus-RTU Master and no-protocol	NX1W-CIF01
	1 RS-422A/485 Transmission Distance: 50 m Connector type: Spring terminal (5 terminals)		NX1W-CIF11
	1 RS-422A/485 port (isolated) Transmission Distance: 500 m Connector type: Spring terminal (5 terminals)		NX1W-CIF12
Analog Inputs and Outputs	2 x Analog inputs Voltage input: 0 to 10 V (Resolution: 1/4,000) Input current: 0 to 20 mA (1/2,000) Connector type: Spring terminal (5 terminals)		NX1W-ADB21
	2 x Analog inputs / 2 x Analog output Voltage input: 0 to 10 V (Resolution: 1/4,000) Input current: 0 to 20 mA (1/2,000) Voltage output: 0 to 10 V (Resolution: 1/4,000) Connector Type: Spring terminal (8 terminals)		NX1W-MAB221

Note: The expansion cards of the NX1P machine controller line are the same as the NX Series I/O cards. For information on virtual axes, refer to the catalog on the website automation.omron.com

Software and Switches

Type	Description	Model
Software	Sysmac Studio IDE Lite Version 1 License	SYSMAC-SE201L
Hub	Hub EtherCAT with 3 Ports	GX-JC03
	Hub EtherCAT with 3 Ports	GX-JC06
	Hub EtherNet/IP with 3 Ports	W451-03B
	Hub EtherNet/IP with 5 Ports	W451-05B

Note: Tables include representative part numbers. Please consult the product page for more details.

NX102 - Machine Automation Controllers



Seamless Integration into Sysmac

- OMRON's complete line of 120+ NX I/O Units
- OMRON's integrated software environment Sysmac Studio
- OMRON Vision, OMRON Motion, OMRON Robotics, and OMRON Safety Components

Leverage the strength of multiple industrial protocols:

- EtherCAT®, IO Link, EtherNET/IP®, CIP Safety, FSOE
- Up to 8 axis of motion control
- EtherCAT® cycle times from 1 to 32 ms in 0.25ms increments
- 32 local I/O per CPU, 400 total I/O per CPU with Remote NX/IO
- 5 MB of program capacity



Product Page



Product Video



Training Services



Fieldbus Communication Configuration

Family	Specifications	Number of Coordinated axes *	Number of point-to-point axes **	Total Axes	SQL	Model
NX102	5 MB of programming memory, Min. cycle up to 1ms	0	4	4	No	NX102-9000
					Yes	NX102-9020
		2		6	No	NX102-1000
					Yes	NX102-1020
		4		8	No	NX102-1100
					Yes	NX102-1120
		8		12	No	NX102-1200
					Yes	NX102-1220

Note: The NX-END02 terminal cover is included with the NX102. The HMC-SD291 memory card is supplied with the NX102-__20. The battery is not mounted when the product is shipped. Refer to the datasheet for details.

For information on virtual axes, refer to the catalog on Omron website automation.omron.com

* Coordinated Axes Include:

- Point to Point Positioning
- Synchronized Motion (Gearing/Camming)
- Multi-Axes Coordinated Motion (Circular/Linear Interpolation)
- Axes grouping

**Point to Point axes Include:

- Only Point to Point Positioning
- No Synchronized Motion
- No Multi-Axes Coordinated Motion
- No Axes Grouping

Software and Switches

Type	Description	Model
Software	Sysmac Studio IDE Lite Version 1 License	SYSMAC-SE201L
Hub	Hub EtherCAT with 3 Ports	GX-JC03
	Hub EtherCAT with 3 Ports	GX-JC06
	Hub EtherNet/IP with 3 Ports	W451-03B
	Hub EtherNet/IP with 5 Ports	W451-05B

Note: Tables include representative part numbers. Please consult the product page for more details.

NX502 - Machine Automation Controllers

Seamless Integration into Sysmac

- OMRON's complete line of 120+ NX I/O Units
- OMRON's integrated software environment Sysmac Studio
- OMRON Vision, OMRON Motion, OMRON Robotics, and OMRON Safety Components

Leverage the strength of multiple industrial protocols:

- EtherCAT®, IO Link, EtherNET/IP™, CIP Safety, FSOE
- OPC UA and SQL as standard while also leveraging Sysmac Studio MQTT function blocks
- EtherCAT® 250µs EtherCAT® Refresh Speed
- 256 EtherCAT® Nodes
- 512 tag sets per EIP Unit
- Up to 256 axis of motion control
- 80 MB of program capacity



Product Page



Product Video



Training Services



Fieldbus Communication Configuration

Family	Specifications	I/O Capacity	Coordinated Axes ¹	Total Axes	OPC UA	SQL	Model
NX502	5 MB of programming memory, Min. cycle up to 0.25ms	1024 Points local	16	16	Yes	Yes	NX502-1300
			32	32	Yes	Yes	NX502-1400
			64	64	Yes	Yes	NX502-1500
			128	128	Yes	Yes	NX502-1600
			256	256	Yes	Yes	NX502-1700

Note: The NX-END02 terminal cover is included with the NX502.

The battery is not mounted when the product is shipped. Refer to the datasheet for details.

For information on virtual axes, refer to the catalog on Omron website automation.omron.com

1. Coordinated Axes Include:

- Point to Point Positioning
- Synchronized Motion (Gearing/Camming)
- Multi-Axes Coordinated Motion (Circular/Linear Interpolation)
- Axes grouping

Software and Network Card

Type	Description	Model
Software	Sysmac Studio Standard Edition, One Seat	SYSMAC-SE201L
Network Card	NX502 Ethernet I/P Module	NX-EIP201

NX701

Machine Automation Controllers




Seamless Integration into Sysmac


- OMRON's complete line of 120+ NX I/O Units
- OMRON's integrated software environment Sysmac Studio
- OMRON Vision, OMRON Motion, OMRON Robotics, and OMRON Safety Components

Leverage the strength of multiple industrial protocols:

- EtherCAT®, IO Link, EtherNET/IP™, FSOE
- Up to 256 Axis of motion control
- EtherCAT® cycle times from 0.125ms to 0.250ms in 0.125ms increments and 0.250ms to 8 ms in 0.250 ms increments.
- 80 MB of program capacity

 [Product Page](#)

 [Training Services](#)

 [Fieldbus Communication Configuration](#)

Family	Specification	Number of Coordinated Axes	SQL	Model Number
NX7	80 MB of programming memory, minimum cycle time 0.125 ms	128	YES	NX701-1620
Power Supplies	Capacity	RUN Indicator	Model	
100 to 240VAC	90W	NO Relay	NX-PA9001	
24 VDC	70W		NX-PD7001	
Software and Switches	Description	Model		
Software	Sysmac Studio IDE Lite Version 1 License	SYSMAC-SE201L		
Hub	Hub EtherCAT with 3 Ports	GX-JC03		
	Hub EtherCAT with 3 Ports	GX-JC06		
	Hub EtherNet/IP with 3 Ports	W451-03B		
	Hub EtherNet/IP with 5 Ports			

Note: Tables include representative part numbers. Please consult the product page for more details.

NX-HTC - Multi-Loop Temperature Controller

- 4 loop and 8 loop models
- 40% Footprint Reduction vs. NX-TC
- .01 °C Temperature Resolution when used with K-type, PT100 thermocouple
- Waveform Digitalization Function Monitors 16 different process features
- Disturbance Suppression Technology
- For use with PLC or IPC



[Product Page](#)

[Training Services](#)

Model	Number of Channels	Input type	Output	Output Capacity	CT Input Capacity	Control type	Safety Standard
NX-HTC4505	8ch	Full Multi-input (Thermocouple, resistance thermometer and analog input)	Voltage output (for driving SSR)	8 points	8 points	Standard control	UC1, CE, RCM, KC, EAC
NX-HTC3510	4ch		Heating output: Voltage output (for driving SSR)	4 points	4 points	Heating and Cooling control	
			Cooling output: Linear current output				

NX-TC - Multi-Loop Temperature Controller

- 2 or 4 loop models
- PID control
- Ethernet/IP&EtherCAT with PLC/Coupler
- Voltage out and Current Out models
- Ability to specify variable to output
- Heater Burnout detection



[Product Page](#)

[Training Services](#)

Product Name	Number of channels	Input Type	Output	Output Capacity	CT Input Capacity	Control Type	Conversion Time	I/O Refreshing Method	Model
Temperature Control Unit 2Ch Type	2 Ch	Multi-input (Thermocouple & Resistance Thermometer)	Voltage (for SSR control)	2 points	2 points	Standard Control	50 m sec	Free-Run refreshing	NX-TC2405
				4 points	None	Heating & Cooling Control			NX-TC2407
Temperature Control Unity 4Ch Type	4 Ch			4 points	4 points	Standard Control			NX-TC3405
				4 points	None	Standard Control			NX-TC3406
				8 points	None	Heating & Cooling Control			NX-TC3407

Note: Tables include representative part numbers. Please consult the product page for more details.

NX - Remote I/O

- Wide variety of high density remote I/O Modules
- Ideal match with Sysmac Machine automation controllers
- EtherCAT and EtherNet/IP coupler options
- Platform Agnostic. Easy connectivity to 3rd party systems
- Removable wiring terminals for easy system assembly and testing



 [Product Page](#)

 [Training Services](#)

Type	Description	Model
Digital I/O	8 Digital Inputs (NPN)	NX-ID4342
	8 Digital Inputs (PNP)	NX-ID4442
	16 Digital Inputs (NPN)	NX-ID5342
	16 Digital Inputs (PNP)	NX-ID5442
	32 Digital Input (NPN)	NX-ID6342
	32 Digital Input (PNP)	NX-ID6442
	8 Relay NO Outputs	NX-OC4633
	8 Digital Outputs (NPN)	NX-OD4121
	8 Digital Outputs (PNP)	NX-OD4256
	16 digital outputs (NPN)	NX-OD5121
	16 digital outputs (PNP)	NX-OD5256
	32 Digital Output (PNP)	NX-OD6121
Analog I/O	4 4-20 mA Analog Inputs	NX-AD3203
	4 4-20mA Analog Outputs	NX-DA3203
	4 Analog Inputs -10 to +10 V	NX-AD3603
	4 Analog Outputs -10 to +10 V	NX-DA3603
Temperature control	4 Thermocouple Inputs	NX-TS3101
	4 RTD Inputs	NX-TS3201
Weighing	1 Input for Load Cell	NX-RS1201
Position control	1 Line-Driver Pulsed Output	NX-PG0122
	1 Incremental Encoder Input	NX-EC0122
Serial Communication	1 RS232C Interface	NX-CIF101
	1 RS485/422A Interface	NX-CIF105
IIoT	IO-Link Master Interface for 4 IO-Link Devices	NX-ILM400
Accessories	Additional Supply for I/Os (4A)	NX-PF0630
	Additional Supply for I/Os (10A)	NX-PF0730
	Additional Source for Communication Bus	NX-PD1000

COUPLERS Network	Communications Cycle	Current Consumption	Maximim I/O power supply current	Model
EtherCAT	250 to 4,000 μ s	1.45 W or lower	4A	NX-ECC201
	125 to 10,000 μ s	1.25 W or lower	10A	NX-ECC202
EtherNet/IP	-	1.50W or lower		NX-EIC203
				NX-EIC202

SLAVE UNIT Network	IO Data Update	Refresh Mode	Model
EtherCAT	1.5 ms	Free Run	NX-ECT101

Note: Tables include representative part numbers. Please consult the product page for more details.

NXR - IP67 EthernetIP Remote IO-Link Master

- EtherNetIP and EtherCAT Models
- Fully configurable ports with up to 8 IO-Link connections, or 2 digital I/O per port (16 Total)
- Dip switch port setting for PC-Less maintenance and setup – Market First (EtherCAT Model Only)
- Dip switch setting for IP/Node Address
- Short Circuit Detection and Protection
- Cable Break Monitoring
- Third Party controller Function Blocks and AOI available for Rockwell and Beckhoff Controllers - Ask your local AM or FAE for details


 Product Page

 Training Services

Unit	IO Capacity	Max Output Load Current	Model
EtherCAT IO-Link Master	8 IO-Link ports (or up to 16 Digital I/O)	2 A per point	NXR-ILM08C-ECT
EtherNet IP IO-Link Master	8 IO-Link ports (or up to 16 Digital I/O)	2 A per point	NXR-ILM08C-EIT
IO-Link Hub	16 Digital Inputs	N/A	NXR-ID166C-IL2
	16 Digital Inputs/Outputs	0.5 A per point	NXR-CD166C-IL2

Communication Cables

M12 to RJ45 - Straight Connectors ¹		M12 to M12 - Straight Connectors ¹	
Length (Meters)	Part Number	Length (Meters)	Part Number
1	XS2W-T421-CMC-SS	1	XS2W-T421-CM2-SS
2	XS2W-T421-DMC-SS	2	XS2W-T421-DM2-SS
5	XS2W-T421-GMC-SS	5	XS2W-T421-GM2-SS
10	XS2W-T421-JMC-SS	10	XS2W-T421-JM2-SS

Power Cables

7/8" connector to flying leads – Straight Connectors ¹		7/8" connector to 7/8" connector - Straight Connectors ¹	
Length (Meters)	Part Number	Length (Meters)	Part Number
1	21349700495010	1	21349697495010
2	21349700495020	2	21349697495020
5	21349700495050	5	21349697495050
10	21349700495100	10	21349697495100

Accessory

Unit	Description	Model
Y Cable Splitter	For connecting two devices to one port	XS5R-D426-1



1. 90 degree connectors are also available. Ask your Omron representative for details

Note: Tables include representative part numbers. Please consult the product page for more details.

NX-V680C - RFID Units

- Data reads/writes are easily performed by simply setting parameters in the machine automation controller memory area
- Simple device configuration, compared to serial communication, coupled with high-speed data processing
- Communication programs can be easily built using the ladder program function blocks "Sysmac Library RFID Communications Library (SYSMAC-XR019)"



[Product Page](#)

[Training Services](#)

Model	Number of Antennas/Amplifiers	Antenna/Amplifier	Operating Frequency	RFID Standard
NX-V680C1	1	V680 Series	13.56 MHz	ISO 15693
NX-V680C2	2			

Note: Tables include representative part numbers. Please consult the product page for more details.

NJ - Machine Automation Controllers

- One integrated controller designed to meet extreme requirements in terms of logic sequence, motion control speed, accuracy, and system size
- EtherCAT and Ethernet IP communication on the same CPU
- Ability to manage logic, motion, safety and vision tasks
- Embedded SQL Client Option
- Expandable I/O Using up to 10 CJ Expansion cards
- Sysmac Studio IDE for flexible, scalable programming


[Product Page](#)

[Training Services](#)

[Fieldbus Communication Configuration](#)

Family	Specifications	Number of axes	OPC UA	SQL	Model
NJ1	64 EtherCAT slaves, 3 MB of programming memory, Min. cycle time: 1ms	0	No	No	NJ101-9000
			No	Yes	NJ101-9020
		2	No	No	NJ101-1000
			No	Yes	NJ101-1020
NJ3	192 EtherCAT slaves, 5 MB of programming memory, Min. cycle time: 1ms	4	No	No	NJ301-1100
		8	No	No	NJ301-1200
NJ5	192 EtherCAT slaves, 20 MB of programming memory, Min. cycle time: 0.5 ms	16	Yes	No	NJ501-1300
			No	Yes	NJ501-1320

Note: For information on virtual axes, refer to the catalog on the website automation.omron.com

Power Supplies

Power Supplies	Capacity	RUN Indicator	Model
100 to 240VAC	30W	NO Relay	NJ-PA3001
24 VDC			NJ-PD3001


Software and Switches

Type	Description	Model
Software	Sysmac Studio IDE 1 License	SYSMAC-SE201L
Hub	Hub EtherCAT with 3 Ports	GX-JC03
	Hub EtherCAT with 6 Ports	GX-JC06
	Hub EtherNet/IP with 3 Ports	W4S1-03B
	Hub EtherNet/IP with 5 Ports	W4S1-05B


Note: Tables include representative part numbers. Please consult the product page for more details.

Sysmac Studio- Integrated Design Environment

- A truly integrated development environment for machine automation. Combining designing, commissioning, and monitoring in a simple interface.
- Transparent software access with a single license.
- More confident designs through built-in simulation.
- Increase uptime through event triggered and time synchronized data playback.



 [Product Page](#)

 [Training Services](#)

License Type	Part Number	# of Users
Sysmac Studio Standard Edition	SYSMAC-SE201L	1
	SYSMAC-SE203L	3
	SYSMAC-SE210L	10
	SYSMAC-SE230L	30
	SYSMAC-SE250L	50
	SYSMAC-SE2XXL	Site
Sysmac Studio Basic Edition	SYSMAC-BA201L	1
Sysmac Studio Advanced Edition	SYSMAC-AD201L	1
Sysmac Studio Lite Edition Limited to NX1, NJ1 Controllers	SYSMAC-LE201L	1
	SYSMAC-LE203L	3
	SYSMAC-LE210L	10
Sysmac Studio Upgrade	SYSMAC-LE201L	1
	SYSMAC-LE203L	3
	SYSMAC-LE210L	10

OS	CPU	RAM	Display
Windows 7 (32-bit) Windows 8 (32-bit) Windows 8.1 (32-bit) Windows 10 (32-bit or 64-bit edition)	Minimum ¹	2 GB	XGA 1,024 x 768, 16 million colors
	Recommended ^{2,3}	4 GB min.	WXGA 1,280 x 800x 16 million colors

1. If you create a user program with a memory size that exceeds 20 MB, use the 64-bit edition of the operating system and 8 GB or more of RAM.
2. If the user program is large, we recommend that you use a 64-bit IBM AT or compatible with an Intel® Core™ i7 processor or better and 8 GB or more of RAM.
3. If you use the Robot Additional Option and execute Vision and Robot integrated simulations, use a 64-bit IBM AT or compatible with an Intel® Core™ i5 processor or better and 8 GB or more of RAM.

Note: Tables include representative part numbers. Please consult the product page for more details.

Sysmac Studio- Integrated Design Environment

- A truly integrated development environment for machine automation. Combining designing, commissioning, and monitoring in a simple interface.
- Transparent software access with a single license.
- More confident designs through built-in simulation.
- Increase uptime through event triggered and time synchronized data playback.


 [Product Page](#)
 [Training Services](#)

OMRON Product Family	OMRON Product Compatibility	Sysmac Studio Basic & Advanced	Sysmac Studio Lite	Sysmac Studio Vision	Sysmac Studio Measurement	Symac Studio Drive	Sysmac Studio Safety	Sysmac Studio NX
Logic	NX1P2	•	•					
	NX102	•	•					
	NX502	•						
	NX701	•						
	NJ101	•	•					
	NJ301	•						
	NJ501	•						
HMI	NA5	•	•					
I/O	NX I/O EtherCAT Coupler	•	•					
	NX I/O EtherNet/IP Coupler	•	•					•
Vision	FH	•	•	•				
	FHV7	•	•	•				
	FQM	•	•	•				
Safety	NX-SL3	•	•				•	•
	NX-SL5/CSG	•	•				•	
Motion	1S	•	•			•		
	G5	•	•			•		
Measurement	ZW	•	•		•			


Note: Tables include representative part numbers. Please consult the product page for more details.

NB - Basic Graphic HMI

- 65K Color TFT display with LED backlight
- Data Logging/Trending, Recipes, Alarms, Remote web viewing
- Graphics Library and Animation
- Free NB Designer programming software
- Preferred for Omron CP controllers



 [Product Page](#)

 [Training Services](#)

Size	Description		Model
	Communication Port	Resolution	
3.5"	RS232C/RS422	320 x 234	NB3Q-TW00B-V1
5.6"	RS232C/RS422, Ethernet		NB5Q-TW01B-V1
5.6"	RS232C/RS422		NB5Q-TW00B-V1
7"	RS232C/RS422, Ethernet	800 x 480	NB7W-TW01B-V1
7"	RS232C/RS422		NB7W-TW00B-V1
10"	RS232C/RS422, Ethernet		NB10W-TW01B-V1

Note: For more information, refer to the catalog on the website automation.omron.com

NA - Advanced High Resolution Graphic Display

- Wide screen high resolution display with 16M colors
- Multimedia including video, Word, Excel and PDF viewers
- Sysmac Studio provides the integrated development environment
- Preferred for NJ/NX controllers



 [Product Page](#)

 [Training Services](#)

Size	Description		Model
	Communication Port	Resolution	
7"	2 Ethernet, USB, RS232	800 x 480	NA5-7W001B-V1
9"			NA5-9W001B-V1
12.1"		1280 x 800	NA5-12W101B-V1
15.4"			NA5-15W101B-V1

Note: Part numbers are for black bezel. Silver bezel available.

Note: Tables include representative part numbers. Please consult the product page for more details.

Soft NA - Software to Emulate the NA Advanced Graphic Display on an Industrial PC

- Sysmac Studio provides the integrated development environment.
- Design or Re -Use applications from the NA Graphic display on your choice of Industrial PC. Omron NY Series of IPC preferred.
- Run Soft-NA and other applications such as Enterprise Resource Planning or others, on an IPC.
- Windows 10 OS based and preferred for NJ/NX controllers.
- Preferred for NJ/NX controllers



[Product Page](#)

[Training Services](#)

Product Name	Specifications	Number of licenses	Media	Model
Soft-NA	The Soft-NA is software that displays information on FA manufacturing sites while providing safety, reliability, and maintainability as an industrial display on which operations can be preformed as necessary. The Soft-NA runs on the following OS: Windows 10 Pro Version 1903 or later 64 bit	- (Media only)	DVD	NA-RTSM
		1 license	USB dongle	NA-RTLDD01
		3 licenses		NA-RTLDD03
		10 licenses		NA-RTLDD10

NY - Box PC

- Omron NY Series Industrial PCs are designed with the Sysmac principals of creating the highest degree of machine performance.
- Increased reliability with simplified thermal design.
- Increased connectivity as standard through flexible operating systems and more built-in ports.
- Increased performance as standard with 11th Generation CPUs.



[Product Page](#)

Product Name	Operating System	CPU	RAM Memory	Storage	Interface option	Type	Model
Industrial Box PC	Windows 10 IoT Enterprise 2021 LTSC - 64 bit	Intel® Xeon® W-11865MRE	32 GB (non-ECC type)	1 TB SSD type (3DTLC)	Ethernet	Yes	NYB2E-515P9
			32 GB (ECC type)				NYB2E-E5P9
		Intel® Core™ i7-1185GRE	16 GB (non-ECC type)	512 GB SSD type (3DTLC)	None	No	NYB37-40530
				512 GB SSD type (3DTLC)	Ethernet	Yes	NYB37-415H9
			16 GB (non-ECC type)	256 GB SSD type (3DTLC)	None	No	NYB55-40520
				256 GB SSD type (3DTLC)	Ethernet	Yes	NYB55-415G9

Note: The NYB family does not come with an industrial monitor.

Note: Tables include representative part numbers. Please consult the product page for more details.

NY - Panel PC




- Omron NY Series Industrial PCs are designed with the Sysmac principals of creating the highest degree of machine performance.
- Increased reliability with simplified thermal design.
- Increased connectivity as standard through flexible operating systems and more built-in ports.
- Increased performance as standard with 11th Generation CPUs.

[Product Page](#)

Product Name	Display size	Operating System	CPU	RAM Memory	Storage	Interface option	Type	Model
Industrial Panel PC	12.1 Inch	Windows 10 IoT Enterprise 2021 LTSC - 64 bit	Intel® Core™ i3-1115GRE	16 GB	128 GB CFast type (MLC)	No	No	NYP13-40520-12WC1000
			Intel® Atom® x6425RE Processor	8 GB	256 GB CFast type (3DTLC)	No	No	NYP3A-3-520-12WC1000
	15.4 Inch		Intel® Core™ i5-1145GRE	16 GB	512 GB CFast type (MLC)	No	No	NYP65-40530-15WC1000
			Intel® Atom® x6425RE Processor	16 GB	256 GB CFast type (3DTLC)	No	No	NYP3A-40520-15WC1000
	18.5 Inch ¹		Intel® Core™ i5-1145GRE	16 GB	256 GB CFast type (3DTLC)	No	No	NYP65-40520-19WC1000
			Intel® Core™ i3-1115GRE	16 GB	256 GB CFast type (3DTLC)	No	No	NYP13-40520-19WC1000

1. 18.5 inch models also available with Nickle Plating front.

NYM - Industrial Monitor



- Multitouch projected capacitive touchscreen
- False touch detection (palm, water)
- Operator can wear gloves
- Optional NY Monitor Link interface for connectivity up to 100m
- Custom logo option

[Product Page](#)

Item	Size	Resolution	Interface	Model
Industrial Monitor	18.5"	1,280 x 800	DVI-D	NYM19W-C1000
	15.4"			NYM15W-C1000
	12.1"			NYM12W-C1000
	18.5"		NY Monitor Link	NYM19W-C1060
	15.4"			NYM15W-C1060
	12.1"			NYM12W-C1060

Note: Tables include representative part numbers. Please consult the product page for more details.

NY5 - IPC Machine Controller

- Models available with AI function and with NC function
- Real Time Operating System runs independently of the Windows OS
- Program the machine control with Sysmac Studio using ladder, ST, SFC.
- Machine control program portable to modular NJ controller
- Available in box and panel versions



[Product Page](#)

[Training Services](#)

Operational System	CPU	Number of axes	RAM Memory	Storage	Type	Model
Windows Embedded Standard 7 64 bit	Intel Core i7 4700EQ	64	8 GB	64GB SSD	15.4" Monitor Panel	NY532-1500-112213910
		32				NY532-1400-112213910
		16				NY532-1300-112213910

Note: For models with NC function or with Artificial Intelligence function, refer to the catalog on the website automation.omron.com

Omron AVEVA Edge

- Omron AVEVA™ Edge offers an Integrated Development Environment (IDE) with the Omron driver set that allows you to design once and deploy anywhere for most Omron control platforms.
- Omron AVEVA™ Edge SCADA – The full Windows based runtime offers all the tools you need for advanced SCADA applications
- Omron AVEVA™ Edge HMI – AVEVA Edge for embedded systems such as Windows Embedded operating systems. The small footprint makes AVEVA Edge HMI ideal for embedded and edge machines



[Product Page](#)

Development or Development and Runtime	Runtime
Omron Aveva Edge Unlimited Tags	
Omron Aveva Edge 512K Tags	Omron Aveva Edge 512K Tags
Omron Aveva Edge 64K Tags	Omron Aveva Edge 64K Tags
Omron Aveva Edge 32K Tags	Omron Aveva Edge 32K Tags
Omron Aveva Edge 16K Tags	Omron Aveva Edge 16K Tags
Omron Aveva Edge 4K Tags	Omron Aveva Edge 4K Tags
Omron Aveva Edge 1.5K Tags	Omron Aveva Edge 1.5K Tags
Omron Aveva Edge 300 Tags	Omron Aveva Edge 300 Tags
Omron Aveva Edge 150 Tags	Omron Aveva Edge 150 Tags

Note: Tables include representative part numbers. Please consult the product page for more details.

MicroHAWK V320-F/V330-F/V420-F/V430-F Barcode Reader

- Ultracompact readers, with several model options and setting possibilities
- High performance in reading 1D and 2D codes on any surface, including Direct Part Marks
- Extremely simple setting via browser - WebLink, without the need for software installation
- Autofocus with liquid lens (V420-F and V430-F)



 [Product Page](#)

 [Product Video](#)

 [Training Services](#)

Line	Acquisition	Sensor	Focus	Communication	Lighting	IP	Power	Model
V320-F	52 fps	0.34 MP Mono	Fixed 102mm	RS-232C, USB/HID, or Ethernet via USB (USB 2.0 Full-Speed)	Built-in White & Red	IP40	5VDC	V320-F102W03M-NNX
	40 fps	1.2 MP Mono						V320-F102W12M-NNX
V330-F	60 fps	0.34 MP Mono	Fixed 102mm	Ethernet TCP/IP	Built-in White & Red	IP40	36 to 57 VDC (PoE, IEEE 802.3af)	V330-F102W03M-NNX
	42 fps	1.2 MP Mono						V330-F102W12M-NNX
V420-F	60 fps	0.34 MP Mono	Autofocus 50-300mm	RS-232C, USB/HID, or Ethernet via USB (USB 2.0 Full-Speed)	Built-in White & Red + External Red (8 LEDs)	IP54	5VDC	V420-F000W03M-SRX
	42 fps	1.2 MP Mono	Autofocus 75-1200mm					V420-F000W12M-SRX
	42 fps	1.2 MP Mono	Autofocus 75-1200mm					V420-F000L12M-SRX
V430-F	60 fps	0.34 MP Mono	Autofocus 50-300mm	RS-232C, Ethernet TCP/IP, EtherNet/IP, PROFINET I/O	External Red (24 LEDs)	IP65/67	5 to 30 VDC	V430-F000W03M-SRX
	42 fps	1.2 MP Mono	Autofocus 50-300mm					V430-F000W12M-SRX
	42 fps	1.2 MP Mono	Autofocus 75-1200mm					V430-F000L12M-SRX
	42 fps	1.2 MP Mono	Autofocus 50-300mm					V430-F000M12M-RRX

Cables And Accessories

Product	Type	Description	Model
V320-F	Power, I/O, Serial and USB	Cable with RJ50 connector, 3m	V320-W8-3M
	RJ50/DB-15 Converter	RJ50 Cable for DB-15, 1m	V320-WR-1M
	Programming	DB-15 cable for USB, 1m	V420-WUB-1M
V330-F	Standard Ethernet Cable	RJ45 Cable for RJ45	XS6W-5PURBSS_00CM-G
V420-F	Programming	DB-15 cable for USB, 1m	V420-WUB-1M
VF430-F	Power, I/O and Serial	Cable with 12-pin M12 connector	V430-W8-_M
	Ethernet	Cable with 8-pin M12 connector for RJ45	V430-WE-_M

Note: Tables include representative part numbers. Please consult the product page for more details.

V410-H - Handheld Barcode Reader

- Labels or Direct Part Mark barcode reading
- High resolution 1280 x 800 pixels
- Read ranges from contact to 28 inches
- Intuitive and insightful WebLink PC utility and run time with image storage, statistics, reader discovery, troubleshooting and extensive tool tips


 [Product Page](#)

Name	Decoding Algorithms	Read Range (10 mil DataMatrix)	Communication	IP Rating	Application	Model
V410-H XD	1D/2D, X-Mode	0 - 12 cm / 0 - 4.6 in	RS-232 / USB	IP52	Direct Part Mark and Labels	V410-HDS4608XD
V410-H SR	1D/2D	2.5 - 29 cm / 1 - 11.5 in			Labels only	V410-HDS4608SR
V410-H HC		0.5 - 24 cm / 0.2 - 9.5 in			Healthcare / Disinfectant resistant	V410-HDS4608HC

Cables And Accessories

Product	Type	Description	Model
V410-H	Cable (Required)	CABLE ASSY, UNIVERSAL STYLE 3 USB, 2m, SHIELDED MOD PLUG-V410-H	V410-WUB-2M
	Cable	CBL ASSY, RS232, DB9F, 2m, for connection to communication module or PLC	V410-WR-2M
	Power Supply	Power Supply required for V410-WR-2M RS-232 Cable	V410-AC0-1
	Intelligent Stand	Stand/holder for using in Hands-free mode	V410-AS0
	Communication Module	Serial to Ethernet TCP and EIP DIN rail mounted converter	OEI-EA3600-R1CP-11
	Cable	2m Serial Cable for OEI-EA3600	OEI-CBA-RF2-CO9ZAR

Note: Tables include representative part numbers. Please consult the product page for more details.

V450-H - Handheld Barcode Reader

- Versatile, powerful decode performance for any application
- Simple Application Configuration via WebLinkPC
- Point-and-shoot decode performance
- Withstands multiple drops from 8' and 5,000 tumbles
- IP 67 Rated
- Industry-Leading DPM Decoding Performance with Omron's X-Mode Imaging Technology
- Wired or Wireless Models



[Product Page](#)

Description	Part Number
V450-H, Handheld Reader DPM, Wired	V450-HDS3608-0001
V450-H, Handheld Reader DPM, Wireless	V450-HDS3678-0001
V450-H, Cradle, Charger	12-9000937-01

Cables And Accessories

Description	Model
Battery, Spare, V450-H / HS-360X	98-9000224-01
Power Supply, Cradle, V450-H / HS-360X	98-9000181-01
Power Supply, 4-Slot Battery Charger, V450-H / HS-360X	98-9000182-01
4-Slot Battery Charger, V450-H / HS-360X	98-9000185-01
Stand, Intelligent, V450-H / HS-360X	98-9000186-01
AC Power Cable, 1.8M, Japan, C13 Connector	12-9001046-01
AC Power Cable, 1.8M, UK, C13 Connector	12-9000961-01
AC Power Cable, 1.8M, EU, C13 Connector	12-9000960-01
AC Power Cable, 1.8M, U.S., C13 Connector	12-9000959-01
AC Power Cable, 1.8M, China, C13 Connector	12-9000962-01
Cable, RS232, DB9, Female, 2M, Straight, V450-H / HS-360X	12-9000953-01
Cable, USB, Shielded, 2M, Ext 12V, V450-H / HS-360X	12-9000942-01
Cable, USB, Shielded, 4.6M, Ext 12V, V450-H / HS-360X	12-9000943-01
Cable, USB, Shielded, 2M, V450-H / HS-360X	12-9000946-01
Cable, USB, Shielded, 4.6M, V450-H / HS-360X	12-9000946-01
Cable, Adapter, Omron CS/CJ/NJ PLC	V430-WPLC-2M

Note: Tables include representative part numbers. Please consult the product page for more details.

V460-H - Handheld Barcode Reader

- All in one rugged industrial handheld barcode reader
- Superior out-of-box performance
- Predictive Auto-focus and Intelligent Lighting
- Hands Free Intelligent Presentation Mode
- Built in PoE with Fieldbus Communications
- Simple PLC integraton with pre-built function blocks
- Rugged design - drop-and-tumble rated




[Product Page](#)

Description	Part Number
V460-H Handheld DPM Reader, PoE Wired, with X-Mode	V460-H0PX

Cables And Accessories

Type	Length	Part Number
Ethernet Communication Cables – Straight Connectors M12 Plug on Reader to RJ45 Connector	1 Meter	V430-WE-1M
	3 Meters	V430-WE-3M
	5 Meters	V430-WE-5M

Note: Tables include representative part numbers. Please consult the product page for more details.

V680S - RFID Reader/Writer

- All in one controller, amplifier, antenna
- Reads and writes to any ISO 18000-3 compliant RFID Tag
- Diagnostic function for easy setup and troubleshooting
- Ethernet, EtherNet/IP and PROFINET connectivity



 [Product Page](#)

Dimensions (mm)	Network	Model
50 x 50 x 30	EtherNet/IP	V680S-HMD63-EIP
	PROFINET	V680S-HMD63-PNT
	Modbus TCP (TCP/IP)	V680S-HMD63-ETN
75 x 75 x 40	EtherNet/IP	V680S-HMD64-EIP
	PROFINET	V680S-HMD64-PNT
	Modbus TCP (TCP/IP)	V680S-HMD64-ETN
120 x 120 x 40	EtherNet/IP	V680S-HMD66-EIP
	PROFINET	V680S-HMD66-PNT
	Modbus TCP (TCP/IP)	V680S-HMD66-ETN

Tags

Type	Memory	Dimensions (mm)	Installation	Model
No Battery	2 K	40 x 40 x 5	For assembly on non-metallic faceted surface	V680S-D2KF67
			For assembly on metallic faceted surface	V680S-D2KF67M
		86 x 54 x 10	For assembly on non-metallic faceted surface	V680S-D2KF68
			For assembly on metallic faceted surface	V680S-D2KF68M
	8 K	40 x 40 x 5	For assembly on non-metallic faceted surface	V680S-D8KF67
			For assembly on metallic faceted surface	V680S-D8KF67M
		86 x 54 x 10	For assembly on non-metallic faceted surface	V680S-D8KF68
			For assembly on metallic faceted surface	V680S-D8KF68M

Note: For tags in other formats, or labels, refer to the Omron website.

Note: Tables include representative part numbers. Please consult the product page for more details.

V780 - UHF Long Range RFID Reader/Writer

- All-in-one antenna/amplifier/controller with up to 6m of read/write range
- Ability to network up to 7 slave antennas with a master for increased tag reading area
- Web browser based setup and configuration with advanced diagnostics
- Ethernet (Modbus TCP, EtherNet/IP™) as a standard feature



[Product Page](#)

[Product Video](#)

Dimensions (mm)	Network	Applicable countries	Model
250 × 250 × 70	Modbus/TCP base (TCP/IP)	United States and Canada	V780-HMD68-ETN-US
		Mexico	V780-HMD68-ETN-MX
	EtherNet/IP	United States and Canada	V780-HMD68-EIP-US
		Mexico	V780-HMD68-EIP-MX
	(Slave Reader/Writer for Multi-Reader/Writer function)	United States and Canada	V780-HMD68-ETN-US-S
		Mexico	V780-HMD68-ETN-MX-S

Cables for V680S and V780

Type of Communication	Length	Power cable	Communication cable
V680S Modbus TCP (TCP/IP)	2 Meters		V680S-A41 2M*
	5 Meters		V680S-A41 5M*
	10 Meters		V680S-A41 10M*
V780 EtherNet/IP and PROFINET	1 Meter	XS5F-D421-C80-F	XS5W-T421-CME-K
V680S EtherNet/IP and PROFINET	2 Meters	XS5F-D421-D80-F	XS5W-T421-DMC-K
	5 Meters	XS5F-D421-G80-F	XS5W-T421-GMC-K
	10 Meters	XS5F-D421-J80-F	XS5W-T421-JMC-K

Note: * Interface Cable with V680S Special Connector to Flying Leads for Power and RJ45 for Communications

Note: Tables include representative part numbers. Please consult the product page for more details.

LVS-95XX - Offline Verifier

- Verify 1D, 2D and direct part marks
- Software automatically selects best lighting performance from integrated red or white dome and 30° angle lighting
- Validates printed barcodes to ISO/IEC, ANSI, GS1, and UDI print quality standards



[Product Page](#)

[Training Services](#)

Type	Field of View	Codes	X-Dimension (min)		Lighting	Power	Communication	Model
			1 D	2 D				
LVS-9510 Desktop	113mm x 85mm	1D & 2D	7.0 mils	9.8 mils	Red (filtered)	12VDC (Supply)	USB 2.0	9510-5-45
LVS-9580 DPM/ LVS-9585 DPM	76mm x 57mm		1D, 2D & DPM	5.0 mils	5.9 mils	Red (filtered)		USB Powered
	45mm x 45mm	5.9 mils			Red, White & 30° angle			
	45mm x 45mm	5.9 mils				9585-DPM		

V275 - Inline Verifier and Print Quality Inspection

- Inspect 100% of labels for print quality.
- Verify 1D and 2D codes to ISO standards.
- Ensure compliance with regulations and quality requirements.
- Check for cosmetic blemishes and errors in printed data.
- Avoid costly chargebacks, recalls, and supply chain disruption.



[Product Page](#)

[Product Video](#)

Type	Print Resolution	Print Speed (max)	Label Width (max)	X-Dimension (min)		Font Size (point)	Communication	Model
				1 D	2 D			
V275	300 dpi	304mm (12")/seg	104mm (4.1")	6.6 mils	10.0 mils	5 point	5 pt Ethernet (via PC)	V275-P46Z61030-CC
V275	600 dpi	152mm (6")/seg	104mm (4.1")					V275-P46Z61060-CC
V275	300 dpi	203mm (8")/seg	167mm (6.6")					V275-P86Z62030-CC

Note: 10.0 mils if Code 1D is vertically printed (ladder orientation)

Note: Tables include representative part numbers. Please consult the product page for more details.

V440-F C-Mount Code Reader

- 5MP global shutter sensor @ 36FPS
- C-Mount lens compatible
- Designed for use with NERLITE Smart Series ring lights
- Power over Ethernet (PoE) or direct 24VDC
- Gigabit Ethernet with locking RJ45 port
- Weblink 3.0 with Enhanced functionality including Matrix Mode and Configuration Database
- IP40-rated



[Product Page](#)

[Training Services](#)

Part Number	Sensor	Optics	Communications	IP Rating	Decode Algorithms
V440-FXXXY50M-NNP	5 MP, Global Shutter, Monochrome	C-Mount	RS232C, Ethernet, EtherNet/IP, PROFINET	IP 40	1D/2D Plus Mode
V440-FXXXY50M-NNX	5 MP, Global Shutter, Monochrome	C-Mount	RS232C, Ethernet, EtherNet/IP, PROFINET	IP 40	1D/2D X-Mode

Note: Lenses, Lights and Cables are selected separately, based on the individual application. Please refer to the V440-F data sheet for all available options.

Mounting Options

Part Number	Description
V440-AM0	1/4-20 Mounting Block for V440-F Reader

NERLITE Smart Series Ring Lights

Part Number	Description
NER-011660900G	R-70, 70mm, Smart Series Ring Light
V440-AM1	R-70 Smart Series Ring Light Mounting Kit
NER-011661100G	R-100, 100mm, Smart Series Ring Light
V440-AM2	R-100 Smart Series Ring Light Mounting Kit

Industrial GigE Ethernet Cable

Part Number	Description	Length
98-000133-01	RJ45 to RJ45, Industrial High Flex GigE Ethernet Cable with Jack Screws	2 Meters
98-000134-01	RJ45 to RJ45, Industrial High Flex GigE Ethernet Cable with Jack Screws	5 Meters
98-000134-02	RJ45 to RJ45, Industrial High Flex GigE Ethernet Cable with Jack Screws	7 Meters

Power & I/O Cable

Part Number	Description	Length
V430-W8-3M	Power & I/O Cable, M12 to Flying Leads Cable, Straight	3 Meters
V430-W8-5M	Power & I/O Cable, M12 to Flying Leads Cable, Straight	5 Meters
61-9000135-01	Y Cable, Reader & Smart Light Power (Continuous On)	1 Meter
61-9000137-01	Y Cable, Reader & Smart Light Power (Strobe Control)	1 Meter

Note: Tables include representative part numbers. Please consult the product page for more details.

MicroHAWK F430/330 - Smart Camera

- Ultracompact Smart Cameras
- Various model options and configuration possibilities
- Two programming software options: AutoVISION (Simplified) or Visionscape (Complete)
- Autofocus with liquid lens (F420-F and F430-F)
- Degree of protection up to IP67



Product Page



Product Video



Training Services

Family	Sensor Color	Sensor Resolution	Shutter Type	Lens Type/ Mount	Focus Distance	Software or License	Model			
F320	Monochrome	0.34 MP	Global	Integrated - fixed focus	102 mm	AutoVISION + Verification + Visionscape	F320-F102W03M-NNV			
	Monochrome	1.2 MP					F320-F102W12M-NNV			
	Color	5 MP	Rolling				F320-F102W50C-NNV			
F330	Monochrome	0.34 MP	Global				Autofocus high speed liquid lens	75 to 1200 mm	AutoVISION + Verification + Visionscape	F330-F102W03M-NNV
	Monochrome	1.2 MP								F330-F102W12M-NNV
	Color	5 MP	Rolling							F330-F102W50C-NNV
F420	Monochrome	1.2 MP	Global	Autofocus high speed liquid lens	50 to 300 mm	AutoVISION Sensor				F420-F000L12M-SRV
	Color	5 MP	Rolling							F420-F000M50C-SWS
	Monochrome	0.34 MP	Global		50 to 300 mm	AutoVISION + Verification + Visionscape				F420-F000W03M-SRV
	Monochrome	1.2 MP					F420-F000W12M-SRV			
	Color	5 MP	Rolling		F420-F000W50C-SWV					
F430	Monochrome	1.2 MP	Global		Autofocus high speed liquid lens	75 to 1200 mm	AutoVISION + Verification + Visionscape	F430-F000L12M-SRV		
	Monochrome	1.2 MP		F430-F000M12M-RRV						
	Monochrome	1.2 MP		50 to 300 mm		AutoVISION + Verification	F430-F000M12M-SRA			
	Monochrome	1.2 MP					F430-F000M12M-SRV			
	Monochrome	1.2 MP		AutoVISION + Verification + Visionscape		F430-F000M12M-SWA				
	Monochrome	0.34 MP				F430-F000W03M-SRV				
	Monochrome	1.2 MP		AutoVISION + Verification + Visionscape	F430-F000W12M-SRV					
	Color	5 MP			AutoVISION Sensor	F430-F000W50C-SWS				
	Color	5 MP	Rolling	AutoVISION + Verification + Visionscape	F430-F000W50C-SWV					

Note: Tables include representative part numbers. Please consult the product page for more details.


F440 Smart Camera

- 5 MP monochrome global shutter sensor
- Up to 35 FPS image acquisition
- Standard C-Mount lens compatible lens
- Optics & Lighting flexibility to solve complex vision applications
- AutoVISION offers twelve easy to use tools that allow users to setup and star jobs within 3 steps



[Product Page](#)

[Training Services](#)

Appearance	Description	Part Number
	F440-F, No Optics, 5 MP, Mono, No Light, AutoVISION Sensor	F440-FXXX50M-NNS
	F440-F, No Optics, 5 MP, Mono, No Light, AutoVISION + Verification	F440-FXXX50M-NNA
	F440-F, No Optics, 5 MP, Mono, No Light, AutoVISION + Verification + Visionscape	F440-FXXX50M-NNV

Note 1: F440-F cameras are sold without lenses, lights, cables, or mounting. All of these items can be found in later sections of this datasheet.

Note 2: The F440-F uses all the same cables and interconnect accessories as the V440-F. The F440-F uses standard Ethernet cables. High-Flex TPE cables and Robot Ethernet cables are shown later in this datasheet.

Software License	Vision Toolset
F440-FXXX50M-NNS: AutoVISION Sensor	Locate Tool, Presence/Absence Tool, Count Tool, Measure Tool, Logic Tool
F440-FXXX50M-NNA: AutoVISION + Verification	All of the Above + Decode Tool, OCR Tool, Match Strings Tool, String Format Tool, OCV Tool, Symbol Quality Verification Tool
F440-FXXX50M-NNV: AutoVISION + Verification + Visionscape	All of the Above + Visionscape Extensive Machine Vision Tool Set

Note: Tables include representative part numbers. Please consult the product page for more details.

FHV7 - Smart Camera

- Several model options and setting possibilities (from 0.4MP to 12MP)
- Dual-Core CPU providing up to 430 fps (0.4MP) acquisition
- Multicolor lighting module (red, green, blue, and infrared, with individual control)
- Degree of protection up to IP67



- [Product Page](#)
- [Product Video](#)
- [Training Services](#)

Family	Sensor Color	Sensor Resolution	Shutter Type	Lens Type/Mount	Software or License	Model
FHV7	Monochrome	0.4 MP	Global	C Mount with option for autofocus accessory	FHV Software or Sysmac Studio Software with License	FHV7X-M004-C
		1.6 MP				FHV7X-M016-C
		3.2 MP				FHV7X-M032-C
		5 MP				FHV7X-M050-C
	Color	0.4 MP		C Mount with option for autofocus accessory		FHV7X-C004-C
		1.6 MP				FHV7X-C016-C
		3.2 MP				FHV7X-C032-C
		5 MP				FHV7X-C050-C
	Monochrome	6.3 MP	Rolling	C Mount with option for autofocus accessory		FHV7X-C063R-C
		12 MP		C Mount		FHV7X-C120R-C
		6.3 MP		C Mount with option for autofocus accessory		FHV7X-M063R-C
		12 MP		C Mount		FHV7X-M120R-C

Lenses

Focal Distance	C-Mount	Autofocus (Standard)	Autofocus (High-speed)
6mm	—	FHV-LEM-S06	FHV-LEM-H06
8mm	SV-0814H	—	—
9mm	—	FHV-LEM-S09	—
12mm	SV-1214H	FHV-LEM-S12	—
16mm	SV-1614H	FHV-LEM-S16	—
19mm	—	—	FHV-LEM-H19
25mm	SV-2514H	FHV-LEM-S25	—

Note: For C-Mount lenses, please refer to Vision Accessory Catalog for complete lens setup. Autofocus lenses and Lighting modules will fit on 0.4MP, 1.6MP, 3.2MP and 6.3MP cameras. [You can also refer to the FHV7 configurator on the product page.](#)

Lighting Modules

Light Color	Model
Multicolor	FHV-LTM-MC
Red	FHV-LTM-R
White	FHV-LTM-W
IR	FHV-LTM-IR

Type	Connector	
	Straight	Right-angle
Ethernet Cable	FHV-VNB2_ M ¹	FHV-VNLB2_ M ¹
I/O Cable	FHV-VDB2_ M ¹	FHV-VDLB2_ M ¹
Data Unit Cable	FHV-VUB2_ M ¹	FHV-VULB2_ M ¹
I/O Cable for Parallel Interface Data Unit	XW2Z-S013- _ ¹	—

Smart Camera Data Unit

Type	Inputs / Outputs	EtherCAT Communication	Model
Parallel Interface	12 Inputs / 24 Outputs	No	FHV-SDU10
EtherCAT Interface	1 Input / 2 Outputs	Yes (Slave)	FHV-SDU30


1. Replace underscore with cable length in Meters (2, 3, 5, 10, 20). Only lengths 2 and 5 are available for the Parallel Interface Data Unit.

Note: Tables include representative part numbers. Please consult the product page for more details.

FH - Vision System

High-speed and standard models include:

- High performance Vision System with AI and more than 100 program tools
- Connection for 2, 4 or 8 cameras on the same controller with independent triggers
- High resolution cameras up to 20 MP
- Real image processing (16 million colors)


 [Product Page](#)
 [Training Services](#)

Controllers

Item	CPU and Processing	Communication	EtherCAT	No. of cameras	Model
Box type controller	High-Speed Controller (4 core)	EtherNet/IP, EtherCAT, EtherNet TCP/UDP, PROFINET, Serial, Parallel I/O	Yes	2	FH-5051
				4	FH-5051-10
	8			FH-5051-20	
	Standard Controller (2 core)			2	FH-2051
				4	FH-2051-10
	8			FH-2051-20	
Lite Controller (2 core)	EtherNet/IP, EtherNet TCP/UDP, PROFINET, Serial, Parallel I/O	No	2	FH-L551	
			4	FH-L551-10	

Cameras

Item	Description	Model	
		Color	Monochrome
CMOS Camera (Rolling Shutter)	5MP, 71.7ms image acquisition time	FH-SC05R	FH-SM05R
	20.4MP, 42.6ms image acquisition time	FH-SC21R	FH-SM21R
Newer high speed CMOS Camera (Global Shutter)	12MP, 24.9ms image acquisition time ¹	FH-SCX12	FH-SMX12
	5MP, 10.3ms image acquisition time ¹	FH-SCX05	FH-SMX05
	3.2MP, 6.6ms image acquisition time ¹	FH-SCX03	FH-SMX03
	1.6MP, 6.5ms image acquisition time	FH-SCX01	FH-SMX01
	0.4MP, 1.9ms image acquisition time	FH-SCX	FH-SMX
High speed CMOS Camera (Global Shutter)	M42 Mount 12MP, 25.7ms image acq time ¹	FH-SC12	FH-SM12
	4MP, 8.5ms image acquisition time ¹	FH-SC04	FH-SM04
	2MP, 4.6ms image acquisition time ¹	FH-SC02	FH-SM02
Integrated CMOS Camera (Global Shutter)	0.3MP, 16.7ms image acquisition time	FZ-SQ100N	—

1. Frame rate in high speed mode when the camera is connected using two camera cables.

Type	Description	Model	Type of Camera	Focal Distance	Model
Cable for camera	2m Length	FZ-VS3 2M	FH-S_X01 FH-S_X03 FH-S_X05 FH-S_05R (1.6MP to 5MP)	6mm	SV-0614H
	5m Length	FZ-VS3 5M		8mm	SV-0814H
	10m Length	FZ-VS3 10M		12mm	SV-1214H
Parallel cable for I/Os	2m Length	XW2Z-S013-2		16mm	SV-1614H
				25mm	SV-2514H
	5m Length	XW2Z-S013-5	6mm	SV-0614V	
			8mm	SV-0813V	
FH-S_X (0.4MP)			12mm	SV-1214V	
			16mm	SV-1614V	
			25mm	SV-2514V	

Note: Tables include representative part numbers. Please consult the product page for more details.
Note: Please refer to Vision Accessory Catalog for complete lens setup.

M Series GigE Vision Cameras

- Power over Ethernet capable
- High Resolution, High Speed, CMOS Sensors.
- Small Form Factor: 29 x 29mm & 30 x 40mm versions.
- IEEE1588 Certified with GigE Vision 2.1
- Compatible with Omron AutoVISION & VisionScape



[Product Page](#)

[Training Services](#)

Global shutter models

Monochrome/Color	Resolution	Frame Rate	Effective Pixels (H × V)	Sensor Size	Cell Size (μm)	Sensor	Lens Mount	Model
Monochrome	0.4M	282.8 fps	720 × 540	1/2.9	6.9 × 6.9	IMX287	C	STC-MBS43POE
Color								STC-MCS43POE
Monochrome	0.5M	166.5 fps	816 × 624	1/1.7	9 × 9	IMX433	C	STC-MBS52POE
Color								STC-MCS52POE
Monochrome	1.3M	61 fps	1280 × 1024	1/1.8	5.3 × 5.3	EV76C560	C	STC-MBE132POE
Color								STC-MCE132POE
Monochrome	1.6M	70.7 fps	1440 × 1088	1/2.9	3.45 × 3.45	IMX273	C	STC-MBS163POE
Color								STC-MCS163POE
Monochrome	2M	54.6 fps	1624 × 1240	1/1.7	4.5 × 4.5	IMX430	C	STC-MBS202POE
Color								STC-MCS202POE
Monochrome	2.3M	41.6 fps	1920 × 1200	1/1.2	5.86 × 5.86	IMX249	C	STC-MBS231POE
Color								STC-MCS231POE
Monochrome	3.2M	34.9 fps	2048 × 2048	2/3	3.45 × 3.45	IMX265	C	STC-MBS312POE
Color								STC-MCS312POE
Monochrome	5M	21.9 fps	2448 × 2048	2/3	3.45 × 3.45	IMX264	C	STC-MBS500POE
Color								STC-MCS500POE
Monochrome	8.9M	12.4 fps	4096 × 2160	1	3.45 × 3.45	IMX267	C	STC-MBS881POE
Color								STC-MCS881POE
Monochrome	12.3M	8.9 fps	4096 × 3000	1.1	3.45 × 3.45	IMX255	C	STC-MBS122BPOE
Color								STC-MCS122BPOE

Note: Tables include representative part numbers. Please consult the product page for more details.

M Series GigE Vision Cameras (continued)

- Power over Ethernet capable
- High Resolution, High Speed, CMOS Sensors.
- Small Form Factor: 29 x 29mm & 30 x 40mm versions.
- IEEE1588 Certified with GigE Vision 2.1
- Compatible with Omron AutoVISION & VisionScape


 [Product Page](#)
 [Training Services](#)

Rolling shutter models

Monochrome/Color	Resolution	Frame Rate	Effective Pixels (H × V)	Sensor Size	Cell Size (μm)	Sensor	Lens Mount	Model
Monochrome	5M	14 fps	2592 × 1944	1/2.5	2.2 × 2.2	MT9P031	C	STC-MBA503POE
Color								STC-MCA503POE
Monochrome	6.4M	17.4 fps	3072 × 2048	1/1.8	2.4 × 2.4	IMX178	C	STC-MBS642POE
Color								STC-MCS642POE
Monochrome	10M	10.3 fps	3856 × 2764	1/2.3	1.67 × 1.67	MT9J003	C	STC-MBA1002POE
Monochrome	12M	9.2 fps	4000 × 3000	1/1.7	1.85 × 1.85	IMX226	C	STC-MBS1242POE
Color								STC-MCS1242POE
Monochrome	20.4M	5.5 fps	5472 × 3648	1	2.4 × 2.4	IMX183	C	STC-MBS2041POE
Color								STC-MCS2041POE

Screw-Fastened GigE Cables

Length	Model
3 m	FJ-VSG 3M
5 m	FJ-VSG 5M
10 m	FJ-VSG 10M
20 m	FJ-VSG 20M
40 m	FJ-VSG 40M

Power Supply and I/O Cables

Length	Model
3 m	FJ-VSP2 3M
5 m	FJ-VSP2 5M
10 m	FJ-VSP2 10M

Note. Please connect the cables according to the external connector specifications prescribed in your camera's specification documents, for faulty wiring can cause failure.

Note: Tables include representative part numbers. Please consult the product page for more details.

FS Series GigE Vision Line Scan Cameras

- Power over Ethernet capable
- Compact case designed for easy mounting
- Offered in 2K, 4K, or 8K
- Available in Single & Dual Line Monochrome and Dual Line Color Models.
- Action Command Triggering: Trigger multiple cameras simultaneously with one command.



[Product Page](#)

[Training Services](#)

Monochrome/Color	Resolution	Line Rate	Pixel size	Sensor	Sensor Type	Lens Mount	Model
Monochrome	2048 × 1	51 kHz	7 μm	DR-2K-7	Single	C	FS-B2KU7GES-C
						F	FS-B2KU7GES-F
						M42	FS-B2KU7GES-M42
Monochrome	4096 × 1	26 kHz	7 μm	DR-4K-7	Single	F	FS-B4KU7GES-F
						M42	FS-B4KU7GES-M42
Monochrome	4096 × 1	26 kHz	3.5 μm	DR-4K-3.5	Single	C	FS-B4KU35GES-C
						F	FS-B4KU35GES-F
						M42	FS-B4KU35GES-M42
Monochrome	8192 × 1	13 kHz	3.5 μm	DR-8K-3.5	Single	F	FS-B8KU35GES-F
						M42	FS-B8KU35GES-M42
Monochrome	2048x1	26kHz	7 μm	DR-2X2K-7-inver	Dual	C	FS-B2KU7DGES-C
						F	FS-B2KU7DGES-F
						M42	FS-B2KU7DGES-M42
Monochrome	4096x2	13kHz	7 μm	DR-2X4K-7-inver	Dual	F	FS-B4KU7DGES-F
						M42	FS-B4KU7DGES-M42
Color	2048x1	26kHz	7 μm	DR-2X2K-7-inver-RGB	Dual	C	FS-C2KU7DGES-C
						F	FS-C2KU7DGES-F
						M42	FS-C2KU7DGES-M42
Color	4096x2	13kHz	7 μm	DR-2X4K-7-inver-RGB	Dual	F	FS-C4KU7DGES-F
						M42	FS-C4KU7DGES-M42

Screw-Fastened GigE Cables

Length	Model
3 m	FJ-VSG 3M
5 m	FJ-VSG 5M
10 m	FJ-VSG 10M
20 m	FJ-VSG 20M
40 m	FJ-VSG 40M

Power Supply and I/O Cables

Length	Model
3 m	FJ-VSP2 3M
5 m	FJ-VSP2 5M
10 m	FJ-VSP2 10M

Note. Please connect the cables according to the external connector specifications prescribed in your camera's specification documents, for faulty wiring can cause failure.

Note: Tables include representative part numbers. Please consult the product page for more details.

1080p HD Output

- True HD 1080p Resolution at 60 FPS
- Easily programmable user profiles
- Optional Wired Remote Control for on-the-fly changes


 [Product Page](#)
 [Training Services](#)

Model	Monochrome/Color	Resolution	Frame Rate	Effective Pixels (HxV)	Sensor Size	Cell Size (µm)	Sensor	Lens Mount	General Specifications
STC-HD213DV	Color	1080P/1080i	60 fps	1920x080	1/2.9	2.9x2.9	IMX291	C	With Memory
STC-HD213DV-CS								CS	
STC-HD213DVN	Color	1080P/1080i	60 fps	1920x1080	1/2.9	2.9x2.9	IMX291	C	No Memory
STC-HD213DVN-B								C	
STC-HD213DVN-CS								CS	
STC-HD213SDI	Color	1080P/1080i	60 fps	1920x080	1/2.9	2.9x2.9	IMX291	C	With Memory
STC-HD213SDI-CS								CS	
STC-HD213SDIN	Color	1080P/1080i	60 fps	1920x1080	1/2.9	2.9x2.9	IMX291	C	No Memory
STC-HD213SDIN-B								C	
STC-HD213SDIN-CS								CS	

Type	Model	Applicable Model	General Specifications
Mount Conversion Adapter	CS-C-R	CS Mount Series	—
Remote Control Unit	JIG-HD133-R	HDMI/DVI/SDI	Ø3.5 stereo pin jack
Type	Model	Description	
Cables	CAB-HDMI-015	4K HDMI Cable; 1.5m	
	CAB-HDMI-02	4K HDMI Cable; 2m	
	CAB-HDMI-03	4K HDMI Cable; 3m	
	CAB-HDMI-05	4K HDMI Cable; 5m	
	CAB-HDMI-100-OPT	4K HDMI Cable; 100m; Power	
	CAB-HDMI-10-OPT	4K HDMI Cable; 10m; Power	
	CAB-HDMI-20-OPT	4K HDMI Cable; 20m; Power	
	CAB-HDMI-30-OPT	4K HDMI Cable; 30m; Power	
	CAB-HDMI-50-OPT	4K HDMI Cable; 50m; Power	
	CAB-HDMI-70-OPT	4K HDMI Cable; 70m; Power	
Power	PWR-DC12-500R-A	Int/Dom Version of DC12	

Note: Tables include representative part numbers. Please consult the product page for more details.

M Series USB3 Vision Cameras

- USB3.0 Compact CMOS Camera
- Offered in resolutions ranging from 0.4M to 20.4M
- Plug and Play functionality
- Compatible with Omron AutoVISION & VisionScape.



[Product Page](#)

[Training Services](#)

Global shutter models

Monochrome/Color	Resolution	Frame Rate	Effective Pixels (H × V)	Sensor Size	Cell Size (μm)	Sensor	Lens Mount	Model
Monochrome	0.4M	527.1 fps	720 × 540	1/2.9	6.9 × 6.9	IMX287	C	STC-MBS43U3V
Color								STC-MCS43U3V
Monochrome	1.3M	60 fps	1280 × 1024	1/1.8	5.3 × 5.3	EV76C560	CS	STC-MBE132U3V
Color								STC-MCE132U3V
Monochrome	1.6M	238 fps	1440 × 1080	1/2.9	3.45 × 3.45	IMX273	C	STC-MBS163U3V
Color								STC-MCS163U3V
Monochrome	2M	167 fps	2048 × 1088	2/3	5.5 × 5.5	CMV2000	C	STC-MBCM200U3V
Monochrome NIR								STC-MBCM200U3V-NIR
Monochrome	2.3M	41.6 fps	1920 × 1200	1/1.2	5.86 × 5.86	IMX249	C	STC-MBS231U3V
Color								STC-MCS231U3V
Monochrome	2.3M	163 fps	1920 × 1200	1/1.2	5.86 × 5.86	IMX174	C	STC-MBS241U3V
Color								STC-MCS241U3V
Monochrome	3.2M	56 fps	2048 × 1536	1/1.8	3.45 × 3.45	IMX265	C	STC-MBS312U3V
Color								STC-MCS312U3V
Monochrome	3.2M	121 fps	2048 × 1536	1/1.8	3.45 × 3.45	IMX252	C	STC-MBS322U3V
Color								STC-MCS322U3V
Monochrome	4M	89 fps	2048 × 2048	1	5.5 × 5.5	CMV4000	C	STC-MBCM401U3V
Color								STC-MCCM401U3V
Monochrome NIR	5M	35.8 fps	2448 × 2048	2/3	3.45 × 3.45	IMX264	C	STC-MBCM401U3V-NIR
Color								STC-MBS500U3V
Monochrome	5M	75.7 fps	2448 × 2048	2/3	3.45 × 3.45	IMX250	C	STC-MCS500U3V
Color								STC-MBS510U3V
Monochrome	5M	75.7 fps	2448 × 2048	2/3	3.45 × 3.45	IMX250	C	STC-MCS510U3V
Color								STC-MBS70BU3V
Monochrome	7.1M	51.2 fps	3216 × 2208	1.1	4.5 × 4.5	IMX428	C	STC-MBS70BU3V
Color								STC-MCS70BU3V
Monochrome	8.9M	32.5 fps	4096 × 2160	1	3.45 × 3.45	IMX267	C	STC-MBS881U3V
Color								STC-MCS881U3V
Monochrome	8.9M	41.9 fps	4096 × 2160	1	3.45 × 3.45	IMX255	C	STC-MBS891U3V
Color								STC-MCS891U3V
Monochrome	12.3M	23.5 fps	4096 × 3000	1.1	3.45 × 3.45	IMX304	C	STC-MBS122BU3V
Color								STC-MCS122BU3V
Monochrome	12.3M	30.4 fps	4096 × 3000	1.1	3.45 × 3.45	IMX253	C	STC-MBS123BU3V
Color								STC-MCS123BU3V

Note. We recommend that you use an external power supply for 8.9M and 12M cameras, for depending on PC performance, power supplied via USB bus connection alone may not be sufficient for these cameras.

Note. Models with “-SE” have been additionally equipped with the Short Exposure Mode feature.

Rolling shutter models

Monochrome/Color	Resolution	Frame Rate	Effective Pixels (H × V)	Sensor Size	Cell Size (μm)	Sensor	Lens Mount	Model
Monochrome	12M	31.2 fps	4000 × 3000	1/1.7	1.85 × 1.85	IMX226	C	STC-MBS1242U3V
Color								STC-MCS1242U3V
Monochrome	20.4M	18.5 fps	5472 × 3648	1	2.4 × 2.4	IMX183	C	STC-MBS2041U3V
Color								STC-MCS2041U3V

Non-USB3 Vision Compliant Models (with Rolling Shutters)


Monochrome/Color	Resolution	Frame Rate	Effective Pixels (H × V)	Sensor Size	Cell Size (μm)	Sensor	Lens Mount	Model
Monochrome	5M	14 fps	2592 × 1944	1/2.5	2.2 × 2.2	MT9P031	CS	STC-MBA5MUSB3
Color								STC-MCA5MUSB3

Short Wave Infrared Industrial Camera Series

- Top of the line, high-end sensors
- Unique Interfaces for Customizability
- One-of-a-kind Heat dissipation technology
- Removes environmental dependency and variability
- SWIR technology allows inspection throughout the full manufacturing process, even under plastic wrap or silicon coating.



 [Product Page](#)

 [Training Services](#)

Part Number	Interface	Resolution	Frame Rate	Sensor Size
STC-LBS34POE-SWIR	GigE Vision	0.3 MP	242 FPS	1/4"
STC-LBS132POE-SWIR	GigE Vision	1.3 MP	84 FPS	1/2"
STC-LBS34U3V-SWIR	USB3 Vision	0.3 MP	260 FPS	1/4"
STC-LBS132U3V-SWIR	USB3 Vision	1.3 MP	134 FPS	1/2"
STC-LBS34CL-SWIR	Camera Link	0.3 MP	258 FPS	1/4"
STC-LBS132CL-SWIR	Camera Link	1.3 MP	125 FPS	1/2"


Note: Tables include representative part numbers. Bold models: Preferred Availability. Please consult the product page for more details.

Factory Drive Recorder

The Omron Factory Drive Recorder offers users the ability to optimize their machine troubleshooting and minimize the time it takes to solve problems in the field through the combination of Omron Industrial Cameras and the easiest to use Event Capture Software on the market.



 [Product Page](#)

 [Training Services](#)

- Record the Moment
 - Record up to 5 minutes of video before an event trigger and 5 minutes of video after an even trigger
- 4 Trigger Options
 - Master Image Comparison
 - Motion Trigger
 - Time Trigger
 - Trigger Signal (via Hardware Trigger)
- Live Monitoring & Manual Viewing
- Connect up to 8 Omron Industrial Cameras to the Software allowing for multiple camera recordings.
- High Speed & High Quality Recording
 - Omron Industrial Cameras feature Frame Rates up to 527 FPS & Resolutions up to 20 MP

Part Number	Description
STC-FDRSW-01	Omron's New Event Capture Software; Factory Drive Recorder

Related Products

Model No.	Product Family	Description
Industrial Camera	M Series GigE Vision Cameras	GigE Vision Industrial Cameras – Area Scan Cased
	M Series USB3 Vision Cameras	USB3 Vision Industrial Cameras – Area Scan Cased
	B Series GigE Vision Cameras	GigE Vision Industrial Cameras – Area Scan Board
	UVC Cameras	UVC Industrial Cameras – Multiple Configurations
	R Series USB3 Vision Remote Head	USB3 Vision Remote Head

Note: Tables include representative part numbers. Bold models: Preferred Availability. Please consult the product page for more details.

G9SP - Safety Controller

- The standalone safety controller for small and mid-sized applications.
- Communication with standard PLC via Ethernet or Serial
- Direct communication with HMI NB Series via Serial
- Four types of standard expansion



[Product Page](#)

[Safety Services](#)

Product	Inputs	Test outputs	Safety outputs	Common outputs	Model
G9SP Series	10	4	Transistor Output: 4	4	G9SP-N10S
	10	6		-	G9SP-N10D
	20	6	Transistor Output: 8	-	G9SP-N20S

Expansion Modules and Accessories

Description	No. of Outputs	No. of Inputs	Model
Expansion Modules	8 (NPN)	12 (NPN)	CP1W-20EDT
	8 (PNP)	12 (PNP)	CP1W-20EDT1
	32 (NPN)		CP1W-32ET
	32 (PNP)		CP1W-32ET1
Connection Cable	80cm (for connecting distant units)		CP1W-CN811
Communication Modules	RS-232 Serial		CP1W-CIF01
	EtherNet/FINS		CP1W-CIF41
	EtherNet/IP		CM-EIP-1
Programming software	1 license		WS02-G9SP01-V1
Cassette Memory			CP1W-ME05M

Note: Tables include representative part numbers. Please consult the product page for more details.

NX-SL5 - Safety Controller

- A versatile safety controller, with EtherCAT and EtherNet/IP capabilities, for integrated or stand-alone solutions, making machine safety design, installation, and maintenance easier
- Enable flexible manufacture by supporting different safety networks, CIP Safety and FSoE. Enable a hybrid system, when combining the NX-SL5 with the NX-102.
- Sysmac Studio offers a set of unique functions to make functional safety management easier as Safety Signature Check and Online Function Verification. In addition, reduce the design cycle with automatic programming and simple automatic test.



Product Page



Product Video



Training Services



Safety Services

Product	Description	Model
NX-SL5 Safety Controller Units	Safety PLC, up to 1024 safety I/O and 128 safety connections	NX-SL5500
	Safety PLC, up to 2032 safety I/O and 254 safety connections	NX-SL5700

Product	Type	Protocol	Am. of Ports	Number of Networks	Safety Inputs	Safety Outputs	Test Outputs	Model
Communication & Remote Safety I/O Units	Network Coupler	EtherNet/IP	3	2				NX-CSG320
	Remote Module of safety I/Os	EtherNet/IP	2	1	12	4	12	GI-SMD1624
					12	-	12	GI-SID1224

Product	Type	No. of Points	Description	Model
Safety Input & Output Units	Input	4	4 safety input points (PNP) with 2 test outputs	NX-SIH400 Ver 1.1
		8	8 safety input points (PNP) with 2 test outputs	NX-SID800
	Output	2	2 safety outputs (PNP)	NX-SOH200
		4	4 safety outputs (PNP)	NX-SOD400

Note: Tables include representative part numbers. Please consult the product page for more details.

NX-SL3 - Safety Controller

- Effortless integration into the most common PLC’s platforms in the market, providing reliable safety solutions while supporting different configurations.
- Offer a direct connection to any PLC using an EtherNet/ IP coupler, and build a stand-alone system. For larger projects, with a higher number of safety devices distributed over a larger area, using an EtherCAT coupler supports EtherCAT and FSoE.
- Sysmac Studio offers a set of unique functions to make functional safety management easier as Safety Signature Check and Online Function Verification. In addition, reduce the design cycle with automatic programming and simple automatic test.



[Product Page](#)

[Training Services](#)

[Safety Services](#)

Product	Type	Model
NX-SL3 Safety Controller Units	Safety PLC, up to 256 safety I/O and 32 safety connections *	NX-SL3300 Ver 1.1
	Safety PLC, up 1024 safety I/O and 128 safety connections *	NX-SL3500 Ver 1.1

* Only FSoE master connections supported

Product	Type	No. of Points	Description	Model
Safety Input & Output Units	Input	4	4 safety input points (PNP) with 2 test outputs	NX-SIH400 Ver 1.1
		8	8 safety input points (PNP) with 2 test outputs	NX-SID800
	Output	2	2 safety outputs (PNP)	NX-SOH200
		4	4 safety outputs (PNP)	NX-SOD400

Product	Communication Cycle	Protocol	Maximum number of NX I/O modules	Maximum Current I/O	Model
Network Couplers	250 to 4,000 us	EtherCAT Slave	63	4A	NX-ECC201
				10A	NX-ECC202
	125 to 10,000 us	EtherNet/IP Slave		10A	NX-ECC203
				4 to 1,000 us	NX-EIC202

F3SG-SR - Machine Guard Safety Light Curtain

- Three-color Area Beam Indicators (ABIs) enable easy alignment and quick troubleshooting
- Up to 30m protection range (25mm resolution and up)
- IO-Link communication capability helps improve preventive maintenance programs
- Advanced programming features (muting, blanking, pre-reset, warning zone, etc.) are available on all models.
- IP67G rating is standard, with IP69K option available (F3SG-SRB only)



 [Product Page](#)

 [Product Video](#)

 [Safety Services](#)

Resolution	Protective Height (mm)	Area Beam Indicators	Part Number
14 mm	160	No	F3SG-4SRB0160-14
	320		F3SG-4SRB0320-14
	400		F3SG-4SRB0400-14
	480		F3SG-4SRB0480-14
	560		F3SG-4SRB0560-14
	640		F3SG-4SRB0640-14
	720		F3SG-4SRB0720-14-F
	1200		F3SG-4SRB1200-14
25 mm	360		F3SG-4SRB0360-25-F
	440		F3SG-4SRB0440-25-F
	600		F3SG-4SRB0600-25-F
	680		F3SG-4SRB0680-25-F
	760		F3SG-4SRB0760-25-F
	840		F3SG-4SRB0840-25-F
	920		F3SG-4SRB0920-25-F
	1000		F3SG-4SRB1000-25-F
	1200	F3SG-4SRB1200-25	
	1440	F3SG-4SRB1440-25	
1520	F3SG-4SRB1520-25		
1600	F3SG-4SRB1600-25		
1840	F3SG-4SRB1840-25		
14 mm	400	Yes	F3SG-4SRA0400-14
	560		F3SG-4SRA0560-14
	720		F3SG-4SRA0720-14-F
	880		F3SG-4SRA0880-14-F
	1200		F3SG-4SRA1200-14
25 mm	280		F3SG-4SRA0280-25-F
	440		F3SG-4SRA0440-25-F
	600		F3SG-4SRA0600-25-F
	760		F3SG-4SRA0760-25-F
	920		F3SG-4SRA0920-25-F
	1200	F3SG-4SRA1200-25	
	1600	F3SG-4SRA1600-25	
		F3SG-4SRA1760-25	

Note: Tables include representative part numbers. Please consult the product page for more details.

F3SG-PG - Perimeter Guard Safety Light Curtain

- Three-color Area Beam Indicators (ABIs) enable easy alignment and quick troubleshooting.
- Protection distance up to 110m
- Robust design for harsh environments (rated IP67G)
- IO-Link communication for remote monitoring



 [Product Page](#)

 [Safety Services](#)

Number of Beams	Beam Gap (mm)	Product Length (mm)	Protection Range (m)	Type	Part Number
2	500	670	up to 30m	Emitter/Receiver	F3SG-4PGA0670-2A
	500	670	up to 8m	Transceiver	F3SG-4PGA0670-2C
	500	670	up to 110m	Emitter/Receiver	F3SG-4PGA0670-2L
3	400	970	up to 30m	Emitter/Receiver	F3SG-4PGA0970-3A
	400	970	up to 110m	Emitter/Receiver	F3SG-4PGA0970-3L
4	300	1070	up to 30m	Emitter/Receiver	F3SG-4PGA1070-4A
	300	1070	up to 8m	Transceiver	F3SG-4PGA1070-4C
	300	1070	up to 110m	Emitter/Receiver	F3SG-4PGA1070-4L
	400	1370	up to 30m	Emitter/Receiver	F3SG-4PGA1370-4A
	400	1370	up to 8m	Transceiver	F3SG-4PGA1370-4C
	400	1370	up to 110m	Emitter/Receiver	F3SG-4PGA1370-4L

Note: Tables include representative part numbers. Please consult the product page for more details.



Safety Light Curtain Accessories and Cables

F3SG-SR/PG Brackets

Description	Part Number
Standard Bracket (non-adjustable)	F39-LSGF
Adjustable Side-Mount Bracket	F39-LSGA
Adjustable Top/Bottom Bracket (F3SJ, F3SN Adaptor)	F39-LSGTB-SJ
Adjustable Top/Bottom Bracket (F3SG-RA/RE Adaptor)	F39-LSGTB-RE
Adjustable Top/Bottom Bracket (MS4800, F3SR Adaptor)	F39-LSGTB-MS

F3SG-SR/PG Root Cables (plug into light curtain)

Description	Length	Emitter Part Number	Receiver Part Number
Root Cable to M12 connector (Standard)	0.3 m	F39-JGR3K-L	F39-JGR3K-D
Root Cable to Flying Leads	3m	F39-JG3C-L	F39-JG3C-D
Root Cable to Flying Leads	7m	F39-JG7C-L	F39-JG7C-D
Root Cable to Flying Leads	10m	F39-JG10C-L	F39-JG10C-D
Root Cable to M12 Connector (F3SJ-B/A, F3SR, or F3SN Conversion)	0.3 m	F39-JGR3K-SJ-L	F39-JGR3K-SJ-D
Root Cable to M12 Connector (F3SG-RE Conversion)	0.3 m	F39-JGR3K-RE-L	F39-JGR3K-RE-D
Root Cable to M12 Connector (MS4800 Conversion)	0.3 m	F39-JGR3K-MS-L	F39-JGR3K-MS-D

F3SG-SR/PG Extension Cables (plug into M12 Root Cable)

Description	Length	Emitter Part Number	Receiver Part Number
M12 to Flying Lead Extension Cable	3 m	F39-JG3A-L	F39-JG3A-D
M12 to Flying Lead Extension Cable	10 m	F39-JG10A-L	F39-JG10A-D
M12 to M12 Extension Cable	3 m	F39-JG3B-L	F39-JG3B-D
M12 to M12 Extension Cable	10 m	F39-JG10B-L	F39-JG10B-D
M12 to M12 Extension Cable	20 m	F39-JG20B-L	F39-JG20B-D

Note: Tables include representative part numbers. Please consult the product page for more details.

Safety Light Curtain Accessories and Cables

F3SG-SR Cascade Cables

Description	Length	Part Number
Side-by-Side Cascading Cable (2 cables per part number)	0.12 m	F39-JGR12L
Extension Cable for Cascading (2 cables per part number)	0.3 m	F39-JGR3W

F3SG-SR/PG IO-Link Cables

Description	Length	Part Number
NX-ILM400 IO-Link Cable	2 m	X55F-D521-DJ0-IL
GX-ILM08C IO-Link Cable	3 m	F39-JG3B-L
GX-ILM08C IO-Link Cable	10 m	F39-JG10B-L
GX-ILM08C IO-Link Cable	20 m	F39-JG20B-L

F3SG-SR/PG Wiring Reduction and Reset Cables

Description	Length	Part Number
Y-Joint Plug/Socket Connector	0.5 m	F39-GCNY2
Reset Switch Connector	0.5 m	F39-GCNY3
Reset Switch Connector to Reset Switch Cable	1 m	X55F-D421-C80-F
Reset Switch Connector to Reset Switch Cable	2 m	X55F-D421-D80-F
Reset Switch Connector to Reset Switch Cable	3 m	X55F-D421-E80-F
Reset Switch Connector to Reset Switch Cable	5 m	X55F-D421-G80-F
Reset Switch Connector to Reset Switch Cable	10 m	X55F-D421-J80-F
Reset Switch Connector to Reset Switch Cable	20 m	X55F-D421-L80-F

Note: Tables include representative part numbers. Please consult the product page for more details.

F3SG-SR/PG Accessories

F3SG-SR, F3SG-PG, and F3SG-R[] Floor Mount Columns

Applicable F3SG-SR/F3SG-R[] Light Curtain	Applicable F3SG-PG Light Curtain	Column Height	Part Number
Protective Height up to 880 mm	F3SG-4PGA0670-2[]	990 mm	F39-ST0990
Protective Height up to 1280 mm	F3SG-4PGA0970-3A/3L F3SG-4PGA1070-4[]	1310 mm	F39-ST1310
Protective Height up to 1520 mm	F3SG-4PGA1370-4[]	1630 mm	F39-ST1630
Protective Height up to 1840 mm	-----	1950 mm	F39-ST1950
Protective Height up to 2080 mm	-----	2270 mm	F39-ST2270

F3SG-SR, F3SG-PG, and F3SG-R[] Mirror Columns

Applicable F3SG-SR/F3SG-R[] Light Curtain	Applicable F3SG-PG Light Curtain	Column Height	Part Number
Protective Height up to 880 mm	F3SG-4PGA0670-2[]	990 mm	F39-SML0990
Protective Height up to 1200 mm	F3SG-4PGA0970-3A/3L F3SG-4PGA1070-4[]	1310 mm	F39-SML1310
Protective Height up to 1520 mm	F3SG-4PGA1370-4[]	1630 mm	F39-SML1630
Protective Height up to 1840 mm	-----	1950 mm	F39-SML1950
-----	F3SG-4PGA0670-2A/2L	990 mm	F39-PML0990-2
-----	F3SG-4PGA0970-3A/3L	1310 mm	F39-PML1310-3
-----	F3SG-4PGA1070-4A/4L	1310 mm	F39-PML1310-4
-----	F3SG-4PGA1370-4A/4L	1950 mm	F39-PML1630-4

Stand and Mirror Base Accessory

Description	Part Number
Adjustable and Rotatable Column Base	F39-STB

F3SG-SR and F3SG-PG Muting Accessories

Description	Length	Part Number
Through Beam Muting Sensor Mounting Arm	150 mm	F39-FMA150T
Through Beam Muting Sensor Mounting Arm	400 mm	F39-FMA400T
Retro-Reflective Muting Sensor Mounting Arm	150 mm	F39-FMA150R
Retro-Reflective Muting Sensor Mounting Arm	400 mm	F39-FMA400R
Muting Arm Bracket for F3SG-SR/PG Mounting	n/a	F39-LMAF1
Muting Sensor Connection Box	n/a	F39-GCN5

Note: Tables include representative part numbers. Please consult the product page for more details.

OS32C - Safety Laser Scanner

- 3m maximum safety zone and 15m warning zone
- Up to 70 different detection zones configurations
- Distance measurement capabilities up to 50m
- 5W power consumption



[Product Page](#)

[Safety Services](#)

Cable Outlet	Safety Range	Ethernet/IP Data	Part Number
Back	3m	No	OS32C-BP
	3m	Yes	OS32C-BP-DM
Side	3m	No	OS32C-SP1
	3m	Yes	OS32C-SP1-DM

OS32C Safety Laser Scanner Cables

Description	Length	Part Number
Power Cable	3 m	OS32C-CBL-03M
	10 m	OS32C-CBL-10M
	20 m	OS32C-CBL-20M
	30 m	OS32C-CBL-30M
Ethernet Cable	2 m	OS32C-ECBL-02M
	5 m	OS32C-ECBL-05M
	15 m	OS32C-ECBL-15M

OS32C Safety Laser Scanner Brackets

Description	Part Number
Bottom/Side Mounting Bracket	OS32C-BKT1
XY Axis Rotation Mounting Bracket	OS32C-BKT2
Simple Mounting Bracket	OS32C-BKT3
Protective Cover for Window	OS32C-BKT4
Mounting Stand	OS32C-MT
Hardware kit for Mounting Stand	OS32C-HDT

OS32C Spare/Replacement Parts

Description	Part Number
Scan Window	OS32C-WIN-KT
Sensor block without I/O 3m Range	OS32C-SN
Sensor block without I/O 3m Range, Ethernet/IP	OS32C-SN-DM
I/O Block with Back Cable Access	OS32C-CBBP
I/O Block with Side Cable Access	OS32C-CBSP1

Note: Tables include representative part numbers. Please consult the product page for more details.

G9SE - Safety Relays

- A compact safety relay for simple safety applications, with screwless terminals and increased diagnostic capabilities for fast troubleshooting and easy wiring
- Modules with two or four safety contacts and OFF-delay timing options
- Compact units, 17.5 or 22.5 mm wide
- Front side wiring using screw less terminals and led indicators for fast diagnostic



 [Product Page](#)

 [Safety Services](#)

Safety Outputs	Auxiliary Output	OFF-delay Max. time	Power	Model
2	1	-	24VDC	G9SE-201
4		-		G9SE-401
2		5 s		G9SE-221-T05
2		30 s		G9SE-221-T30

Note: Tables include representative part numbers. Please consult the product page for more details.

G9SA - Expandable Safety Relay

- All-purpose expandable safety relays series ideal for high demand applications.
- Ideal for high demand applications.
- Expandable outputs options only, up to 8: instantaneous or time-delay
- Simple expansion connection available



[Product Page](#)

[Safety Services](#)

Safety Outputs	Auxiliary Outputs	Power	Model
3	1	24VDC	G9SA-301 AC/DC24
5	1		G9SA-501 AC/DC24
3	1		G9SA-EX301
3	1		G9SA-TH301 AC/DC24*

*Two hand controller (type III C, EN 574)

Note: Tables include representative part numbers. Please consult the product page for more details.

G9SX - Safety Modules

- A versatile safety relay series, ideal for scalable safety solution, support logical “AND” functions for expansion and offer special modules for dedicated safety functions
- G9SX-family modules can be connected by a logical “AND” function to implement partial/global stopping of a machine
- Solid-state outputs, detailed LED diagnosis and clever feedback signals help to keep maintenance easy
- Expansion units with safe timing functions complete the line-up



 [Product Page](#)

 [Safety Services](#)

Terminal Block Type	Safety Output Instantaneous	Safety Output – Off-Delayed	Safety Standstill detection output	Safety slow-speed/ stopping detection output	Auxiliary Outputs	Power	Model
Screw Terminal	2	0	0	0	2	24VDC	G9SX-BC202-RT DC24
Spring-cage terminals	3	2	0	0	2		G9SX-AD322-T15-RC DC24*
Screw Terminals	0	0	3	0	2		G9SX-SM032-RT
Screw Terminals	2	0	0	2	4		G9SX-LM224-F10-RT **
Screw Terminals	2	0	0	0	2		G9SX-NS202-RT DC24 ***
Screw Terminals	2	2	0	0	2		G9SX-NSA222-T03-RT DC24

*Off-Delay:

T15: 0/0.2/0.3/0.4/0.5/0.6/0.7/1/1.5/2/3/4/5/7/10/15 s

T03: 0/0.2/0.3/0.4/0.5/0.6/0.7/0.8/0.9/1.0/1.2/1.4/1.8/2.0/2.5/3.0 s

** Safe Standstill monitoring unit based on Back EMF operation for two and three phase systems.

*** Limited speed monitoring unit

Note: Tables include representative part numbers. Please consult the product page for more details.

D41D - High-Coded Non-Contact Safety Door Switch

- Type 4 High-coded door switch, RFID
- Easy and quick automatic pairing with Individual coding, single or multiple teaching type
- Three sizes of actuator, including flat and miniature to fit in narrow spaces or inside corners
- Symmetrical design for left and right mounting
- Approach direction can be either from the front or side
- Extensive diagnostic via a three-color LED indicators and diagnostic output
- Up to 31 safety door switches from D41 Series can be connected


 [Product Page](#)
 [Safety Services](#)

Sensor	Part Number	Coding Level	Connector
Sensor	D41D-1CD-N1	High, Individual coding	M8 connector
	D41D-2CD-025N2	High, Individual coding with no limitation	M12 with 250 mm cable
Part Number		Type	Dimensions
Actuator ¹	D41D-A1	Standard	W x D x H= 39 x 29.5 x 18 (mm)
	D41D-A2	Flat	W x D x H= 60 x 16 x 6.8 (mm)
	D41D-A3	Miniature	W x D x H= 22 x 9 x 7 (mm)

1. Actuators sold separately

Accessories

	Part Number	Description
Cables	D41D-8P5-CFM8-702M	Cable, 2m, M8 connector, IP67
	D41D-8P5-CFM8-705M	Cable, 5m, M8 connector , IP67
	D41D-8P5-CFM8-710M	Cable, 10m, M8 connector , IP67
	D41L-8P5-CFM12-905M	Cable, 5m, M12 connector, IP69
	D41L-8P5-CFM12-910M	Cable, 10m, M12 connector, IP69
Sealing Kits	D41D-SK	Seal mounting holes. Contains: 4 flat plugs and 4 plugs with rim for high screw head
Mounting Kits	D41D-MS	Contains: 2 mounting plates and 4 ferrule plugs

Note: Tables include representative part numbers. Please consult the product page for more details.

D41L - Type 4 High-Coded Guard Lock Switch

- Type 4 High-coded door switch, RFID
- Easy and quick automatic pairing with Individual coding, single or multiple teaching type
- Improved hygiene: resistant to wide range of cleaning agents, easy to clean
- Protection class IP66, IP67 and IP69 and ECOLAB certified
- Large actuator tolerances and easy latching force adjustment
- Power to lock or power to unlock versions with optional emergency exit
- 3 actuating directions with identical mounting for left and right hinged doors



 [Product Page](#)

 [Safety Services](#)

- 3 LED indicators for smart diagnostics
- Star handle instead of key hole to prevent water and foreign material to collect
- Device can be used as an end stop for sliding door applications
- Up to 31 devices connected in series

Part Number	Lock and Release	Teaching	OSSD Configuration	Connection Method
D41L-1YDG-N2	Power to lock (solenoid lock)	Individual coding, single teaching	Guard monitoring and lock monitoring	No
D41L-2YDG-N2		Individual coding, multiple teaching	Only guard monitoring	Yes
D41L-2ZDGE-N2				No
D41L-1ZDA-N2	Power to unlock (mechanical release)	Individual coding, single teaching	Guard monitoring and lock monitoring	No
D41L-2YDA-N2		Individual coding, multiple teaching		Yes
D41L-2YDAE-N2				
Part Number	Description			
Actuator¹	D41L-A1	Compatible with D41L models		

1. Actuators sold separately

Accessories

	Part Number	Description
Cables	D41L-8P5-CFM12-905M	Cable, 5m, M12 connector, IP69
	D41L-8P5-CFM12-910M	Cable, 10m, M8 connector, IP69
Mounting Plate	D41L-MP	Mounting plate for sensor only
Mounting Set	D41L-MS	Mounting set for actuator only

Note: Tables include representative part numbers. Please consult the product page for more details.

D41G - Type 4 High-Coded Guard Lock Switch

- Type 4 High-coded door switch, RFID
- Easy and quick automatic pairing with individual coding, single or multiple teaching type
- Power to lock and power to unlock versions available
- OSSD configuration for guard monitoring only or guard and lock monitoring
- Extensive diagnostic via a three-color LED indicators and diagnostic output
- Easily mounted to standard aluminum profile systems
- Up to 31 devices connected in series



[Product Page](#)

[Safety Services](#)

	Part Number	Lock and Release	Teaching	OSSD Configuration	Connection Method
Sensor ¹	D41G-1YDA-N2	Power to unlock	Individual coding, single teaching	Guard monitoring and lock monitoring	M12 connector
	D41G-2YDA-N2	Power to unlock	Individual coding, multiple teaching		
	D41G-2YDG-N2	Power to lock			
	D41G-2YDG-N2	Power to lock			
	D41G-2YDG-T1	Power to lock		Only guard monitoring	Screw Terminal
	D41G-2ZDA-T1	Power to unlock			

1. Actuators sold separately

Accessories

	Part Number	Description
Cables	D41L-8P5-CFM12-905M	Cable, 5m, M12 connector, IP69
	D41L-8P5-CFM12-910M	Cable, 10m, M8 connector, IP69

Note: Tables include representative part numbers. Bold models: Preferred Availability. Please consult the product page for more details.

D41G Actuators

- Actuators for right and left hinged doors with door handle and optional emergency exit and lock-out tag as well as options available for sliding doors
- Actuators for right and left sliding doors



[Product Page](#)

[Safety Services](#)


Actuator Type ¹	Part Number	Handle Position	Emergency Exit Unit	Lock-out option
With door handle	D41G-A2L-E1	Left	Yes	-
	D41G-A2L-E1T		Yes	Yes
	D41G-A2R-E1	Right	Yes	-
	D41G-A2R-E1T		Yes	Yes
Non door handle	D41G-A1L	Left	-	-
	D41G-A1R	Right	-	-

1. Actuators sold separately

Note: Tables include representative part numbers. Bold models: Preferred Availability. Please consult the product page for more details.

D40P - Non-Contact Safety Switches

- Hall effect technology provides solid state outputs for increased longevity
- LED indicates operation state
- Operates with all OMRON safety controllers and safety relays
- Connect up to 20 switches in series, up to PLd acc. EN ISO 13849-1



[Product Page](#)

[Safety Services](#)

Body Size	Housing	Contacts	Cable Connection	Model
Elongated	Polyester Housing	2NC / 1NO	M12, 8 pin, fitted with 250 mm cable	D40P-LPC-21-M12
Small			M12, 8 pin, fitted with 250 mm cable	D40P-SPC-21-M12
Barrel			5 m pre-wired	D40P-BPC-21-05
Small	Stainless Steel		5 m pre-wired	D40P-SMC-21-05
Small	Hygienic	2NC / 1NO	M12, 8 pin, fitted with 250 mm cable	D40P-SHC-21-M12

Accessories

Type	Description	Model
Cables, M12 female - 8 pin to flying leads	5m	D40ML-CBL-M12-5M
Cables, M12 female - 8 pin to flying leads	10m	D40ML-CBL-M12-10M
T-Connector Connection Cable	T-Connector for M12 cable	D40P-8PTC-M12

D40ML - RFID Magnetic Locking Safety Switch

- Magnetic latching combines with RFID technology to deliver high holding force and tamper resistance
- Residual magnetism acts as light door latch after unlocking and it provides multiple holding forces
- Clean/Sanitize in Place – stainless steel versions are rated IP69K
- For use on machines with no rundown time if power is lost



[Product Page](#)

[Safety Services](#)

Actuator Type	Case Material	Holding Force	Cable Connection	Model
Basic	Diecast Metal (IP67)	1500N	Pigtail w/ M12 Connector	D40ML-M1-B-M12
Basic	Plastic (IP67)	1500N		D40ML-P1-B-M12
Basic	316 Stainless Steel (IP69K)	950N		D40ML-SS1-B-M12
Unique	316 Stainless Steel (IP69K)	600N	5m Cable	D40ML-SS2-U-5M

Accessories

Type	Description	Model
Cables, M12 female - 8 pin to flying leads	5m	D40ML-CBL-M12-5M
Cables, M12 female - 8 pin to flying leads	10m	D40ML-CBL-M12-10M

Note: Tables include representative part numbers. Please consult the product page for more details.

D4SL-N - Guard Lock Safety Door Switch

- A wide variety of built-in switches can be used for various devices (4-, 5-, and 6-contact models are available)
- Removable terminal block for easy wiring and quick maintenance
- Key holding force of 1,300N
- Slide key available to prevent workers from becoming trapped inside the hazardous area
- Can be easily mounted on 40 × 40 mm aluminum frames



[Product Page](#)

[Safety Services](#)

Type	Conduit Size	Contact Model	Head Material	Door Lock and Release	Indicator	Model
D4SL-N	1/2-14NPT *	2NC/1NO + 2NC/1NO	Metal	Mechanical lock/24VDC solenoid release	Yes	D4SL-N3NDA-D
	1/2-14NPT *	2NC/1NO + 2NC/1NO	Metal	24VDC solenoid lock/mechanical release	Yes	D4SL-N3NDG-D
	M20	3NC + 1NC/1NO	Resin	Mechanical lock/24VDC solenoid release	Yes	D4SL-N4GFA-D
	G1/2	2NC/1NO + 2NC/1NO	Resin	Mechanical lock/24VDC solenoid release	Yes	D4SL-N2NFA-D4

* M20, includes M20-to-1/2-14NPT conversion adapter.

Slides Key for D4SL

- Lockout Key to prevent workers from becoming trapped inside the hazardous area
- The plastic material makes the Slide Key suitable for lightweight doors



[Product Page](#)

[Safety Services](#)

Description	Model
Slide Key Kit	D4SL-NSK10-LK
Slide Key with inner lever	D4SL-NSK10-LKH

Operation Keys for D4SL

Mounting Orientation	Special Function	Model
Horizontal	-	D4SL-NK1
Horizontal	Rubber cushions	D4SL-NK1G
Vertical	-	D4SL-NK2
Horizontal	Adjustable	D4SL-NK3

Note: Tables include representative part numbers. Please consult the product page for more details.

PMAC Motion Controllers CK3 Series CK3E - EtherCAT Based Controllers

- 32, 16 or 8 axes motion control
- Up to 250 μs cycle time
- Compatible with standard G-Code functions
- Save space & wiring thanks to compact design
- CAD/CAM for easy motion control
- EtherCAT for flexible configuration



[Product Page](#)

[Training Services](#)

Number of Axis	Memory capacity	Programming language	Model
8	1G	G-Code/ANSI C/original programming language	CK3E-1210
16			CK3E-1310
32			CK3E-1410

By combining global leading Delta Tau Data Systems' Motion Control technologies, Omron can open up new applications and solutions. The CK3E is a controller designed for precise multi-axis control. You can build a system capable of controlling up to 32 axes of motion and incorporate customized control algorithms into the system. The CK3E allows you to program in C language and reuse existing software assets. The compact design saves space in machines and control panels. EtherCAT® connects servo drives, I/O, and other devices to the CK3E, reducing the number of cables.

CK3M - Modular Controllers

- Local axes for nanoscale precision
- Ultra high-speed synchronous control (50μs/5 axes)
- Custom servo regulation algorithms
- Flexibility on using multi-vendor actuators and encoders
- Flexibility on programming on G-code, ANSI C or original programming language



[Product Page](#)

[Training Services](#)

Product Type	Memory capacity	EtherCAT® port	EtherCAT Axes	Expansion	Model
CPU Units	RAM: 1 GB Built-In flash memory: 1 GB	-	-	One expansion rack can be connected using the expansion master unit and expansion slave unit	CK3M-CPU101
		EtherCATEtherCAT®: 1 port (DC sync)	4 8		CK3M-CPU111 CK3M-CPU121
	RAM: 2 GB Built-in flash memory: 4 GB	EtherCATEtherCAT®: 1 port (DC sync)	16 32		CK5M-CPU131 CK5M-CPU141

Maximize your machine's performance: Performing precise linear motor drive control and nanoscale positioning, the PMAC (Programmable Multi Axis Controller) has been appreciated by manufacturers of semiconductor manufacturing equipment and other leading-edge equipment. Omron now offers a next generation motion controller CK3M that packs PMAC's superior motion control capability, multi-vendor connectivity, and flexible development capability into its compact design. The CK3M removes constraints and barriers and maximizes your machine's capabilities.

Note: Tables include representative part numbers. Please consult the product page for more details.



Product Type	Amplifier interface	Encoder interface	Output type	Model
Axial Interface Units	DirectPWM output	Digital quadrature encoder/serial encoder	NPN type	CK3W-AX1313N
	DA output (Filtered PWM)			CK3W-AX1414N
	DA output (True DAC)			CK3W-AX1515N
	DirectPWM output	Sinusoidal encoder/Serial encoder		CK3W-AX2323N
	DirectPWM output	Digital quadrature encoder/serial encoder	PNP type	CK3W-AX1313P
	DA output (Filtered PWM)			CK3W-AX1414P
	DA output (True DAC)			CK3W-AX1515P
	DirectPWM output	Sinusoidal encoder/Serial encoder		CK3W-AX2323P

Product Type	Feedback interface	Output type	TCR Output	Model
Laser Interface Units	XY2-100	PWM output		CK3W-GC1100
			TCR Output	CK3W-GC1200
	SL2-100			CK3W-GC2100
			TCR Output	CK3W-GC2200

Product Type	Feedback interface	Feedback type	Number of channels	Model
Serial Encoder Interface Unit	Serial Encoder	BiSS-C, Endat2.2, and 1S Motor	4	CK3W-ECS300

Product Type	Description	Model
Power Supply Unit	Rated output voltage: 5 VDC / 24 VDC	CK3W-PD048

Product Type	Number of inputs	Number of outputs	I/O type	Model
Digital I/O Units	16 points	16 points	NPN	CK3W-MD7110
			PNP	CK3W-MD7120



Product Type	Input Range	Number of inputs	Model
Analog Input Units	Unit -10 to 10 V	4 points	CK3W-AD2100
		8 points	CK3W-AD3100

Product Type	Product Name	Function	Model
Expansion Master Unit and Expansion Slave Unit	Expansion Master Unit	Expansion Master Unit connects to the right side of the CPU Unit	CK3W-EXM01
	Expansion Slave Unit	Expansion Slave Unit connects to the right side of the Power Supply Unit	CK3W-EXS02
	Expansion cable	To connection between the Expansion Master Unit and Slave Unit (0.3m)	CK3W-CAX003A

Note: Tables include representative part numbers. Please consult the product page for more details.

CK3C - Compact PMAC Controller

- ARM Dual Core 1GHz Processor
- Memory: 1GB RAM, 1GB Flash
- Local/direct amplifier interface as well as EtherCAT
- Multiple encoder interfaces available with ACC modules
- On Borad IO available with ACC modules
- EtherCAT for flexible configuration


 [Product Page](#)
 [Training Services](#)

Model	Analog I/O	Ethernet Port(s)	EtherCAT License	Extended Pin
CK3C-AX1100	No	1	No	No
CK3C-AX1100E	No	1	No	Yes
CK3C-AX1201	"4x 16-bit AI 1x Filtered PWM AO "	2	No	No
CK3C-AX1201E	"4x 16-bit AI 1x Filtered PWM AO "	2	No	Yes
CK3C-AX1211	"4x 16-bit AI 1x Filtered PWM AO "	2	I/O Only	No
CK3C-AX1211E	"4x 16-bit AI 1x Filtered PWM AO "	2	I/O Only	Yes
CK3C-AX1231	"4x 16-bit AI 1x Filtered PWM AO "	2	8 Servo	No
CK3C-AX1231E	"4x 16-bit AI 1x Filtered PWM AO "	2	8 Servo	Yes

Model	Analog I/O	
ACC-24S3	3-4050000-000-000000	4-Channel expansion
	3-4050000-000-010000	4-Channel expansion with 4 analog inputs & 1 Filtered PWM output
ACC-51S	3-3674-0-0002-000000	2 channel 4096x interpolator board for sinusoidal encoders
	3-3674-0-0012-000000	4 channel 4096x interpolator board for sinusoidal encoders
ACC-84S	3-3936-0-0002-000000	4-Channel SSI serial encoder protocol
	3-3936-0-0003-000000	4-Channel ENDAT serial encoder protocol
	3-3936-0-0006-000000	4-Channel Yaskawa Sigma II & III serial encoder protocol
	3-3936-0-0008-000000	4-Channel Panasonic serial encoder protocol
	3-3936-0-000D-000000	4-Channel Mitsubishi serial encoder protocol
	3-3936-0-000E-000000	4-Channel 1S serial encoder protocol
	3-3936-0-0TBC-000000	4-Channel table based compare protocol
	3-3936-0-0XY2-000000	XY2-100 serial link for 2-axis and 3-axis laser scan heads and galvanometers
ACC-8AS	3A0-603673-10X	4-Channel dual 16-bit DAC analog board
ACC-8FS	3F0-603673-10X	4-Channel direct PWM breakout board
Breakout Board	CBB4-00-000-000-1000	CK3C breakout board with separate connectors for each encoder, each flag set, and servo amplifier output


Note: Tables include representative part numbers. Please consult the product page for more details.

Power PMAC IDE (Integrated Development Environment)

- Based on Microsoft® Visual Studio®
- ANSI C or original programming language
- Easy tuning
- Simple setting
- Troubleshooting
- Debugger



 [Product Page](#)

 [Training Services](#)

Note: Tables include representative part numbers. Please consult the product page for more details.

1S Series - Servomotor

- Advanced design allows easy installation and wiring
- EtherCAT communications up to 125µsec
- Safety over the EtherCAT network
- Motor has 23-bit battery less absolute encoder
- 350% momentary torque (200 V, 750 W max.)



[Product Page](#)

[Training Services](#)

[Servo Tuning](#)

RPM	Capacity	Torque	Motor	Drive	Motor	Drive
			100V VAC		480V VAC	
3000 RPM	0.05 kW	0.159 Nm	R88M-1M05030S-(1)S2	R88D-1SN01L-ECT		
	0.1 kW	0.318 Nm	R88M-1M10030S-(1)S2	R88D-1SN01L-ECT		
	0.2 kW	0.637 Nm	R88M-1M20030S-(1)S2	R88D-1SN02L-ECT		
	0.4 kW	1.27 Nm	R88M-1M40030S-(1)S2	R88D-1SN04L-ECT		
			200V VAC			
	0.05 kW	0.159 Nm	R88M-1M05030T-(1)S2	R88D-1SN01H-ECT		
	0.1 kW	0.318 Nm	R88M-1M10030T-(1)S2	R88D-1SN01H-ECT		
	0.2 kW	0.637 Nm	R88M-1M20030T-(1)S2	R88D-1SN02H-ECT		
	0.4 kW	1.27 Nm	R88M-1M40030T-(1)S2	R88D-1SN04H-ECT		
	0.75 kW	2.39 Nm	R88M-1M75030T-(1)S2	R88D-1SN08H-ECT	R88M-1L75030C-(1)S2	R88D-1SN10F-ECT
	1.0 kW	3.18 Nm	R88M-1L1K030T-(1)S2	R88D-1SN10H-ECT	R88M-1L1K030C-(1)S2	R88D-1SN10F-ECT
	1.5 kW	4.77 Nm	R88M-1L1K530T-(1)S2	R88D-1SN15H-ECT	R88M-1L1K530C-(1)S2	R88D-1SN15F-ECT
	2.0 kW	6.37 Nm	R88M-1L2K030T-(1)S2	R88D-1SN20H-ECT	R88M-1L2K030C-(1)S2	R88D-1SN20F-ECT
	3.0 kW	9.55 Nm	R88M-1L3K030T-(1)S2	R88D-1SN30H-ECT	R88M-1L3K030C-(1)S2	R88D-1SN30F-ECT
	4.0 kW	12.7 Nm	R88M-1L4K030T-(1)S2	R88D-1SN55H-ECT	R88M-1L4K030C-(1)S2	R88D-1SN55F-ECT
	4.7 kW	15.0 Nm	R88M-1L4K730T-(1)S2	R88D-1SN55H-ECT		
5.0 kW	15.9 Nm			R88M-1L5K030C-(1)S2	R88D-1SN55F-ECT	
2000 RPM	0.4 kW	1.91 Nm			R88M-1M40020C-(1)S2	R88D-1SN06F-ECT
	0.6 kW	2.86 Nm			R88M-1M60020C-(1)S2	R88D-1SN06F-ECT
	1.0 kW	4.77 Nm	R88M-1M1K020T-(1)S2	R88D-1SN10H-ECT	R88M-1M1K020C-(1)S2	R88D-1SN10F-ECT
	1.5 kW	7.16 Nm	R88M-1M1K520T-(1)S2	R88D-1SN15H-ECT	R88M-1M1K520C-(1)S2	R88D-1SN15F-ECT
	2.0 kW	9.55 Nm	R88M-1M2K020T-(1)S2	R88D-1SN20H-ECT	R88M-1M2K020C-(1)S2	R88D-1SN20F-ECT
	3.0 kW	14.3 Nm	R88M-1M3K020T-(1)S2	R88D-1SN30H-ECT	R88M-1M3K020C-(1)S2	R88D-1SN30F-ECT
1500 RPM	4 kW	25.5 Nm	R88M-1M4K015T-(1)S2	R88D-1SN55H-ECT	R88M-1M4K015C-(1)S2	R88D-1SN55F-ECT
	5.0 kW	31.8 Nm	R88M-1M5K015T-(1)S2	R88D-1SN55H-ECT		
	5.5 kW	35 Nm			R88M-1M5K515C-(1)S2	R88D-1SN55F-ECT
	7.5kW	47.8 Nm	R88M-1M7K515T-(1)S2	R88D-1SN75H-ECT	R88M-1M7K515C-(1)S2	R88D-1SN75F-ECT
	11 kW	70 Nm	R88M-1M11K015T-(1)S2	R88D-1SN150H-ECT	R88M-1M11K015C-(1)S2	R88D-1SN150F-ECT
1000 RPM	15 kW	95.5 Nm	R88M-1M15K015T-(1)S2	R88D-1SN150H-ECT	R88M-1M15K015C-(1)S2	R88D-1SN150F-ECT
	0.9 kW	8.59 Nm	R88M-1M90010T-(1)S2	R88D-1SN10H-ECT	R88M-1M90010C-(1)S2	R88D-1SN10F-ECT
	2.0 kW	19.1 Nm	R88M-1M2K010T-(1)S2	R88D-1SN20H-ECT	R88M-1M2K010C-(1)S2	R88D-1SN20F-ECT
	3.0 kW	28.7 Nm	R88M-1M3K010T-(1)S2	R88D-1SN30H-ECT	R88M-1M3K010C-(1)S2	R88D-1SN30F-ECT

Note: (1) B - Motor with brake WHITE - Without brake

Note: Tables include representative part numbers. Please consult the product page for more details.

1SA Series - Servomotor & Drive

- PLe/SIL3 safety functions
- STO, SS1, SS2, SOS, SLS, SLP, SDI, & SBC
- Drive with EtherCAT Communication
- Single cable design
- Right angle, rotatable, connector on motor
- Absolute encoder without the need for battery



[Product Page](#)

[Servo Tuning](#)

RPM	Capacity	Torque	Motor	Drive	Motor	Drive
			200V VAC		400V VAC	
3000 RPM	0.2 kW	0.637 Nm	R88M-1AM20030T-(1)S2	R88D-1SAN02H-ECT		
	0.4 kW	1.27 Nm	R88M-1AM40030T-(1)S2	R88D-1SAN04H-ECT		
	0.75 kW	2.39 Nm	R88M-1AM75030T-(1)S2	R88D-1SAN08H-ECT	R88M-1AL75030C-(1)S2	R88D-1SAN10F-ECT
	1.0 kW	3.18 Nm	R88M-1AL1K030T-(1)S2	R88D-1SAN10H-ECT	R88M-1AL1K030C-(1)S2	R88D-1SAN10F-ECT
	1.5 kW	4.77 Nm	R88M-1AL1K530T-(1)S2	R88D-1SAN15H-ECT	R88M-1AL1K530C-(1)S2	R88D-1SAN15F-ECT
	2.0 kW	6.37 Nm	R88M-1AL2K030T-(1)S2	R88D-1SAN20H-ECT	R88M-1AL2K030C-(1)S2	R88D-1SAN20F-ECT
	2.6 kW	8.28 Nm	R88M-1AL2K630T-(1)S2	R88D-1SAN30H-ECT		
1500 RPM	3.0 kW	9.55 Nm			R88M-1AL3K030C-(1)S2	R88D-1SAN30F-ECT
	1.5 kW	9.55 Nm	R88M-1AM1K515T-(1)S2	R88D-1SAN15H-ECT	R88M-1AM1K515C-(1)S2	R88D-1SAN15F-ECT
	2.7 kW	17.2 Nm	R88M-1AM2K715T-(1)S2	R88D-1SAN30H-ECT		
	3.0 kW	19.1 Nm			R88M-1AM3K015C-(1)S2	R88D-1SAN30F-ECT

Note: (1) B - Motor with brake WHITE - Without brake

Note: Tables include representative part numbers. Please consult the product page for more details.

LD Series – Autonomous Mobile Robots

- Simplified programming and navigation using digital mapping
- In compliance with safety standards ISO 12100, ISO 14121-2 and ISO 13849-1
- Rechargeable battery with autonomy of 12 to 15 hours and self-management for recharging
- Connectivity with factory management software (MES/WMS)
- Cleanroom and ESD options available



Product Page



Product Video



Training Services



Service Contracts

Part Number Configurator

37□□2-□
(1) (2) (4)

No.	Item	Specification		Symbol
1	Robot Type	LD 60/LD 90		0
		LD 250		2
2	Speed & Payload	0.9m/s (Excludes LD 250)	90Kg (LD90)	6
		1.2m/s (LD 250 Only)	250Kg	2
		1.3m/s (Excludes LD 250)	90Kg (LD90)	4
		1.8 m/s/ (LD 60 Only)	60Kg	3
3	Configuration	Standard LD60 / LD 90 / LD 250	Robot	00000
			Robot, Dock	00002
			Robot, Dock, Joystick, Top Plate	10004
		ESD	Robot	20000
			Robot, Dock	20002
			Robot, Dock, Joystick, Top Plate	20004

Accessories¹

Item	Description	Model
Battery ²	Power battery	20452000
Fleet Manager	Primary Fleet Manager	20271-900
	Secondary Fleet Manager (Backup Unit)	20271-901
Fleet Simulator	Simulation of up to 10 AMRs	20271-903
FLOW iQ	Analytics and visualization of fleet operations (5yr)	20271-705
Cell Alignment Positioning System (CAPS)	Improved positioning of AMRs for high accuracy applications (Sold per AMR)	20271-805

1. Additional accessories available, contact your Omron Sales Representative for additional details

2. The battery 20452000 must be purchased separately

Note: Tables include representative part numbers. Please consult the product page for more details.

MD Series - Autonomous Mobile Robots



- Natural feature navigation: Automatically plans efficient routes and prevents collisions
- Fleet management: Operates in coordination with an entire fleet of Omron AMRs
- Easy deployment: Installs quickly, without facility modifications
- 650 & 900 Kg capacity payloads
- Dynamic intelligent 360° safety with automatic footprint switching
- Integrated automation controller

- [Product Page](#)
- [Product Video](#)
- [Training Services](#)
- [Service Contracts](#)

Model	Max Payload	Pendant	Charging Station	Battery	Part Number
MD-650	650kg	No	No	No	37350-10000
		No	Yes	No	37350-10002
		Yes	Yes	No	37350-10004
MD-900	900kg	No	No	No	37370-10000
		No	Yes	No	37370-10002
		Yes	Yes	No	37370-10004

Accessories¹

Item	Description	Model
Battery ²	Power battery	73330-100
Power Supply Box	Power battery Supplies power to the Charging Dock for charging MD and HD AMRs	73990-000
Charging Dock	Supports docking (charging) for both MD Series and HD Series AMRs	68910-000
Fleet Management	Primary Fleet Manager	20271-900
	Secondary Fleet Manager (Backup Unit)	20271-901
Fleet Simulator	Simulation of up to 10 AMRs	20271-903
FLOW iQ	Analytics and visualization of fleet operations (5yr)	20271-705
Cell Alignment Positioning System (CAPS)	Improved positioning of AMRs for high accuracy applications (Sold per AMR)	20271-805

1. Additional accessories available, contact your Omron Sales Representative for additional details
 2. Vehicle Battery (68330000) must be purchased separately from the robot and is shipped separate from the HD Vehicle.

Note: Tables include representative part numbers. Please consult the product page for more details.

Omron TM - Collaborative Robots

- Designed to promote a safe and harmonious workplace between humans and machines.
- Easy-to-use graphical programming environment for quick startup and operation.
- Built-in vision-based robot control enables visual servoing, inspection, and measurement operations.
- TMvision and landmark allows truly flexible, fast changeover.



- [Product Page](#)
- [Product Video](#)
- [Training Services](#)
- [Service Contracts](#)

Part Number Configurator RT6-
 (1) (2) (3) (4) (5) (6) (7) (8)

No.	Item	Specifications	Symbol
(1)	Omron TM Collaborative Robots		
(2)	Model Type	TM5	0
		TM12	1
		TM14	2
		TM16	3
		TM20	4
(3)	Power Supply	AC	0
		DC	1
(4)	Vision System	Integrated Camera	0
		No Camera (X Model)	1
(5)(6)	Arm Length	700	70
		900	90
		1100	11
		1300	13
(7)	Configuration	Standard	0
		Semi S2 Certification	1
		Standard with Ethernet/IP and PROFINET (Fieldbus)	2
		Food Grade Grease	3"
		Food Grade Grease with Ethernet/IP and PROFINET (Fieldbus)	4"
(8)	Cable Length	Standard Length (3m/1.5m)*	1
		Extended Length (12m)*	2

Note: 1.5m cable is only standard on DC models. 12m cable is not available on DC models.

Accessories¹

Type	Notes	Model
Landmark	3D position referencing label (2 units included in the robot code)	RT6-A000021
Mobile Station	Compatible with OMRON TM5 only	RT6-A000010
Portable Pedestal	Compatible only with OMRON TM5/Adjustable Height	RT6-A000009
SSD Card with cable	128 GB of memory with SATA cable	RT6-A000012
Calibration kit	Required for TCP calibration and manual vision	RT6-A000002
Pneumatic Box	Recommended to attach to the robot pedestal	RT6-A000015
Polarizer Light Module	Not compatible with OMRON TM S Series	RT6-A000022

1. Additional accessories available, contact your Omron Sales Representative for additional details

Note: Tables include representative part numbers. Please consult the product page for more details.

Omron TMS - Collaborative Robots

- Advanced hardware options and expanded safety features
- 31 safety functions, all ISO 13849-1, Cat.3, PLd, certified
- Easy-to-use programming interface (Flowchart and Script programming language available)
- Anti cutting oil corrosion joint covers
- Include all the built-in vision and landmark capabilities of standard Omron TM Cobots



Part Number Configurator RT6- □□□□□□□□
 (1) (2) (3) (4) (5) (6) (7) (8)

No.	Item	Specifications	Symbol
(1)		Omron TM Collaborative Robots	
(2)	Model Type	TM5S	0
		TM7S	6
		TM12S	1
		TM14S	2
(3)	Power Supply	AC	0
		DC	1
(4)	Vision System	Integrated Camera	0
		No Camera (X Model) ¹	1
(5)(6)	Arm Length	700	70
		900	90
		1100	11
		1300	13
(7)	Configuration	Standard	0
		Semi S2 Certification ²	1
		Standard with Ethernet/IP and PROFINET (Fieldbus)	2
		Semi S2 Certification with EtherNet/IP and PROFINET (Fieldbus)	5
(8)	Cable Length	Standard Length (3m/1.5m) ³	4
		Extended Length (12m) ³	5

1. Not available for DC versions.
 2. Available for TM12S and TM14S only.
 3. 1.5m cable is only standard on DC models. 12m cable is not available on DC models.

Accessories⁴

Type	Notes	Model
Landmark	3D position referencing label (2 units included in the robot code)	RT6-A000021
Mobile Station	Compatible with OMRON TM5S, TM7S, TM5-700, and TM5-900	RT6-A000010
Portable Pedestal	Compatible only with OMRON TM5/Adjustable Height	RT6-A000009
SSD Card with cable	128 GB of memory with SATA cable	RT6-A000012
Calibration kit	Required for TCP calibration and manual vision	RT6-A000002
Polarizer Light Module	Not compatible with OMRON TM S Series	RT6-A000022

4. Additional accessories available, contact your Omron Sales Representative for additional details


Note: Tables include representative part numbers. Please consult the product page for more details.

TMFlow - Omron TM Collaborative Robot Software

- Intuitive, graphical programming enables users to create complex robot solutions without requiring extensive training or programming experience
- Built-in vision-based robot tasks including barcode scanning, pattern matching, and fiducial mark matching are simple to integrate into a project
- Landmarks can be used as reference points for the robot, allowing the robot to be flexibly relocated between workstations while minimizing changeover times
- The Plug & Play ecosystem of tools and peripherals can quickly and easily be configured within TMFlow



 [Product Page](#)

 [Training Services](#)

Part Numbers

Product Name	Add-On Product Names	Remarks	Part Number	Add-On Part Numbers
USB Dongle	—	Required for all extra software licenses.	RT6-A000004	—
TMFlow	—	Software required to control the cobot. Free download.	—	—
	TM Identify & Measure	License, add-on to TMFlow. Includes: Identification of pose variation, specific color area size, subtract reference image, line/circle burr, counting and gauge.	—	RT6-S100000
	TM External Vision	License, add-on to TMFlow. Required when using eye-to-hand cameras.	—	RT6-S100002
	TM OCR	License, add-on to TMFlow. Includes: Text OCR and Number OCR	—	RT6-S100003
TMFlow Editor	—	License, provides a convenient way to open and edit project offline.	RT6-S200001	—
	TMFlow editor - Offline AOI	License, add-on to TMFlow Editor. Enables TMFlow Editor to offline edit a TMFlow project that includes AOI vision.	—	RT6-S100005

Note: Tables include representative part numbers. Please consult the product page for more details.

Hornet 565 - Parallel Robots (Standalone)

- High-speed operation tracks up to a conveyor speed of 1.4 m/s
- Designed with a high payload to support multi-hand (multi-picking)
- Supports fast Pick & Place on a fast conveyor
- Maximum working diameter 1,130 mm
- Maximum payload 8 kg
- Programmable through ACE software and eV+ language, or through the familiar IEC 61131-3 when using ePLC Connect



Product Page



Training Services



Service Contracts

Item	Number of Axes	IP	Maximum Payload	Working volume		
				X,Y axis (stroke)	Z axis (stroke)	theta axis (rotation angle)
Hornet 565	3 axes	Standard	8 kg	1130 mm	425 mm	-
		IP65/67				
	4 axes	Standard	3 kg			±360°
		IP65/67				

Note: Additional accessories available, contact your Omron Sales Representative for additional details

Part Number Configurator
 1720-□-456□□
 (1) (2) (3)

No.	Item	Specification	Symbol	
1	Bundle Type	Without Smart Controller EX	eV+	0
			ePLC	1
			Add-On	3
		With Smart Controller EX	eV+	2
PLC	4			
2	IP Rating (Topside/Underside/Platform & Arms)	IP20/IP65/IP67	0	
		IP65/IP65/IP67	1	
3	Number of Axes & Max Payload	3 Axis / 8kg	0	
		4 Axis / 3kg	4	

Note: Tables include representative part numbers. Please consult the product page for more details.

iX3-565 Parallel Robots (Integrated Controller)



- High-speed operation tracks up to a conveyor speed of 1.4 m/s
- Designed with a high payload to support multi-hand (multi-picking)
- Supports fast Pick & Place on a fast conveyor
- Maximum working diameter 1,130 mm
- Maximum payload 8 kg
- EtherCAT connectivity to the Omron NJ501-R Integrated Controller and programming through familiar IEC 61131-3 programming language or scripting (eV+)

[Product Page](#)

[Training Services](#)

[Service Contracts](#)

Item	Number of Axes	IP	Maximum Payload	Working volume		
				X,Y axis (stroke)	Z axis (stroke)	theta axis (rotation angle)
iX3-565	3 axes	Standard	8 kg	1130 mm	425 mm	-
		IP65/67				
	4 axes	Standard	3 kg			±360°
		IP65/67				

Note: Additional accessories available, contact your Omron Sales Representative for additional details

Part Number Configurator
 RX3-20656
 (1) (2)

No.	Item	Specification	Symbol
1	Protection Rating	IP20 Topside/IP65 Underside/IP67 Platform & Arms	0
		IP65 Topside & Underside/IP67 Platform & Arms	1
2	Number of Axes	3 Axes	0
		4 Axes	4


Note: Tables include representative part numbers. Please consult the product page for more details.

Quattro Parallel Robots (Standalone)

- Four-axis arm evenly distributes the load on the robot to achieve fast, high-precision motion
- Designed with a high payload to support multi-hand (multi-picking)
- Supports high-speed Pick & Place operations on fast moving conveyors
- Maximum working diameter of 1,300mm & 1,600mm
- Maximum payloads of 10kg & 15kg
- Programmable through ACE software and eV+ language, or through the familiar IEC 61131-3 when using ePLC Connect
- USDA compliant versions available



 [Product Page](#)

 [Training Services](#)

 [Service Contracts](#)

Item	Number of Axes	Type	IP	Maximum Payload	Working volume		
					X,Y axis (stroke)	Z axis (stroke)	theta axis (rotation angle)
Quattro 650H/HS	4	H	Standard	6 kg (P30: 15 kg)	1300 mm	500 mm	0° (fixed) (P30) ±46.25° (P31) ±92.5° (P32) ±185° (P34)
			IP65/67				
HS		Standard	3 kg (P30: 12 kg)				
Quattro 800H/HS		H	Standard	4 kg (P30:10 kg)	1600 mm		
	IP65/67						
		HS	Standard	1 kg (P30: 7 kg)			

Note: Additional accessories available, contact your Omron Sales Representative for additional details

1721-□-26□□□
 Part Number Configurator (1) (2) (3) (4)

No.	Item	Specification		Symbol
1	Bundle Type	Without Smart Controller EX	Add-On	3
		With Smart Controller EX	eV+	2
			ePLC	4
2	Reach		650mm (1300mm total)	0
			800mm (1600mm total)	3
3	Max Payload (650mm/800mm)	"3kg/1kg (12kg/7kg with P30)"	IP65/IP65/IP67, Stainless Steel Platform (HS)	1
	IP Rating (Topside/Underside/Platform & Arms)	"6kg/4kg (12kg/10kg with P30)"	IP20/IP65/IP67 (H)	0
IP66/IP66/IP67 (H)			2	
4	Platform Type / Rotation		(P30) / No Rotation	0
			(P31) / ± 46.25°	1
			(P32) / ± 92.5°	2
			(P34) / ± 185°	4

Note: Tables include representative part numbers. Please consult the product page for more details.

iX4 – Parallel Robots (Integrated Controller)

- Four-axis arm evenly distributes the load on the robot to achieve fast, high-precision motion
- Designed with a high payload to support multi-hand (multi-picking)
- Supports high-speed Pick & Place operations on fast moving conveyors
- Maximum working diameter of 1,300mm & 1,600mm
- Maximum payloads of 10kg & 15kg
- EtherCAT connectivity to the Omron NJ501-R Integrated Controller and programming through familiar IEC 61131-3 programming language or scripting (eV+)
- USDA compliant versions available



[Product Page](#)

[Training Services](#)

[Service Contracts](#)

Item	Number of Axes	Type	IP	Maximum Payload	Working volume		
					X,Y axis (stroke)	Z axis (stroke)	theta axis (rotation angle)
iX4-650H/HS	4	H	Standard IP65/67	6 kg (P30: 15 kg)	1300 mm	500 mm	0° (fixed) (P30) ±46.25° (P31) ±92.5° (P32) ±185° (P34)
		HS	Standard	3 kg (P30: 12 kg)			
iX4-800H/HS		H	Standard IP65/67	4 kg (P30:10 kg)	1600 mm		
		HS	Standard	1 kg (P30: 7 kg)			

Note: Additional accessories available, contact your Omron Sales Representative for additional details

Part Number Configurator

RX4-2166
(1) (2) (3)

No.	Item	Specification	Type	Symbol
1	Reach	650mm		0
		800mm		3
2	Protection Rating	IP20 Topside/IP65 Underside/IP67 Platform & Arms	H	0
		IP65 Topside & Underside/IP67 Platform & Arms		1
		IP66 Topside & Underside/IP67 Platform & Arms	HS	2
3	Z Rotation / Max Payload	No Rotation / H: 15kg HS: 12kg (650mm Reach)H: 10kg HS: 7kg (800mm Reach)		0
		± 46.25° / H: 6kg HS: 3kg (650mm Reach)H: 4kg HS: 1kg (800mm Reach)		1
		± 92.5° / H: 6kg HS: 3kg (650mm Reach)H: 4kg HS: 1kg (800mm Reach)		2
		± 185° / H: 6kg HS:3kg (650mm Reach)H: 4kg HS: 1kg (800mm Reach)		4


Note: Tables include representative part numbers. Please consult the product page for more details.

i4L – SCARA Robots

- 5kg payload, high inertia and high duty ratings enable the i4L to tackle more challenging processes with ease
- Compact built-in internal controller, out-of-the-box table or wall mounting and options for rear or bottom cabling reduces the physical area required and enables a customized installation
- High visibility, customizable, multi-colored LED dome light provides an intuitive visual indication of status
- Available in 350mm, 450mm, and 550mm reaches to accommodate a wide range of applications
- Easily integrates with the full line of Omron Automation products as well as 3rd party automation platforms



 [Product Page](#)

 [Training Services](#)

 [Service Contracts](#)

Part Number Configurator RS4-20□□□0□
 (1) (2) (3) (4)

No.	Item	Specification	Symbol
1	Control Type	Standard Control	5
		Integrated Control	6
2	Reach	350mm	3
		450mm	4
		550mm	5
3	Cabling	Rear Panel	0
		Bottom Panel	1
4	Quill Length	180mm	2
		350mm (550mm Reach Only)	4

Note: Additional accessories available, contact your Omron Sales Representative for additional details

Note: Tables include representative part numbers. Please consult the product page for more details.

i4H – SCARA Robots

- 15kg payload, high inertia and high duty ratings enable the i4H to tackle applications that require high performance
- Compact built-in internal controller, and choice of standard or inverted configurations reduces the physical area required and enables a customized installation
- High visibility, customizable, multi-colored LED ring light and LCD screen provides an intuitive visual indication of status
- Available in 650mm, 750mm, and 850mm reaches to accommodate a wide range of applications



 [Product Page](#)

 [Training Services](#)

 [Service Contracts](#)

Part Number Configurator **RS4-20**

(1) (2) (3) (4) (5)

No.	Item	Specification	Symbol
1	Control Type	Standard Control	5
		Integrated Control	6
2	Reach	650 mm	6
		750 mm	7
		850 mm	8
3	Mount Configuration	Standard	5
		Inverted	7
4	Protection Rating / Feature	IP20 with standard lubrication	0
		IP20 with Food Grade lubrication	5
		IP65 with Food Grade lubrication	4
		Cleanroom / ESD with Standard lubrication	1
5	Z-axis Quill Stroke Length	210 mm w/standard lubrication (IP20 and Clean Room only)	2
		210 mm w/Food Grade lubrication (IP20 and IP65 only)	3
		410 mm w/standard lubrication (IP20 and Clean Room only)	4
		410 mm w/Food Grade lubrication (IP20 and IP65 only)	5

Note: Additional accessories available, contact your Omron Sales Representative for additional details

Note: Tables include representative part numbers. Please consult the product page for more details.

Automation Control Environment (ACE) – Fixed Robot Software

- Provides an easy-to-use interface for setting up, programming, troubleshooting and operating Omron fixed industrial robots
- Fast emulation and 3D visualization of robot applications for quick proof of concept tasks
- Wizard-based user-friendly interface to calibrate and teach the robots
- Simplification of application development tasks, by means of the Application Manager modules
- Recipe Manager simplifies management of manufacturing processes and handles a range of product variations, ideal for flexible automation to reduce changeover time
- Robot Vision Manager provides algorithms and tools for easily integrating vision systems into robotic applications
- Robot Vision Manager also includes vision inspection tools to improve quality assurance and traceability



Product Page



Training Services

- Pack Manager can manage scalable packaging lines from integration to deployment without complex scripting via step-by-step setup wizards that configure process specific items, such as controllers, robots, and conveyor belts

ACE License Configuration

Product Name	Add-On Product Names	Remarks
Ace PackManager (for ACE 4.x)	20409-000	Enables full functionality of the ACE PackManager software.
Robot Vision Manager (for ACE 4.x)	20410-000	Enables the Robot Vision Manager functionality and inspection tools library.
Dual (PackManager plus Vision)	20433-000	Enables functionality of both PackManager and Robot Vision Manager

Note: When you create robot programs without using PackManager wizards and vision system, the ACE license is not required

Note: Tables include representative part numbers. Please consult the product page for more details.

IPC Application Controller – Robot Process Manager and Vision System

- Built-in vision processor with 128GB SSD, optimized to process high resolution, high frame rate images
- Supports Omron “Manager” software packages (ie: Robot Vision Manager, PackManager, RecipeManager, 3D PickManager)
- Easy setup with ACE or Sysmac Studio
- Unique simplified thermal design to maximize uptime
- GigE PoE and USB 3.0 ports for increased connectivity and fast data transmission
- Supports up to 8 cameras simultaneously
- Compact design minimizes panel space and allows 2 mounting orientations
- Compatible with Omron S8BA Series UPS


 [Product Page](#)

Specifications

Item		Specifications
Part Number		AC1-152000
Main System	CPU	Intel® Core™ i5-7440EQ
	Main Memory	8 GB DDR4
	Graphics Controller	Intel® HD Graphics
Operating System		Windows 10 IoT Enterprise LTSB - 64 bit
Storage Devices	Hard Drive	128 GB SSD Additional 3.5" hard drive slot available Additional SD memory card slot available, up to 32 GB capacity
Power Supply		20.4 to 28.8VDC
Communications Port	Power Connector	24 VDC
	I/O Connector	2 inputs (UPS signal and power OFF control) and 1 output (industrial Box PC power state)
	Ethernet Connector	Gigabit Ethernet x 3, Gigabit Ethernet with POE x 4 3W max power consumption per port
	USB	USB 3.0 x 4 (3m max cable length), USB 2.0 x 2 (5m max cable length)
	Display	DVI-Connector x 1 (up to 1,920 x 1,200 @60Hz)
	RS-232C	Standard DSUB9 connector (Non-isolated)

Note: Tables include representative part numbers. Please consult the product page for more details.

NJ501-R – Integrated Robot Controller



[Product Page](#)

- Integration of Robotics, Logic, and Motion in one CPU
- Programming with variables allows users to create complex programs efficiently
- Offers speed without compromising on reliability and robustness expected from PLCs
- Conforms to IEC 61131-3 (JIS B 3503) standard programming and PLCopen function blocks for motion control and traditional V+ scripting for robot and motion control
- Complete RAS Functions: Transmission frame error check, Timeout, Bus diagnosis, Watchdog (WDT), Memory check, and Topology check, etc.
- Fast and accurate control by synchronizing all EtherCAT devices, such as vision, servos, robots, and IO with a single controller

Specifications

Item	Product Description	
Product Name	NJ50-R[] [] []	
Description	Machine controller with sequence, motion and robotics functionality	
Software	Sysmac Studio	
Programming	IEC 61131-3 (Ladder, Structured Text, Function Blocks) eV + Scripting	
Program Capacity	20 MB	
Memory Card	SD/SDHC memory card	
Variable Capacity	No retain attribute	4 MB
	Retain attribute	2 MB
Built-in Ports	EtherCAT, Ethernet/IP, USB 2.0	
Number of EtherCAT slaves	192	
Max Number of robots	8	
Max Numbers of Axes	64, 32, 16	

Part Numbers

Type	Part Number
Integrated Controller (16 Axis, NO Database)	NJ501-R300
Integrated Controller (32 Axis, NO Database)	NJ501-R400
Integrated Controller (64 Axis, NO Database)	NJ501-R500
Integrated Controller (16 Axis, WITH Database)	NJ501-R320
Integrated Controller (32 Axis, WITH Database)	NJ501-R420
Integrated Controller (64 Axis, WITH Database)	NJ501-R520

Note: Tables include representative part numbers. Please consult the product page for more details.

Robotics Complete Care Service Contracts

- Comprehensive program which provides support and parts needed for robot maintenance
- Eliminates budget uncertainty while prolonging the robot lifespan with proper inspection and maintenance at a fixed cost
- Maximizes productivity by identifying potential problems before they result in unscheduled downtime
- Includes below coverage for 2 years with option to renew each year thereafter:
 - Annual Wellness Visit for preventative maintenance
 - 100% coverage for all service labor and parts for repairs
 - Priority dispatch for Field Service Support
 - Premium Technical Support (24/7 access with priority status)
 - No travel costs for any on-site visit
 - Discounts on additional training for your team



[Services Page](#)

	Coverage	Standard Warranty	Registered Robot	Complete Care
Year 1	Parts	•	•	•
	Labor	•	•	•
	Travel			•
	Annual Wellness Visit			•
	Priority Status	•	•	•
Year 2	Parts		•	•
	Labor		•	•
	Travel			•
	Annual Wellness Visit			•
	Priority Status		•	•

Safety Services

- Omron provides turn-key safety services from risk assessments to design and installation to address machine safety hazards. Be confident that your machines are properly safeguarded by partnering with a global safety expert.



1. Risk Assessment
2. Engineering Design
3. Implementation
4. Validation

- Protect your employees from unnecessary risks
- Maintain compliance with safety standards
- Avoid incident-related costs such as regulatory fines, downtime, legal fees and increased OSHA inspections
- Harness advanced safety technologies to preserve your productivity
- Partner with a global safety provider for consistent, world class support



 [Services Page](#)

Empowering people through automation

OMRON

Industrial Automation

Spring, 2024

automation.omron.com



BOOK A DEMO >

OMRON Automation | 800.556.6766 | automation.omron.com