E3ZM-B

CSM_E3ZM-B_DS_E_4_5

Excellent PET Bottle Detection

- New detection method that is independent of bottle shape, position, and contents.
- Automatic compensation against effects of contamination and temperature (except E3ZM-B□T).
- Product lineup includes models with adjuster (E3ZM-B T).
- Detects transparent objects made by PET, resin, and glass.





Refer to Safety Precautions on page 10.

Features


Industry Top P-opaquing and a Coaxial Optical System Eliminate Dependence on the Bottle's Shape, Position, Transparency, and Contents.

P-opaquing: Polarization-opaquing

Patented

(Refer to page 9 for a technical description.)

The E3ZM-B more than triples conventional detection performance, with outstanding stability.



Industry Top AC³ Function Automatically Compensates Effects of Soiling and Temperature

AC3: Auto Compensation Control for Contamination

Patented (Refer to page 9 for a technical description.)

Parameters require resetting when static electricity causes dust to adhere to the surface of the Sensor or Reflector, or when the light emission power drops due to temperature- or time-related changes. Original OMRON light emission control technology greatly reduces the resetting work involved.



Initial Condition . . . Contamination . . . Auto Compensation

Teaching with No Workpiece Required -- Quick and Easy Setting

There is no need for delicate sensitivity adjustments. Simply adjust the optical axes of the Sensor and Reflector, then press the Teaching button twice.

This high-reliability design eliminates worries about variations in the sensitivity settings of different operators.



Industry Top IP69K Degree of Protection with an SUS316L Housing

The housing is constructed of corrosion-resistant SUS316L, and the display cover is PES (polyethersulfone).

Both materials are highly resistant to the effects of detergents and disinfectants.

IP69K degree of protection also allows the E3ZM-B to withstand washing with high-temperature, high-pressure water.


This makes the E3ZM-B well suited to use in sites requiring a high level of hygiene.





A Wide Ambient Temperature Range of -40 to 60°C

This wide temperature range meets the needs of the many and diverse applications in the beverage industry.



Applications



Detecting Plastic Bottles

Precautions for Correct Use The E3ZM-B□1/-B□6 are not applicable for detecting transparent objects that exhibit no birefringence, such as glass bottles.

Transparent objects made of resin also exhibit little birefringence, and cannot be detected with complete stability. Check the detection stability of objects such as these prior to actual operation.

Ordering Information

Sensors [Refer to *Dimensions* on page 12.]

Red light

	Appear-	Sensitivity	Connection	nnection		Model	
Sensing method	ance	adjustment	method	Sensing distance	Special reflector	NPN output	PNP output
			Pre-wired (2 m) *2		Order	E3ZM-B61 2M	E3ZM-B81 2M
		Teaching	Connector (M8, 4 pins)		separately	E3ZM-B66	E3ZM-B86
		type	Pre-wired (2 m) *2		Included	E3ZM-B61-C 2M	E3ZM-B81-C 2M
Retroreflective			Connector (M8, 4 pins)	500 mm		E3ZM-B66-C	E3ZM-B86-C
with MSR function		Pre-wired (2 m)	[100 mm]*1	Order	E3ZM-B61T 2M	E3ZM-B81T 2M	
		One-turn adjuster type	Connector (M8, 4 pins)		separately	E3ZM-B66T	E3ZM-B86T
			Pre-wired (2 m)		Included		E3ZM-B81T-C 2M
			Connector (M8, 4 pins)		included	E3ZM-B66T-C	E3ZM-B86T-C

Accessories

Special Retroreflective Reflector (A Retroreflector is provided depending on the model number. Check the model number in the remarks column.) [Refer to *Dimensions* on page 12.]

Name	Model	Sensing distance (rated) E3ZM-B□1(T)/-B□6(T)	Quantity	Remarks
	E39-RP1	500 mm [100 mm]*	1	A Reflector is provided with the E3ZM-B□□(T)-C. A Reflector is not provided with other Sensors.
Special Polarizing Reflector	E39-RSP1	250 mm [0 mm] *	1	A Reflector is not provided with the Sensor. The MSR function is enabled.
	E39-RP37	250 mm [0 mm] *	1	A Reflector is not provided with the Sensor. The MSR function is enabled.

Note: Previous OMRON Retroreflective Reflectors (E39-R1/-R1S/-R2/-R3/-R9/-R10/-R1K/-RS1/-RS2/-RS3, etc.) cannot be used with the E3ZM-B. *Values in parentheses indicate the minimum required distance between the Sensor and Reflector.

^{*1.} Values in parentheses indicate the minimum required distance between the Sensor and Reflector.
*2. Models with a 5-m pre-wired cable are also available. When ordering, add the cable length to the end of the model number (e.g., E3ZM-B61 5M).

Mounting Brackets A Mounting Bracket is not provided with the Sensor. Order a Mounting Bracket separately if required. [Refer to *Dimensions* on E39-L/F39-L/E39-S/E39-R, E39-L□.]

Appearance	Model	Quantity	Remarks	Appearance	Model	Quantity	Remarks
	E39-L153 (SUS304)	1	- Mounting Brackets		E39-L98 (SUS304)	1	Metal Protective Cover Bracket *
ac a	E39-L104 (SUS304)	1	Woulding Drackets		E39-L150 (SUS304)	1 set	(Sensor adjuster)
io .	E39-L43 (SUS304)	1	Horizontal Mounting Bracket *		E39-L151	1 set	Easily mounted to the aluminum frame rails of conveyors and easily adjusted. For vertical angle
	E39-L142 (SUS304)	1	Horizontal Protective Cover Bracket *		(SUS304)	1 361	adjustment
	E39-L44 (SUS304)	1	Rear Mounting Bracket		E39-L144 (SUS304)	1	Compact Protective Cover Bracket *

^{*}Cannot be used for Standard Connector models.

Sensor I/O Connectors (Models for Connectors: A Connector is not provided with the Sensor. Be sure to order a Connector separately.) [Refer to *Dimensions* on XS3.]

Size	Specifications	Appearance		Cable		Model	
		Straight *1		2 m		XS3F-E421-402-A	
MQ (4 pipo)	Standard	Straight	THE PARTY OF THE P	5 m	4-wire	XS3F-E421-405-A	
M8 (4 pins)	(4 piris) Standard	L-shaped *1 *2	2	2 m		XS3F-E422-402-A	
		L-Shapeu i Z		5 m		XS3F-E422-405-A	

Note: The outer cover of the cable is made of PVC (polyvinyl chloride), the nut is make of SUS316L stainless steel, and the degree of protection is IP67 (IEC 60529). When high-pressure washing will be used, select an I/O Connector that has IP69K degree of protection.


^{*1.} The connector will not rotate after connecting.

^{*2.} The cable is fixed at an angle of 180° from the sensor emitter/receiver surface.

Ratings and Specifications

	Sensing method	Retroreflective with P-opaq	uing (*1) and MSR functions				
Model	NPN output	E3ZM-B61(-C)/-B66(-C)	E3ZM-B61T(-C)/-B66T(-C) (*2)				
Item	PNP output	E3ZM-B81(-C)/-B86(-C)	E3ZM-B81T(-C)/-B86T(-C) (*2)				
Sensing distance		100 to 500 mm (Using E39-RP1)					
Standard s	sensing object	500-ml, transparent, round PET bottle (65-mm dia.)					
Directional angle		Sensor: 3° to 10° Reflector: 30°					
Light sour	ce (wavelength)	Red LED (650 nm)					
Power sup	ply voltage	10 to 30 VDC, including 10% ripple (p-p)					
Current co	nsumption	450 mW max. (current consumption for a 30-V power supply voltage: 15 mA max.)	25 mA max.				
Control ou	tput	Load power supply voltage: 30 VDC max., Load cur Open-collector output (NPN/PNP output depending					
Operation	mode	Light ON/Dark ON cable switch selectable	Light ON/Dark ON switch selectable				
Protection	circuits	Reversed power supply polarity, Load short-circuit pand Reversed output polarity protection	protection, Mutual interference prevention,				
Response time		Operate or reset: 1 ms max.					
Sensitivity	adjustment	Teaching method	One-turn adjuster				
Ambient il	lumination	Incandescent lamp: 3,000 lx max., Sunlight: 10,000 lx max.					
Ambient temperature range		Operating: -40 to 60°C (*3), Storage: -40 to 70°C (with no icing or condensation)	Operating: -25 to 55°C (*3), Storage: -40 to 70°C (with no icing or condensation)				
Ambient h	umidity range	Operating: 35% to 85%, Storage: 35% to 95% (with no condensation)					
Insulation	resistance	20 MΩ min. at 500 VDC					
Dielectric :	strength	1,000 VAC, 50/60 Hz for 1 min					
Vibration r	esistance	Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions					
Shock resi	stance	Destruction: 500 m/s² 3 times each in X, Y, and Z directions					
Degree of	protection *4	IEC IP67, DIN 40050-9: IP69K					
Connectio	n method	Pre-wired cable (standard length: 2 m) or M8 4-pin connector					
Indicators		Operation indicator (yellow), Stability indicator (green), and Teaching indicator (red)					
Weight (packed state)		Pre-wired models: Approx. 85 g Connector models: Approx. 35 g	Pre-wired models (2-m cable): Approx. 70 g Connector models: Approx. 20 g				
Housing		SUS316L					
Lens Materials Indication		PMMA (polymethylmethacrylate)					
		PES (polyethersulfone)					
	Buttons	Fluoro rubber					
Cable		PVC (polyvinyl chloride)					
Accessori	es *5	Instruction sheet, Special Reflector (E3ZM-B□□-C	only)				

*5. Mounting Brackets must be ordered separately.



^{*1.} For information on the P-opaquing function, refer to → pages 1 and 9.
*2. If a sensing object such as a glass plate is being used, the light reception level may not be attenuated sufficiently. In the following cases, be sure to test operation sufficiently under actual operating conditions.

¹⁾ If the temperature varies more than 5°C

²⁾ If the Sensor or Reflector moves due to vibration

*3. Do not bend the cable in temperatures of –25°C or lower.

*4. IP69K Degree of Protection Specification
IP69K is a protection standard against high temperature and high-pressure water defined in the German standard DIN 40050, Part 9. The test piece is sprayed with water at 80°C at a water pressure of 80 to 100 BAR using a specified nozzle shape at a rate


The distance between the test piece and nozzle is 10 to 15 cm, and water is sprayed horizontally for 30 seconds each at 0°, 30°, $60^{\circ},$ and 90° while rotating the test piece on a horizontal plane.

Engineering Data (Typical)

Parallel Operating Range (Horizontal)

E3ZM-B 1/B 6 +


E39-RP1 (Special Reflector)



Parallel Operating Range (Vertical)

E3ZM-B□1/B□6 +


E39-RP1 (Special Reflector)



Excess Gain vs. Distance


E3ZM-B 1/B 6 +

E39-RP1 (Special Reflector)




Note: The AC^3 function controls the excess gain ratio to be a constant multiple of 2.

Dark Excess Gain vs. Sensing Object Characteristics



Dark Excess Gain vs. Position



I/O Circuit Diagrams

NPN Output


Model	Operation mode	Timing charts	Operation selector switch	Output circuit
E3ZM-B61	Light ON	Incident light No incident light Operation indicator ON (yellow) Otput transistor OFF Load Operate (e.g., relay) Between brown (1) and black (4) leads	Connect pink lead (2) to brown lead (1).	Operation (Vellow) Photo- electric Sensor main circuit Stability indicator (Green) Stability indicator (Green) Brown 10 to 30 VDC Light ON Load (Relay) 100 mA max. (Control output) oircuit O V
E3ZM-B66	Dark ON	Incident light Operation indicator ON (yellow) Other transistor ON Load (e.g., relay) Operate Resettween brown (1) and black (4) leads	Connect pink lead (2) to blue lead (3) or leave open.	Indicator (red) M8 Connector Pin Arrangement
E3ZM-B61T	Light ON	Light incident Light interrupted Operation indicator ON (yellow) OFF OFF Load Operate (e.g., relay) Reset (Between brown and black leads)	L side (LIGHT ON)	Operation indicator (Yellow) Stability indicator (Green) (Control output) Max. Operation 10 to 30 VDC (Control output) Max. Output) The stability output ou
E3ZM-B66T	Dark ON	Light incident Light interrupted Operation indicator ON (yellow) OFF Output transistor ON Load Operate (e.g., relay) Reset (Between brown and black leads)	D side (DARK ON)	Photo- electric Sensor Main Circuit ZD Black Blue

PNP Output

Model	Operation mode	Timing charts	Operation selector switch	Output circuit
E3ZM-B81	Light ON	Incident light No incident light Operation indicator ON (yellow) OFF Output transistor ON Load Operate (e.g., relay) Reset Between blue (3) and black (4) leads	Connect pink lead (2) to brown lead (1).	Operation (Green) Stability indicator (Yellow) Photo-electric Sensor main circuit Teaching Operation 10 to 30 VDC Brown 10 to 30 VDC Light ON; 100 mA max. (Control output) Black: Output) Blue OV
E3ZM-B86	Dark ON	Incident light No incident light Operation indicator ON (yellow) OFF Output transistor ON Load (e.g., relay) Operate Reset Between blue (3) and black (4) leads	Connect pink lead (2) to blue lead (3) or leave open.	I fleaching indicator indicator (red) M8 Connector Pin Arrangement
E3ZM-B81T	Light ON	Light incident Light interrupted Operation indicator ON (yellow) OFF Output transistor ON OFF Load Operate (e.g., relay) Reset (Between blue and black leads)	L side (LIGHT ON)	Operation Stability Brown 10 to 30 VDC indicator (Yellow) Black
E3ZM-B86T	Dark ON	Light incident Light interrupted Operation indicator ON (yellow) OFF Output transistor OFF Load Operate (e.g., relay) Operate (Between blue and black leads)	D side (DARK ON)	Photo- electric Sensor Main Circuit 100 mA Load max. (Relay) Blue 0 V

Plugs (Sensor I/O Connectors)

M8 4-pin Connectors



Classification	Wire color	Connector pin No.	Application
	Brown	1	Power supply (+V)
DC	White	2	Operation selection *
DC	Blue	3	Power supply (0 V)
•	Black	4	Output

Note: The above M8 Connectors made by OMRON are IP67. Do not use them in an environment where IP69K is required.

^{*}Not available on the E3ZM-B□□T.

Nomenclature

Teaching Models



One-turn Adjuster Models

E3ZM-B□T



Teaching Method

Note: When the Sensor is first unpacked and used, the teaching indicator (red) will flash slowly to show that teaching has not yet been done. This does not indicate a malfunction. Use the following procedure to conduct teaching.


1. Install the Sensor and Reflector and adjust the optical axis (without placing a Sensing objects between them).

Then press and hold the TEACH button for at least 2 seconds.



The teaching indicator (red) will start flashing quickly.

Perform the following operation within 7 seconds after first starting to press the TEACH button. (After 7 seconds, the Unit will return to its initial condition.)



1

The stability indicator (green) and operation indicator (yellow) will retain their lit or OFF status, and the teaching indicator (red) will flash.

2. Press the TEACH button again.

Teaching will then begin.

The teaching indicator (red) will remain lit during the teaching operation.



When Teaching Is Successful

The teaching indicator (red) will go out. The Unit will then enter normal operating condition.

Dark ON setting



Light ON setting



When Teaching Is Not Successful

The teaching indicator (red) will flash slowly or quickly.



Flashes slowly or quickly

The teaching indicator (red) will then begin flashing even more slowly, indicating that the teaching operation should begin.



more slowly

Repeat the operation starting with step 1.

Note: Depending on the amount of light received, the operation indicator and stability indicator may also change during the teaching operation.

Technical Descriptions

New Technology for Detecting Transparent Objects Exhibiting Birefringence Patented P-opaquing (Polarization-opaquing)


Conventional photoelectric sensors for detecting PET bottles depend on refraction due to the bottle's shape or on the attenuation of light intensity caused by surface reflection. However, it is difficult to attain a sufficient level of excess gain with these methods.


The E3ZM-B utilizes the birefringent (double refraction) property of PET bottles to dramatically increase the level of excess gain. The polarization component that is disturbed by the PET bottles as they pass along the line is cut by a special and unique OMRON polarization filter. This greatly lowers the intensity of the light received to provide stable detection with simple sensitivity adjustment.

"P-opaquing" is a word that was coined to refer to the process of applying polarization in order to opaque transparent objects that exhibit the property of birefringence.

The excess gain of the E3ZM-B is doubled for both light-ON and dark-ON applications.

The excellent stability of the E3ZM-B prevents malfunctions from occurring even if something causes the intensity of light received to fluctuate by $\pm 50\%$.






New Technology for Achieving Long-term Stability Patented AC³ (AC cube: Auto Compensation Control for Contamination) (Not available on the E3ZM-B□T)


Conventional photoelectric sensors with built-in amplifiers are not equipped with functions to compensate for changes in the intensity of light received caused by dust and other lens-soiling matter, ambient temperature, and changes that occur in the LED over time. This makes it comparatively difficult to achieve long-term, stable detection of objects that exhibit little change in the intensity of light received, such as transparent objects.

The AC³ (AC cube) function provided on the E3ZM-B periodically feeds the intensity of light received during light-ON operation back to the light-emitting circuit, to keep the intensity equal to the value set by teaching.

This allows the E3ZM-B to attain long-term, stable detection while helping to cut down on maintenance requirements and improve the equipment operating ratio.

Note: The AC3 function cannot be used for dark-ON operation.





Intensity of light received is compensated every 30 s. E3ZM-B

Safety Precautions

Refer to Warranty and Limitations of Liability.

MARNING

This product is not designed or rated for directly or indirectly ensuring safety of persons.



Do not use it for such a purpose.

⚠ CAUTION

Do not use the product with voltage in excess of the rated voltage.



Excess voltage may result in malfunction or fire.

Never use the product with an AC power supply.



Otherwise, explosion may result.

When cleaning the product, do not apply a high-pressure spray of water to one part of the product. Otherwise, parts may become damaged and the degree of protection may be degraded.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation of the Sensor.

Operating Environment

Do not use the Sensor in an environment where explosive or flammable gas is present.

Connecting Connectors

Be sure to hold the connector cover when inserting or removing the connector.

When using an XS3F Connector, be sure to tighten the connector lock by hand; do not use pliers or other tools. If the tightening is insufficient, the degree of protection will not be maintained and the Sensor may become loose due to vibration. The appropriate tightening torque is 0.3 to 0.4 N·m. When using another, commercially available connector, follow the usage and tightening torque instructions provided by the manufacturer.

Load

Do not use a load that exceeds the rated load.

Low-temperature Environments

Do not touch the metal surface with your bare hands when the temperature is low. Touching the surface may result in a cold burn.

Oily Environments

Do not use the Sensor in oily environments. They may damage parts and reduce the degree of protection.

Modifications

Do not attempt to disassemble, repair, or modify the Sensor.

Outdoor Use

Do not use the Sensor in locations subject to direct sunlight.

Cleaning

Do not use thinner, alcohol, or other organic solvents. Otherwise, the optical properties and degree of protection may be degraded.

Cleaning

Do not use highly concentrated cleaning agents. Otherwise, malfunction may result. Also, do not use high-pressure water with a level of pressure that exceeds the stipulated level. Otherwise, the degree of protection may be reduced.

Surface Temperature

Burn injury may occur. The Sensor surface temperature rises depending on application conditions, such as the ambient temperature and the power supply voltage. Use caution when operating or performing maintenance on the Sensor.

Cable Bending

Do not bend the cable in temperatures of -25° C or below. Otherwise, the cable may be damaged.

Precautions for Correct Use

Do not use the Sensor in any atmosphere or environment that exceeds the ratings.

Do not install the Sensor in the following locations.

- (1) Locations subject to direct sunlight
- (2) Locations subject to condensation due to high humidity
- (3) Locations subject to corrosive gas
- (4) Locations where the Sensor may receive direct vibration or shock

Connecting and Mounting

- (1) The maximum power supply voltage is 30 VDC. Before turning the power ON, make sure that the power supply voltage does not exceed the maximum voltage.
- (2) Laying Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in malfunction or damage due to induction. As a general rule, wire the Sensor in a separate conduit or use shielded cable.
- (3) Use an extension cable with a minimum thickness of 0.3 mm² and less than 100 m long.
- (4) Do not pull on the cable with excessive force.
- (5) Pounding the Photoelectric Sensor with a hammer or other tool during mounting will impair water resistance. Also, use M3 screws.
- (6) Mount the Sensor either using the bracket (order separately) or on a flat surface.
- (7) Be sure to turn OFF the power supply before inserting or removing the connector.

Power Supply

If a commercial switching regulator is used, ground the FG (frame ground) terminal.

Power Supply Reset Time

The Sensor will be able to detect objects 100 ms after the power supply is tuned ON. Start using the Sensor 100 ms or more after turning ON the power supply. If the load and the Sensor are connected to separate power supplies, be sure to turn ON the Sensor first.

Turning OFF the Power Supply

Output pulses may be generated even when the power supply is OFF. Therefore, it is recommended to first turn OFF the power supply for the load or the load line.

Load Short-circuit Protection

This Sensor is equipped with load short-circuit protection, but be sure to not short circuit the load. Be sure to not use an output current flow that exceeds the rated current. If a load short circuit occurs, the output will turn OFF, so check the wiring before turning ON the power supply again. The short-circuit protection circuit will be reset. The load short-circuit protection will operate when the current flow reaches 1.8 times the rated load current. When using a capacitive load, use an inrush current of 1.8 times the rated load current or lower.


Water Resistance

Do not use the Sensor in water, rainfall, or outdoors.

When disposing of the Sensor, treat it as industrial waste.

Mounting Diagram

Use a mounting torque of 0.5 N·m max.



Resistance to Detergents, Disinfectants, and Chemicals

- The Sensor will maintain sufficient performance in typical detergents and disinfectants, but performance may suffer in some types of detergents, disinfectants, and chemicals.
 Refer to the following table prior to use.
- The E3ZM has passed detergent and disinfectant resistance testing for the substances listed in the following table. Use this table as a guide when considering detergents and disinfectants.

Туре	Product name	Con- centra- tion	Tem- pera- ture	Time
	Sodium hydroxide, NaOH	1.5%	70°C	240 h
	Potassium hydroxide, KOH	1.5%	70°C	240 h
Chemicals	Phosphoric acid, H ₃ PO ₄	2.5%	70°C	240 h
	Sodium hypochlorite, NaClO	0.3%	25°C	240 h
	Hydrogen peroxide, H ₂ O ₂	6.5%	25°C	240 h
Alkaline foaming cleansers	Topax 66s (Ecolab)	3.0%	70°C	240 h
Acidic foaming cleansers	Topax 56 (Ecolab)	5.0%	70°C	240 h
Disinfectants	Oxonia Active 90 (Ecolab)	1.0%	25°C	240 h
Distribution	TEK121 (ABC Compounding)	1.1%	25°C	240 h

Note: The Sensor was immersed in the above chemicals, detergents, and disinfectants for 240 h at the temperatures given, and then passed an insulation resistance test at 100 M Ω min.


Dimensions

Sensors

Retro-reflective Models

Pre-wired Models E3ZM-B61 E3ZM-B81







Retro-reflective Models

M8 Connector E3ZM-B66 E3ZM-B86






Lens 6 dia.



Terminal No.	Specifications
1	+V
2	Operation selection
3	0 V
4	Output


Retro-reflective Models

Pre-wired Models E3ZM-B61T(-C) E3ZM-B81T(-C)



Retro-reflective Models

M8 Connector E3ZM-B66T(-C) E3ZM-B86T(-C)




Accessory

Special Retroreflective Reflector

E39-RP1






Material: <Reflective surface> acrylic <Rear surface> ABS

Special Retroreflective Reflector

E39-RP37



Material: <Reflective surface> acrylic

<Mounting plate> stainless steel (SUS301)

Note: The reflective plate and mounting plate (1) come as a set.

Special Retroreflective

Reflector

E39-RSP1



Terms and Conditions of Sale

- Offer; Acceptance. These terms and conditions (these "Terms") are deemed part of all quotes, agreements, purchase orders, acknowledgments, price lists, catalogs, manuals, brochures and other documents, whether electronic or in catalogs, manuals, brochures and other documents, whether electronic or in writing, relating to the sale of products or services (collectively, the "Products") by Omron Electronics LLC and its subsidiary companies ("Omron"). Omron objects to any terms or conditions proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these Terms. Prices: Payment Terms. All prices stated are current, subject to change without notice by Omron. Omron reserves the right to increase or decrease prices on any unshipped portions of outstanding orders. Payments for Products are due net 30 days unless otherwise stated in the invoice. Discounts. Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (i) the invoice is paid according to Omron's payment terms and (ii) Buyer has no past due amounts.

- and (ii) Buyer has no past due amounts.

 Interest. Omron, at its option, may charge Buyer 1-1/2% interest per month or the maximum legal rate, whichever is less, on any balance not paid within the
- Orders. Omron will accept no order less than \$200 net billing.

 Governmental Approvals. Buyer shall be responsible for, and shall bear all costs involved in, obtaining any government approvals required for the importation or sale of the Products.
- Taxes. All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Omron or required to be collected directly or indirectly by Omron for the manufacture, production, sale, delivery, importation, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Omron.

 Financial. If the financial position of Buyer at any time becomes unsatisfactory
- <u>Financial</u>. If the financial position of Buyer at any time becomes unsatisfactory to Omron, Omron reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Omron may (without liability and in addition to other remedies) cancel any unshipped portion of Products sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid accounts. unpaid accounts
- Cancellation: Etc. Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Omron against all related costs or expenses.

 10. Force Majeure. Omron shall not be liable for any delay or failure in delivery
- resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.

 11. Shipping: Delivery. Unless otherwise expressly agreed in writing by Omron:
 a. Shipments shall be by a carrier selected by Omron; Omron will not drop ship
- - except in "break down" situations.
 b. Such carrier shall act as the agent of Buyer and delivery to such carrier shall
- constitute delivery to Buyer; c. All sales and shipments of Products shall be FOB shipping point (unless oth- c. All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Omron), at which point title and risk of loss shall pass from Omron to Buyer; provided that Omron shall retain a security interest in the Products until the full purchase price is paid;
 d. Delivery and shipping dates are estimates only; and
 e. Omron will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.

 12. Claims. Any claim by Buyer against Omron for shortage or damage to the Products occurring before delivery to the carrier must be presented in writing to Omron within 30 days of receipt of shipment and include the original transportation bill signed by the carrier noting that the carrier received the Products.
- portation bill signed by the carrier noting that the carrier received the Products from Omron in the condition claimed.
- Warranties. (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

 (b) <u>Limitations</u>. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABIL-

- ITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by tion, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty. See http://www.omron247.com or contact your Omron representative for published information.
- lished information.

 Limitation on Liability: Etc. OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.
- Indemnities. Buyer shall indemnify and hold harmless Omron Companies and their employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, investigation, litigation or proceeding (whether or not Omron is a party) which arises or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products. Without limiting the foregoing, Buyer (at its own expense) shall indemnify and hold harmless Omron and defend or settle any action brought against such Companies to the extent based on a claim that any Product made to Buyer specifications infringed intellectual property rights of another party.
- rights of another party.

 <u>Property: Confidentiality.</u> Any intellectual property in the Products is the exclusive property of Omron Companies and Buyer shall not attempt to duplicate it in any way without the written permission of Omron. Notwithstanding any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Omron. All information and materials supplied by Omron to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and strictly prevent disclosure to any third party.
- prevent disclosure to any third party.

 <u>Export Controls.</u> Buyer shall comply with all applicable laws, regulations and licenses regarding (i) export of products or information; (iii) sale of products to "forbidden" or other proscribed persons; and (ii) disclosure to non-citizens of
- "forbidden" or other proscribed persons; and (ii) disclosure to non-citizens of regulated technology or information.

 Miscellaneous. (a) Waiver. No failure or delay by Omron in exercising any right and no course of dealing between Buyer and Omron shall operate as a waiver of rights by Omron. (b) Assignment. Buyer may not assign its rights hereunder without Omron's written consent. (c) Law. These Terms are governed by the law of the jurisdiction of the home office of the Omron company from which Buyer is purchasing the Products (without regard to conflict of law principles). (d) Amendment. These Terms constitute the entire agreement between Buyer and Omron relating to the Products, and no provision may be changed or waived unless in writing signed by the parties. (e) Severability If any provior waived unless in writing signed by the parties. (e) <u>Severability</u> If any provision hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision. (f) Setoff. Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice. (g) <u>Definitions</u>. As used herein, "<u>including</u>" means "including without limitation"; and "<u>Omron Companies</u>" (or similar words) mean Omron Corporation and any direct or indirect subsidiary or affiliate thereof.

Certain Precautions on Specifications and Use

- Suitability of Use. Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request. Omron will provide application of use of the Product. At Buyer's lequest, omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given:

 (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document.

 (ii) Use in consumer products or any use in significant quantities.

 (iii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject and industrial constants.
 - ment, and installations subject to separate industry or government regulations. (iv) Systems, machines and equipment that could present a risk to life or prop erty. Please know and observe all prohibitions of use applicable to this Prod-
 - NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO

- ADDRESS THE RISKS, AND THAT THE OMRON'S PRODUCT IS PROP-ERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.
- Programmable Products. Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof. Performance Data. Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requires ments. Actual performance is subject to the Omron's Warranty and Limitations
- Change in Specifications. Product specifications and accessories may be change in specifications. Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time
- to confirm actual specifications of purchased Product.

 <u>Errors and Omissions.</u> Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.



OMRON INDUSTRIAL AUTOMATION • THE AMERICAS HEADQUARTERS

Schaumburg, IL USA • 847.843.7900 • 800.556.6766 • www.omron247.com

OMRON CANADA, INC. • HEAD OFFICE

Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • www.omron247.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE

México DF • 52.55.59.01.43.00 • 001.800.556.6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE

Apodaca, N.L. • 52.81.11.56.99.20 • 001.800.556.6766 • mela@omron.com

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE

São Paulo, SP, Brasil • 55.11.2101.6300 • www.omron.com.br

OMRON ARGENTINA • SALES OFFICE

Cono Sur • 54.11.4783.5300

OMRON CHILE • SALES OFFICE

Santiago • 56.9.9917.3920

OTHER OMRON LATIN AMERICA SALES

54.11.4783.5300

OMRON EUROPE B.V. • Wegalaan 67-69, NL-2132 JD, Hoofddorp, The Netherlands. • Tel: +31 (0) 23 568 13 00 Fax: +31 (0) 23 568 13 88 • www.industrial.omron.eu