

Discontinuation Notice of eLearning Courses

Due to changes in our learning platform, Omron's eLearning courses will be unavailable after December 22, 2023. We understand the importance of training your staff on introductory topics in automation and apologize for the disruption this may cause. Please stay tuned as we release new content which will be rolled out over the next year.

Note: This change does not affect our On-Demand Product Training courses, nor does it impact our Virtual or In-Person trainings. We will continue to offer our courses such as programming, maintenance, skill builder, and TÜV certification training. Please visit <https://automation.omron.com/en/us/support/training/courses/> for the most current list of training courses.

Course Code	Course Title
A009	Introduction to Factory Automation
A063	Introduction to Safety
A064	Introductory course of IEC 61131-3
A069	Introduction to FA Open Networks
A074	Fundamentals of Electricity for Industrial Automation
B001	Photoelectric Sensors
B002	Proximity Sensors
B003	Power Supplies
B003	Power Supplies (Japanese version)
B005	General Purpose Relays
B005	General Purpose Relays (Japanese version)
B006	AC Drives Basics
B007	Fiber Optic Sensors
B008	Basic Motion Control
B010	PLC Basics
B012	OMRON FA Network Basics
B013	Industrial Timers
B014	Industrial Counters
B015	Displacement & Measurement Sensors
B016	Vision Basics
B017	Vision Lighting
B018	Vision Optics
B020	Servo Basics
B025	Safety Light Curtain Basics
B026	Energy Saving Basics
B027	Introduction to Sysmac Automation Platform
B027	Pengenalan Sysmac Automation Platform
B028	Dasar-dasar NJ Series
B028	NJ Series Basics
B035	61F Floatless Level Switch Basics

B037	Safety Interlock Switch Basics
B038	Ladder Programming Basics (Japanese version)
B040	RFID Basics
B046	IEC 61131-3 Compliant ST Language Basics
B062	Temperature Controller Basics
B070	EtherNet/IP Basics
B071	EtherCAT® Basics
B073	Introduction to Ladder Programming
C011	CP1 Operation
C022	E3X Operation
C023	H5CX Operation
C024	FZ4 Setup and Basic Operation
C029	Pengoperasian Sysmac Studio
C029	Sysmac Studio Operation
C030	NJ Operation Machine Control
C031	NB Setup and Basic Operation
C032	E5CC Temperature Controller Operation
C033	K3HB Operation
C034	H7CX Operation
C036	FQ-M Operation
C039	Programmable Controller Set-up and Operation -CJ2 Series
C045	FH Setup and Operation
C049	NA Basic Operation
C060	Sysmac Studio Operation -with the NX Series Safety Control Unit-
C061	E3X-HD Fiber Optic Sensor Operation
C065	Sysmac Studio Operation (ST Program)
CIC028	Introduction to Automated Optical Inspection
CMA009	Introduction to FA_June,2020 version
CMA074	Fundamentals of Electricity for Industrial Automation_June,2020 version
CMA084	Introduction to Robotics_June,2020 version
CMB010	PLC Basics_June,2020 version
CMB062	Temperature Controllers Basics_June,2020 version
CMB075	General Purpose Relays Basics_May,2020 version
CMB076	Power Supplies Basics May,2020 version
CMB077	Photoelectric Sensors_May,2020 version
CMB078	Proximity Sensors Basics_May,2020 version
CMC029	Sysmac Studio Operation_June,2020 version
CMC049	NA Basic Operation_June,2020 version
CMD001	Maintenance Training Pack - Electrical Maintenance
CMD002	Maintenance Training Pack - Detection Device Maintenance
CMD003	Maintenance Training Pack - PLC Maintenance
FIA001	Robot Basics
FIA002	Service Cloud
FIA003	Bare Basics in Omron Robotics Systems
FIA004	Intro to Omron TM Collaborative Robots
FIC001	Techman Collaborative Robots - TMflow Programming
FIC003	V780 RFID Reader/Writer Overview

FIC004	V780 RFID Reader/Writer Overview
LIA0054	Packaging Machines Pre-Study
LIA0068	Measuring and Monitoring Products (K8AK)
LIA1001	Introduction to Robotics
LIA1002	Automation Center Americas
LIA1090	Basics of Barcode Technology
LIC1004	Omron Motor Sizing Tool Basics
LIC1040	CJ Maintenance Pre-Study
LIC1041	Sysmac Maintenance Pre-Study
LIC1042	NS Maintenance Pre-Study
LIC1044	NY Industrial PC Maintenance
LIC1052	V780 RFID Reader/Writer Overview
LIE1031	Automated Line Change-over
LIE1032	High-Speed Temperature Control
LIE1033	Package or Product Inspection
LIE1034	Packaging Machine Safety
LIE1035	Quality Control for Labels & Markings
LIE1036	SKU Control
LIE1037	Scrap/Waste Reduction
LIE1038	Package Sortation & Placement
LIE1039	Moving Forward Safety with Collaborative Applications
LIE1043	PackML
LIE1044	Vibration Suppression
B079	Fiber Optic Sensors (Japanese version)
B081	PLC Basics (Japanese version)
B082	Programmable Controller Set-up and Operation (Japanese version)
C083	Ladder Programming Basics - CJ Series (Japanese version)
B067	Safety Interlock Switch Basics (Japanese version)
B070	EtherNet/IP (Japanese version)
OEF0025	Safety Light Curtains Basics
OEF0035	Safety Interlock Switch Basics
OEFB062	Temperature Controllers
OEFB075	General Purpose Relays Basics
OEFB076	Power Supplies Basics
OEFB077	Photoelectric Sensors Basics
OEFB078	Proximity Sensors Basics
OEFB080	UPS Basics
OEFB081	AC drives Basics
OEFB082	Measuring & Monitoring Relays
FIA005	Introdução à ISO - OMRON - Qualidade

[Discontinuation date]

December 22, 2023